



Honeywell Sensing and Control

Search

narrow your search

- Products
- Controls Monitoring and Lighting (354)
 - Machine Safety (1726)
 - Sensors (7074)
 - Switches (9814)

- Technology
- Control and Instrumentation (1063)
 - Electromechanical (9357)
 - Microstructure (2328)
 - Optical/Infrared (1077)
 - Thick Film (1764)
 - More...

Need Help?
Click here to contact us

53C17500 Conductive Plastic Potentiometers
(Home : Products)



Actual product appearance may vary.

53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 7.5 kOhm Resistance Value

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Potentiometer Type	Industrial
Element Type	Conductive Plastic
Terminal	Solder lug
Power Rating	2 W
Resistance Value	7.5 KOhm
Resistance Tolerance	± 10 %
Linearity	± 5 %
Bushing Thread	9,53 mm [0.375 in] x 32 NEF-2A
Bushing Length	9,53 mm [0.375 in]
Bushing Type	Standard
Shaft Diameter	6,35 mm [0.25 in]
Shaft Length	50,80 mm [2.0 in]
Shaft Ending	Plain round
Body	27.8 mm [1.094 in] diameter max. except at terminal standoff
Electrical Taper	Linear
Operating Temperature	-55 °C to 120 °C [-67 °F to 248 °F]
Working Voltage (Max.)	500 V
Rotational Life	25000 cycles
Mechanical Rotation	312°
Availability	Global
Series Name	53
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers