

VL series

Professional LED indicators

Distinctive features and specifications

- ☐ Indicators with red, yellow or green built-in LED
- ☐ Antirotation flatted bushing
- ☐ 2 bushing diameters : 6 mm (.236) and 8 mm (.314)
- ☐ Sealed or unsealed
- ☐ Bright or matt black chrome finish

ELECTRICAL SPECIFICATIONS

- Insulation resistance : 1.000 M Ω min.
- Dielectric strength : 250 Vrms 50 Hz min.
- Electrical life at high temperature : 72 H at 85°C

LED specifications (TA 25°C)

- Forward voltage : 2VDC ($\leq 2,6V$)
- Nominal current : 10mA
- Max. surge current ($t_p < 10\mu s$) : 0,5A
- Max. reversed voltage : 25V
- Max. forward current : 40mA
- Max. power dissipation : 100mW
- Correct polarity of D.C supply to diode electrodes must be observed :
 - longer lead : anode (+)
 - shorter lead : cathode (-) on flat side of bushing (see drawings).
- The LED is not removable.

MATERIALS


- Bushing and collar : brass, bright or matt black chrome plated
- Lens : polycarbonate
- LED

GENERAL SPECIFICATIONS


- Torque : 1,25 Nm (.922 Ft.lb) max. applied to nut
- Climatic category : 40/085/21
- Protection level for sealed models: IP 67 according to IEC 529
- In accordance with NFC 93680 standard

PANEL CUT-OUT

For $\varnothing$ 6 (.236)




For $\varnothing$ 8 (.314)




STANDARD HARDWARE

For $\varnothing$ 6 (.236)



For $\varnothing$ 8 (.314)



ABOUT THIS SERIES

Complete part numbers are shown on the following pages.

Dimensions : first dimensions are in mm while inches are shown as bracketted numbers.



Mounting accessories : standard hardware supplied with all models : nickel plated hex nut 9 mm (.354) across flats for indicators $\varnothing$ 6 (.236) or 10 mm (.393) across flats for indicators $\varnothing$ 8 (.314).




Packaging unit : 50 pieces.

Professional LED indicators

→ Flat



LED colour	Bright finish (standard)	Matt black finish
Red	VL1000P600	VL100GP600
Yellow	VL1000P500	VL100GP500
Green	VL1000P300	VL100GP300




Max. panel thickness 5,50 (.216)

→ Flat



LED colour	Bright finish (standard)	Matt black finish
Red	VL3000P600	VL300GP600
Yellow	VL3000P500	VL300GP500
Green	VL3000P300	VL300GP300




Max. panel thickness 8 (.314)

→ Flat



LED colour	Bright finish	Matt black finish (standard)
Red	VL1CK0P600	VL1CKGP600
Yellow	VL1CK0P500	VL1CKGP500
Green	VL1CK0P300	VL1CKGP300

Lens cap in the same colour as the LED.




Max. panel thickness 3,70 (.145)

→ Flat



LED colour	Bright finish	Matt black finish (standard)
Red	VL3CK0P600	VL3CKGP600
Yellow	VL3CK0P500	VL3CKGP500
Green	VL3CK0P300	VL3CKGP300

Lens cap in the same colour as the LED.



Max. panel thickness 4 (.157)

Option : Bushing without flat, lockwasher : on request.