






1. MATERIAL:
HOUSING AND EJECTOR:
HIGH TEMPERATURE NYLON
CONTACT:
PHOSPHOR BRONZE
2. FINISH:
CONTACT AREA:
0.000760[.000030] MIN GOLD OVER
0.001270[.000050] MIN THICK NICKEL
SOLDER TAIL:
0.00381[.000150] MIN THICK MATTE TIN OVER
0.00064[.000025] MIN THICK NICKEL
3. MODULE BOARD PADS:
FOR OPTIMUM PERFORMANCE PADS SHOULD BE SMOOTH AND FLAT
PADS TO BE PLATED WITH:
0.00102[.000040] MIN THICK GOLD OVER
0.00127[.000050] MIN THICK NICKEL
4. PN: 5390402-6 IS THE SAME CONNECTOR AS 5390402-3
WITH LUBRICANT ADDED TO THE CONTACTS.
5. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




	4.50 [.177]	DETAIL B	184 POSN. DDR, 2.5V	5390402-7
5	3.18 [.125]	DETAIL B	184 POSN. DDR, 2.5V	5390402-6
	3.18 [.125]	DETAIL A	184 POSN. DDR, 1.8V	5390402-4
	3.18 [.125]	DETAIL B	184 POSN. DDR, 2.5V	5390402-3
5	2.62 [.103]	DETAIL A	184 POSN. DDR, 1.8V	5390402-2
	2.62 [.103]	DETAIL B	184 POSN. DDR, 2.5V	5390402-1
	DIM A	KEY POSITIONS	DESCRIPTION	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WAITMAN 11OCT04	Tyco Electronics Corporation	
DIMENSIONS: mm		CHK M.YEOMANS 11OCT04	Harriaburg, Pa 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		AP'D M.YEOMANS 11OCT04	NAME	
0 PLC ± -		PRODUCT SPEC		
1 PLC ± -		APPLICATION SPEC		
2 PLC ± 0.13[.005]		SIZE CAGE CODE DRAWING NO		
3 PLC ± -		RESTRICTED TO		
4 PLC ± -		WEIGHT		
ANGLES ± -		A1 00779 5390402		
FINISH		CUSTOMER DRAWING		



DETAIL A
SCALE 8:1



DETAIL B
SCALE 8:1



DETAIL C
SCALE 8:1


KEY POSITIONS

D

C

B


A



SECTION L-L
SCALE 2:1


MINIMUM REPAIRABLE
SOCKET TO SOCKET REPAIRING

WITH THE MODULES REMOVED SOCKETS ON 15.88[.625]
OR GREATER SPACING CAN BE INDIVIDUALLY UNSOLDERED
FROM THE BOARD AND REMOVED IF NECESSARY



MINIMUM SOCKET TO SOCKET SPACING

WITH A 4.00[.158] WIDE MODULE BOARD, A SOCKET TO SOCKET SPACING OF 13.34[.525] WILL LEAVE APPROXIMATELY 0.65[.026] OF CLEARANCE BETWEEN THE MODULE AND THE NEXT SOCKET BODY. THIS SPACING MAY OR MAY NOT BE SUITABLE DEPENDING ON YOUR MINIMUM GAP REQUIREMNETS.



POSSIBLE SOCKET TO SOCKET SPACING FOR 9MM MODULE

WITH A 9.00[.355] WIDE MODULE BOARD; A SOCKET TO SOCKET SPACING OF 22.86[.900] WILL LEAVE APPROXIMATELY 0.66[.026] CLEARANCE BETWEEN THE ADJACENT MODULES. THIS SPACING MAY OR MAY NOT BE SUITABLE DEPENDING ON YOUR MINIMUM GAP REQUIREMENTS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S.WAITMAN
11OCT04

CHK
M.YEOMANS
11OCT04

APVD
M.YEOMANS
11OCT04

mm

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13[.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL

Tyco
Electronics

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME
SCKEY ASSEMBLY, 184 POS, DDR
LOW PROFILE DIMM2P, LEAD FREE

SIZE
A1

CAGE CODE
00779

DRAWING NO
5390402

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
3

OF
3

REV
A1