

W3G280-EQ20-43

EC axial fan

sickled blades (S series)

Automotive



ebm-papst Mulfingen GmbH & Co. KG

Bachmühle 2

D-74673 Mulfingen

Phone: +49(0)7938/81-0

Fax: +49(0)7938/81-110

info1@de.ebmpapst.com

www.ebmpapst.com

Nominal data


Type	W3G280-EQ20-43	
Motor	M3G074-CF	
Nominal voltage	[VDC]	26
Type of data definition		rfa
Speed	[min ⁻¹]	3100
Power input	[W]	200
Current draw	[A]	7.5
Max. ambient temperature	[°C]	70

ml = max. load · me = max. efficiency · rfa = running at free air · cs = customer specs · cu = customer unit
Subject to alterations

Technical features

Leakage current	<= 0.25 mA
Size	280 mm
Operation mode	S1
Direction of rotation	Clockwise, seen on rotor
Electrical leads	With plug
Humidity class	F3-2
Insulation class	"B"
Cable exit	Lateral
Bearing motor	Ball bearing
Mass	2.4 kg
Material of impeller	PA/SPS plastic, color: black (in accordance with UL 94 HB) (wall ring of PP plastic)
Motor protection	Reverse polarity and locked-rotor protection
Number of blades	5
Type of protection	IP 24 KM
Approval	E1


Product drawing




EC axial fan

sickled blades (S series)
Automotive

Connection screen



Charts: Air flow



Measured values

	n	P ₁	η _{Ges}
	[min ⁻¹]	[W]	[%]
1	3100	200	34
2	3085	197	40
3	3090	192	42
4	3105	213	37