







N=Number of poles



P.C.B LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER

Material

- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Contact: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
 - Solid wire(AWG): 12-24
 - Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:

RoHS Compliant

PART NUMBER:

OSTT2XX0150

No. of Poles
02: 2 Poles
03: 3 Poles
...
24: 24 Poles

COLOR:
0: Black
5: Green (Standard)
6: Blue
8: Grey
C: Green (RAL 6018/U)



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE	OSTT2 - 5.0mm series Stackable						
PART NO.	OSTT2XX0150			DWG NO.	OSTT2XX0150.DWG		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
Shi Jun 2006.10.20	Shi Jun 2006.10.20	xionghaitao 2006.01.23	xionghaitao 2006.01.23		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					SHEET: 01/01	REV: D	X.XX ±0.10
						X° ±1°	