



CUSTOMISED

AUTO-BLOQUEO
SELF-LOCKING
COUPLE D'AUTOBLOCAGE
SELBSTHEMMUNG



RUEDA DE BRONCE
BRONZE WHEEL
ROUE EN BRONZE
GETRIEBERAD AUS BRONZE



EJE DELANTERO Y POSTERIOR
FRONT AND REAR SHAFT
ARBRE ARRIERE
VORDERWELLE UND HINTERWELLE




SENSOR HALL
HALL SENSOR
CAPTEUR HALL
HALLSENSOR



Y MUCHO MÁS
AND MANY MORE
ET BEAUCOUP D'AUTRES
UND VIELEN ANDEREN



REFERENCIA REFERENCE REFERENZNUMMERN	TENSION NOMINAL NOMINAL VOLTAGE TENSION NOMINALE NENNSPANUNG	PAR NOMINAL NOMINAL TORQUE COUPLE NOMINAL DREHMOMENT NOMINAL	VELOCIDAD NOMINAL NOMINAL SPEED VITESSE NOMINALE GESCHWINDIGKEIT NOMINAL	CORRIENTE NOMINAL NOMINAL CURRENT COURANT NOMINAL NOMINALSTROM	PAR DE ARRANQUE STARTING TORQUE COUPLE DE DEVIARRAGE ANZUGSDREHMOMENT	CORRIENTE DE ARRANQUE STARTING CURRENT COURANT DE DEVIARRAGE ANLAUFSTROM	EJE SHAFT WELLE	CONEXIONES CONNECTIONS CONNEXIONS ANSCHLUSSART	ESQUEMA ELÉCTRICO WIRING DIAGRAM SCHEMA ELECTRIQUE SCHALTBIID	RELACIÓN DE REDUCCIÓN TRANSMISSION RATIO RAPPORT DE REDUCTEUR ÜBERSETZUNG	PESO APROXIMADO APPROXIMATE WEIGHT POIDS APPROXIMATIF GEWICHT (ca.)	GRADO DE ESTANQUEIDAD WATER TIGHTNESS ÉTANCHÉITÉ FEUCHTIGKEITSSCHUTZKLASSE	MATERIAL RUEDA WHEEL MATERIAL MATERIAU ROUE MAT. DES SCHNECKENRADES	CURVA CURVE KURVE
	Un (V)	Mn (N.m./lbf.in)	n _n (r.p.m.)	In (A)	Ma (N.m./lbf.in)	Ia (A)				i	P (kg/lb.t)	IP		
316.2711.20.00	12	2 / 17.70	38	3.4	10 / 88.5	12	E22	C30	EE4	62:1	0.90/2.41	IP40	PLA	56
316.2711.30.00	24	2 / 17.70	38	1.7	10 / 88.5	6	E22	C30	EE4	62:1	0.90/2.41	IP40	PLA	56
316.2761.20.00	12	2 / 17.70	38	3.4	10 / 88.5	12	E30	C30	EE4	62:1	0.90/2.41	IP40	PLA	56
316.2761.30.00	24	2 / 17.70	38	1.7	10 / 88.5	6	E30	C30	EE4	62:1	0.90/2.41	IP40	PLA	56
316.2761.20.00E	12	2 / 17.70	38	3.4	10 / 88.5	12	E30	C30	F4	62:1	0.90/2.41	IP40	PLA	56
316.2761.30.00E	24	2 / 17.70	38	1.7	10 / 88.5	6	E30	C30	F4	62:1	0.90/2.41	IP40	PLA	56
316.9728.30.00	24	2 / 17.70	38	1.7	10 / 88.5	6	E30	C30	EE4	62:1	0.90/2.41	IP40	BRO	56
316.9731.20.00	12	*1.5/13.27	65	6.0	10 / 88.5	22	E30	C30	EE4	62:1	0.90/2.41	IP40	PLA	57
316.9731.30.00	24	*1.5/13.27	65	3.0	10 / 88.5	11	E30	C30	EE4	62:1	0.90/2.41	IP40	PLA	57

* (VDE 0530) S3 - 10% (10 min.)




mm / in



EJE - SHAFT - ARBRE - WELLE



CONEXIONES - CONNECTIONS - CONNEXIONS - ANSCHLUSSART



ESQUEMA ELÉCTRICO - WIRING DIAGRAM SCHÉME ÉLECTRIQUE - SCHALTBIID



CURVAS - CURVES - COURBES - KURVEN

