

A

B-FORMAT 2002

Dwg. No.	GRS-2012-2XXX
----------	---------------

OPTIONS:

Figure 1 shows the dimensions of the switch assembly. The top view indicates a central opening of .745 (18.92) and side flanges of .125 (3.18) TYP. The bottom view shows the switch assembly with labels for POLARIZING FEATURES and INSULATING BARRIERS.

.250" Wide Terminal is standard as Shown in drawing.
.187" Wide Terminal is optional.

PANEL PIERING

Front View: Overall width is $1.125^{+.005}_{-.000}$ (28.58 $^{+0.13}_{-0.00}$). Overall height is $.550^{+.005}_{-.000}$ (13.97 $^{+0.13}_{-0.00}$). Centerline is labeled ϕ of switch.

Top View: Overall width is $1.235 \pm .015$ (31.37 ± 0.38). Overall height is $.680 \pm .010$ (17.27 ± 0.25). Centerline is labeled ϕ of switch.

Side View: Overall height is 1.230 (31.24) REF. Overall width is $.540 \pm .010$ (13.72 ± 0.25). TYP. label is present.

Bottom View: Overall width is 1.120 (28.44). Overall height is $.370 \pm .025$ (9.4 ± 0.64). A reference dimension of $.288$ (7.32) REF. is shown for the top flange.

1	2	3	4	5	6	7	8	9	10
---	---	---	---	---	---	---	---	---	----

 INDUSTRIES Southampton, Pa. 18966	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
2 Place Decimal ± 0.10 3 Place Decimal ± 0.005 Angles $\pm 1^\circ$	METRIC 1 Place Dec. $\pm 0.25\text{mm}$ 2 Place Dec. $\pm 0.13\text{mm}$
Made for: CW IND.	
Drawn by: DGW 7-06-2010	
Checked by:	
Approval:	

Title:	ROCKER SWITCH ASSEMBLY S.P.D.T. WITH OPTIONS 1.125 x .550 PANEL
Division:	SWITCH
Dwg. No.	GRS-2012-2XXX