

MATERIALS AND FINISHES





BODY: BRASS
PLATED GOLD

INSULATOR: TEFLON




CONTACT: BERYLLIUM COPPER
PLATED GOLD

CRIMP TUBE: BRASS
SEE TABLE

MATING FORCE: 3.4 LBS MAX
UN-MATING FORCE: 1.0-3.0 LBS



NOTE:
EXCESSIVE TORQUE TO CABLE
OR CONNECTOR MAY DAMAGE CABLE
CENTER CONDUCTOR.



73415-3412	GOLD	1 PIECE 73415-3410 IN SINGLE BAG WITH LABEL
73415-3411	BLACK ZINC	STANDARD
73415-3410	GOLD	STANDARD
PART NO.	FINISH	PACKAGING

PS-89675-1920	PRODUCT SPECIFICATION
CECC-22-340	INTERFACE
SPECIFICATION	DESCRIPTION

CHG: REDREW IN SD. ADDED -3412 FOR SINGLE BAG OPTION. ADDED CABLE ASSY INSTRS. EC NO: URF2011-0576 DRAWN: AROBERTSON 2011/04/04 CHKD: SSS 2011/04/04 APPR: JWIENER 2011/04/15		QUALITY SYMBOLS ▽=0 ▽=0
REV K2		DESCRIPTION

GENERAL TOLERANCES (UNLESS SPECIFIED) <table> <tr> <th></th><th>mm</th><th>INCH</th></tr> <tr> <td>4 PLACES</td><td>$\pm .005$</td><td>$\pm .0004$</td></tr> <tr> <td>3 PLACES</td><td>$\pm .004$</td><td>$\pm .0003$</td></tr> <tr> <td>2 PLACES</td><td>$\pm .003$</td><td>$\pm .0002$</td></tr> <tr> <td>1 PLACE</td><td>$\pm .002$</td><td>$\pm .0001$</td></tr> </table> ANGULAR $\pm 2^\circ$			mm	INCH	4 PLACES	$\pm .005$	$\pm .0004$	3 PLACES	$\pm .004$	$\pm .0003$	2 PLACES	$\pm .003$	$\pm .0002$	1 PLACE	$\pm .002$	$\pm .0001$	DIMENSION STYLE MM/IN
	mm	INCH															
4 PLACES	$\pm .005$	$\pm .0004$															
3 PLACES	$\pm .004$	$\pm .0003$															
2 PLACES	$\pm .003$	$\pm .0002$															
1 PLACE	$\pm .002$	$\pm .0001$															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SCALE DESIGN UNITS METRIC															
THIRD ANGLE PROJECTION		TITLE MMCX JACK STRAIGHT FOR 1.13 CABLE MMCX-JC, EWR-4677															
MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-73415-341															
SIZE C		SHEET NO. 1 OF 1															