



revos
Industrial Multipole Connectors

Catalog 2013





▲ Sales and Marketing Center in Bamberg



▲ Company headquarters in Bamberg



▲ STOCKO main plant in Wuppertal

wieland group

ACTIVE WORLDWIDE.

The Wieland Group employs more than 2,000 people all around the globe. With some 15 locations and subsidiaries, and sales partners in more than 70 countries, the Wieland Holding is present in nearly all important key markets worldwide.

Always with a clear commitment to the German location where most of the products are still manufactured.



automation

building

electronics

The group makes us strong

The Wieland Holding is based in Bamberg, Bavaria, and comprises two independently acting subsidiaries: Wieland Electric and STOCKO Contact.

Groundbreaking innovations made Wieland Electric one of the leading suppliers of electrical connection technology. This company, founded in Bamberg in 1910, is the largest subsidiary of the Wieland Holding.

STOCKO Contact is based in Wuppertal and joined the Wieland Group in 2001. Stocko has also more than 100 years of company history to its credit and is one of the greatest manufacturers of connector systems and crimp contacts.



Established in industries

Control cabinet engineering, industrial automation, building system technology – our large product portfolio provides solutions for all kinds of applications.

From innovative interface and network technology to terminal blocks to „safety first“ – with modular system solutions and safety components. With Wieland products in your control cabinet, you are always on the safe side.

Energy bus systems for distributed automation or indoor and outdoor field

bus components – Wieland technology can be found everywhere, and in all kinds of applications.

In building system technology, Wieland Electric is the world market leader in pluggable electrical installation.

There are good reasons why our system solutions can be found in the most spectacular building projects worldwide. When it comes to electronic networking, Wieland leads the way to the “intelligent house”.

Welcome Future

Wieland Electric is 100 years young, and full of innovative energy. And our commitment for the future is not only to find constantly new system solutions for our customers but also social responsibility.

Environmentally friendly high-tech products, manufactured to the latest production standards, an audited environmental management system and substantial investments in our locations are all part to this concept.

Global commitment and sustainable regional action – Wieland Electric is fit for the future: Contacts are green.



| CONTENTS |





8	An overview of heavy duty connectors
10	General design of a revos industrial multipole connectors
12	The locking mechanism of the industrial multipole connectors
14	Connection technologies
16	Housing series
20	Contact inserts - Overview
24	Product matrix
26	Contact inserts
28	revos MINI
32	revos BASIC
58	revos DD
60	revos HD
68	revos POWER
80–91	Connector and Multipole adapter with trigger action frame
96	revos IT
98	revos 
100	revos FLEX
116	Housings
118	revos MINI
120	revos BASIC
224	revos HD
238	revos 
258	Multipole connector sets with 4 components Screw connection
260	Accessories
262	Mounting frames
264	Cover- and Reducer plate
266	Coding accessories
270	Cable glands
274	Protective covers
278	Tools
279	Marking tag carriers
282	facts&DATA
284	Conductor connections, Current load capacity, tightening torque
288	Explanations of applications in hazardous areas
290	Installation spacing and mounting dimensions
294	Crimping tool and Assignment of contacts to appropriate crimping tool
296	Selection criteria and characteristics of the different contact surfaces
298	Definition of the IP degrees of protection
301	Derating behavior of revos industrial multipole connectors
302	Detailed table of contents
304	Spanning various industries and products.
306	Service Support
307	Wieland subsidiaries



The *revos* program

An overview of heavy duty connectors

Heavy duty connectors are specifically designed for use in especially tough environment conditions.

The main areas of use are the automotive industry, in packaging machinery and equipment, as well as for instrumentation, control and automation equipment.

They permit simple and time-saving installation of machinery and equipment. Their housings protect against mechanical impact and prevent entry of spray water and dust. The system's sub-assemblies can undergo a quality check in house, which simplifies installation and commissioning at their end use location.



Overview of the industrial multipole connector range **revos**

Contact inserts:


revos MINI



The contact inserts for the **revos** MINI connector series are very compact and available with 3 to 12 poles.

You will find the contact inserts for the **revos** MINI connectors on pages 28–31.


revos BASIC



The proven connectors and multipole adapters are available in 6 to 92 pole design with screw, spring clamp and crimp connection technology.

You will find **revos** BASIC contact inserts on pages 32–57; You can find terminal block adapters and inserts with integral cable strain relief on pages 78–91.


revos DD



High contact density in the most compact space – this is what the space-saving contact inserts of **revos** DD offer. The inserts fit into the BASIC housing sizes 6/6H, 10/10H, 16/16H, 24/24H. Connection is made with the proven turned crimp contacts, with a diameter of Ø 1.6 mm, which offer a connection range from 0.14 to 2.5 mm² at a rated voltage of 250 V (600 V CSA/UL).

You will find **revos** DD contact inserts on pages 58–59.

revos HD



Contact inserts and multipole adapters with 15 to 64 poles and for currents up to 10 A designed according to DIN EN 175301-801 (previously DIN 46352). The contact inserts are designed in crimp connection technology.

You will find **revos** HD contact inserts on pages 60–67 and terminal block adapters on pages 92–95.


revos POWER



The contact inserts and multipole adapters are designed for >16 A currents; they are also available with mixed contacts and screw connection.

You will find **revos** POWER contact inserts and terminal block adapters on pages 68–77.

revos FLEX



The modular system for the economical and clever mixture of contact inserts. With this flexible system you can customize your connector, to meet the requirements of your application.

You will find **revos** FLEX contact inserts on pages 100–113.

Housing families:

revos MINI




The design of the housings for the connectors of **revos** MINI is very compact and available in two materials:

- Die cast zinc alloy
- Polyamide

You will find **revos** MINI-housings on pages 118–119.

revos BASIC



PG
threads
are available
on request!

The housing of the BASIC series are available in size 6 to 48. For convenient connection of the cables this series is also available with enlarged cable entry in increased height design in sizes 6H–24H. The housings are made of die cast aluminum with, silicon-free finish.

You will find **revos** BASIC-housings on pages 120–223.

revos HD



PG
threads
are available
on request!

The housings of the HD series are available in size 10/15 to 32/50.

You will find **revos** HD-housings on pages 224–237.

Special multipole connector designs:

revos Ex



revos Ex multipole connectors are designed for special applications in hazardous areas. Their use in zone 1 for intrinsic circuits has been approved by the BVS test institute. The housings for the multipole connectors are manufactured from die cast zinc alloy.

You will find **revos** Ex-contact inserts on pages 98–99.

You will find **revos** Ex-housings on pages 238–257.

Operating instructions for Ex plug connectors, see facts&DATA.

revos IT



Data cable feed-throughs – the ideal solution for the installation of pre-assembled cables to enclosures. Sealed and with strain relief. Inserts with D-Sub connectors 9 to 100 pole.

You will find **revos** IT products on pages 96–97.


revos MOT



revos MOT plug connectors with plastic housings, simple and easy handling due to its unique latching system.

You will find **revos** MOT products on pages 114–115.

General design of a *revos* industrial multipole connectors



1. Cable glands

For **revos** industrial connectors the following cable glands are available:

- Cable gland without strain relief, protection degree IP54, 7x.xxx.xxxx.0 fully assembled
- Cable glands, protection degree IP68, available as accessories in plastic or brass
- EMC cable glands

2. Hoods

Aluminum die cast alloy, silicon-free finish (housings for **revos**  - and **revos** MINI are manufactured from die cast zinc alloy)

- Low and increased height designs available
- Cable entry at the side, on top or at the front
- With or without locking levers

3. Female inserts

Available in the following connection techniques:

- Screw connection
- Spring clamp connection
- Crimp connection

4. Coding accessories

Coding pins, female coding pieces and coding bolts

5. Coding bolts

Coding pieces are used for coding 690 V contact inserts. In the 690 V housings the coding ribs are removed and insulating tape is attached inside the housing in order ensure the creepage distances and clearances to live parts. This mechanical coding prevents the 690 V contact inserts from being mounted in 500 V housings.

6. Male inserts

Available in the following connection techniques:

- Screw connection
- Spring clamp connection
- Crimp connection

7. Locking levers

Single or double locking lever in plastic, steel or stainless steel design.

8. Bases

Aluminum die cast alloy, silicon-free finish (housings for (**revos**  - und **revos** MINI are manufactured from die cast zinc alloy)

- Low and increased height designs available
- Open-bottom and closed-bottom bases
- Single or double locking lever of plastic, steel or stainless steel
- Coupling for "cable-to-cable connections"


The locking mechanism of the **revos** BASIC industrial multipole connectors

The locking levers secure the mechanical connection between hood and housing. The locking mechanism is also a main determinant of the connector's IP protection rating. Wieland's standard **revos** BASIC connectors in size 6 to 24 are equipped with locking levers that are made of two components.

The handle consists of flame-retardant and halogen-free plastic material and ensures convenient and almost wear-free locking. The retention force is provided by a spring component that is made of V2A stainless steel and also resists aggressive environmental conditions.

Locking features:

- Low-wear locking mechanism
- High holding forces
- Plastic material suitable for outdoor applications
- Salt and seawater resistant, UV resistant
- During overhead mounting the lever will remain in the open position
- Replaceable
- Self-extinguishing plastic material according to UL 94 V0



In general we distinguish levers on the hood and levers on the base, as well as single locking levers (on the long side) and double locking levers (on the narrow side).

On the opposite hood or base there are studs to which the lever latches.

The following lock types are available:



One long-side lever
(single locking lever)



Two narrow-side levers
(double locking lever)

Connectors for cable-to-cable couplings:



One long-side lever
(single locking lever)




Two narrow-side levers
(double locking lever)

Locking levers made of steel or stainless steel are available on request.

In case of any questions our connector hotline (+49 951/9324-997) will be happy to assist you.

Connection technologies



Screw connection technology:

This connection technology is the one most frequently used today. Screw connectors are designed according to EN 60 999/VDE 0609.


Features of this connection technology:

- Operation is simple and easy
- No special tools required
- High-quality connection that can be used for all areas of application
- Non-permanent connection, rewiring possible

The contact point can be delivered with or without wire protection.

Clamping bodies with wire protection do not require any preparation of the wires.

Clamping bodies without wire protection require appropriate preparation of the wires in case fine-stranded wires are used.



Spring clamp connection technology:


In the last few years this connection technology has been established as an industrial standard. Spring clamp connectors are designed according to EN 60 999/VDE 0609.

Features of this connection technology:

- Easy handling
- No special tools required
- High-quality connection even under vibration
- Non-permanent connection, rewiring possible

For contact inserts with spring clamp connection technology all wire types (solid, stranded, fine-stranded) can be used without special preparation of the wires.

When ferrules are used they must be crimped to the wire by means of a special positively driven crimping tool.



Crimp connection technology:

This connection technology provides the highest quality, but is also the most demanding. The technical requirements for crimp connections are defined in the IEC 60 352-2 standard. Crimp connections must always be produced using a crimping tool that has been designed for the contact. Wieland crimping tools are specifically adapted to the contacts and thus ensure a permanent and corrosion-resistant connection.

Features of this connection technology:

- High-quality connection similar to cold welding
- Consistent repeatability of the crimp connection
- Suitable for automation during pre-assembly of cable harnesses
- Compact design that allows a high contact density
- Special crimping tool required
- Permanent connection

Screw connection technology:

Screw terminals are measured in accordance with EN 60 999/VDE 0609.
Please refer to the respective tightening torques from table 4 on page 287.


Spring clamp connection technology:

Operating instructions:

1. Insert the screwdriver using a slight curving motion into the rectangular opening.
2. Open the clamping body.
The screwdriver will stay in position, and hold the clamping body open.
3. Insert the wire into the round wire entry guide and remove the screwdriver.

Screwdriver: 0.6 mm x 3.5 mm

Part number: 06.502.4000.0



Crimp connection technology:

Using the suitable tools when producing crimp connections is essential. Correct and gas-tight connections can only be ensured by tools that are particularly adapted to the contact.

Wieland crimping tools compress the contact point with a so-called B crimp or a square crimp to make it gas-tight.

A contact to tool assignment can be found on page 295.



**Micrograph
of a B crimp**



**Micrograph
of a square crimp**

Contact materials:

revos-connectors are available with tin-plated, silver-plated or gold-plated contacts.

The basic material is a high-quality copper alloy.

For exact explanations, see pages 296–297.

Housing series *revos* BASIC

Single locking lever

Hoods



Bases



Size (GB):

- GB 6, 10, 16, 24, 48
- GB 6H, 10H, 16H, 24H

Motor connector
housing

Coupling housings


Double locking lever

Hoods



GB 16XL, 24XL with extra
large wiring space

Bases



Coupling housings

Size (GB):

- GB 6, 10, 16, 24, 32
- GB 10H, 16H, 24H, 16XL, 24 XL

H $\triangleq$ increased height design; XL $\triangleq$ extra large wiring space. All bases are also available with a protective cover. For an assignment of the contact inserts to the housing sizes see page 20-23 as well as the product matrix on page 24-25.

Housing series *revos* HD

Single locking lever

Hoods



Bases



Size (GB):

- GB 10/15, 16/25

Double locking lever

Hoods



Bases



Size (GB):

- GB 32/50

Coupling housings

All bases are also available with a protective cover.

For an assignment of the contact inserts to the housing sizes see page 20-23 as well as the product matrix on page 24-25.

Housing series *revos* MINI and *revos*

revos MINI

Hoods



Bases




revos

Hoods



Bases



Size (GB):




- GB 10Ex, 16Ex, 24Ex, double locking lever
- GB 6Ex, 48Ex, single locking lever

Coupling housings

Bases are also available with a protective cover!

Contact inserts


Contact inserts for the housings of the **revos**^{BASIC} series

Size	BASIC 500 V / 16 A	BASIC 400/690 V / 16 A	BASIC 690 V / 16 A	BASIC 830 V / 16 A	EE 500 V / 16 A
6/ 6H	 6 + ground		 4/2 Switching contacts + ground		 10 + ground
10/ 10H	 10 + ground	 3/2 Switching contacts + ground	 8/2 Switching contacts + ground	 3/2 Switching contacts + ground	 18 + ground
16/ 16H	 16 + ground	 6/2 Switching contacts + ground	 14/2 Switching contacts + ground	 6/2 Switching contacts + ground	 32 + ground
24/ 24H	 24 + ground	 10/2 Switching contacts + ground	 22/2 Switching contacts + ground	 10/2 Switching contacts + ground	 46 + ground
32	 32 + ground	 20/4 Switching contacts + ground	 28/4 Switching contacts + ground		
48	 48 + ground	 26/4 Switching contacts + ground	 32/4 Switching contacts + ground	 44/4 Switching contacts + ground	 20/4 Switching contacts + ground

DD 250 V / 10 A	HD 250 V / 10 A	POWER 230–690 V / 16–100 A	FLEX 100 – 1000 V / 4 – 82 A	Size
 24 + ground			 2 Modules	6/ 6H
 42 + ground			 3 Modules	10/ 10H
 72 + ground	 40 + ground	 6/6 + ground  4/6 + ground  6 + ground  4/2 + ground  4 + ground	 5 Modules	16/ 16H
 108 + ground	 64 + ground	 3/3/6 + ground	 7 Modules	24/ 24H
	 80 + ground			32
				48

Contact inserts



Contact inserts für **revos** HD-housings

Size	HD 10/16 250 V / 16 A	HD 15/25 250 V / 10 A
10/ 15	 10 + ground	 15 + ground
16/ 25	 16 + ground	 25 + ground
32/ 50	 32 + ground	 50 + ground

Contact inserts for **revos** MINI-housings

Size	250 – 400 V / 10 A	400 V / 10 A	400 V / 16 A	50 – 250 V / 10 A	50 V / 10 A	690 V / 10 A
3	 3 + ground	 4 + ground	 5 + ground	 7 + ground	 8	 12

Contact inserts for **revos** -housings

Size	6Ex	10Ex	16Ex	24Ex	48Ex
 90 V 16 A	 6 + PE	 10 + PE	 16 + PE	 24 + PE	 48 + PE

Contact inserts

revos FLEX-modular inserts

Modules for power supply				
				
2-pole 1000 V/82 A Screw	3-pole 630 V/40 A Crimp	5-pole 250 V/20 A Crimp	4-pole 1000 V/16 A Crimp	4-pole 400 V/14 A Federkraft
Modules for signal distribution		High voltage	Compressed air	
				
10-pole 250 V/10 A Crimp/LWL-POF	20-pole 100 V/4 A Crimp	2-pole 5.5 kV/20 A Crimp	Pneumatic 1-pole 10 bar – Ø 2.5/4 mm	Pneumatic 2-pole 10 bar – Ø 2.5/4 mm
Bus systems			Special modules	
				
USB 4-pole 30 V/1 A Screw	Profibus 4-pole 30 V/1 A Screw	Ethernet 8 plus 4-pole 30 V/1 A / 400 V/10 A Crimp/optical fiber	Modular blind piece	

revos MOT special designs

690 V / 16 A

10 + ground

Product matrix

The **revos** product matrix provides an overview of the available families of contact inserts and their matching housing series. Horizontally you can find the contact inserts sorted per family and with indications for rated voltage, rated current and connection technology. Vertically the housing series and their variations in size are shown. Matching combinations are found in the matrix.

The restrictions of the **revos**^{FLEX} and **revos**^{HD} contact inserts are caused by their depth and cable density inside the housing when fully equipped with contact inserts. In case of any questions regarding these combinations, our connector hotline (+49 951 9324-991) will be happy to assist you.

Housing series	Material	Variation	Size (GB)	Locking levers	Hoods page	Bases page
BASIC 	Aluminum die cast	500 V	6	Single	120	124
			10	Single	132	136
				Double	140	146
			16	Single	160	164
				Double	168–170	174
			24	Single	188	192
				Double	196–198	202
		500 V/690 V	32	Double	216	217
			48	Single	218	220
		690 V	6	Single	128	130
			10	Single	150	152
				Double	154–156	158
			16	Single	178	180
				Double	182	186
			24	Single	206	208
				Double	210–212	214
		500 V Increased height design	6H	Single	122	126
			10H	Single	134	138
				Double	144	148
			16H	Single	162	166
				Double	172	176
			24H	Single	190	194
				Double	200–201	204
		690 V – large wiring space	16XL	Double	183	
			24XL	Double	211	
		EMC housings	6/6H	Single	222	223
			10/10H	Double	222	223
			16/16H	Double	222	223
			24/24H	Double	222	223
HD 	Aluminum die cast	250 V	10/15	Single	224	226
			16/25	Single	228	230
			32/50	Double	232,234	236
MINI 	Polyamide Die cast zinc alloy	Plastic	3	Single	118	119
		Metal	3	Single	118	119
	Die cast zinc alloy	90 V	6 	Single	238	240
			10 	Double	242	244
			16 	Double	246	248
			24 	Double	250	252
			48 	Single	254	256
MOT 	Polyamide	690 V	10 + ground	Push-Pull	114	114

H $\triangle$ Increased height design; XL $\triangle$ Large wiring space

Wiring technique

S = screw F = spring clamp C = srimp L = optical fiber

- = usable subject to restrictions
- = usable without any restrictions



revos contact inserts offer many possibilities

The task of the contact inserts is distribution of power and signals. The contact inserts are available in 2- to 216-pin design. They are suitable for current from 4 to 100 A and voltages up to 5.5 kV.

revos MINI - Their especially compact design allows them to fit in applications for machine, control and switching systems, or also in small motors and lighting equipment, and also serve as classic contact inserts for industrial heavy duty connectors.

The contact inserts are available in 6 to 92-pin design.

revos BASIC is able to meet the toughest demands and so is used, for example, in the automotive industry, the machinery and equipment industry, in conveyor systems and in measurement and control technology.




Contact inserts



Contact inserts *revos* MINI



3-pole + ground




4-pole + ground




Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> MINI			
Male insert	3-pole + ground MIN STS 3 2.5 40	73.310.0353.0	10
Female insert	MIN BUS 3 2.5 40	73.300.0353.0	10
Contact inserts <i>revos</i> MINI			
Male insert	4-pole + ground MIN STS 4 2.5 40 AG	73.310.0453.0	10
Female insert	MIN BUS 4 2.5 40 AG	73.300.0453.0	10
Technical data			
Rated voltage		3-pole + ground	4-pole + ground
Installed in a plastic housing	400 V		
Installed in a metal housing	L-PE 250 V / L-L 400 V	400 V	
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage			
Plastic housing	4 kV		
Metal housing	4 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	18 – 16 AWG	22 – 12 AWG	
CSA	22 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn	Ag	
Insulation strip length	4 mm		
Contact resistance	≤ 2 mΩ	≤ 1.5 mΩ	
Mating cycles	50	200	
Screws head design / recomm. torque			
Mounting screws	M3 / 0.5 – 0.7 Nm		
Clamping screws	M3 / 0.5 – 0.7 Nm		
Ground conductor screws	M3 / 0.5 – 0.7 Nm		
Temperature range	-40 – +120 °C		
Housing <i>revos</i> MINI		Page 118–119	

Dimensions


3-pole + ground




4-pole + ground




7-pole + ground



8-pole





Contact inserts


Contact inserts *revos* MINI



7-pole + ground




8-pole




Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> MINI			
7-pole + ground			
Male insert without crimp contacts	MIN STC 7 25	73.710.0753.0	10
Female insert without crimp contacts	MIN BUC 7 25	73.700.0753.0	10
Contact inserts <i>revos</i> MINI			
8-pole			
Male insert without crimp contacts	MIN STC 8 05	73.710.0853.0	10
Female insert without crimp contacts	MIN BUC 8 05	73.700.0853.0	10
Contacts for crimp version			
	mm ² / AWG		
Male reel contacts, Sn	0.2 – 0.56 / 24-20	05.544.0900.0	5000
Female reel contacts, Sn	0.2 – 0.56 / 24-20	02.124.0900.0	5000
Male reel contacts, Sn	0.75 – 1.5 / 18-16	05.544.1000.0	5000
Female reel contacts, Sn	0.75 – 1.5 / 18-16	02.124.1000.0	5000
Male single contacts, Sn	0.2 – 0.56 / 24-20	05.544.0929.0	200
Female single contacts, Sn	0.2 – 0.56 / 24-20	02.124.0929.0	200
Male single contacts, Sn	0.75 – 1.5 / 18-16	05.544.1029.0	200
Female single contacts, Sn	0.75 – 1.5 / 18-16	02.124.1029.0	200
Male reel contacts, Au	0.5 – 1.5 / 20-16	05.544.1400.0	5000
Female reel contacts, Au	0.5 – 1.5 / 20-16	02.124.1400.0	5000
Male single contacts, Au	0.5 – 1.5 / 20-16	05.544.1429.0	200
Female single contacts, Au	0.5 – 1.5 / 20-16	02.124.1429.0	200
Technical data			
		7-pole + ground	8-pole
Rated voltage			
Installed in a plastic housing	250 V		50 V
Installed in a metal housing	50 V		50 V
Rated voltage according to UL/CSA	600 V		42 V
Rated impulse voltage			
Plastic housing	4 kV		0.8 kV
Metal housing	0.8 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.2 – 1.5 mm ²		
UL	18 – 16 AWG		
CSA	24 – 16 AWG		
Contacts			
Material	Copper alloy		
Surface	Au or SN		
Insulation strip length	4 mm		
Contact resistance	4 mΩ		
Mating cycles	Sn 50 / Au 500		
Screws head design / recomm. torque			
Mounting screws	M3 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	-		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"E"	05.502.2400.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0000.0	1
Housing <i>revos</i> MINI		Page 118–119	

Derating curve
according to IEC 60512 sec. 3
revos MINI
10 A / 2.5 mm² / 1.5 mm²

- 3-pole
- 4-pole
- 7-pole
- 8-pole



Contact inserts



Contact inserts *revos* MINI




5-pole + ground




Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> MINI			
5-pole + ground			
Male insert without crimp contacts	MIN STC 5 25 AG	73.710.0553.0	10
Female insert without crimp contacts	MIN BUC 5 25 AG	73.700.0553.0	10
Contacts for crimp version			
	mm ² / AWG, turned ø 2.5 mm		
Male insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.75xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface	silver-plated xx = 02 / gold-plated xx = 01		
Technical data			
Rated voltage			
Installed in a plastic housing	L-PE 250 V / L-L 400 V		
Installed in a metal housing	L-PE 250 V / L-L 400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage			
Plastic housing	4 kV		
Metal housing	4 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ² , ground: 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Au or Ag		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	M3 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	M3 / 0.5 – 0.7 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	“B”	05.502.2100.0	1
Contact positioner	“3”	05.502.3300.0	1
Extraction tool		05.502.3500.0	1
Housing <i>revos</i> MINI		Page 118–119	


Dimensions

5-pole + ground



12-pole + ground





Contact inserts

Contact inserts *revos* MINI



12-pole + ground



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> MINI			
12-pole + ground			
Male insert without crimp contacts	MIN STC 12 40 AG	73.710.1253.0	10
Female insert without crimp contacts	MIN BUC 12 40 AG	73.700.1253.0	10
Contacts for crimp version			
	mm ² / AWG, turned ø 2.5 mm		
Male insert	0.14 – 0.37 / 26 – 22	05.544.4129.x	100
Female insert	0.14 – 0.37 / 26 – 22	02.125.4129.x	100
Male insert	0.5 / 20	05.544.4229.x	100
Female insert	0.5 / 20	02.125.4229.x	100
Male insert	0.75 – 1.0 / 18	05.544.4329.x	100
Female insert	0.75 – 1.0 / 18	02.125.4329.x	100
Male insert	1.5 / 16	05.544.4429.x	100
Female insert	1.5 / 16	02.125.4429.x	100
Male insert	2.5 / 14	05.544.4529.x	100
Female insert	2.5 / 14	02.125.4529.x	100
Surface	silver-plated x = 8 / gold-plated x = 7		
LWL POF Contacts Ø 0.16			
Male insert		02.125.2421.0	5
Female insert		05.544.8121.0	5
Technical data			
Rated voltage			
Installed in a plastic housing	L-PE 400 V / L-L 690 V		
Installed in a metal housing	L-PE 400 V / L-L 690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage			
Plastic housing	6 kV		
Metal housing	6 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.14 – 2.5 mm ² , ground: 2.5 mm ²		
UL	26 – 14 AWG		
CSA	26 – 14 AWG		
Contacts			
Material	Copper alloy		
Surface	Au or Ag		
Mating cycles	200		
Screws head design / recomb. torque			
Mounting screws	M3 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	M3 / 0.5 – 0.7 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"1"	05.502.0710.0	1
Extraction tool		05.502.1010.0	1
Set of tools for optical fiber POF contacts		95.101.2000.0	1
Coding piece	MIN KOD	05.568.0353.0	20
Star jumper	MIN BR ST 12 BU	27.280.4327.0	5
Housing <i>revos</i> MINI			Page 118–119


Derating curve

according to IEC 60512 sec. 3

revos MINI

wire size 1.5 mm²

- 5-pole
- 12-pole



500 V contact inserts, screw connection



Contact inserts **revos** BASIC



6-pole + ground Size 6




10-pole + ground Size 10




16-pole + ground Size 16



24-pole + ground Size 24



32-pole + ground Size 32



48-pole + ground Size 48




* Preparation of the wire required:
ferrule, ultrasonic welding for
flexible cables


Description	Type	Part No.	P.U.
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn	6-pole + ground BAS STS 6 2.5 50	70.310.0640.0	10
Male insert with wire protection, Ag	BAS STS 6 2.5 50 AG	70.310.0602.0	10
Male insert with wire protection, Au	BAS STS 6 2.5 50 AU	70.311.0640.0	10
Male insert without wire protection, Sn*	BAS STS OD 6 2.5 50	70.312.0640.0	10
Female insert with wire protection, Sn	BAS BUS 6 2.5 50	70.300.0640.0	10
Female insert with wire protection, Ag	BAS BUS 6 2.5 50 AG	70.300.0602.0	10
Female insert with wire protection, Au	BAS BUS 6 2.5 50 AU	70.301.0640.0	10
Female insert without wire protection, Sn*	BAS BUS OD 6 2.5 50	70.302.0640.0	10
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn	10-pole + ground BAS STS 10 2.5 50	70.310.1040.0	10
Male insert with wire protection, Ag	BAS STS 10 2.5 50 AG	70.310.1002.0	10
Male insert with wire protection, Au	BAS STS 10 2.5 50 AU	70.311.1040.0	10
Male insert without wire protection, Sn*	BAS STS OD 10 2.5 50	70.312.1040.0	10
Female insert with wire protection, Sn	BAS BUS 10 2.5 50	70.300.1040.0	10
Female insert with wire protection, Ag	BAS BUS 10 2.5 50 AG	70.300.1002.0	10
Female insert with wire protection, Au	BAS BUS 10 2.5 50 AU	70.301.1040.0	10
Female insert without wire protection, Sn*	BAS BUS OD 10 2.5 50	70.302.1040.0	10
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn	16-pole + ground BAS STS 16 2.5 50	70.310.1640.0	10
Male insert with wire protection, Ag	BAS STS 16 2.5 50 AG	70.310.1602.0	10
Male insert with wire protection, Au	BAS STS 16 2.5 50 AU	70.311.1640.0	10
Male insert without wire protection, Sn*	BAS STS OD 16 2.5 50	70.312.1640.0	10
Female insert with wire protection, Sn	BAS BUS 16 2.5 50	70.300.1640.0	10
Female insert with wire protection, Ag	BAS BUS 16 2.5 50 AG	70.300.1602.0	10
Female insert with wire protection, Au	BAS BUS 16 2.5 50 AU	70.301.1640.0	10
Female insert without wire protection, Sn*	BAS BUS OD 16 2.5 50	70.302.1640.0	10
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn	24-pole + ground BAS STS 24 2.5 50	70.310.2440.0	10
Male insert with wire protection, Ag	BAS STS 24 2.5 50 AG	70.310.2402.0	10
Male insert with wire protection, Au	BAS STS 24 2.5 50 AU	70.311.2440.0	10
Male insert without wire protection, Sn*	BAS STS OD 24 2.5 50	70.312.2440.0	10
Female insert with wire protection, Sn	BAS BUS 24 2.5 50	70.300.2440.0	10
Female insert with wire protection, Ag	BAS BUS 24 2.5 50 AG	70.300.2402.0	10
Female insert with wire protection, Au	BAS BUS 24 2.5 50 AU	70.301.2440.0	10
Female insert without wire protection, Sn*	BAS BUS OD 24 2.5 50	70.302.2440.0	10
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn, marked 1-16, 17-32	32-pole + ground BAS STS 32 2.5 50	70.310.3253.0	5
Male insert with wire protection, Ag, marked 1-16, 17-32	BAS STS 32 2.5 50 AG	70.310.3202.0	5
Female insert with wire protection, Sn, marked 1-16, 17-32	BAS BUS 32 2.5 50	70.300.3253.0	5
Female insert with wire protection, Ag, marked 1-16, 17-32	BAS BUS 32 2.5 50 AG	70.300.3202.0	5
Contact inserts revos BASIC 500 V			
Male insert with wire protection, Sn, marked 1-24, 25-48	48-pole + ground BAS STS 48 2.5 50	70.310.4840.0	5
Female insert with wire protection, Sn, marked 1-24, 25-48	BAS BUS 48 2.5 50	70.300.4840.0	5
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn, Ag, Au		
Insulation strip length	7 mm		
Contact resistance	≤ 1,5 mΩ		
Mating cycles	Sn 200 / Ag, Au 500		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	
Size	32	Page 216–217	
Size	48	Page 218–221	

Dimensions


6-pole + ground – 24-pole + ground




6-pole + ground




10-pole + ground




16-pole + ground




24-pole + ground



32-pole + ground



48-pole + ground




Derating curve

according to IEC 60512 sec. 3


revos BASIC

Screw version 500V / 16 A / 2.5 mm²

- 6-pole
- 10-pole
- 16-pole
- 24-pole



500 V contact inserts, spring clamp connection



Contact inserts **revos** BASIC




6-pole + ground Size 6




10-pole + ground Size 10




16-pole + ground Size 16



24-pole + ground Size 24



32-pole + ground Size 32



48-pole + ground Size 48



Description	Type	Part No.	P.U.
Contact inserts revos BASIC 500 V			
Male insert	6-pole + ground BAS STF 6 2.5 50	70.510.0653.0	10
Female insert	BAS BUF 6 2.5 50	70.500.0653.0	10
Contact inserts revos BASIC 500 V			
Male insert	10-pole + ground BAS STF 10 2.5 50	70.510.1053.0	10
Female insert	BAS BUF 10 2.5 50	70.500.1053.0	10
Contact inserts revos BASIC 500 V			
Male insert	16-pole + ground BAS STF 16 2.5 50	70.510.1653.0	10
Female insert	BAS BUF 16 2.5 50	70.500.1653.0	10
Contact inserts revos BASIC 500 V			
Male insert	24-pole + ground BAS STF 24 2.5 50	70.510.2453.0	10
Female insert	BAS BUS 24 2.5 50	70.500.2453.0	10
Contact inserts revos BASIC 500 V			
Male insert, marked 1-16, 17-32	32-pole + ground BAS STF 32 2.5 50	70.510.3253.0	5
Female insert, marked 1-16, 17-32	BAS BUF 32 2.5 50	70.500.3253.0	5
Contact inserts revos BASIC 500 V			
Male insert, marked 1-24, 25-48	48-pole + ground BAS STF 48 2.5 50	70.510.4853.0	5
Female insert, marked 1-24, 25-48	BAS BUF 48 2.5 50	70.500.4853.0	5

Technical data

Rated voltage	500 V
Rated voltage according to UL/CSA	600 V
Rated impulse voltage	6 kV
Rated current	16 A
Degree of pollution	3

Rated cross section

EN 60999	0.14 – 2.5 mm ²
UL	26 – 12 AWG
CSA	26 – 12 AWG

Contacts

Material	Copper alloy
Surface	Ag
Insulation strip length	7 mm
Contact resistance	≤ 3 mΩ
Mating cycles	500


Screws head design / recomm. torque

Mounting screws	H1 / 0.5 – 0.7 Nm
Clamping screws	-
Ground conductor screws	H2 / 1.2 – 1.6 Nm
Temperature range	-40 – +120 °C

Description	Type	Part No.	P.U.
Accessories			
Screwdriver blade	DIN 5264 A 0.6 x 3.5	06.502.4000.0	5
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	
Size	32	Page 216–217	
Size	48	Page 218–221	


Dimensions

6-pole + ground – 24-pole + ground




Number of poles	L1 [mm]	L2 [mm]
6	50.0	44.0
10	63.0	57.0
16	83.0	77.5
24	110.0	104.0


6-pole + ground




10-pole + ground




16-pole + ground




24-pole + ground



32-pole + ground




48-pole + ground




Derating curve
according to IEC 60512 sec. 3
revos^{BASIC}
Spring version
500V / 16 A / 2.5 mm²

- 6-pole
- 10-pole
- 16-pole
- 24-pole



500 V contact inserts, double spring clamp connection



Contact inserts **revos** BASIC




6-pole + ground Size 6H




10-pole + ground Size 10H



16-pole + ground Size 16H




24-pole + ground Size 24H




Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> BASIC 500 V			
6-pole + ground			
Male insert	BAS STM 6 2.5 50 AG	70.512.0653.0	1
Female insert	BAS BUM 6 2.5 50 AG	70.502.0653.0	1
Contact inserts <i>revos</i> BASIC 500 V			
10-pole + ground			
Male insert	BAS STM 10 2.5 50 AG	70.512.1053.0	1
Female insert	BAS BUM 10 2.5 50 AG	70.502.1053.0	1
Contact inserts <i>revos</i> BASIC 500 V			
16-pole + ground			
Male insert	BAS STM 16 2.5 50 AG	70.512.1653.0	1
Female insert	BAS BUM 16 2.5 50 AG	70.502.1653.0	1
Contact inserts <i>revos</i> BASIC 500 V			
24-pole + ground			
Male insert	BAS STM 24 2.5 50 AG	70.512.2453.0	1
Female insert	BAS BUM 24 2.5 50 AG	70.502.2453.0	1
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.14 – 2.5 mm ²		
UL	26 – 14 AWG		
CSA	26 – 14 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	9 – 11 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	500		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Screwdriver blade	DIN 5264 A 0.6 x 3.5	06.502.4000.0	5
Housing 500 V			
Size	6H	Page 122–123, 126–127	
Size	10H	Page 134, 138, 144, 148	
Size	16H	Page 162, 166, 172, 176	
Size	24H	Page 190, 194, 200, 204	

Dimensions


6-pole + ground – 24-pole + ground




6-pole + ground




10-pole + ground



16-pole + ground



24-pole + ground




Derating curve


according to IEC 60512 sec. 3

revos BASIC

Spring version with double connection
500V / 16 A / 2.5 mm²

- 6-pole
- 10-pole
- 16-pole
- 24-pole





500 V contact inserts, crimp connection

Contact inserts **revos** BASIC



6-pole + ground Size 6




10-pole + ground Size 10




16-pole + ground Size 16




24-pole + ground Size 24



32-pole + ground Size 32




48-pole + ground Size 48



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> BASIC 500 V			
Male insert	6-pole + ground BAS STC 6 50	70.710.0658.0	10
Female insert	BAS BUC 6 50	70.700.0658.0	10
Contact inserts <i>revos</i> BASIC 500 V			
Male insert	10-pole + ground BAS STC 10 50	70.710.1058.0	10
Female insert	BAS BUC 10 50	70.700.1058.0	10
Contact inserts <i>revos</i> BASIC 500 V			
Male insert	16-pole + ground BAS STC 16 50	70.710.1658.0	10
Female insert	BAS BUC 16 50	70.700.1658.0	10
Contact inserts <i>revos</i> BASIC 500 V			
Male insert	24-pole + ground BAS STC 24 50	70.710.2458.0	10
Female insert	BAS BUC 24 50	70.700.2458.0	10
Contact inserts <i>revos</i> BASIC 500 V			
Male insert, marked 1-16, 17-32	32-pole + ground BAS STC 32 50	70.710.3253.0	5
Female insert, marked 1-16, 17-32	BAS BUC 32 50	70.700.3253.0	5
Contact inserts <i>revos</i> BASIC 500 V			
Male insert, marked 1-24, 25-48	48-pole + ground BAS STC 48 50	70.710.4858.0	5
Female insert, marked 1-24, 25-48	BAS BUC 48 50	70.700.4858.0	5
Contacts for crimp connection			
	mm² / AWG		
Male insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.74xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn, Ag, Au		
Insulation strip length	7 mm		
Contact resistance	≤ 1,5 mΩ		
Mating cycles	Sn 200 / Ag, Au 500		
Screws head design / recomb. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	“B”	05.502.2100.0	1
Contact positioner	“3”	05.502.3300.0	1
Extraction tool		05.502.3500.0	1
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	
Size	32	Page 216–217	
Size	48	Page 218–221	


Dimensions

6-pole + ground – 24-pole + ground




Number of poles	L1 [mm]	L2 [mm]
6	50.0	44.0
10	63.0	57.0
16	83.0	77.5
24	110.0	104.0


6-pole + ground




10-pole + ground




16-pole + ground




24-pole + ground



32-pole + ground




48-pole + ground



Derating curve according to IEC 60512 sec. 3


revosBASIC crimp version 500V / 16 A / 1.5 mm²




■ 6-pole ■ 10-pole ■ 16-pole ■ 24-pole

Derating curve according to IEC 60512 sec. 3

revosBASIC crimp version 500V / 16 A / 2.5 mm²






500 V contact inserts with crimp connection


Contact inserts **revos** BASIC EE




10-pole + ground Size 6/6H



18-pole + ground Size 10/10H



32-pole + ground Size 16/16H



46-pole + ground Size 24/24H



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> BASIC EE 500 V			
Male insert	10-pole + ground BAS STCK 10 50	70.810.1056.0	1
Female insert	BAS BUCK 10 50	70.800.1056.0	1
Contact inserts <i>revos</i> BASIC EE 500 V			
Male insert	18-pole + ground BAS STCK 18 50	70.810.1856.0	1
Female insert	BAS BUCK 18 50	70.800.1856.0	1
Contact inserts <i>revos</i> BASIC EE 500 V			
Male insert	32-pole + ground BAS STCK 32 50	70.810.3256.0	1
Female insert	BAS BUCK 32 50	70.800.3256.0	1
Contact inserts <i>revos</i> BASIC EE 500 V			
Male insert	46-pole + ground BAS STCK 46 50	70.810.4656.0	1
Female insert	BAS BUCK 46 50	70.800.4656.0	1
Contacts for crimp connection			
	mm ² / AWG		
Male insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.74xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag, Au		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	Sn 200 / Ag, Au 500		
Screws head design / recomb. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"3"	05.502.3300.0	1
Extraction tool		05.502.3500.0	1
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	



Dimensions

10-pole + ground – 46-pole + ground



Number of poles	L1 [mm]	L2 [mm]
10	44.0	44.0
18	64.0	57.0
32	84.5	77.5
46	111.0	104.0

10-pole + ground

Connection side




Cut-out



18-pole + ground

Connection side




Cut-out



32-pole + ground

Connection side




Cut-out




36-pole + ground

Connection side




Cut-out




Derating curve according to IEC 60512 sec. 3

revosBASIC EE 500V / 16 A / 1.5 mm²



Derating curve according to IEC 60512 sec. 3

revosBASIC EE 500V / 16 A / 2.5 mm²





500 V multipole adapter with screw connection


Multipole adapter **revos** BASIC




6-pole + ground Size 6




10-pole + ground Size 10



16-pole + ground Size 16




24-pole + ground Size 24




Description	Type	Part No.	P.U.
Multipole adapter revos BASIC 500 V	6-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS SAS LR 6 4.0 50	70.115.0653.3	10
Female insert, ground right	BAS BAS LR 6 4.0 50	70.105.0653.3	10
Male insert, ground left	BAS SAS LL 6 4.0 50	70.110.0653.3	10
Female insert, ground left	BAS BAS LL 6 4.0 50	70.100.0653.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS SAS KR 6 4.0 50	70.115.0653.4	10
Female insert, ground right	BAS BAS KR 6 4.0 50	70.105.0653.4	10
Male insert, ground left	BAS SAS KL 6 4.0 50	70.110.0653.4	10
Female insert, ground left	BAS BAS KL 6 4.0 50	70.100.0653.4	10
Multipole adapter revos BASIC 500 V	10-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS SAS LR 10 4.0 50	70.115.1053.3	10
Female insert, ground right	BAS BAS LR 10 4.0 50	70.105.1053.3	10
Male insert, ground left	BAS SAS LL 10 4.0 50	70.110.1053.3	10
Female insert, ground left	BAS BAS LL 10 4.0 50	70.100.1053.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS SAS KR 10 4.0 50	70.115.1053.4	10
Female insert, ground right	BAS BAS KR 10 4.0 50	70.105.1053.4	10
Male insert, ground left	BAS SAS KL 10 4.0 50	70.110.1053.4	10
Female insert, ground left	BAS BAS KL 10 4.0 50	70.100.1053.4	10
Multipole adapter revos BASIC 500 V	16-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS SAS LR 16 4.0 50	70.115.1653.3	10
Female insert, ground right	BAS BAS LR 16 4.0 50	70.105.1653.3	10
Male insert, ground left	BAS SAS LL 16 4.0 50	70.110.1653.3	10
Female insert, ground left	BAS BAS LL 16 4.0 50	70.100.1653.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS SAS KR 16 4.0 50	70.115.1653.4	10
Female insert, ground right	BAS BAS KR 16 4.0 50	70.105.1653.4	10
Male insert, ground left	BAS SAS KL 16 4.0 50	70.110.1653.4	10
Female insert, ground left	BAS BAS KL 16 4.0 50	70.100.1653.4	10
Multipole adapter revos BASIC 500 V	24-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS SAS LR 24 4.0 50	70.115.2453.3	10
Female insert, ground right	BAS BAS LR 24 4.0 50	70.105.2453.3	10
Male insert, ground left	BAS SAS LL 24 4.0 50	70.110.2453.3	10
Female insert, ground left	BAS BAS LL 24 4.0 50	70.100.2453.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS SAS KR 24 4.0 50	70.115.2453.4	10
Female insert, ground right	BAS BAS KR 24 4.0 50	70.105.2453.4	10
Male insert, ground left	BAS SAS KL 24 4.0 50	70.110.2453.4	10
Female insert, ground left	BAS BAS KL 24 4.0 50	70.100.2453.4	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	12 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	200		
Screws head design / recomb. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	M3 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Open-bottom base 500 V			
Size	6	Page 124	
Size	10	Page 136, 146	
Size	16	Page 164, 174	
Size	24	Page 192, 202	

Dimensions

6-pole + ground




Long design




Short design

10-pole + ground




Long design




Short design

16-pole + ground




Long design




Short design

24-pole + ground




Long design



Short design

500 V multipole adapter with screw connection

Sets of 2 components with Bottom base, Single locking lever



Multipole adapter **revos** BASIC + Bottom base with single locking lever



6-pole + ground Size 6



10-pole + ground Size 10



16-pole + ground Size 16



24-pole + ground Size 24




Description	Type	Part No.	P.U.
Multipole adapter revos BASIC 500 V	6-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAESHRS 6 4.0 50	70.955.0653.3	10
Female insert, ground right	BAS GAESHRB 6 4.0 50	70.945.0653.3	10
Male insert, ground left	BAS GAESHL 6 4.0 50	70.950.0653.3	10
Female insert, ground left	BAS GAESHLB 6 4.0 50	70.940.0653.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAESNRS 6 4.0 50	70.955.0653.4	10
Female insert, ground right	BAS GAESNRB 6 4.0 50	70.945.0653.4	10
Male insert, ground left	BAS GAESNLS 6 4.0 50	70.950.0653.4	10
Female insert, ground left	BAS GAESNLB 6 4.0 50	70.940.0653.4	10
Multipole adapter revos BASIC 500 V	10-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAESHRS 10 4.0 50	71.955.1053.3	10
Female insert, ground right	BAS GAESHRB 10 4.0 50	71.945.1053.3	10
Male insert, ground left	BAS GAESHL 10 4.0 50	71.950.1053.3	10
Female insert, ground left	BAS GAESHLB 10 4.0 50	71.940.1053.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAESNRS 10 4.0 50	71.955.1053.4	10
Female insert, ground right	BAS GAESNRB 10 4.0 50	71.945.1053.4	10
Male insert, ground left	BAS GAESNLS 10 4.0 50	71.950.1053.4	10
Female insert, ground left	BAS GAESNLB 10 4.0 50	71.940.1053.4	10
Multipole adapter revos BASIC 500 V	16-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAESHRS 16 4.0 50	71.955.1653.3	10
Female insert, ground right	BAS GAESHRB 16 4.0 50	71.945.1653.3	10
Male insert, ground left	BAS GAESHL 16 4.0 50	71.950.1653.3	10
Female insert, ground left	BAS GAESHLB 16 4.0 50	71.940.1653.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAESNRS 16 4.0 50	71.955.1653.4	10
Female insert, ground right	BAS GAESNRB 16 4.0 50	71.945.1653.4	10
Male insert, ground left	BAS GAESNLS 16 4.0 50	71.950.1653.4	10
Female insert, ground left	BAS GAESNLB 16 4.0 50	71.940.1653.4	10
Multipole adapter revos BASIC 500 V	24-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAESHRS 24 4.0 50	71.955.2453.3	10
Female insert, ground right	BAS GAESHRB 24 4.0 50	71.945.2453.3	10
Male insert, ground left	BAS GAESHL 24 4.0 50	71.950.2453.3	10
Female insert, ground left	BAS GAESHLB 24 4.0 50	71.940.2453.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAESNRS 24 4.0 50	71.955.2453.4	10
Female insert, ground right	BAS GAESNRB 24 4.0 50	71.945.2453.4	10
Male insert, ground left	BAS GAESNLS 24 4.0 50	71.950.2453.4	10
Female insert, ground left	BAS GAESNLB 24 4.0 50	71.940.2453.4	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	12 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	M3 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		

These multipole adapters can be mounted inside the control cabinet.
Please use the version B coding accessory..



Coding accessories can be found on page 266–269.

Dimensions

6-pole + ground




Long design





Short design

10-pole + ground




Long design





Short design

16-pole + ground




Long design





Short design

24-pole + ground




Long design



Short design

500 V multipole adapter with screw connection

Sets of 2 components with Bottom base, Double locking lever



Multipole adapter **revos** BASIC + Bottom base with double locking lever



10-pole + ground Size 10



16-pole + ground Size 16



24-pole + ground Size 24




Description	Type	Part No.	P.U.
Multipole adapter revos BASIC 500 V	10-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAZSHRS 10 4.0 50	70.955.1053.3	10
Female insert, ground right	BAS GAZSHRB 10 4.0 50	70.945.1053.3	10
Male insert, ground left	BAS GAZSHLS 10 4.0 50	70.950.1053.3	10
Female insert, ground left	BAS GAZSHLB 10 4.0 50	70.940.1053.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAZSNRS 10 4.0 50	70.955.1053.4	10
Female insert, ground right	BAS GAZSNRB 10 4.0 50	70.945.1053.4	10
Male insert, ground left	BAS GAZSNLS 10 4.0 50	70.950.1053.4	10
Female insert, ground left	BAS GAZSNLB 10 4.0 50	70.940.1053.4	10
Multipole adapter revos BASIC 500 V	16-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAZSHRS 16 4.0 50	70.955.1653.3	10
Female insert, ground right	BAS GAZSHRB 16 4.0 50	70.945.1653.3	10
Male insert, ground left	BAS GAZSHLS 16 4.0 50	70.950.1653.3	10
Female insert, ground left	BAS GAZSHLB 16 4.0 50	70.940.1653.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAZSNRS 16 4.0 50	70.955.1653.4	10
Female insert, ground right	BAS GAZSNRB 16 4.0 50	70.945.1653.4	10
Male insert, ground left	BAS GAZSNLS 16 4.0 50	70.950.1653.4	10
Female insert, ground left	BAS GAZSNLB 16 4.0 50	70.940.1653.4	10
Multipole adapter revos BASIC 500 V	24-pole + ground		
Long design (6 marking fields)			
Male insert, ground right	BAS GAZSHRS 24 4.0 50	70.955.2453.3	10
Female insert, ground right	BAS GAZSHRB 24 4.0 50	70.945.2453.3	10
Male insert, ground left	BAS GAZSHLS 24 4.0 50	70.950.2453.3	10
Female insert, ground left	BAS GAZSHLB 24 4.0 50	70.940.2453.3	10
Short design (4 marking fields)			
Male insert, ground right	BAS GAZSNRS 24 4.0 50	70.955.2453.4	10
Female insert, ground right	BAS GAZSNRB 24 4.0 50	70.945.2453.4	10
Male insert, ground left	BAS GAZSNLS 24 4.0 50	70.950.2453.4	10
Female insert, ground left	BAS GAZSNLB 24 4.0 50	70.940.2453.4	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	12 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	M3 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		

These multipole adapters can be mounted inside the control cabinet.
Please use the version B coding accessory..


Coding accessories can be found on page 266–269.

Dimensions


10-pole + ground




16-pole + ground



24-pole + ground



500 V multipole adapter with spring clamp connection




Multipole adapter *revos* BASIC




6-pole + ground Size 6




10-pole + ground Size 10



16-pole + ground Size 16




24-pole + ground Size 24




Description	Type	Part No.	P.U.
Multipole adapter <i>revos</i> BASIC 500 V			
Short design (6 marking fields)			
Male insert, ground right	BAS SAF KR 6 2.5 50	70.116.0653.0	10
Female insert, ground right	BAS BAF KR 6 2.5 50	70.106.0653.0	10
Male insert, ground left	BAS SAF KL 6 2.5 50	70.111.0653.0	10
Female insert, ground left	BAS BAF KL 6 2.5 50	70.101.0653.0	10
Multipole adapter <i>revos</i> BASIC 500 V			
Short design (6 marking fields)			
Male insert, ground right	BAS SAF KR 10 2.5 50	70.116.1053.0	10
Female insert, ground right	BAS BAF KR 10 2.5 50	70.106.1053.0	10
Male insert, ground left	BAS SAF KL 10 2.5 50	70.111.1053.0	10
Female insert, ground left	BAS BAF KL 10 2.5 50	70.101.1053.0	10
Multipole adapter <i>revos</i> BASIC 500 V			
Short design (6 marking fields)			
Male insert, ground right	BAS SAF KR 16 2.5 50	70.116.1653.0	10
Female insert, ground right	BAS BAF KR 16 2.5 50	70.106.1653.0	10
Male insert, ground left	BAS SAF KL 16 2.5 50	70.111.1653.0	10
Female insert, ground left	BAS BAF KL 16 2.5 50	70.101.1653.0	10
Multipole adapter <i>revos</i> BASIC 500 V			
Short design (6 marking fields)			
Male insert, ground right	BAS SAF KR 24 2.5 50	70.116.2453.0	10
Female insert, ground right	BAS BAF KR 24 2.5 50	70.106.2453.0	10
Male insert, ground left	BAS SAF KL 24 2.5 50	70.111.2453.0	10
Female insert, ground left	BAS BAF KL 24 2.5 50	70.101.2453.0	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	9 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Screwdriver blade	DIN 5264 A 0.6 x 3.5	06.502.4000	5
Open-bottom base 500 V			
Size	6	Page 124	
Size	10	Page 136, 146	
Size	16	Page 164, 174	
Size	24	Page 192, 202	

Dimensions


6-pole + ground




10-pole + ground



16-pole + ground



24-pole + ground





400/690 V contact inserts, screw connection

Contact inserts **revos** BASIC



3-pole + 2 switching contacts + ground, Size 10



6-pole + 2 switching contacts + ground, Size 16



10-pole + 2 switching contacts + ground, Size 24



16-pole + 2 switching contacts + ground, Size 24



20-pole + 4 switching contacts + ground, Size 48



26-pole + 4 switching contacts + ground, Size 48




32-pole + 4 switching contacts + ground, Size 48



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> BASIC 400/690 V			
3-pole + ground			
Male insert	BAS STS 3 2.5 64	70.410.0340.0	10
Female insert	BAS BUS 3 2.5 64	70.400.0340.0	10
Contact inserts <i>revos</i> BASIC 400/690 V			
6-pole + ground			
Male insert	BAS STS 6 2.5 64	70.410.0640.0	10
Female insert	BAS BUS 6 2.5 64	70.400.0640.0	10
Contact inserts <i>revos</i> BASIC 400/690 V			
10-pole + ground			
Male insert	BAS STS 10 2.5 64	70.410.1040.0	10
Female insert	BAS BUS 10 2.5 64	70.400.1040.0	10
Contact inserts <i>revos</i> BASIC 400/690 V			
16-pole + ground			
Male insert	BAS STS 16 2.5 64	70.410.1640.0	10
Female insert	BAS BUS 16 2.5 64	70.400.1640.0	10
Contact inserts <i>revos</i> BASIC 400/690 V			
20-pole + ground			
Male insert	BAS STS 20 2.5 64	70.410.2040.0	5
Female insert	BAS BUS 20 2.5 64	70.400.2040.0	5
Contact inserts <i>revos</i> BASIC 400/690 V			
26-pole + ground			
Male insert	BAS STS 26 2.5 64	70.410.2640.0	5
Female insert	BAS BUS 26 2.5 64	70.400.2640.0	5
Contact inserts <i>revos</i> BASIC 400/690 V			
32-pole + ground			
Male insert	BAS STS 32 2.5 64	70.410.3240.0	5
Female insert	BAS BUS 32 2.5 64	70.400.3240.0	5
Technical data			
Rated voltage	L-PE 400 V / L-L 690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Housing 690 V			
Housing Size	10	Page 150–159	
Housing Size	16	Page 178–187	
Housing Size	24	Page 206–215	
Housing Size	48	Page 218–221	


Dimensions

3-pole + ground – 32-pole + ground




Number of poles	L1 [mm]	L2 [mm]
3	63.0	57.0
6	83.0	77.5
10	110.0	104.0
16	110.0	104.0
20	110.0	104.0
26	110.0	104.0
32	110.0	104.0


3-pole + ground




6-pole + ground




10-pole + ground




16-pole + ground




20-pole + ground



26-pole + ground



32-pole + ground



X = shortened switching contacts



690 V contact inserts, screw connection

Contact inserts *revos* BASIC



6-pole + ground Size 6



10-pole + ground Size 10



16-pole + ground Size 16




24-pole + ground Size 24



32-pole + ground Size 32



48-pole + ground Size 48



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> BASIC 690 V			
Male insert	6-pole + ground BAS STS 6 2.5 69	72.310.0653.0	10
Female insert	BAS BUS 6 2.5 69	72.300.0653.0	10
Contact inserts <i>revos</i> BASIC 690 V			
Male insert	10-pole + ground BAS STS 10 2.5 69	72.310.1053.0	10
Female insert	BAS BUS 10 2.5 69	72.300.1053.0	10
Contact inserts <i>revos</i> BASIC 690 V			
Male insert	16-pole + ground BAS STS 16 2.5 69	72.310.1653.0	10
Female insert	BAS BUS 16 2.5 69	72.300.1653.0	10
Contact inserts <i>revos</i> BASIC 690 V			
Male insert	24-pole + ground BAS STS 24 2.5 69	72.310.2453.0	10
Female insert	BAS BUS 24 2.5 69	72.300.2453.0	10
Contact inserts <i>revos</i> BASIC 690 V			
Male insert, marked 1-16, 17-32	32-pole + ground BAS STS 32 2.5 69	72.310.3253.0	5
Female insert, marked 1-16, 17-32	BAS BUS 32 2.5 69	72.300.3253.0	5
Contact inserts <i>revos</i> BASIC 690 V			
Male insert, marked 1-24, 25-48	48-pole + ground BAS STS 48 2.5 69	72.310.4853.0	5
Female insert, marked 1-24, 25-48	BAS BUS 48 2.5 69	72.300.4853.0	5

Technical data

Rated voltage	690 V
Rated voltage according to UL/CSA	600 V
Rated impulse voltage	8 kV
Rated current	16 A
Degree of pollution	3

Rated cross section

EN 60999	0.5 – 2.5 mm ²
UL	20 – 12 AWG
CSA	20 – 12 AWG

Contacts

Material	Copper alloy
Surface	Sn
Insulation strip length	7 mm
Contact resistance	≤ 1.5 mΩ
Mating cycles	200

Screws head design / recomm. torque


Mounting screws	H1 / 0.5 – 0.7 Nm
Clamping screws	H1 / 0.5 – 0.7 Nm
Ground conductor screws	H2 / 1.2 – 1.6 Nm
Temperature range	-40 – +120 °C

Housing 690 V

Size	6	Page 128–131
Size	10	Page 150–159
Size	16	Page 178–187
Size	24	Page 206–215
Size	32	Page 216–217
Size	48	Page 218–221


Dimensions

6-pole + ground – 24-pole + ground




Number of poles	L1 [mm]	L2 [mm]
6	44.0	50.0
10	57.0	63.0
16	77.5	83
24	104.0	110.0
32	77.5	83
48	104.0	110.0


6-pole + ground




10-pole + ground




16-pole + ground




24-pole + ground




32-pole + ground



48-pole + ground



X = shortened switching contacts



690 V contact inserts, crimp connection

Contact inserts **revos** BASIC



6-pole + ground Size 6



10-pole + ground Size 10




16-pole + ground Size 16




24-pole + ground Size 24



32-pole + ground Size 32



48-pole + ground Size 48



Description	Type	Part No.	P.U.
Contact inserts revos BASIC 690 V			
Male insert	6-pole + ground BAS STC 6 69	72.710.0658.0	10
Female insert	BAS BUC 6 69	72.700.0658.0	10
Contact inserts revos BASIC 690 V			
Male insert	10-pole + ground BAS STC 10 69	72.710.1058.0	10
Female insert	BAS BUC 10 69	72.700.1058.0	10
Contact inserts revos BASIC 690 V			
Male insert	16-pole + ground BAS STC 16 69	72.710.1658.0	10
Female insert	BAS BUC 16 69	72.700.1658.0	10
Contact inserts revos BASIC 690 V			
Male insert	24-pole + ground BAS STC 24 69	72.710.2458.0	10
Female insert	BAS BUC 24 69	72.700.2458.0	10
Contact inserts revos BASIC 690 V			
Male insert, marked 1-16, 17-32	32-pole + ground BAS STC 32 69	72.710.3258.0	5
Female insert, marked 1-16, 17-32	BAS BUC 32 69	72.700.3258.0	5
Contact inserts revos BASIC 690 V			
Male insert, marked 1-24, 25-48	48-pole + ground BAS STC 48 69	72.710.4858.0	5
Female insert, marked 1-24, 25-48	BAS BUC 48 69	72.700.4858.0	5
Contacts for crimp connection			
	mm ² / AWG		
Male insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.74xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Connector switching contacts (2 contacts required)	0.5 / 20	05.543.9021.0	200
Connector switching contacts (2 contacts required)	0.75 – 1 / 18	05.543.9121.0	200
Connector switching contacts (2 contacts required)	1.5 / 16	05.543.9221.0	200
Connector switching contacts (2 contacts required)	2.5 / 14	05.543.9321.0	200
Connector switching contacts (2 contacts required)	4 / 12	05.543.9421.0	200

Technical data

Rated voltage	690 V
Rated voltage according to UL/CSA	600 V
Rated impulse voltage	8 kV
Rated current	16 A
Degree of pollution	3

Rated cross section

EN 60999	0.5 – 4 mm ²
UL	20 – 12 AWG
CSA	20 – 12 AWG

Contacts

Material	Copper alloy
Surface	Sn, Ag, Au
Insulation strip length	7 mm
Contact resistance	≤ 1.5 mΩ
Mating cycles	Sn 200 / Ag, Au 500

Screws

	head design / recomm. torque
Mounting screws	H1 / 0.5 – 0.7 Nm
Clamping screws	-
Ground conductor screws	H2 / 1.2 – 1.6 Nm
Temperature range	-40 – +120 °C


Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"3"	05.502.3300.0	1
Extraction tool		05.502.3500.0	1

Housing 690 V

Size	6	Page 128–131
Size	10	Page 150–159
Size	16	Page 178–187
Size	24	Page 206–215
Size	32	Page 216–217
Size	48	Page 218–221


Dimensions

6-pole + ground – 24-pole + ground




Number of poles	L1 [mm]	L2 [mm]
6	44.0	50.0
10	57.0	63.0
16	77.0	83
24	104.0	110.0
32	77.0	83
48	104.0	110.0


6-pole + ground




10-pole + ground




16-pole + ground




24-pole + ground



32-pole + ground




48-pole + ground



X = shortened switching contacts

830 V contact inserts, spring clamp connection



Contact inserts **revos** BASIC



3-pole + 2 switching contacts + ground, Size 10




6-pole + 2 switching contacts + ground, Size 16



10-pole + 2 switching contacts + ground, Size 24




20-pole + 2 switching contacts + ground, Size 48



Description	Type	Part No.	P.U.
Contact inserts revos BASIC 830 V			
3-pole + ground			
Male insert	BAS STF 3 2.5 83 AG	70.516.0353.0	10
Female insert	BAS BUF 3 2.5 83 AG	70.506.0353.0	10
Contact inserts revos BASIC 830 V			
6-pole + ground			
Male insert	BAS STF 6 2.5 83 AG	70.516.0653.0	10
Female insert	BAS BUF 6 2.5 83 AG	70.506.0653.0	10
Contact inserts revos BASIC 830 V			
10-pole + ground			
Male insert	BAS STF 10 2.5 83 AG	70.516.1053.0	10
Female insert	BAS BUF 10 2.5 83 AG	70.506.1053.0	10
Contact inserts revos BASIC 830 V			
20-pole + ground			
Male insert	BAS STF 20 2.5 83 AG	70.516.2053.0	10
Female insert	BAS BUF 20 2.5 83 AG	70.506.2053.0	10
Technical data			
Rated voltage	830 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.14 – 2.5 mm ²		
UL	26 – 12 AWG		
CSA	26 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	7 mm		
Contact resistance	≤ 3 mΩ		
Mating cycles	500		
Screws head design / recomb. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Screwdriver blade	DIN 5264 A 0.6 x 3.5	06.502.4000.0	5
Housing 690 V			
Size	10	Page 150–159	
Size	16	Page 178–187	
Size	24	Page 206–215	
Size	48	Page 218–221	


Dimensions

3-pole + 2 switching contacts + ground – 20-pole + 2 switching contacts + ground




Number of poles	L1 [mm]	L2 [mm]
3	63.0	57.0
6	83.0	77.5
10	110.0	104.0
20	110.0	104.0


3-pole + 2 switching contacts + ground




6-pole + 2 switching contacts + ground



10-pole + 2 switching contacts + ground



20-pole + 2 switching contacts + ground





X = shortened switching contacts

Derating curve according to IEC 60512 sec. 3

revos BASIC
Spring version
830 V / 16 A / 2.5 mm²

- 3+2-pole
- 6+2-pole
- 10+2-pole





250 V contact inserts, with crimp connection


Contact inserts **revos**DD



24-pole + ground Size 6/6H




42-pole + ground Size 10/10H



72-pole + ground Size 16/16H




108-pole + ground Size 24/24H



Description	Type	Part No.	P.U.
Contact inserts revosDD 250 V			
24-pole + ground			
Male insert	DD STC 24 1.5 25	73.810.2453.0	10
Female insert	DD BUC 24 1.5 25	73.800.2453.0	10
Contact inserts revosDD 250 V			
42-pole + ground			
Male insert	DD STC 42 1.5 25	73.810.4253.0	10
Female insert	DD BUC 42 1.5 25	73.800.4253.0	10
Contact inserts revosDD 250 V			
72-pole + ground			
Male insert	DD STC 72 1.5 25	73.810.7253.0	10
Female insert	DD BUC 72 1.5 25	73.800.7253.0	10
Contact inserts revosDD 250 V			
108-pole + ground			
Male insert	DD STC 108 1.5 25	73.810.0853.0	10
Female insert	DD BUC 108 1.5 25	73.800.0853.0	10
Contacts for crimp connection			
	mm ² / AWG		
Male insert	0.14 – 0.37 / 20	05.544.4129.8	200
Female insert	0.14 – 0.37 / 20	02.125.4129.8	200
Male insert	0.5 / 20	05.544.4229.8	200
Female insert	0.5 / 20	02.125.4229.8	200
Male insert	0.75 – 1 / 18	05.544.4329.8	200
Female insert	0.75 – 1 / 18	02.125.4329.8	200
Male insert	1.5 / 16	05.544.4429.8	200
Female insert	1.5 / 16	02.125.4429.8	200
Male insert	2.5 / 14	05.544.4529.8	200
Female insert	2.5 / 14	02.125.4529.8	200
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V AC (CSA)		
Rated impulse voltage	2.5 kV		
Rated current	10 A		
Degree of pollution	2 (3 in Housing with IP54 and higher)		
Rated cross section			
EN 60999	0.14 – 2.5 mm ²		
UL	26 – 14 AWG		
CSA	26 – 14 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn, Ag, Au		
Insulation strip length	8 mm		
Contact resistance	< 5 mΩ		
Mating cycles	Ag, Au 500		
Screws head design / recomm. torque			
Mounting screws	Z1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	Z2 / 1.2 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"E"	05.502.2400.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0000.0	1
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	

Dimensions


24-pole + ground – 108-pole + ground




Number of poles	L1 [mm]	L2 [mm]
24	50.5	44.0
42	63.5	57.0
72	84	77.5
108	110.5	104.0

24-pole + ground

Connection side




Cut-out




42-pole + ground

Connection side




Cut-out




72-pole + ground

Connection side




Cut-out




108-pole + ground

Connection side




Cut-out




Derating curve according to IEC 60512 sec. 3

revos^{DD} 250V / 10 A / 1.5 mm²



Derating curve according to IEC 60512 sec. 3

revos^{DD} 250V / 16 A / 2.5 mm²





250 V contact inserts, screw connection

Contact inserts *revos* HD




10-pole + ground Size 10/15



16-pole + ground Size 16/25, 32/50



32-pole + ground Size 32/50




Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> HD 250 V		10-pole + ground	
Male insert	HD STS 10 2.5 25 AG	73.310.1053.0	10
Female insert	HD BUS 10 2.5 25 AG	73.300.1053.0	10
Contact inserts <i>revos</i> HD 250 V		16-pole + ground	
Male insert	HD STS 16 2.5 25 AG	73.310.1653.0	10
Female insert	HD BUS 16 2.5 25 AG	73.300.1653.0	10
Male insert, marked 17-32	HD STS SB 16 2.5 25 AG	73.310.1653.3	10
Female insert, marked 17-32	HD BUS SB 16 2.5 25 AG	73.300.1653.3	10
Contact inserts <i>revos</i> HD 250 V		32-pole + ground	
Male insert, marked 1-16, marked 17-32	HD STS 32 2.5 25 AG	73.310.3253.0	5
Female insert, marked 1-16, marked 17-32	HD BUS 32 2.5 25 AG	73.300.3253.0	5
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	4 kV		
Rated current	VDE 16 A / CSA 16 A / UL 14 A		
Degree of pollution	3		
Rated cross section			
EN 60999	e* 0.5 – 1.5 mm²/f** 0.75 – 2.5 mm²		
UL	20 – 14 AWG		
CSA	20 – 14 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	7 mm		
Contact resistance	≤ 4 mΩ		
Mating cycles	100		
Screws	head design / recomm. torque		
Mounting screws	Z1 / 0.5 Nm		
Clamping screws	Z1 / 0.5 Nm		
Ground conductor screws	Z2 / 1.2 Nm		
Temperature range	-40 – +120 °C		
Housing 250 V			
Size	10/15	Page 224–227	
Size	16/25	Page 228–231	
Size	32/50	Page 232–237	

* Solid

** Fine stranded

Dimensions

10-pole + ground – 32-pole + ground




Number of poles	L1 [mm]	L2 [mm]
10	56.5	49.5
16	73.0	66.0
32	73.0	66.0


10-pole + ground

Connection side

Male Female




Cut-out



16-pole + ground

Connection side

Male Female




Cut-out




32-pole + ground

Connection side


Male Female




Cut-out




Derating curve according to IEC 60512 sec. 3
revos HD 10/16 250 V / 16 A / 1.5 mm²



Derating curve according to IEC 60512 sec. 3
revos HD 10/16 250 V / 16 A / 2.5 mm²





250 V contact inserts, with crimp connection


Contact inserts *revos*^{HD}



15-pole + ground Size 10/15




25-pole + ground Size 16/25, 32/50



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i>^{HD} 250 V			
Male insert	HD STC 15 25	73.710.1553.0	10
Female insert	HD BUC 15 25	73.700.1553.0	10
Contact inserts <i>revos</i>^{HD} 250 V			
Male insert	HD STC 25 25	73.710.2553.0	10
Female insert	HD BUC 25 25	73.700.2553.0	10
Contacts for crimp connection			
	mm ² / AWG		
Male reel contacts, Sn	0.2 – 0.56 / 24 – 20	05.544.0900.0	5000
Female reel contacts, Sn	0.2 – 0.56 / 24 – 20	02.124.0900.0	5000
Male reel contacts, Sn	0.75 – 1.5 / 18 – 16	05.544.1000.0	5000
Female reel contacts, Sn	0.75 – 1.5 / 18 – 16	02.124.1000.0	5000
Male single contacts, Sn	0.2 – 0.56 / 24 – 20	05.544.0929.0	200
Female single contacts, Sn	0.2 – 0.56 / 24 – 20	02.124.0929.0	200
Male single contacts, Sn	0.75 – 1.5 / 18 – 16	05.544.1029.0	200
Female single contacts, Sn	0.75 – 1.5 / 18 – 16	02.124.1029.0	200
Male reel contacts, Au	0.5 – 1.5 / 20 – 16	05.544.1400.0	5000
Female reel contacts, Au	0.5 – 1.5 / 20 – 16	02.124.1400.0	5000
Male single contacts, Au	0.5 – 1.5 / 20 – 16	05.544.1429.0	200
Female single contacts, Au	0.5 – 1.5 / 20 – 16	02.124.1429.0	200
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	4 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.2 – 1.5 mm ²		
UL	24 – 16 AWG		
CSA	24 – 16 AWG		
Contacts			
Material	Copper alloy		
Surface	Au, Sn		
Insulation strip length	4 mm		
Contact resistance	≤ 4 mΩ		
Mating cycles	Au 500 / Sn 50		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	M3.5 / 0.8 – 1.0 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"E"	05.502.2400.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0000.0	1
Housing 250 V			
Size	10/15	Page 224–227	
Size	16/25	Page 228–231	
Size	32/50	Page 232–237	

Dimensions


15-pole + ground




Connection side

Cut-out

Male Female




25-pole + ground



Connection side


Cut-out

Male Female




Derating curve according to IEC 60512 sec. 3


73.700/710.1553.0 **revos**^{HD} 15-pole 250 V / 10 A / 1.5 mm²



Derating curve according to IEC 60512 sec. 3

73.700/710.2553.0 **revos**^{HD} 25-pole 250 V / 10 A / 1.5 mm²






250 V contact inserts, with crimp connection


Contact inserts **revos**^{HD}



40-pole + ground Size 16



64-pole + ground Size 24




80-pole + ground Size 32



Description	Type	Part No.	P.U.
Contact inserts revos^{HD} 250 V			
Male insert	HD STC 40 25	73.710.4058.0	10
Female insert	HD BUC 40 25	73.700.4058.0	10
Contact inserts revos^{HD} 250 V			
Male insert	HD STC 64 25	73.710.6458.0	10
Female insert	HD BUC 64 25	73.700.6458.0	10
Contact inserts revos^{HD} 250 V			
Male insert, marked 1-40, marked 41-80	HD STC 80 25	73.710.8058.0	5
Female insert, marked 1-40, marked 41-80	HD BUC 80 25	73.700.8058.0	5
Contacts for crimp connection			
	mm ² / AWG		
Male contact Sn, reel	0.2 – 0.56 / 24 – 20	05.544.0900.0	5000
Female contact Sn, reel	0.2 – 0.56 / 24 – 20	02.124.0900.0	5000
Male contact Sn, reel	0.75 – 1.5 / 18 – 16	05.544.1000.0	5000
Female contact Sn, reel	0.75 – 1.5 / 18 – 16	02.124.1000.0	5000
Male contact Sn, single	0.2 – 0.56 / 24 – 20	05.544.0929.0	200
Female contact Sn, single	0.2 – 0.56 / 24 – 20	02.124.0929.0	200
Male contact Sn, single	0.75 – 1.5 / 18 – 16	05.544.1029.0	200
Female contact Sn, single	0.75 – 1.5 / 18 – 16	02.124.1029.0	200
Male contact Au, reel	0.5 – 1.5 / 20 – 16	05.544.1400.0	5000
Female contact Au, reel	0.5 – 1.5 / 20 – 16	02.124.1400.0	5000
Male contact Au, single	0.5 – 1.5 / 20 – 16	05.544.1429.0	200
Female contact Au, single	0.5 – 1.5 / 20 – 16	02.124.1429.0	200
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	4 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.2 – 1.5 mm ²		
UL	24 – 16 AWG		
CSA	24 – 16 AWG		
Contacts			
Material	Copper alloy		
Surface	Au, Sn		
Insulation strip length	4 mm		
Contact resistance	≤ 4 mΩ		
Mating cycles	Au 500 / Sn 50		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	M3.5 / 0.8 – 1.0 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"E"	05.502.2400.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0000.0	1
Housing 500 V			
Size	16H	Page 162, 166, 172, 176	
Size	24H	Page 190, 194, 200, 201, 204	
Size	32	Page 216	

Dimensions


40-pole + ground – 80-pole + ground




Number of poles	L1 [mm]	L2 [mm]	L3 [mm]	L4 [mm]
40	83.3	77.5	14.5	33.0
64	109.8	104.0	14.4	33.5
80	83.3	77.5	14.5	33.0

40-pole + ground

Connection side




Cut-out




64-pole + ground

Connection side




Cut-out




80-pole + ground

Connection side



Cut-out





250 V multipole adapter, screw connection

Multipole adapter *revos*^{HD}



40-pole + ground Size 16



64-pole + ground Size 24



Description	Type	Part No.	P.U.
Multipole adapter <i>revos</i>^{HD} 250 V			
Male insert, ground right	HD SAS WR40 2.5 25	73.115.4053.0	4
Female insert, ground right	HD BAS WR40 2.5 25	73.105.4053.0	4
Male insert, ground left	HD SAS WL40 2.5 25	73.110.4053.0	4
Female insert, ground left	HD BAS WL40 2.5 25	73.100.4053.0	4
Multipole adapter <i>revos</i>^{HD} 250 V			
Male insert, ground right	HD SAS WR64 2.5 25	73.115.6453.3	2
Female insert, ground right	HD BAS WR64 2.5 25	73.105.6453.3	2
Male insert, ground left	HD SAS WL64 2.5 25	73.110.6453.3	2
Female insert, ground left	HD BAS WL64 2.5 25	73.100.6453.3	2

Technical data

Rated voltage	250 V
Rated voltage according to UL/CSA	600 V
Rated impulse voltage	4 kV
Rated current	10 A
Degree of pollution	3

Rated cross section

EN 60999	0.5 – 2.5 mm ²
UL	20 – 14 AWG
CSA	20 – 14 AWG

Contacts

Material	Copper alloy
Surface	Sn
Insulation strip length	12 mm
Contact resistance	≤ 6 mΩ
Mating cycles	50

Screws

	head design / recomm. torque
Mounting screws	H1 / 0.5 – 0.7 Nm
Clamping screws	M2.5 / 0.4 – 0.6 Nm
Ground conductor screws	H1 / 1.2 – 1.6 Nm
Temperature range	-40 – +120 °C


Housing

These multipole adapters may only be used with the following bases:

Description	Type	Part No.	P.U.
Open-bottom base, Size 16			
without cover, double locking lever	BAS GUT GX 16H 50 A	73.326.4028.0	1
with cover, double locking lever	BAS GUT GY 16H 50 A	73.327.4028.0	1
without cover, single locking lever	BAS GUT GV 16H 50 A	76.326.4028.0	1
with cover, single locking lever	BAS GUT GW 16H 50 A	76.327.4028.0	1
Open-bottom base, Size 24			
without cover, double locking lever	BAS GUT GX 24H 50 A	73.326.6428.0	1
with cover, double locking lever	BAS GUT GY 24H 50 A	73.327.6428.0	1
without cover, single locking lever	BAS GUT GV 24H 50 A	76.326.6428.0	1
with cover, single locking lever	BAS GUT GW 24H 50 A	76.327.6428.0	1

Dimensions

40-pole + ground




Connection side



Cut-out



64-pole + ground



Connection side



Cut-out





400 V 35 A contact inserts, screw connection

Contact inserts **revos**POWER

6-pole + ground


400 V

Size 16

Description	Type	Part No.	P.U.
Contact inserts revosPOWER			
Male insert	POW STS 6 6.0 40 AG	70.210.0653.0	10
Female insert	POW BUS 6 6.0 40 AG	70.200.0653.0	10
Technical data			
Rated voltage	400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	35 A		
Degree of pollution	3		
Rated cross section			
EN 60999	2.5 – 6 mm ²		
UL	14 – 8 AWG		
CSA	14 – 8 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	10 mm		
Contact resistance	≤ 0.6 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 1.2 – 1.6 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Housing 500 V			
Size	16/16H	Page 160–177	
Size	16XL	Page 183	


Dimensions

6-pole + ground 400 V



Derating curve
according to IEC 60512 sec. 3
revosPOWER
70.200/210.0653.0 **revos**POWER
6-pole 400 V / 35 A / 6.0 mm²

Corrected current AC [A]






690 V 35 A contact inserts, screw connection

Contact inserts **revos**POWER




6-pole + ground
690 V
Size 16



Description	Type	Part No.	P.U.
Contact inserts revosPOWER			
Male insert	6-pole + ground POW STS 6 6.0 40 AG	72.210.0653.0	10
Female insert	POW BUS 6 6.0 40 AG	72.200.0653.0	10
Technical data			
Rated voltage	690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kv		
Rated current	35 A		
Degree of pollution	3		
Rated cross section			
EN 60999	2.5 – 6 mm ²		
UL	14 – 8 AWG		
CSA	14 – 8 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	10 mm		
Contact resistance	≤ 0.6 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 1.2 – 1.6 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Housing 500 V			
Size	16/16H	Page 160–177	
Size	16XL	Page 183	


Dimensions

6-pole + ground 690 V




Derating curve
according to IEC 60512 sec. 3
revosPOWER
72.200/210.0653.0 **revos**POWER
6-pole 690 V / 35 A / 6.0 mm²

— Corrected current AC [A]



400/690 V 82 A

Contact inserts, screw connection



Contact inserts **revos** POWER




4-pole + ground
400/690 V
Size 16H



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> POWER		4-pole + ground	
Male insert	POW STS 4 16 64 AG	72.218.0453.0	10
Female insert	POW BUS 4 16 64 AG	72.208.0453.0	10
Technical data			
Rated voltage	L-PE 400 V / L-L 690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	82 A		
Degree of pollution	3		
Rated cross section			
EN 60999	6 – 16 mm ²		
UL	10 – 4 AWG		
CSA	10 – 4 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	10 mm		
Contact resistance	≤ 0.6 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H2 / 2.5 – 3.0 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Housing 500 V			
Size	16H	Page 162, 166, 172, 176	
Size	16XL	Page 183	
Open-bottom base, Size	16	Page 164, 174	

Dimensions

4-pole + ground 400/690 V




Derating curve

according to IEC 60512 sec. 3

72.208/218.0453.0 **revos** POWER

4-pole 690 V / 400 V / 82 A / 16.0 mm²

— Corrected current AC [A]



690 V 4 x 35 A, 6 x 16 A

Contact inserts, screw connection



Contact inserts **revos** POWER




4-/6-pole + ground
690 V
Size 16



Description	Type	Part No.	P.U.
Contact inserts revos POWER			
Male insert	4-/6-pole + ground POW STS 4/6 DA D AG	72.215.1053.0	10
Female insert	POW BUS 4/6 DA D AG	72.205.1053.0	10
Technical data			
Rated voltage	690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	4 Contacts 35 A / 6 Contacts 16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	4 x 2.5 – 6 mm ² and 6 x 1 – 2.5 mm ²		
UL	4 x 14 – 8 AWG and 6 x 16 – 12 AWG		
CSA	4 x 14 – 8 AWG and 6 x 16 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	>16 A Ag / 16 A Sn		
Insulation strip length	10 mm / 7 mm		
Contact resistance	≤ 1.0 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	4 x H1 / 1.2 – 1.6 Nm / 6 x H1 / 0.5 – 0.7 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Housing 690 V			
Size	16	Page 178–182, 184–187	
Size	16XL	Page 183	

Dimensions

4-/6-pole + ground 690 V



Derating curve


according to IEC 60512 sec. 3

72.215/205.1053.0 **revos** POWER

6+4-pole 690 V

35 A / 16 A / 6,0 mm² / 2.5 mm²

— Corrected current AC [A]



400/690 V 40 A + 230/400 V 16 A

Contact inserts, screw connection



Contact inserts **revos** POWER




6-/6-pole + ground
Size 16/16XL



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> POWER			
Male insert	6-/6-pole + ground POW STS 6/6 GC CA AG	72.215.1253.0	10
Female insert	POW BUS 6/6 GC CA AG	72.205.1253.0	10
Technical data			
Rated voltage	L-PE 400 V / L-L 690 V and L-PE 230 V / L-L 400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 Contacts 6 kV / 6 Contacts 4 kV		
Rated current	6 Contacts 40 A / 6 Contacts 16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	6 x 4 – 10 mm² and 6 x 1 – 2.5 mm²		
UL	6 x 12 – 16 AWG and 6 x 16 – 12 AWG		
CSA	6 x 12 – 16 AWG and 6 x 16 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	>16 A Ag / 16 A Sn		
Insulation strip length	10 mm / 7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	6 x H1 / 0.5 – 0.7 Nm / 6 x M5 / 0.8 – 1.0 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Housing 690 V			
Hood, Size 16 XL	POW GOT GA 16 M40 69 A2	72.250.1635.2	1
Open-bottom base, Size 16	BAS GUT GA 16 69 A	72.320.1628.0	1

Dimensions

6-/6-pole + ground




Derating curve

according to IEC 60512 sec. 3

72.205/215.1253.0 **revos** POWER
6+6-pole 690 V / 400 V / 230 V
40 A / 16 A / 10.0 mm² / 2.5 mm²

— Corrected current AC [A]




400/690 V 100 A + 400/690 V 40 A + 230/400 V 16 A Contact inserts, screw connection



Contact inserts **revos**POWER




3-/3-/6-pole + ground Size 24/24XL



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i>POWER			
3-/3-/6-pole + ground			
Male insert	POW STS 3/3/6 HEA CA AG	72.213.1253.0	10
Female insert	POW BUS 3/3/6 HEA CA AG	72.203.1253.0	10
Technical data			
Rated voltage	L-PE 400 V / L-L 690 V and L-PE 400 V / L-L 690 V and L-PE 230 V / L-L 400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	3 Contacts 6 kV / 3 Contacts 6 kV / 6 Contacts 4 kV		
Rated current	3 Contacts 100 A / 3 Contacts 40 A / 6 Contacts 16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	3 x 10 – 25 mm ² and 3 x 4 – 10 mm ² and 6 x 1 – 2.5 mm ²		
UL	3 x 8 – 4 AWG and 3 x 12 – 8 AWG and 6 x 18 – 14 AWG		
CSA	3 x 8 – 4 AWG and 3 x 12 – 8 AWG and 6 x 18 – 14 AWG		
Contacts			
Material	Copper alloy		
Surface	>16 A Ag / 16 A Sn		
Insulation strip length	14 mm / 10 mm / 7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws	head design / recomm. torque		
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	3 x M6 / 1.2 – 1.6 Nm and 3 x M5 / 0.8 – 1.0 Nm and 6 x H1 / 0.5 – 0.7		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Housing 690 V			
Hood, Size 24 XL	POW GOT GA 24 M50 69 A2	72.250.2435.2	1
Open-bottom base, Size 24	BAS GUT GA 24 69 A	72.320.2428.0	1

Dimensions

3-/3-/6-pole + ground



Derating curve

according to IEC 60512 sec. 3


72.203/213.1253.0 **revos**POWER

3+3+6-pole 690 V / 230 V

100 A / 40 A / 16 A

25 mm² / 16.0 mm² / 2.5 mm²

— Corrected current AC [A]



690 V 82 A + 400 V 16A


Contact inserts, screw connection



Contact inserts **revos** POWER




4-/2-pole + ground
690/400 V
Size 16



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> POWER		4-/2-pole + ground	
Male insert	POW STS 4/2 FA DB AG	72.215.0653.0	10
Female insert	POW BUS 4/2 FA DB AG	72.205.0653.0	10
Technical data			
Rated voltage	690 V and 400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV / 6 kV		
Rated current	4 Contacts 82 A (CSA 70 A) / 2 Contacts 16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	4 x 6 – 16 mm ² and 2 x 1 – 2.5 mm ²		
UL	4 x 10 – 4 AWG and 2 x 16 – 12 AWG		
CSA	4 x 10 – 4 AWG and 2 x 16 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	>16 A Ag / 16 A Sn		
Insulation strip length	15 mm / 9 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	4 x M6 / 1.2 – 1.6 Nm / 2 x H1 / 0.5 – 0.7 Nm		
Ground conductor screws	M5 / 2.0 – 2.5 Nm		
Temperature range	-40 – +120 °C		
Housing 500 V			
Hood, Size	16H	Page 162–163, 172–173	
Hood, Size	16XL	Page 183	
Open-bottom base, Size	16	Page 164, 174	
Closed-bottom base, Size	16H	Page 166–167, 176–177	

Dimensions

4-/2-pole + ground 690/400 V




Derating curve

according to IEC 60512 sec. 3

72.205/215.0653.0 **revos** POWER
4+2-pole 690 V / 400 V
82 A / 16 A / 16.0 mm² / 2.5 mm²

— Corrected current AC [A]



400 V and 690 V multipole adapter, screw connection




Multipole adapter **revos** POWER




6-pole + ground 400 V Size 16

Compatible with 72.200/210.0653.0



6-pole + ground 690 V Size 16


Compatible with 72.200/210.0653.0



Description	Type	Part No.	P.U.
Multipole adapter revos POWER			
6-pole + ground 400 V			
Male insert, ground right	POW SAS WR 6 6.0 40 AG	70.015.0653.0	10
Female insert, ground right	POW BAS WR 6 6.0 40 AG	70.005.0653.0	10
Male insert, ground left	POW SAS WL 6 6.0 40 AG	70.010.0653.0	10
Female insert, ground left	POW BAS WL 6 6.0 40 AG	70.000.0653.0	10
Multipole adapter revos POWER			
6-pole + ground 690 V			
Male insert, ground right	POW SAS WR 6 6.0 69 AG	72.015.0653.0	10
Female insert, ground right	POW BAS WR 6 6.0 69 AG	72.005.0653.0	10
Male insert, ground left	POW SAS WL 6 6.0 69 AG	72.010.0653.0	10
Female insert, ground left	POW BAS WL 6 6.0 69 AG	72.000.0653.0	10
Technical data			
Rated voltage	400 V	690 V	
Rated impulse voltage	6 kv	8 kv	
Rated voltage according to UL/CSA	600 V		
Rated current	35 A		
Degree of pollution	3		
Rated cross section			
EN 60999	2.5 – 6 mm ²		
UL	14 – 8 AWG		
CSA	14 – 8 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag		
Insulation strip length	12 mm		
Contact resistance	≤ 1 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.8 – 1.0 Nm		
Ground conductor screws	H1 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Open-bottom base			
Size 16, double locking lever	BAS GUT GA 16 50 A	70.320.1628.0	1
Size 16, double locking lever	BAS GUT GE 16 50 A	70.325.1628.0	1
Size 16, single locking lever	BAS GUT GK 16 50 A	71.320.1628.0	1
Size 16, single locking lever	BAS GUT GP 16 50 A	71.325.1628.0	1

Dimensions

6-pole + ground 400 V and 690 V



500 V multipole adapter, screw connection




Multipole adapter **revos** POWER



4-/6-pole + ground 500 V Size 16


Compatible with 72.205/210.1053.0



Description	Type	Part No.	P.U.
Multipole adapter revos POWER			
4-/6-pole + ground			
Male insert, ground right	POW SAS WR 4/6 DB 69 AG	72.117.1053.0	10
Female insert, ground right	POW BAS WR 4/6 DB 69 AG	72.107.1053.0	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	35 A / 16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	4 x 2.5 – 6 mm ² and 6 x 1.5 – 4 mm ²		
UL	4 x 14 – 8 AWG and 6 x 16-12 AWG		
CSA	4 x 14 – 8 AWG and 6 x 16-12 AWG		
Contacts			
Material	Copper alloy		
Surface	Ag / Sn		
Insulation strip length	12 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	6 x M3 / 0.5 – 0.7 Nm / 4 x M3.5 / 0.8 – 1.0 Nm		
Ground conductor screws	H1 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Open-bottom base, 690 V			
Size 16, double locking lever	BAS GUT GA 16 69 A	72.320.1628.0	1
Size 16, double locking lever	BAS GUT GE 16 69 A	72.325.1628.0	1
Size 16, single locking lever	BAS GUT GK 16 69 A	77.320.1628.0	1
Size 16, single locking lever	BAS GUT GP 16 69 A	77.325.1628.0	1

Dimensions

4-/6-pole + ground 500 V



Trigger action frame **revos** BASIC

The trigger action frames of the **revos** BASIC family are an economical option for implementing a pluggable feed-through connection for low-voltage switching systems. They can also be used as a cable-to-cable coupling that is mounted on a DIN rail TS35 according to DIN EN 50022 in a control cabinet.

The connection provides protection degree IP20.

The mounting application may influence the air and creepage distances and thus the rated voltage.

Plug diagram for strain relief frame

Male Female	Connector with trigger action frame without locking levers, with strain relief	Connector with trigger action frame without locking levers, without strain relief	Connector with trigger action frame with locking levers, with strain relief	Connector with trigger action frame with locking levers, without strain relief	Multipole adapter with trigger action frame, without locking levers, SL left
Connector with trigger action frame without locking levers, with strain relief	●	○	●	●	○
Connector with trigger action frame without locking levers, without strain relief	○	○	●	●	○
Connector with trigger action frame with locking levers, with strain relief	●	●	○	○	●
Connector with trigger action frame with locking levers, without strain relief	●	●	○	○	●
Multipole adapter with trigger action frame, without locking levers, SL left	○	○	●	●	○
Multipole adapter with trigger action frame, without locking levers, SL right	○	○	●	●	○
Multipole adapter with trigger action frame, with locking levers, SL left	●	●	○	○	●
Multipole adapter with trigger action frame, with locking levers, SL right	●	●	○	○	●
Multipole adapter with trigger action frame, without locking levers, SL left, with U-foot	○	○	●	●	○
Multipole adapter with trigger action frame, without locking levers, SL right, with U-foot	○	○	●	●	○
Multipole adapter with trigger action frame, with locking levers, SL left, with U-foot	●	●	○	○	●
Multipole adapter with trigger action frame, with locking levers, SL right, with U-foot	●	●	○	○	●

- pluggable
- not pluggable

The system has the following advantages:

- Reduction of material and mounting costs
- Easy accessibility to the connector for testing purposes
- Simple and trouble-free maintenance
- Marking options with Wieland's marking system

Multipole adapter with trigger action frame, without locking levers, SL right	Multipole adapter with trigger action frame, with locking levers, SL left	Multipole adapter with trigger action frame, with locking levers, SL right	Multipole adapter with trigger action frame, without locking levers, SL left, with U-foot	Multipole adapter with trigger action frame, without locking levers, SL right, with U-foot	Multipole adapter with trigger action frame, with locking levers, SL left, with U-foot	Multipole adapter with trigger action frame, with locking levers, SL right, with U-foot
						
						
						
						
						
						
						
						
						
						
						
						

Connector with trigger action frame 500 V, screw connection

Trigger action frame **revos** BASIC 6/10/16/24-pole + ground



without locking levers
with strain relief



without locking levers
without strain relief



with locking levers
with strain relief



with locking levers
without strain relief




Description	Type	Part No.	P.U.
Trigger action frame <i>revos</i> BASIC 500 V			
Male insert		6-pole + ground	
without locking levers, with strain relief	ST 70.3 / 6 REVZ	Z5.571.0156.0	10
without locking levers, without strain relief	ST 70.3 / 6 REV	Z5.571.1156.0	10
with locking levers, with strain relief	ST 70.3 / 6 RVZ	Z5.571.2156.0	10
with locking levers, without strain relief	ST 70.3 / 6 RV	Z5.571.3156.0	10
Female insert			
without locking levers, with strain relief	BU 70.3 / 6 REVZ	Z5.570.0156.0	10
without locking levers, without strain relief	BU 70.3 / 6 REV	Z5.570.1156.0	10
with locking levers, with strain relief	BU 70.3 / 6 RVZ	Z5.570.2156.0	10
with locking levers, without strain relief	BU 70.3 / 6 RV	Z5.570.3156.0	10
Trigger action frame <i>revos</i> BASIC 500 V			
Male insert		10-pole + ground	
without locking levers, with strain relief	ST 70.3 / 10 REVZ	Z5.571.0256.0	10
without locking levers, without strain relief	ST 70.3 / 10 REV	Z5.571.1256.0	10
with locking levers, with strain relief	ST 70.3 / 10 RVZ	Z5.571.2256.0	10
with locking levers, without strain relief	ST 70.3 / 10 RV	Z5.571.3256.0	10
Female insert			
without locking levers, with strain relief	BU 70.3 / 10 REVZ	Z5.570.0256.0	10
without locking levers, without strain relief	BU 70.3 / 10 REV	Z5.570.1256.0	10
with locking levers, with strain relief	BU 70.3 / 10 RVZ	Z5.570.2256.0	10
with locking levers, without strain relief	BU 70.3 / 10 RV	Z5.570.3256.0	10
Trigger action frame <i>revos</i> BASIC 500 V			
Male insert		16-pole + ground	
without locking levers, with strain relief	ST 70.3 / 16 REVZ	Z5.571.0056.0	10
without locking levers, without strain relief	ST 70.3 / 16 REV	Z5.571.1056.0	10
with locking levers, with strain relief	ST 70.3 / 16 RVZ	Z5.571.2056.0	10
with locking levers, without strain relief	ST 70.3 / 16 RV	Z5.571.3056.0	10
Female insert			
without locking levers, with strain relief	BU 70.3 / 16 REVZ	Z5.570.0056.0	10
without locking levers, without strain relief	BU 70.3 / 16 REV	Z5.570.1056.0	10
with locking levers, with strain relief	BU 70.3 / 16 RVZ	Z5.570.2056.0	10
with locking levers, without strain relief	BU 70.3 / 16 RV	Z5.570.3056.0	10
Trigger action frame <i>revos</i> BASIC 500 V			
Male insert		24-pole + ground	
without locking levers, with strain relief	ST 70.3 / 24 REVZ	Z5.571.0356.0	10
without locking levers, without strain relief	ST 70.3 / 24 REV	Z5.571.1356.0	10
with locking levers, with strain relief	ST 70.3 / 24 RVZ	Z5.571.2356.0	10
with locking levers, without strain relief	ST 70.3 / 24 RV	Z5.571.3356.0	10
Female insert			
without locking levers, with strain relief	BU 70.3 / 24 REVZ	Z5.570.0356.0	10
without locking levers, without strain relief	BU 70.3 / 24 REV	Z5.570.1356.0	10
with locking levers, with strain relief	BU 70.3 / 24 RVZ	Z5.570.2356.0	10
with locking levers, without strain relief	BU 70.3 / 24 RV	Z5.570.3356.0	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	Sn 200		
Screws		head design / recomm. torque	
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers
with strain relief



without locking levers
without strain relief




Sheet metal cutout for
trigger action frame




sheet metal thickness
 2 ± 0.05 mm

with locking levers
with strain relief



with locking levers
without strain relief




Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Derating curve according to IEC 60512 sec. 3

revos BASIC screw version
500 V / 16 A / 2.5 mm²

- 6-pole
- 10-pole
- 16-pole
- 24-pole



Multipole adapter with trigger action frame 500 V, screw connection

Multipole adapter **revos** BASIC



without locking levers



with locking levers



without locking levers



with locking levers



Description		Type	Part No.	P.U.
Multipole adapter revos BASIC 500 V		6-pole + ground		
Male insert				
without locking levers,	ground right	ST 70.1 / 6 REV WR	Z5.573.1156.0	10
without locking levers,	ground right, with U-foot	ST 70.1 / 6 REV U WR	Z5.573.5156.0	10
without locking levers,	ground left	ST 70.1 / 6 REV WL	Z5.573.0156.0	10
without locking levers,	ground left, with U-foot	ST 70.1 / 6 REV U WL	Z5.573.4156.0	10
with locking levers,	ground right	ST 70.1 / 6 RV WR	Z5.573.3156.0	10
with locking levers,	ground right, with U-foot	ST 70.1 / 6 RV U WR	Z5.573.7156.0	10
with locking levers,	ground left	ST 70.1 / 6 RV WL	Z5.573.2156.0	10
with locking levers,	ground left, with U-foot	ST 70.1 / 6 RV U WL	Z5.573.6156.0	10
Female insert				
without locking levers,	ground right	BU 70.1 / 6 REV WR	Z5.572.1156.0	10
without locking levers,	ground right, with U-foot	BU 70.1 / 6 REV U WR	Z5.572.5156.0	10
without locking levers,	ground left	BU 70.1 / 6 REV WL	Z5.572.0156.0	10
without locking levers,	ground left, with U-foot	BU 70.1 / 6 REV U WL	Z5.572.4156.0	10
with locking levers,	ground right	BU 70.1 / 6 RV WR	Z5.572.3156.0	10
with locking levers,	ground right, with U-foot	BU 70.1 / 6 RV U WR	Z5.572.7156.0	10
with locking levers,	ground left	BU 70.1 / 6 RV WL	Z5.572.2156.0	10
with locking levers,	ground left, with U-foot	BU 70.1 / 6 RV U WL	Z5.572.6156.0	10
Multipole adapter revos BASIC 500 V		10-pole + ground		
Male insert				
without locking levers,	ground right	ST 70.1 / 10 REV WR	Z5.573.1256.0	10
without locking levers,	ground right, with U-foot	ST 70.1 / 10 REV U WR	Z5.573.5256.0	10
without locking levers,	ground left	ST 70.1 / 10 REV WL	Z5.573.0256.0	10
without locking levers,	ground left, with U-foot	ST 70.1 / 10 REV U WL	Z5.573.4256.0	10
with locking levers,	ground right	ST 70.1 / 10 RV WR	Z5.573.3256.0	10
with locking levers,	ground right, with U-foot	ST 70.1 / 10 RV U WR	Z5.573.7256.0	10
with locking levers,	ground left	ST 70.1 / 10 RV WL	Z5.573.2256.0	10
with locking levers,	ground left, with U-foot	ST 70.1 / 10 RV U WL	Z5.573.6256.0	10
Female insert				
without locking levers,	ground right	BU 70.1 / 10 REV WR	Z5.572.1256.0	10
without locking levers,	ground right, with U-foot	BU 70.1 / 10 REV U WR	Z5.572.5256.0	10
without locking levers,	ground left	BU 70.1 / 10 REV WL	Z5.572.0256.0	10
without locking levers,	ground left, with U-foot	BU 70.1 / 10 REV U WL	Z5.572.4256.0	10
with locking levers,	ground right	BU 70.1 / 10 RV WR	Z5.572.3256.0	10
with locking levers,	ground right, with U-foot	BU 70.1 / 10 RV U WR	Z5.572.7256.0	10
with locking levers,	ground left	BU 70.1 / 10 RV WL	Z5.572.2256.0	10
with locking levers,	ground left, with U-foot	BU 70.1 / 10 RV U WL	Z5.572.6256.0	10
Multipole adapter revos BASIC 500 V		16-pole + ground		
Male insert				
without locking levers,	ground right	ST 70.1 / 16 REV WR	Z5.573.1056.0	10
without locking levers,	ground right, with U-foot	ST 70.1 / 16 REV U WR	Z5.573.5056.0	10
without locking levers,	ground left	ST 70.1 / 16 REV WL	Z5.573.0056.0	10
without locking levers,	ground left, with U-foot	ST 70.1 / 16 REV U WL	Z5.573.4056.0	10
with locking levers,	ground right	ST 70.1 / 16 RV WR	Z5.573.3056.0	10
with locking levers,	ground right, with U-foot	ST 70.1 / 16 RV U WR	Z5.573.7056.0	10
with locking levers,	ground left	ST 70.1 / 16 RV WL	Z5.573.2056.0	10
with locking levers,	ground left, with U-foot	ST 70.1 / 16 RV U WL	Z5.573.6056.0	10
Female insert				
without locking levers,	ground right	BU 70.1 / 16 REV WR	Z5.572.1056.0	10
without locking levers,	ground right, with U-foot	BU 70.1 / 16 REV U WR	Z5.572.5056.0	10
without locking levers,	ground left	BU 70.1 / 16 REV WL	Z5.572.0056.0	10
without locking levers,	ground left, with U-foot	BU 70.1 / 16 REV U WL	Z5.572.4056.0	10
with locking levers,	ground right	BU 70.1 / 16 RV WR	Z5.572.3056.0	10
with locking levers,	ground right, with U-foot	BU 70.1 / 16 RV U WR	Z5.572.7056.0	10
with locking levers,	ground left	BU 70.1 / 16 RV WL	Z5.572.2056.0	10
with locking levers,	ground left, with U-foot	BU 70.1 / 16 RV U WL	Z5.572.6056.0	10
Multipole adapter revos BASIC 500 V		24-pole + ground		
Male insert				
without locking levers,	ground right	ST 70.1 / 24 REV WR	Z5.573.1356.0	10
without locking levers,	ground right, with U-foot	ST 70.1 / 24 REV U WR	Z5.573.5356.0	10
without locking levers,	ground left	ST 70.1 / 24 REV WL	Z5.573.0356.0	10
without locking levers,	ground left, with U-foot	ST 70.1 / 24 REV U WL	Z5.573.4356.0	10
with locking levers,	ground right	ST 70.1 / 24 RV WR	Z5.573.3356.0	10
with locking levers,	ground right, with U-foot	ST 70.1 / 24 RV U WR	Z5.573.7356.0	10
with locking levers,	ground left	ST 70.1 / 24 RV WL	Z5.573.2356.0	10
with locking levers,	ground left, with U-foot	ST 70.1 / 24 RV U WL	Z5.573.6356.0	10
Female insert				
without locking levers,	ground right	BU 70.1 / 24 REV WR	Z5.572.1356.0	10
without locking levers,	ground right, with U-foot	BU 70.1 / 24 REV U WR	Z5.572.5356.0	10
without locking levers,	ground left	BU 70.1 / 24 REV WL	Z5.572.0356.0	10
without locking levers,	ground left, with U-foot	BU 70.1 / 24 REV U WL	Z5.572.4356.0	10
with locking levers,	ground right	BU 70.1 / 24 RV WR	Z5.572.3356.0	10
with locking levers,	ground right, with U-foot	BU 70.1 / 24 RV U WR	Z5.572.7356.0	10
with locking levers,	ground left	BU 70.1 / 24 RV WL	Z5.572.2356.0	10
with locking levers,	ground left, with U-foot	BU 70.1 / 24 RV U WL	Z5.572.6356.0	10


Technical data, Dimensions

Multipole adapter <i>revos</i> BASIC	Technical data		
	Rated voltage	500 V	
	Rated voltage according to UL/CSA	600 V	
	Rated impulse voltage	6 kV	
	Rated current	16 A	
	Degree of pollution	3	
	Rated cross section		
	EN 60999	0.5 – 4 mm ²	
	UL	20 – 12 AWG	
	CSA	20 – 12 AWG	
	Contacts		
	Material	Copper alloy	
	Surface	Sn	
	Insulation strip length	12 mm	
	Contact resistance	≤ 3 mΩ	
	Mating cycles	Sn 200	
	Screws head design / recomm. torque		
	Mounting screws	H1 / 0.5 – 0.7 Nm	
	Clamping screws	M3 / 0.5 – 0.7 Nm	
	Ground conductor screws	H2 / 1.2 – 1.6 Nm	
	Temperature range	-40 – +120 °C	
Description		Type	Part No. P.U.
Accessories			
Universal foot		23 mm wide	05.583.0053.0 50


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers



with locking levers



Sheet metal cutout for trigger action frame



Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Connector with trigger action frame 500 V, crimp connection

Trigger action frame **revos** BASIC



**without locking levers
with strain relief**



**without locking levers
without strain relief**



**with locking levers
with strain relief**



**with locking levers
without strain relief**



Description	Type	Part No.	P.U.
Trigger action frame revos BASIC 500 V			
Male insert			
without locking levers, with strain relief	ST 70.7 / 6 REVZ	Z5.571.4156.0	10
without locking levers, without strain relief	ST 70.7 / 6 REV	Z5.571.5156.0	10
with locking levers, with strain relief	ST 70.7 / 6 RVZ	Z5.571.6656.0	10
with locking levers, without strain relief	ST 70.7 / 6 RV	Z5.571.8656.0	10
Female insert			
without locking levers, with strain relief	BU 70.7 / 6 REVZ	Z5.570.4156.0	10
without locking levers, without strain relief	BU 70.7 / 6 REV	Z5.570.5156.0	10
with locking levers, with strain relief	BU 70.7 / 6 RVZ	Z5.570.6656.0	10
with locking levers, without strain relief	BU 70.7 / 6 RV	Z5.570.8656.0	10
Multipole adapter revos BASIC 500 V			
Male insert			
without locking levers, with strain relief	ST 70.7 / 10 REVZ	Z5.571.4256.0	10
without locking levers, without strain relief	ST 70.7 / 10 REV	Z5.571.5256.0	10
with locking levers, with strain relief	ST 70.7 / 10 RVZ	Z5.571.6756.0	10
with locking levers, without strain relief	ST 70.7 / 10 RV	Z5.571.8756.0	10
Female insert			
without locking levers, with strain relief	BU 70.7 / 10 REVZ	Z5.570.4256.0	10
without locking levers, without strain relief	BU 70.7 / 10 REV	Z5.570.5256.0	10
with locking levers, with strain relief	BU 70.7 / 10 RVZ	Z5.570.6756.0	10
with locking levers, without strain relief	BU 70.7 / 10 RV	Z5.570.8756.0	10
Multipole adapter revos BASIC 500 V			
Male insert			
without locking levers, with strain relief	ST 70.7 / 16 REVZ	Z5.571.4056.0	10
without locking levers, without strain relief	ST 70.7 / 16 REV	Z5.571.5056.0	10
with locking levers, with strain relief	ST 70.7 / 16 RVZ	Z5.571.6556.0	10
with locking levers, without strain relief	ST 70.7 / 16 RV	Z5.571.8556.0	10
Female insert			
without locking levers, with strain relief	BU 70.7 / 16 REVZ	Z5.570.4056.0	10
without locking levers, without strain relief	BU 70.7 / 16 REV	Z5.570.5056.0	10
with locking levers, with strain relief	BU 70.7 / 16 RVZ	Z5.570.6556.0	10
with locking levers, without strain relief	BU 70.7 / 16 RV	Z5.570.8556.0	10
Multipole adapter revos BASIC 500 V			
Male insert			
without locking levers, with strain relief	ST 70.7 / 24 REVZ	Z5.571.4356.0	10
without locking levers, without strain relief	ST 70.7 / 24 REV	Z5.571.5356.0	10
with locking levers, with strain relief	ST 70.7 / 24 RVZ	Z5.571.6856.0	10
with locking levers, without strain relief	ST 70.7 / 24 RV	Z5.571.8856.0	10
Female insert			
without locking levers, with strain relief	BU 70.7 / 24 REVZ	Z5.570.4356.0	10
without locking levers, without strain relief	BU 70.7 / 24 REV	Z5.570.5356.0	10
with locking levers, with strain relief	BU 70.7 / 24 RVZ	Z5.570.6856.0	10
with locking levers, without strain relief	BU 70.7 / 24 RV	Z5.570.8856.0	10
Technical data			
Rated voltage	500 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Temperature range	-40 – +120 °C		

The mounting application may influence the air and creepage distances and thus the rated voltage.

Contacts, Dimensions

Contacts **revos**BASIC



tin-plated



silver-plated




gold-plated

Example:


Female insert, silver-plated, 1.5 mm²
Part No. 02.123.7202.0

Description	Type	Part No.	P.U.
Contacts for crimp connection			
Male insert	mm² / AWG		
Female insert	0.5 / 20	05.543.70xx.0	200
Male insert	0.5 / 20	02.123.70xx.0	200
Female insert	0.75 – 1 / 18	05.543.71xx.0	200
Male insert	0.75 – 1 / 18	02.123.71xx.0	200
Female insert	1.5 / 16	05.543.72xx.0	200
Male insert	1.5 / 16	02.123.72xx.0	200
Female insert	2.5 / 14	05.543.73xx.0	200
Male insert	2.5 / 14	02.123.73xx.0	200
Female insert	4 / 12	05.543.74xx.0	200
Male insert	4 / 12	02.123.74xx.0	200
Surface	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Technical data			
Contacts			
Material	Copper alloy		
Surface	Sn, Ag, Au		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	Sn 200		
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	“B”	05.502.2100.0	1
Contact positioner	“3”	05.502.3300.0	1
Extraction tool		05.502.3500.0	1


**without locking levers,
with and without strain relief**



**with locking levers,
with and without strain relief**



**Sheet metal cutout for
trigger action frame**




sheet metal thickness
2 ± 0.05 mm

Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Derating curve according to IEC 60512 sec. 3

revosBASIC crimp version
500 V / 16 A / 1.5 mm²

- 6-pole
- 10-pole
- 16-pole
- 24-pole



Connector with trigger action frame 690 V, screw connection

Trigger action frame **revos** BASIC




without locking levers with strain relief



without locking levers without strain relief



with locking levers with strain relief



with locking levers without strain relief




Description	Type	Part No.	P.U.
Trigger action frame revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.3 / 6 REVZ	Z5.571.0656.0	10
without locking levers, without strain relief	ST 72.3 / 6 REV	Z5.571.1656.0	10
with locking levers, with strain relief	ST 72.3 / 6 RVZ	Z5.571.2656.0	10
with locking levers, without strain relief	ST 72.3 / 6 RV	Z5.571.3656.0	10
Female insert			
without locking levers, with strain relief	BU 72.3 / 6 REVZ	Z5.570.0656.0	10
without locking levers, without strain relief	BU 72.3 / 6 REV	Z5.570.1656.0	10
with locking levers, with strain relief	BU 72.3 / 6 RVZ	Z5.570.2656.0	10
with locking levers, without strain relief	BU 72.3 / 6 RV	Z5.570.3656.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.3 / 10 REVZ	Z5.571.0756.0	10
without locking levers, without strain relief	ST 72.3 / 10 REV	Z5.571.1756.0	10
with locking levers, with strain relief	ST 72.3 / 10 RVZ	Z5.571.2756.0	10
with locking levers, without strain relief	ST 72.3 / 10 RV	Z5.571.3756.0	10
Female insert			
without locking levers, with strain relief	BU 72.3 / 10 REVZ	Z5.570.0756.0	10
without locking levers, without strain relief	BU 72.3 / 10 REV	Z5.570.1756.0	10
with locking levers, with strain relief	BU 72.3 / 10 RVZ	Z5.570.2756.0	10
with locking levers, without strain relief	BU 72.3 / 10 RV	Z5.570.3756.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.3 / 16 REVZ	Z5.571.0556.0	10
without locking levers, without strain relief	ST 72.3 / 16 REV	Z5.571.1556.0	10
with locking levers, with strain relief	ST 72.3 / 16 RVZ	Z5.571.2556.0	10
with locking levers, without strain relief	ST 72.3 / 16 RV	Z5.571.3556.0	10
Female insert			
without locking levers, with strain relief	BU 72.3 / 16 REVZ	Z5.570.0556.0	10
without locking levers, without strain relief	BU 72.3 / 16 REV	Z5.570.1556.0	10
with locking levers, with strain relief	BU 72.3 / 16 RVZ	Z5.570.2556.0	10
with locking levers, without strain relief	BU 72.3 / 16 RV	Z5.570.3556.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.3 / 24 REVZ	Z5.571.0856.0	10
without locking levers, without strain relief	ST 72.3 / 24 REV	Z5.571.1856.0	10
with locking levers, with strain relief	ST 72.3 / 24 RVZ	Z5.571.2856.0	10
with locking levers, without strain relief	ST 72.3 / 24 RV	Z5.571.3856.0	10
Female insert			
without locking levers, with strain relief	BU 72.3 / 24 REVZ	Z5.570.0856.0	10
without locking levers, without strain relief	BU 72.3 / 24 REV	Z5.570.1856.0	10
with locking levers, with strain relief	BU 72.3 / 24 RVZ	Z5.570.2856.0	10
with locking levers, without strain relief	BU 72.3 / 24 RV	Z5.570.3856.0	10
Technical data			
Rated voltage	690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Contacts			
Material	Copper alloy		
Surface	Sn		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	200		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-40 – +120 °C		


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers
with strain relief




with locking levers
with strain relief




without locking levers
without strain relief



with locking levers
without strain relief



Sheet metal cutout for
trigger action frame



sheet metal thickness
 2 ± 0.05 mm

Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Multipole adapter with trigger action frame 690 V, with and without locking levers, screw connection

Multipole adapter **revos** BASIC




without locking levers




with locking levers



without locking levers



with locking levers



Description		Type	Part No.	P.U.
Multipole adapter revos BASIC 690 V		6-pole + ground		
Male insert				
without locking levers,	ground right	ST 72.1 / 6 REV WR	Z5.573.1656.0	10
without locking levers,	ground right, with U-foot	ST 72.1 / 6 REV U WR	Z5.573.5656.0	10
without locking levers,	ground left	ST 72.1 / 6 REV WL	Z5.573.0656.0	10
without locking levers,	ground left, with U-foot	ST 72.1 / 6 REV U WL	Z5.573.4656.0	10
with locking levers,	ground right	ST 72.1 / 6 RV WR	Z5.573.3656.0	10
with locking levers,	ground right, with U-foot	ST 72.1 / 6 RV U WR	Z5.573.7656.0	10
with locking levers,	ground left	ST 72.1 / 6 RV WL	Z5.573.2656.0	10
with locking levers,	ground left, with U-foot	ST 72.1 / 6 RV U WL	Z5.573.6656.0	10
Female insert				
without locking levers,	ground right	BU 72.1 / 6 REV WR	Z5.572.1656.0	10
without locking levers,	ground right, with U-foot	BU 72.1 / 6 REV U WR	Z5.572.5656.0	10
without locking levers,	ground left	BU 72.1 / 6 REV WL	Z5.572.0656.0	10
without locking levers,	ground left, with U-foot	BU 72.1 / 6 REV U WL	Z5.572.4656.0	10
with locking levers,	ground right	BU 72.1 / 6 RV WR	Z5.572.3656.0	10
with locking levers,	ground right, with U-foot	BU 72.1 / 6 RV U WR	Z5.572.7656.0	10
with locking levers,	ground left	BU 72.1 / 6 RV WL	Z5.572.2656.0	10
with locking levers,	ground left, with U-foot	BU 72.1 / 6 RV U WL	Z5.572.6656.0	10
Multipole adapter revos BASIC 690 V		10-pole + ground		
Male insert				
without locking levers,	ground right	ST 72.1 / 10 REV WR	Z5.573.1756.0	10
without locking levers,	ground right, with U-foot	ST 72.1 / 10 REV U WR	Z5.573.5756.0	10
without locking levers,	ground left	ST 72.1 / 10 REV WL	Z5.573.0756.0	10
without locking levers,	ground left, with U-foot	ST 72.1 / 10 REV U WL	Z5.573.4756.0	10
with locking levers,	ground right	ST 72.1 / 10 RV WR	Z5.573.3756.0	10
with locking levers,	ground right, with U-foot	ST 72.1 / 10 RV U WR	Z5.573.7756.0	10
with locking levers,	ground left	ST 72.1 / 10 RV WL	Z5.573.2756.0	10
with locking levers,	ground left, with U-foot	ST 72.1 / 10 RV U WL	Z5.573.6756.0	10
Female insert				
without locking levers,	ground right	BU 72.1 / 10 REV WR	Z5.572.1756.0	10
without locking levers,	ground right, with U-foot	BU 72.1 / 10 REV U WR	Z5.572.5756.0	10
without locking levers,	ground left	BU 72.1 / 10 REV WL	Z5.572.0756.0	10
without locking levers,	ground left, with U-foot	BU 72.1 / 10 REV U WL	Z5.572.4756.0	10
with locking levers,	ground right	BU 72.1 / 10 RV WR	Z5.572.3756.0	10
with locking levers,	ground right, with U-foot	BU 72.1 / 10 RV U WR	Z5.572.7756.0	10
with locking levers,	ground left	BU 72.1 / 10 RV WL	Z5.572.2756.0	10
with locking levers,	ground left, with U-foot	BU 72.1 / 10 RV U WL	Z5.572.6756.0	10
Multipole adapter revos BASIC 690 V		16-pole + ground		
Male insert				
without locking levers,	ground right	ST 72.1 / 16 REV WR	Z5.573.1556.0	10
without locking levers,	ground right, with U-foot	ST 72.1 / 16 REV U WR	Z5.573.5556.0	10
without locking levers,	ground left	ST 72.1 / 16 REV WL	Z5.573.0556.0	10
without locking levers,	ground left, with U-foot	ST 72.1 / 16 REV U WL	Z5.573.4556.0	10
with locking levers,	ground right	ST 72.1 / 16 RV WR	Z5.573.3556.0	10
with locking levers,	ground right, with U-foot	ST 72.1 / 16 RV U WR	Z5.573.7556.0	10
with locking levers,	ground left	ST 72.1 / 16 RV WL	Z5.573.2556.0	10
with locking levers,	ground left, with U-foot	ST 72.1 / 16 RV U WL	Z5.573.6556.0	10
Female insert				
without locking levers,	ground right	BU 72.1 / 16 REV WR	Z5.572.1556.0	10
without locking levers,	ground right, with U-foot	BU 72.1 / 16 REV U WR	Z5.572.5556.0	10
without locking levers,	ground left	BU 72.1 / 16 REV WL	Z5.572.0556.0	10
without locking levers,	ground left, with U-foot	BU 72.1 / 16 REV U WL	Z5.572.4556.0	10
with locking levers,	ground right	BU 72.1 / 16 RV WR	Z5.572.3556.0	10
with locking levers,	ground right, with U-foot	BU 72.1 / 16 RV U WR	Z5.572.7556.0	10
with locking levers,	ground left	BU 72.1 / 16 RV WL	Z5.572.2556.0	10
with locking levers,	ground left, with U-foot	BU 72.1 / 16 RV U WL	Z5.572.6556.0	10
Multipole adapter revos BASIC 690 V		24-pole + ground		
Male insert				
without locking levers,	ground right	ST 72.1 / 24 REV WR	Z5.573.1856.0	10
without locking levers,	ground right, with U-foot	ST 72.1 / 24 REV U WR	Z5.573.5856.0	10
without locking levers,	ground left	ST 72.1 / 24 REV WL	Z5.573.0856.0	10
without locking levers,	ground left, with U-foot	ST 72.1 / 24 REV U WL	Z5.573.4856.0	10
with locking levers,	ground right	ST 72.1 / 24 RV WR	Z5.573.3856.0	10
with locking levers,	ground right, with U-foot	ST 72.1 / 24 RV U WR	Z5.573.7856.0	10
with locking levers,	ground left	ST 72.1 / 24 RV WL	Z5.573.2856.0	10
with locking levers,	ground left, with U-foot	ST 72.1 / 24 RV U WL	Z5.573.6856.0	10
Female insert				
without locking levers,	ground right	BU 72.1 / 24 REV WR	Z5.572.1856.0	10
without locking levers,	ground right, with U-foot	BU 72.1 / 24 REV U WR	Z5.572.5856.0	10
without locking levers,	ground left	BU 72.1 / 24 REV WL	Z5.572.0856.0	10
without locking levers,	ground left, with U-foot	BU 72.1 / 24 REV U WL	Z5.572.4856.0	10
with locking levers,	ground right	BU 72.1 / 24 RV WR	Z5.572.3856.0	10
with locking levers,	ground right, with U-foot	BU 72.1 / 24 RV U WR	Z5.572.7856.0	10
with locking levers,	ground left	BU 72.1 / 24 RV WL	Z5.572.2856.0	10
with locking levers,	ground left, with U-foot	BU 72.1 / 24 RV U WL	Z5.572.6856.0	10

Technical data, Dimensions


Multipole adapter *revos*BASIC

Technical data				
Rated voltage		500 V		
Rated voltage according to UL/CSA		600 V		
Rated impulse voltage		6 kV		
Rated current		16 A		
Degree of pollution		3		
Rated cross section				
EN 60999		0.5 – 4 mm²		
UL		20 – 12 AWG		
CSA		20 – 12 AWG		
Contacts				
Material		Copper alloy		
Surface		Sn		
Insulation strip length		12 mm		
Contact resistance		≤ 3 mΩ		
Mating cycles		200		
Screws		head design / recomm. torque		
Mounting screws		H1 / 0.5 – 0.7 Nm		
Clamping screws		M3 / 0.5 – 0.7 Nm		
Ground conductor screws		H2 / 1.2 – 1.6 Nm		
Temperature range		-40 – +120 °C		
Description		Type	Part No.	P.U.
Accessories				
Universal foot		23 mm wide	05.583.0053.0	50


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers



Sheet metal cutout for trigger action frame



with locking levers



Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Connector with trigger action frame 690 V, crimp connection

Trigger action frame **revos** BASIC




**without locking levers
with strain relief**



**without locking levers
without strain relief**



**with locking levers
with strain relief**



**with locking levers
without strain relief**



Description	Type	Part No.	P.U.
Trigger action frame revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.7 / 6 REVZ	Z5.571.4656.0	10
without locking levers, without strain relief	ST 72.7 / 6 REV	Z5.571.5656.0	10
with locking levers, with strain relief	ST 72.7 / 6 RVZ	Z5.571.7656.0	10
with locking levers, without strain relief	ST 72.7 / 6 RV	Z5.571.9656.0	10
Female insert			
without locking levers, with strain relief	BU 72.7 / 6 REVZ	Z5.570.4656.0	10
without locking levers, without strain relief	BU 72.7 / 6 REV	Z5.570.5656.0	10
with locking levers, with strain relief	BU 72.7 / 6 RVZ	Z5.570.7656.0	10
with locking levers, without strain relief	BU 72.7 / 6 RV	Z5.570.9656.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.7 / 10 REVZ	Z5.571.4756.0	10
without locking levers, without strain relief	ST 72.7 / 10 REV	Z5.571.5756.0	10
with locking levers, with strain relief	ST 72.7 / 10 RVZ	Z5.571.7756.0	10
with locking levers, without strain relief	ST 72.7 / 10 RV	Z5.571.9756.0	10
Female insert			
without locking levers, with strain relief	BU 72.7 / 10 REVZ	Z5.570.4756.0	10
without locking levers, without strain relief	BU 72.7 / 10 REV	Z5.570.5756.0	10
with locking levers, with strain relief	BU 72.7 / 10 RVZ	Z5.570.7756.0	10
with locking levers, without strain relief	BU 72.7 / 10 RV	Z5.570.9756.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.7 / 16 REVZ	Z5.571.4556.0	10
without locking levers, without strain relief	ST 72.7 / 16 REV	Z5.571.5556.0	10
with locking levers, with strain relief	ST 72.7 / 16 RVZ	Z5.571.7556.0	10
with locking levers, without strain relief	ST 72.7 / 16 RV	Z5.571.9556.0	10
Female insert			
without locking levers, with strain relief	BU 72.7 / 16 REVZ	Z5.570.4556.0	10
without locking levers, without strain relief	BU 72.7 / 16 REV	Z5.570.5556.0	10
with locking levers, with strain relief	BU 72.7 / 16 RVZ	Z5.570.7556.0	10
with locking levers, without strain relief	BU 72.7 / 16 RV	Z5.570.9556.0	10
Multipole adapter revos BASIC 690 V			
Male insert			
without locking levers, with strain relief	ST 72.7 / 24 REVZ	Z5.571.4856.0	10
without locking levers, without strain relief	ST 72.7 / 24 REV	Z5.571.5856.0	10
with locking levers, with strain relief	ST 72.7 / 24 RVZ	Z5.571.7856.0	10
with locking levers, without strain relief	ST 72.7 / 24 RV	Z5.571.9856.0	10
Female insert			
without locking levers, with strain relief	BU 72.7 / 24 REVZ	Z5.570.4856.0	10
without locking levers, without strain relief	BU 72.7 / 24 REV	Z5.570.5856.0	10
with locking levers, with strain relief	BU 72.7 / 24 RVZ	Z5.570.7856.0	10
with locking levers, without strain relief	BU 72.7 / 24 RV	Z5.570.9856.0	10
Technical data			
Rated voltage	690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	16 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 4 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Temperature range	-40 – +120 °C		

The mounting application may influence the air and creepage distances and thus the rated voltage.

Contacts, Dimensions

Contacts **revos**BASIC



tin-plated



silver-plated




gold-plated

Example:


Female insert, silver-plated, 1.5 mm²
Part No. 02.123.7202.0

Description	Type	Part No.	P.U.
Contacts for crimp connection			
Male insert	mm ² / AWG		
Female insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.74xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Connector switching contacts (2 contacts required)	0,5 / 20	05.543.9021.0	200
Connector switching contacts (2 contacts required)	0,75 – 1 / 18	05.543.9121.0	200
Connector switching contacts (2 contacts required)	1,5 / 16	05.543.9221.0	200
Connector switching contacts (2 contacts required)	2,5 / 14	05.543.9321.0	200
Connector switching contacts (2 contacts required)	4 / 12	05.543.9421.0	200
Technical data			
Contacts			
Material	Copper alloy		
Surface	Sn, Au, Ag		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	Sn 200 / Au, Ag 500		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"3"	05.502.3300.0	1
Extraction tool		05.502.3500.0	1


without locking levers with strain relief,




without locking levers without strain relief



Sheet metal cutout for trigger action frame



with locking levers with strain relief,



with locking levers without strain relief,



Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
6	67.5	74.1	62.5
10	80.9	87.5	75.9
16	101.0	106.5	96.0
24	127.8	134.4	122.8

Connector with trigger action frame 250 V, crimp connection

Trigger action frame **revos** HD



without locking levers
with strain relief



without locking levers
without strain relief



with locking levers
with strain relief



with locking levers
without strain relief




Description	Type	Part No.	P.U.
Trigger action frame revos HD 250 V			
Male insert			
without locking levers, with strain relief	ST 73.7 / 40 REVZ	Z5.571.6056.0	10
without locking levers, without strain relief	ST 73.7 / 40 REV	Z5.571.7056.0	10
with locking levers, with strain relief	ST 73.7 / 40 RVZ	Z5.571.8056.0	10
with locking levers, without strain relief	ST 73.7 / 40 RV	Z5.571.9056.0	10
Female insert			
without locking levers, with strain relief	BU 73.7 / 40 REVZ	Z5.570.6056.0	10
without locking levers, without strain relief	BU 73.7 / 40 REV	Z5.570.7056.0	10
with locking levers, with strain relief	BU 73.7 / 40 RVZ	Z5.570.8056.0	10
with locking levers, without strain relief	BU 73.7 / 40 RV	Z5.570.9056.0	10
Multipole adapter revos HD 250 V			
Male insert			
without locking levers, with strain relief	ST 73.7 / 64 REVZ	Z5.571.6156.0	10
without locking levers, without strain relief	ST 73.7 / 64 REV	Z5.571.7156.0	10
with locking levers, with strain relief	ST 73.7 / 64 RVZ	Z5.571.8156.0	10
with locking levers, without strain relief	ST 73.7 / 64 RV	Z5.571.9156.0	10
Female insert			
without locking levers, with strain relief	BU 73.7 / 64 REVZ	Z5.570.6156.0	10
without locking levers, without strain relief	BU 73.7 / 64 REV	Z5.570.7156.0	10
with locking levers, with strain relief	BU 73.7 / 64 RVZ	Z5.570.8156.0	10
with locking levers, without strain relief	BU 73.7 / 64 RV	Z5.570.9156.0	10
Contacts for crimp connection			
	mm ² / AWG		
Male contact Sn, reel	0.2 – 0.56 / 24 – 20	05.544.0900.0	5000
Female contact Sn, reel	0.2 – 0.56 / 24 – 20	02.124.0900.0	5000
Male contact Sn, reel	0.75 – 1.5 / 18 – 16	05.544.1000.0	5000
Female contact Sn, reel	0.75 – 1.5 / 18 – 16	02.124.1000.0	5000
Male contact Sn, single	0.2 – 0.56 / 24 – 20	05.544.0929.0	200
Female contact Sn, single	0.2 – 0.56 / 24 – 20	02.124.0929.0	200
Male contact Sn, single	0.75 – 1.5 / 18 – 16	05.544.1029.0	200
Female contact Sn, single	0.75 – 1.5 / 18 – 16	02.124.1029.0	200
Male contact Au, reel	0.5 – 1.5 / 20 – 16	05.544.1400.0	5000
Female contact Au, reel	0.5 – 1.5 / 20 – 16	02.124.1400.0	5000
Male contact Au, single	0.5 – 1.5 / 20 – 16	05.544.1429.0	200
Female contact Au, single	0.5 – 1.5 / 20 – 16	02.124.1429.0	200
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	4 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.2 – 1.5 mm ²		
UL	24 – 16 AWG		
CSA	24 – 16 AWG		
Contacts			
Material	-		
Surface	-		
Insulation strip length	4 mm		
Contact resistance	≤ 4 mΩ		
Mating cycles	Au 500 / Sn 50		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"E"	05.502.2400.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0000.0	1


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers
with strain relief




with locking levers
with strain relief




without locking levers
without strain relief



with locking levers
without strain relief



Sheet metal cutout for
trigger action frame



Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
40	101.0	106.5	96.0
64	127.8	134.4	122.8

Multipole adapter with trigger action frame 250 V, screw connection


Multipole adapter *revos* HD



without locking levers



with locking levers




Description	Type	Part No.	P.U.
Multipole adapter <i>revos</i> HD 250 V			
40-pole + ground			
Male insert			
without locking levers, ground right	ST 73.1 / 40 REV WR	Z5.573.8356.0	4
without locking levers, ground right, with U-foot	ST 73.1 / 40 REV U WR	Z5.573.9356.0	2
without locking levers, ground left	ST 73.1 / 40 REV WL	Z5.573.8056.0	4
without locking levers, ground left, with U-foot	ST 73.1 / 40 REV U WL	Z5.573.9156.0	2
with locking levers, ground right	ST 73.1 / 40 RV WR	Z5.573.8956.0	4
with locking levers, ground right, with U-foot	ST 73.1 / 40 RV U WR	Z5.573.9756.0	2
with locking levers, ground left	ST 73.1 / 40 RV WL	Z5.573.8656.0	4
with locking levers, ground left, with U-foot	ST 73.1 / 40 RV U WL	Z5.573.9556.0	2
Female insert			
without locking levers, ground right	BU 73.1 / 40 REV WR	Z5.572.8356.0	4
without locking levers, ground right, with U-foot	BU 73.1 / 40 REV U WR	Z5.572.9356.0	2
without locking levers, ground left	BU 73.1 / 40 REV WL	Z5.572.8056.0	4
without locking levers, ground left, with U-foot	BU 73.1 / 40 REV U WL	Z5.572.9156.0	2
with locking levers, ground right	BU 73.1 / 40 RV WR	Z5.572.8956.0	4
with locking levers, ground right, with U-foot	BU 73.1 / 40 RV U WR	Z5.572.9756.0	2
with locking levers, ground left	BU 73.1 / 40 RV WL	Z5.572.8656.0	4
with locking levers, ground left, with U-foot	BU 73.1 / 40 RV U WL	Z5.572.9556.0	2
Multipole adapter <i>revos</i> HD 250 V			
64-pole + ground			
Male insert			
without locking levers, ground right	ST 73.1 / 64 REV WR	Z5.573.8456.0	2
without locking levers, ground right, with U-foot	ST 73.1 / 64 REV U WR	Z5.573.9456.0	2
without locking levers, ground left	ST 73.1 / 64 REV WL	Z5.573.8156.0	2
without locking levers, ground left, with U-foot	ST 73.1 / 64 REV U WL	Z5.573.9256.0	2
with locking levers, ground right	ST 73.1 / 64 RV WR	Z5.573.9056.0	2
with locking levers, ground right, with U-foot	ST 73.1 / 64 RV U WR	Z5.573.9856.0	2
with locking levers, ground left	ST 73.1 / 64 RV WL	Z5.573.8756.0	2
with locking levers, ground left, with U-foot	ST 73.1 / 64 RV U WL	Z5.573.9656.0	2
Female insert			
without locking levers, ground right	BU 73.1 / 64 REV WR	Z5.572.8456.0	2
without locking levers, ground right, with U-foot	BU 73.1 / 64 REV U WR	Z5.572.9456.0	2
without locking levers, ground left	BU 73.1 / 64 REV WL	Z5.572.8156.0	2
without locking levers, ground left, with U-foot	BU 73.1 / 64 REV U WL	Z5.572.9256.0	2
with locking levers, ground right	BU 73.1 / 64 RV WR	Z5.572.9056.0	2
with locking levers, ground right, with U-foot	BU 73.1 / 64 RV U WR	Z5.572.9856.0	2
with locking levers, ground left	BU 73.1 / 64 RV WL	Z5.572.8756.0	2
with locking levers, ground left, with U-foot	BU 73.1 / 64 RV U WL	Z5.572.9656.0	2
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	4 kV		
Rated current	10 A		
Degree of pollution	3		
Rated cross section			
EN 60999	0.2 – 1.5 mm²		
UL	24 – 16 AWG		
CSA	24 – 16 AWG		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	-		
Ground conductor screws	M3 / 0.8 – 1.0 Nm		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Universal foot	23 mm wide	05.583.0053.0	50


The mounting application may influence the air and creepage distances and thus the rated voltage.

Dimensions


without locking levers



Sheet metal cutout for trigger action frame



with locking levers



Number of poles	L1 [mm]	L2 [mm]	L3 [mm]
40	101.0	106.5	96.0
64	127.8	134.4	122.8

Data cable feed-through

Data cable feed-through revos IT

2 bushings



3 bushings



4 bushings



Description	Type	Part No.	P.U.
Data cable feed-through revos IT			
2 bushings, Size 10	IT DKE 10	70.060.1028.0	10
3 bushings, Size 16	IT DKE 16	70.060.1628.0	10
4 bushings, Size 24	IT DKE 24	70.060.2428.0	5

Technical data

Number of Bushings

2 bushings	2
3 bushings	3
4 bushings	4

Cable diameter

2 bushings	1 x 4.5 – 10 mm and 1 x 9 – 15 mm
3 bushings	2 x 4.5 – 10 mm and 1 x 9 – 15 mm
4 bushings	2 x 4.5 – 10 mm and 2 x 9 – 15 mm

Material

Housing	Die cast aluminum
Gaskets	Neoprene (oil-resistant and anti-ageing)
Clamping screws	galvanically zinc-plated steel

Protection degree according to EN60529

IP 65

Temperature range

-40 – +100 °C

Description	Type	Part No.	P.U.
Accessories			
Rubber gasket for Connection range	2 mm – 10 mm	05.562.3183.0	20
Rubber gasket for Connection range	9 mm – 15 mm	05.562.3283.0	10

Housing Size 10

without cover	70.320.1028.0
---------------	---------------

Housing Size 16


without cover	70.320.1628.0
---------------	---------------

Housing Size 24


without cover	70.320.2428.0
---------------	---------------

Dimensions


2 bushings



3 bushings



4 bushings



D-Sub connectors

D-Sub connectors

revos IT

Male



Female





Female





Description	Type	Part No.	P.U.
D-Sub connectors <i>revos</i> IT	9-pole		
Male, Size 6	IT GOSL 1 M20 0.5 4 AU	Z7.415.0235.0	10
Female, Size 6	IT GUBL 1 0.5 4 AU	Z7.415.0010.0	10
D-Sub connectors <i>revos</i> IT	2 x 9-pole		
Male, Size 6	IT GOSL 2 M20 0.5 4 AU	Z7.415.0335.0	10
Female, Size 6	IT GUBL 2 0.5 4 AU	Z7.415.0110.0	10
D-Sub connectors <i>revos</i> IT	15-pole		
Male, Size 6	IT GOSL 3 M20 0.5 4 AU	Z7.415.1035.0	10
Female, Size 6	IT GUBL 3 0.5 4 AU	Z7.415.0810.0	10
D-Sub connectors <i>revos</i> IT	2 x 15-pole		
Male, Size 6	IT GOSL 4 M20 0.5 4 AU	Z7.415.1135.0	10
Female, Size 6	IT GUBL 4 0.5 4 AU	Z7.415.0910.0	10
D-Sub connectors <i>revos</i> IT	25-pole		
Male, Size 10	IT GOSL 5 M20 0.5 4 AU	Z7.415.1935.0	10
Female, Size 10	IT GUBL 5 0.5 4 AU	Z7.415.1610.0	10
D-Sub connectors <i>revos</i> IT	15 + 25-pole		
Male, Size 10	IT GOSL 6 M20 0.5 4 AU	Z7.415.2135.0	10
Female, Size 10	IT GUBL 6 0.5 4 AU	Z7.415.1810.0	10
D-Sub connectors <i>revos</i> IT	2 x 25-pole		
Male, Size 10	IT GOSL 7 M20 0.5 4 AU	Z7.415.2035.0	10
Female, Size 10	IT GUBL 7 0.5 4 AU	Z7.415.1710.0	10
D-Sub connectors <i>revos</i> IT	37-pole		
Male, Size 16	IT GOSL 8 M20 0.5 4 AU	Z7.415.2635.0	10
Female, Size 16	IT GUBL 8 0.5 4 AU	Z7.415.2410.0	10
D-Sub connectors <i>revos</i> IT	2 x 37-pole		
Male, Size 16	IT GOSL 9 M20 0.5 4 AU	Z7.415.2735.0	10
Female, Size 16	IT GUBL 9 0.5 4 AU	Z7.415.2510.0	10
D-Sub connectors <i>revos</i> IT	50-pole		
Male, Size 16	IT GOSL 10 M20 0.5 4 AU	Z7.415.3335.0	10
Female, Size 16	IT GUBL 10 0.5 4 AU	Z7.415.3210.0	10
D-Sub connectors <i>revos</i> IT	2 x 50-pole		
Male, Size 16	IT GOSL 11 M20 0.5 4 AU	Z7.415.3535.0	10
Female, Size 16	IT GUBL 11 0.5 4 AU	Z7.415.3410.0	10
Technical data			
Rated voltage	40 V		
Rated voltage according to UL/CSA	-		
Rated impulse voltage	1 kV		
Current carrying capability at 20 °C	5 A		
Degree of pollution	2		
Rated cross section			
EN 60947	Solder connection max. 0.5 mm²		
UL	-		
CSA	-		
Contacts	hard gold plating over nickel plating		
Temperature range	-40 – +100 °C		

Dimensions



9-pole Size 6



25-pole Size 10



37-pole Size 16



90 V contact inserts

Contact inserts **revos** Ex



6-pole + ground Size 6



10-pole + ground Size 10



16-pole + ground Size 16



24-pole + ground Size 24



48-pole + ground Size 48



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i> Ex 90 V			
6-pole + ground			
Male insert	EX STS 6 2.5 09IA	72.310.0653.9	10
Female insert	EX BUS 6 2.5 09IA	72.300.0653.9	10
Male insert, AU	EX STS 6 2.5 09IA AU	72.311.0653.9	10
Female insert, AU	EX BUS 6 2.5 09IA AU	72.301.0653.9	10
Contact inserts <i>revos</i> Ex 90 V			
10-pole + ground			
Male insert	EX STS 10 2.5 09IA	72.310.1053.9	10
Female insert	EX BUS 10 2.5 09IA	72.300.1053.9	10
Male insert, AU	EX STS 10 2.5 09IA AU	72.311.1053.9	10
Female insert, AU	EX BUS 10 2.5 09IA AU	72.301.1053.9	10
Contact inserts <i>revos</i> Ex 90 V			
16-pole + ground			
Male insert	EX STS 16 2.5 09IA	72.310.1653.9	10
Female insert	EX BUS 16 2.5 09IA	72.300.1653.9	10
Male insert, AU	EX STS 16 2.5 09IA AU	72.311.1653.9	10
Female insert, AU	EX BUS 16 2.5 09IA AU	72.301.1653.9	10
Contact inserts <i>revos</i> Ex 90 V			
24-pole + ground			
Male insert	EX STS 24 2.5 09IA	72.310.2453.9	10
Female insert	EX BUS 24 2.5 09IA	72.300.2453.9	10
Male insert, AU	EX STS 24 2.5 09IA AU	72.311.2453.9	10
Female insert, AU	EX BUS 24 2.5 09IA AU	72.301.2453.9	10
Contact inserts <i>revos</i> Ex 90 V			
48-pole + ground			
Male insert with wire protection, marked 1-24, 25-48	EX STS 48 2.5 09IA	72.310.4853.9	5
Female insert with wire protection, marked 1-24, 25-48	EX BUS 48 2.5 09IA	72.300.4853.9	5
Technical data			
Rated voltage	90 V		
Rated voltage according to UL/CSA	-		
Rated impulse voltage	-		
Rated current	Dependent on the wire cross section*)		
Degree of pollution	3		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	-		
CSA	-		
Contacts			
Material	Copper alloy		
Surface	Sn. Au		
Insulation strip length	7 mm		
Contact resistance	≤ 1.5 mΩ		
Mating cycles	Sn 200 / Au 500		
Screws head design / recomm. torque			
Mounting screws	H1 / 0.5 – 0.7 Nm		
Clamping screws	H1 / 0.5 – 0.7 Nm		
Ground conductor screws	H2 / 1.2 – 1.6 Nm		
Temperature range	-20 – +60 °C		
Housing			
Size	6Ex	Page 238–241	
Size	10Ex	Page 242–245	
Size	16Ex	Page 246–249	
Size	24Ex	Page 250–253	
Size	48Ex	Page 254–257	

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I

BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000

Special conditions for safe use:


1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The heavy duty connectors can be used in an ambient temperature ranges from -20 °C to +60 °C.

*Wire cross section

Permitted wire cross section	Max. input current
1.5 mm ² bis 2.5 mm ²	16 A
1.0 mm ²	10 A
0.75 mm ²	6 A
0.5 mm ²	3 A


Dimensions

6-pole + ground – 48-pole + ground




Number of poles	L1 [mm]	L2 [mm]
6	44.0	50.0
10	57.0	63.0
16	77.5	83.0
24	104.0	110.0
48	104.0	110.0


6-pole + ground




10-pole + ground




16-pole + ground



24-pole + ground



48-pole + ground



Modular connector system 3-pole

Modular inserts revos FLEX




3-pole



Description	Type	Part No.	P.U.
Modular inserts revos FLEX			
3-pole			
Male insert	FLE STC 3 69	78.014.0353.0	10
Female insert	FLE BUC 3 69	78.004.0353.0	10
Contacts			
	mm ² / AWG, turned Ø 3.6 mm		
Male insert, Ag (Crimping die B)	1.5 / 16	05.544.1829.8	100
Female insert, Ag (Crimping die B)	1.5 / 16	02.125.2929.8	100
Male insert, Ag (Crimping die B)	2.5 / 14	05.544.1929.8	100
Female insert, Ag (Crimping die B)	2.5 / 14	02.125.3029.8	100
Male insert, Ag (Crimping die D)	4 / 12	05.544.3129.8	100
Female insert, Ag (Crimping die D)	4 / 12	02.125.3129.8	100
Male insert, Ag (Crimping die D)	6 / 10	05.544.3229.8	100
Female insert, Ag (Crimping die D)	6 / 10	02.125.3229.8	100
Male insert, Ag (Crimping die D)	10 / 8	05.544.3329.8	100
Female insert, Ag (Crimping die D)	10 / 8	02.125.3329.8	100
Technical data			
Rated voltage	630 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	40 A (UL 40 A, CSA 35 A)		
Degree of pollution	3		
Insulation strip length	10 mm		
Contact resistance	≤ 1 mΩ		
Mating cycles	500		
Insulating material	Polycarbonate, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Derating curve	Page 105		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Crimping die	"D"	05.502.2300.0	1
Contact positioner	"1"	05.502.3100.0	1
Extraction tool		05.502.0910.0	1
Extraction tool for modular inserts		05.502.1010.0	1

Dimensions



Modular connector system 4-pole + ground

Modular inserts **revos**FLEX




4-pole + ground



Description	Type	Part No.	P.U.
Modular inserts revosFLEX			
Male insert	4-pole + ground FLE STC 4P 1K	78.013.0453.0	10
Female insert	FLE BUC 4P 1K	78.003.0453.0	10
Contacts			
	mm ² / AWG, stamped Ø 2.5 mm		
Male insert, Ag	0.5 – 1.5 / 20 – 16	05.544.3429.8	100
Female insert, Ag	0.5 – 1.5 / 20 – 16	02.125.3429.8	100
Male insert, Ag	1.5 – 2.5 / 16 – 14	05.544.3529.8	100
Female insert, Ag	1.5 – 2.5 / 16 – 14	02.125.3529.8	100
Technical data			
Rated voltage	1000 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	16 A (UL 13 A, CSA 16 A)		
Degree of pollution	3		
Insulation strip length	4 mm		
Contact resistance	≤ 5 mΩ		
Mating cycles	500		
Insulating material	Polyamide 6.6 GF, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Derating curve	Page 105		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"C"	05.502.2200.0	1
Contact positioner	"2"	05.502.3200.0	1
Extraction tool		05.502.0610.0	1
Extraction tool for modular inserts		05.502.1010.0	1

Dimensions



Modular connector system 5-pole

Modular inserts revos FLEX




5-pole



Description	Type	Part No.	P.U.
Modular inserts revos FLEX			
5-pole			
Male insert	FLE STC 5 25	78.013.0553.0	10
Female insert	FLE BUC 5 5	78.003.0553.0	10
Contacts			
	mm ² / AWG, turned Ø 2.5 mm		
Male insert, Ag	0.5 / 20	05.544.3629.8	100
Female insert, Ag	0.5 / 20	02.125.3629.8	100
Male insert, Ag	0.75 – 1.0 / 18	05.544.3729.8	100
Female insert, Ag	0.75 – 1.0 / 18	02.125.3729.8	100
Male insert, Ag	1.5 / 16	05.544.3829.8	100
Female insert, Ag	1.5 / 16	02.125.3829.8	100
Male insert, Ag	2.5 / 14	05.544.3929.8	100
Female insert, Ag	2.5 / 14	02.125.3929.8	100
Male insert, Ag	4 / 12	05.544.4029.8	100
Female insert, Ag	4 / 12	02.125.4029.8	100
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	UL 400 V, CSA 600 V		
Rated impulse voltage	6 kV		
Rated current	20 A (UL 20 A, CSA 16 A)		
Degree of pollution	3		
Insulation strip length	8 mm		
Contact resistance	≤ 2 mΩ		
Mating cycles	500		
Insulating material	Polycarbonate, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Derating curve	Page 105		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"1"	05.502.3100.0	1
Extraction tool		05.502.0810.0	1
Extraction tool for modular inserts		05.502.1010.0	1

Dimensions



Modular connector system 10-pole

Modular inserts *revos*^{FLEX}




10-pole



Description	Type	Part No.	P.U.
Modular inserts <i>revos</i>^{FLEX}			
Male insert	FLE STC 10 25	78.012.1053.0	10
Female insert	FLE BUC 10 5	78.002.1053.0	10
Contacts			
	mm ² / AWG, turned Ø 1.6 mm		
Male insert, Ag	0.14 – 0.37 / 26 – 22	05.544.4129.8	100
Female insert, Ag	0.14 – 0.37 / 26 – 22	02.125.4129.8	100
Male insert, Ag	0.5 / 20	05.544.4229.8	100
Female insert, Ag	0.5 / 20	02.125.4229.8	100
Male insert, Ag	0.75 – 1.0 / 18	05.544.4329.8	100
Female insert, Ag	0.75 – 1.0 / 18	02.125.4329.8	100
Male insert, Ag	1.5 / 16	05.544.4429.8	100
Female insert, Ag	1.5 / 16	02.125.4429.8	100
Male insert, Ag	2.5 / 14	05.544.4529.8	100
Female insert, Ag	2.5 / 14	02.125.4529.8	100
Male insert, LWL POF	Ø 1.6 mm	05.544.8121.0	5
Female insert, LWL POF	Ø 1.6 mm	02.125.2421.0	5
Technical data			
Rated voltage	250 V		
Rated voltage according to UL/CSA	UL 240 V, CSA 600 V		
Rated impulse voltage	4 kV		
Rated current	10 A		
Degree of pollution	3		
Insulation strip length	8 mm		
Contact resistance	≤ 5 mΩ		
Mating cycles	500		
Insulating material	Polycarbonate, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Derating curve			
	Page 105		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"1"	05.502.3100.0	1
Extraction tool		05.502.0710.0	1
Extraction tool for modular inserts		05.502.1010.0	1
Set of tools for optical fiber POF contacts		95.101.2000.0	1

Dimensions



Modular connector system

Modular inserts revos FLEX



20-pole



Description	Type	Part No.	P.U.
Modular inserts revos FLEX			
Male insert	FLE STC 20 10	78.011.2053.0	10
Female insert	FLE BUC 20 10	78.001.2053.0	10
Contacts			
	mm ² / AWG, stamped Ø 1.0 mm		
Male insert, Au	0.09 – 0.25 / 28 – 24	05.544.4629.7	100
Female insert, Au	0.09 – 0.25 / 28 – 24	02.125.4629.7	100
Male insert, Au	0.25 – 0.5 / 24 – 20	05.544.4729.7	100
Female insert, Au	0.25 – 0.5 / 24 – 20	02.125.4729.7	100


Technical data			
Rated voltage	100 V		
Rated voltage according to UL/CSA	60 V		
Rated impulse voltage	1,5 kV		
Rated current	4 A (UL, CSA 5 A)		
Degree of pollution	3		
Insulation strip length	3 mm		
Contact resistance	≤ 5 mΩ		
Mating cycles	500		
Insulating material	Polycarbonate, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Derating curve	Page 105		

Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"A"	05.502.2000.0	1
Contact positioner	"4"	05.502.3800.0	1
Extraction tool		05.502.0410.0	1
Extraction tool for modular inserts		05.502.1010.0	1

Modular inserts revos FLEX



Blind module




Description	Type	Part No.	P.U.
Modular inserts revos FLEX			
Male	Blind module	05.562.6353.0	10
Female		05.562.6453.0	10


Technical data			
Insulating material	Polyamide 66, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		

Dimensions

20-pole



Blind module



Derating curve


Derating curve

according to IEC 60512 sec. 3

revos^{FLEX}

Size 6,
equipped with 2 modules

- Contact Ø 1 mm stamped, 0.5 mm², 2x20 poles
- Contact Ø 1.6 mm turned, 1.5 mm², 2x10 poles
- Contact Ø 2.5 mm turned, 2.5 mm², 2x5 poles
- Contact Ø 3.6 mm turned, 6 mm², 2x3 poles




Derating curve

according to IEC 60512 sec. 3

revos^{FLEX}

Size 10,
equipped with 3 modules

- Contact Ø 1 mm stamped, 0.5 mm², 3x20 poles
- Contact Ø 1.6 mm turned, 1.5 mm², 3x10 poles
- Contact Ø 2.5 mm turned, 2.5 mm², 3x5 poles
- Contact Ø 3.6 mm turned, 6 mm², 3x3 poles




Derating curve

according to IEC 60512 sec. 3

revos^{FLEX}

Size 16,
equipped with 5 modules

- Contact Ø 1 mm stamped, 0.5 mm², 5x20 poles
- Contact Ø 1.6 mm turned, 1.5 mm², 5x10 poles
- Contact Ø 2.5 mm turned, 2.5 mm², 5x5 poles
- Contact Ø 3.6 mm turned, 6 mm², 5x3 poles




Derating curve

according to IEC 60512 sec. 3

revos^{FLEX}

Size 24,
equipped with 7 modules

- Contact Ø 1 mm stamped, 0.5 mm², 7x20 poles
- Contact Ø 1.6 mm turned, 1.5 mm², 7x10 poles
- Contact Ø 2.5 mm turned, 2.5 mm², 7x5 poles
- Contact Ø 3.6 mm turned, 6 mm², 7x3 poles



Modular connector system

Modular inserts **revos**FLEX

Pneumatic module 1 connection



Pneumatic module 2 connections




Description	Type	Part No.	P.U.
Modular inserts revosFLEX			
1 connection			
Male insert	FLE STP 1 2.5	78.913.0153.0	5
Female insert with valve	FLE BUP 1 2.5	78.903.0153.0	5
2 connections			
Male insert	FLE STP 2 2.5	78.913.0253.0	5
Female insert with valve	FLE BUP 2 2.5	78.903.0253.0	5
Modular inserts revosFLEX			
1 connection			
Male insert	FLE STP 1 4	78.914.0153.0	5
Female insert with valve	FLE BUP 1 4	78.904.0153.0	5
2 connections			
Male insert	FLE STP 2 4	78.914.0253.0	5
Female insert with valve	FLE BUP 2 4	78.904.0253.0	5
Technical data			
Hose connection	Type / Ø inside	Module Ø 2.5 mm / 2.5 mm	Module Ø 4 mm / 4 mm
Operational pressure		10 bar	
Material of the pneumatic contact		Brass MS 58	
Insulating material		Polyamide 6.6 GF	
Flammability class		UL 94 V-0	
Temperature range		-40 – +100 °C	


Dimensions

Pneumatic module Ø 2.5 mm

1 connection




2 connections




Pneumatic module Ø 4 mm

1 connection



2 connections



Modular connector system

Modular inserts **revos**FLEX




High voltage module 2-pole



Description	Type	Part No.	P.U.
Modular inserts revosFLEX			
2-pole			
Male insert	FLE SUC 2 5K	78.013.0253.0	5
Female insert	FLE BUC 5 5K	78.003.0253.0	5
Contacts			
	mm ² / AWG, turned Ø 2.5 mm		
Male insert, Ag	0.5 / 20	05.544.3629.8	100
Female insert, Ag	0.5 / 20	02.125.3629.8	100
Male insert, Ag	0.75 – 1.0 / 18	05.544.3729.8	100
Female insert, Ag	0.75 – 1.0 / 18	02.125.3729.8	100
Male insert, Ag	1.5 / 16	05.544.3829.8	100
Female insert, Ag	1.5 / 16	02.125.3829.8	100
Male insert, Ag	2.5 / 14	05.544.3929.8	100
Female insert, Ag	2.5 / 14	02.125.3929.8	100
Male insert, Ag	4 / 12	05.544.4029.8	100
Female insert, Ag	4 / 12	02.125.4029.8	100
Technical data			
Rated voltage	2.8 kV / 5.5 kV at pollution degree 2		
Rated voltage according to UL/CSA	-		
Rated impulse voltage	18 kV		
Rated current	20 A		
Degree of pollution	3		
Insulating material	Polyamid 6.6		
Flammability class	UL 94 V-0		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"1"	05.502.3100.0	1
Extraction tool		05.502.0810.0	1
Extraction tool for modular inserts		05.502.1010.0	1

Dimensions




Modular connector system

Modular inserts revos^{FLEX}



High voltage module 1-pole + ground




High voltage module 2-pole




Description	Type	Part No.	P.U.
Modular inserts revos^{FLEX}			
1-pole + ground			
Male insert	FLE STS 1P 25 1K AG	78.116.0153.0	5
Female insert	FLE BUS 1P 25 1K AG	78.106.0153.0	5
Modular inserts revos^{FLEX}			
2-pole			
Male insert	FLE STS 2 25 1K AG	78.116.0253.0	5
Female insert	FLE BUS 2 25 1K AG	78.106.0253.0	5
Technical data			
Rated voltage	1000 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	82 A		
Degree of pollution	3		
Insulation strip length	15 mm		
Rated cross section			
EN 60999	10 – 25 mm ²		
UL	8 – 4 AWG		
CSA	8 – 4 AWG		
Mating cycles	100		
Contact resistance	≤ 2 mΩ		
Surface	Ag		
Insulating material	PA 6.6		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Screws head design	Clamping screws M6		
Recomm. torque	2.5 Nm slot		

Dimensions

1-pole + ground



2-pole



Derating curve

according to IEC 60512 sec. 3

revos^{FLEX}


high voltage module 78.106/116.01/0253.0

1000 V / 82 A

10 mm²

16 mm²

25 mm²




Modular connector system

Modular inserts **revos**FLEX




Spring clamp module 4-pole



Description	Type	Part No.	P.U.
Modular inserts revosFLEX			
Male insert	FLE STF 4 2.5 40 AG	78.213.0453.0	10
Female insert	FLE BUS 4 2.5 40 AG	78.203.0453.0	10
Technical data			
Rated voltage	400 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	6 kV		
Rated current	14 A		
Degree of pollution	3		
Insulation strip length	10 mm		
Rated cross section			
EN 60999	0.5 – 2.5 mm ²		
UL	20 – 12 AWG		
CSA	20 – 12 AWG		
Mating cycles	200		
Contact resistance	≤ 5 mΩ		
Surface	Ag		
Mating cycles	100		
Insulating material	Polycarbonate, halogen-free		
Flammability	UL 94 V-0		
Temperature range	-40 – +120 °C		
Description	Type	Part No.	P.U.
Accessories			
Screwdriver blade	DIN 5264 A 0.6 x 3.5 mm	06.502.4000.0	5

Dimensions

Spring clamp module 4-pole



Derating curve


according to IEC 60512 sec. 3

revosFLEX

Spring clamp module 78.203/213.0153.0

400 V / 14 A / 2,5 mm² / 0,5 mm²

- 2.5 mm² highest number of pole (28-contacts / Size 24)
- 2.5 mm² highest number of pole (8-contacts / Size 6)
- 0.5 mm² highest number of pole (28-contacts / Size 24)
- 0.5 mm² highest number of pole (8-contacts / Size 6)



Modular connector system

Modular inserts **revos**FLEX

USB module




Profibus module




Description	Type	Part No.	P.U.
Modular inserts <i>revos</i>^{FLEX}		USB module	
Male insert	FLE STK 4S 1.5 03 AU	78.111.0453.0	5
Female insert	FLE BUK 4S 1.5 03 AU	78.101.0453.0	5
Modular inserts <i>revos</i>^{FLEX}		Profibus module	
Male insert	FLE STD 2S 1.5 03 AU	78.191.0453.0	5
Female insert	FLE BUD 2S 1.5 03 AU	78.181.0453.0	5
Technical data			
Rated voltage	30 V		
Rated voltage according to UL/CSA	-		
Conductor cross section			
USB module	0.8 – 1.5 mm ² / 28 – 16 AWG		
Profibus module	according to PROFIBUS DP regulations		
Rated current	1 A		
Number of poles			
USB module	4+screen		
Profibus module	2+screen		
Connection torques	screen / PCB connector	0.5 Nm / 0.2 Nm	
Data transmission rate			
USB module	12 MBit/s		
Profibus module	1.5 MBit/s		
Insulating material	Polycarbonate		
Flammability class of insulating housing	UL 94 V-0		
Temperature range	-20 – +85 °C		

Dimensions

USB module



Profibus module



Modular connector system

Modular inserts **revos**FLEX




RJ45 module



Description	Type	Part No.	P.U.
Modular inserts revosFLEX			
RJ45 module			
Male insert	FLE SRC 4 40	78.930.0453.0	5
Female insert	FLE BRC 4 40	78.920.0453.0	5
Contacts			
	mm ² / AWG, turned Ø 1.6 mm		
Male insert	0.14 – 0.37 / 26 – 22	05.544.4129.8	100
Female insert	0.14 – 0.37 / 26 – 22	02.125.4129.8	100
Male insert	0.5 / 20	05.544.4229.8	100
Female insert	0.5 / 20	02.125.4229.8	100
Male insert	0.75 – 1.0 / 18	05.544.4329.8	100
Female insert	0.75 – 1.0 / 18	02.125.4329.8	100
Male insert	1.5 / 16	05.544.4429.8	100
Female insert	1.5 / 16	02.125.4429.8	100
Male insert	2.5 / 14	05.544.4529.8	100
Female insert	2.5 / 14	02.125.4529.8	100
Male insert, LWL POF	Ø 1.6 mm	05.544.8121.0	5
Female insert, LWL POF	Ø 1.6 mm	02.125.2421.0	5
Technical data			
Rated voltage	Data 30 V / power contacts 400 V		
Transmission rate	according to Category 5, ≤ 100 MBit/s		
Rated current	Data 1 A / power contacts 10 A		
Degree of pollution	3		
Insulating material	Polyamide 6.6		
Flammability	UL 94 V-0		
Temperature range	-20 – +80 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	"B"	05.502.2100.0	1
Contact positioner	"1"	05.502.3100.0	1
Extraction tool		05.502.0710.0	1
Extraction tool for modular inserts		05.502.1010.0	1
Set of tools for optical fiber POF contacts		95.101.2000.0	1


Dimensions

RJ45 module



Modular connector system

Module frame *revos*^{FLEX}




Figures:
2-Slots and 7-Slots
Male / Female


Description	Type	Part No.	P.U.
Module frame <i>revos</i>^{FLEX} gray RAL 7032			
2-Slots, Size 6			
Male	FLE MRS 6	78.010.0653.0	10
Female	FLE MRB 6	78.000.0653.0	10
Module frame <i>revos</i>^{FLEX} gray RAL 7032			
3-Slots, Size 10			
Male	FLE MRS 10	78.010.1053.0	10
Female	FLE MRB 10	78.000.1053.0	10
Module frame <i>revos</i>^{FLEX} gray RAL 7032			
5-Slots, Size 16			
Male	FLE MRS 16	78.010.1653.0	10
Female	FLE MRB 16	78.000.1653.0	10
Module frame <i>revos</i>^{FLEX} gray RAL 7032			
7-Slots, Size 24			
Male	FLE MRS 24	78.010.2453.0	10
Female	FLE MRB 24	78.000.2453.0	10
Technical data			
Insulating material	Polycarbonate, halogen-free		
Flammability class	UL 94 V-0		
Temperature range	-40 – +120 °C		
Housing 500 V			
Size	6/6H	Page 120–127	
Size	10/10H	Page 132–149	
Size	16/16H	Page 160–177	
Size	24/24H	Page 188–205	

Dimensions


2-Slots




3-Slots




5-Slots



7-Slots




690 V plastic connector


plastic connector <i>revos</i>MOT  10-pole + ground  Open-bottom base 	DescriptionTypePart No.P.U.			
	plastic connector <i>revos</i> MOT			
	Hood, side cable entry			
	10-pole + ground			
	with M25 gland →Ø 7 – 16 mm			
	MOT GOT 2 W25 SW P0			
	75.013.0051.0			
	10			
	with threaded bore hole M25			
	MOT GOT 2 W25 SW P2			
	75.013.0051.2			
	10			
	Bases			
	open			
	MOT GUT 2 O SW P			
	75.013.5051.0			
	10			
	Technical data			
	Insulating material			
	Polyamide			
	Flammability class			
	UL 94 V-0			
	Degree of protection			
	IP65			
	Color			
	black RAL 9005			
	Temperature range			
	-40 – +80 °C			
DescriptionTypePart No.P.U.				
Accessories				
Cable gland, M25 x 1.5, Plastic material, black				
Connection range 9 – 16 mm				
Z5.507.1453.1				
10				
Cable gland, M25 x 1.5, Plastic material, black				
Connection range 13 – 18 mm				
Z5.507.1553.1				
10				

Dimensions

Hood 10-pole + ground
side cable entry



Bases 10-pole + ground
open



690 V contact inserts

Contact inserts

revos MOT




10-pole + ground



Description	Type	Part No.	P.U.
Contact inserts <i>revos</i>^{MOT}			
10-pole + ground			
Male insert	MOT STC 2 10 69	75.012.5053.0	10
Female insert	MOT BUC 2 10 69	75.012.0053.0	10
Contacts			
	mm ² / AWG		
Male insert	0.5 / 20	05.543.70xx.0	200
Female insert	0.5 / 20	02.123.70xx.0	200
Male insert	0.75 – 1 / 18	05.543.71xx.0	200
Female insert	0.75 – 1 / 18	02.123.71xx.0	200
Male insert	1.5 / 16	05.543.72xx.0	200
Female insert	1.5 / 16	02.123.72xx.0	200
Male insert	2.5 / 14	05.543.73xx.0	200
Female insert	2.5 / 14	02.123.73xx.0	200
Male insert	4 / 12	05.543.74xx.0	200
Female insert	4 / 12	02.123.74xx.0	200
Surface:	tin-plated xx = 21 / silver-plated xx = 02 / gold-plated xx = 01		
Example:	Female insert, silver-plated, 1.5 mm ² / Part No. 02.123.7202.0		
Technical data			
Rated voltage	690 V		
Rated voltage according to UL/CSA	600 V		
Rated impulse voltage	8 kV		
Rated current	16 A		
Degree of pollution	3		
Insulating material	Polyamid		
Flammability class	UL 94 V-0		
Color	gray RAL 7035		
Temperature range	-40 – +80 °C		
Description	Type	Part No.	P.U.
Accessories			
Crimping tool		95.101.0800.0	1
Crimping die	“B”	05.502.2100.0	1
Contact positioner	“3”	05.502.3300.0	1
Extraction tool		05.502.3500.0	1

Dimensions

Contact inserts 10-pole + ground





revos housing components – simply, safely protected

The **revos** housing components for heavy duty connectors consist of high-quality aluminum and zinc die casting. Wieland has designed the housings to be corrosion-resistant, water and dust tight, and usable under the toughest environmental conditions.



Hoods

Hoods

Metal housings for *revos*^{MINI}



Lateral cable entry



Top cable entry



for cable-to-cable couplings

Plastic housings for *revos*^{MINI}



Lateral cable entry



Top cable entry




for cable-to-cable couplings

Description	Type	M	Part No.	P.U.
Hoods				
Metal housings for <i>revos</i>^{MINI}				
Lateral cable entry M20				
with cable gland, IP54, $\varnothing$ 3 – 14.5 mm	MIN GOT GA 7 M20 25 Z0	20	76.350.0736.0	10
with threaded collar	MIN GOT GA 7 M20 25 Z1	20	76.350.0736.1	10
Top cable entry M20				
with cable gland, IP54, $\varnothing$ 3 – 14.5 mm	MIN GOT GB 7 M20 25 Z0	20	76.352.0736.0	10
with threaded collar	MIN GOT GB 7 M20 25 Z1	20	76.352.0736.1	10
for cable-to-cable couplings M20				
with cable gland, IP54, $\varnothing$ 3 – 14.5 mm	MIN GOT GC 7 M20 25 Z0	20	76.372.0736.0	10
with threaded collar	MIN GOT GC 7 M20 25 Z1	20	76.372.0736.1	10
Plastic housings for <i>revos</i>^{MINI}				
Lateral cable entry M20				
with threaded collar	MIN GOT GA 7 M20 25 P1	20	76.350.0760.1	10
with cable gland, IP68, $\varnothing$ 6 – 12 mm	MIN GOT GA 7 M20 25 P5	20	76.350.0760.5	10
Top cable entry M20				
with cable gland, IP54, $\varnothing$ 3 – 14.5 mm	MIN GOT GB 7 M20 25 P0	20	76.352.0760.0	10
with threaded collar	MIN GOT GB 7 M20 25 P1	20	76.352.0760.1	10
with cable gland, IP68	MIN GOT GB 7 M20 25 P5	20	76.352.0760.5	10
for cable-to-cable couplings M20				
with threaded collar	MIN GOT GC 7 M20 25 P1	20	76.372.0760.1	10
with cable gland, IP68, $\varnothing$ 6 – 12 mm	MIN GOT GC 7 M20 25 P5	20	76.372.0760.5	10
Technical data				
Material	metal	plastic		
	Die cast zinc alloy	Polyamide		
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type		Part No.	P.U.
Accessories				
Cover without gasket for male insert				
Metal, nickel-plated	MIN AD DA 7 Z		07.417.6729.0	10
Plastic material, gray	MIN AD DA 7 P		07.417.6753.0	10
Cover with gasket for female insert				
Metal, nickel-plated	MIN AD DB 7 Z		07.417.6829.0	10
Plastic material, gray	MIN AD DB 7 P		07.417.6853.0	10
Contact inserts			Page 28–31	


Dimensions

Hoods


Lateral cable entry



Top cable entry




for cable-to-cable couplings




Bases

Bases

Metal housings for *revos* MINI



Plastic housings for *revos* MINI




Description	Type	M	Part No.	P.U.
Bases	Metal housings for <i>revos</i> MINI			
open	MIN GUT GA 7 25 Z	-	76.320.0729.0	10
open, angled	MIN GUT GB 7 25 Z	-	76.321.0729.0	10
closed M20				
with cable gland, IP54, $\rightarrow \text{Ø}$ 3 – 14.5 mm	MIN GUT GC 7 M20 25 Z0	20	76.322.0736.0	10
with threaded collar	MIN GUT GC 7 M20 25 Z1	20	76.322.0736.1	10
Bases	Plastic housings for <i>revos</i> MINI			
open	MIN GUT GA 7 25 P	-	76.320.0753.0	10
open, angled	MIN GUT GB 7 25 P	-	76.321.0753.0	10
closed M20				
with cable gland, IP68, $\rightarrow \text{Ø}$ 6 – 12 mm	MIN GUT GC 7 M20 25 P5	20	76.322.0760.5	10

Technical data		
Material	metal	plastic
	Die cast zinc alloy	Polyamide
Surface	silicon-free	
Locking levers	zinc-plated steel	
Gasket	NBR	
Degree of protection		
with latched locking levers	IP54	
with appropriate cable glands	IP65	
Temperature range	-40 – +120 °C	

Description	Type	Part No.	P.U.
-------------	------	----------	------

Accessories			
Cover without gasket for male insert			
Metal, nickel-plated	MIN AD DA 7 Z	07.417.6729.0	10
Plastic material, gray	MIN AD DA 7 P	07.417.6753.0	10
Cover with gasket for female insert			
Metal, nickel-plated	MIN AD DB 7 Z	07.417.6829.0	10
Plastic material, gray	MIN AD DB 7 P	07.417.6853.0	10
Contact inserts		Page 28–31	




Drilling Template


Dimensions

Bases


open



open, angled



closed




500 V Hoods, single locking lever Size 6

500 V Hoods Size 6



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 6				
Aluminum housing				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GG 6 M20 50 A0	20	70.350.0635.0	1
with threaded collar	BAS GOT GG 6 M20 50 A1	20	70.350.0635.1	1
with intermediate support	BAS GOT GG 6 M20 50 A2	20	70.350.0635.2	1
with strain relief, IP54	BAS GOT GG 6 M20 50 A3	20	70.350.0635.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 6 M25 50 A0	25	70.353.0635.0	1
with threaded collar	BAS GOT GG 6 M25 50 A1	25	70.353.0635.1	1
with intermediate support	BAS GOT GG 6 M25 50 A2	25	70.353.0635.2	1
with strain relief, IP54	BAS GOT GG 6 M25 50 A3	25	70.353.0635.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 6 M20 50 A0	20	70.352.0635.0	1
with threaded collar	BAS GOT GI 6 M20 50 A1	20	70.352.0635.1	1
with intermediate support	BAS GOT GI 6 M20 50 A2	20	70.352.0635.2	1
with strain relief, IP54	BAS GOT GI 6 M20 50 A3	20	70.352.0635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 6 M25 50 A0	25	70.354.0635.0	1
with threaded collar	BAS GOT GI 6 M25 50 A1	25	70.354.0635.1	1
with intermediate support	BAS GOT GI 6 M25 50 A2	25	70.354.0635.2	1
with strain relief, IP54	BAS GOT GI 6 M25 50 A3	25	70.354.0635.3	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 6 M20 50 A0	20	70.352.0635.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GL 6 M20 50 A0	20	70.372.0635.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 6 M20 50 A1	20	70.352.0635.1	1
with threaded collar	BAS GOT GL 6 M20 50 A1	20	70.372.0635.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GI 6 M20 50 A3	20	70.352.0635.3	1
with strain relief, IP54	BAS GOT GL 6 M20 50 A3	20	70.372.0635.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free/–			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
Size 6 see the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V / 690 V Hoods, single locking lever Size 6H, increased height design

500 V / 690 V Hoods, Size 6H, increased height design

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V / 690 V Hoods, size 6H				
Lateral cable entry M25	Aluminum housing			
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GG 6H M25 50 A0	25	73.350.0635.0	1
with threaded collar	BAS GOT GG 6H M25 50 A1	25	73.350.0635.1	1
with intermediate support	BAS GOT GG 6H M25 50 A2	25	73.350.0635.2	1
with strain relief, IP54	BAS GOT GG 6H M25 50 A3	25	73.350.0635.3	1
Lateral cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GG 6H M32 50 A0	32	73.353.0635.0	1
with threaded collar	BAS GOT GG 6H M32 50 A1	32	73.353.0635.1	1
with intermediate support	BAS GOT GG 6H M32 50 A2	32	73.353.0635.2	1
with strain relief, IP54	BAS GOT GG 6H M32 50 A3	32	73.353.0635.3	1
Top cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GI 6H M25 50 A0	25	73.352.0635.0	1
with threaded collar	BAS GOT GI 6H M25 50 A1	25	73.352.0635.1	1
with intermediate support	BAS GOT GI 6H M25 50 A2	25	73.352.0635.2	1
with strain relief, IP54	BAS GOT GI 6H M25 50 A3	25	73.352.0635.3	1
Top cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GI 6H M32 50 A0	32	73.354.0635.0	1
with threaded collar	BAS GOT GI 6H M32 50 A1	32	73.354.0635.1	1
with intermediate support	BAS GOT GI 6H M32 50 A2	32	73.354.0635.2	1
with strain relief, IP54	BAS GOT GI 6H M32 50 A3	32	73.354.0635.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
Size 6H see the product matrix			Page 24–25	

Note:


In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

Dimensions


Hoods

Lateral cable entry,


with cable gland
IP54




with threaded
collar



with intermediate
support




with strain relief
IP54




Top cable entry,


with cable gland
IP54




with threaded
collar



with intermediate
support



with strain relief
IP54



500 V Bases, single locking lever Size 6

500 V Bases, Size 6



open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 6				
Open-bottom base				
without cover	BAS GUT GK 6 50 A		70.320.0628.0	1
with cover	BAS GUT GP 6 50 A		70.325.0628.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GL 6 M20 50 A0	20	70.330.0635.0	1
with threaded collar	BAS GUT GL 6 M20 50 A1	20	70.330.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GR 6 M20 50 A0	20	70.340.0635.0	1
with threaded collar	BAS GUT GR 6 M20 50 A1	20	70.340.0635.1	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GL 6 M25 50 A0	25	70.334.0635.0	1
with threaded collar	BAS GUT GL 6 M25 50 A1	25	70.334.0635.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GM 6 M20 50 A0	20	70.331.0635.0	1
with threaded collar	BAS GUT GM 6 M20 50 A1	20	70.331.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GS 6 M20 50 A0	20	70.341.0635.0	1
with threaded collar	BAS GUT GS 6 M20 50 A1	20	70.341.0635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GM 6 M25 50 A0	25	70.335.0635.0	1
with threaded collar	BAS GUT GM 6 M25 50 A1	25	70.335.0635.1	1
1 cable gland, right, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GN 6 M20 50 A0	20	70.332.0635.0	1
with threaded collar	BAS GUT GN 6 M20 50 A1	20	70.332.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GT 6 M20 50 A0	20	70.342.0635.0	1
with threaded collar	BAS GUT GT 6 M20 50 A1	20	70.342.0635.1	1
1 cable gland, right, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GN 6 M25 50 A0	25	70.336.0635.0	1
with threaded collar	BAS GUT GN 6 M25 50 A1	25	70.336.0635.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GO 6 M20 50 A0	20	70.333.0635.0	1
with threaded collar	BAS GUT GO 6 M20 50 A1	20	70.333.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GU 6 M20 50 A0	20	70.343.0635.0	1
with threaded collar	BAS GUT GU 6 M20 50 A1	20	70.343.0635.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GO 6 M25 50 A0	25	70.337.0635.0	1
with threaded collar	BAS GUT GO 6 M25 50 A1	25	70.337.0635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
Size 6 see the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V/690 V Bases, single locking lever Size 6H, increased height design

500 V Bases Size 6H, increased height design

closed M25 2 cable glands



closed M32 2 cable glands




Description	Type	M	Part No.	P.U.
500 V Bases, size 6H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GL 6H M25 69 A0	25	73.330.0635.0	1
with threaded collar	BAS GUT GL 6H M25 69 A1	25	73.330.0635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GR 6H M25 69 A0	25	73.340.0635.0	1
with threaded collar	BAS GUT GR 6H M25 69 A1	25	73.340.0635.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GL 6H M32 69 A0	32	73.334.0635.0	1
with threaded collar	BAS GUT GL 6H M32 69 A1	32	73.334.0635.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GR 6H M32 69 A0	32	73.344.0635.0	1
with threaded collar	BAS GUT GR 6H M32 69 A1	32	73.344.0635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GM 6H M25 69 A0	25	73.331.0635.0	1
with threaded collar	BAS GUT GM 6H M25 69 A1	25	73.331.0635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GS 6H M25 69 A0	25	73.341.0635.0	1
with threaded collar	BAS GUT GS 6H M25 69 A1	25	73.341.0635.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GM 6H M32 69 A0	32	73.335.0635.0	1
with threaded collar	BAS GUT GM 6H M32 69 A1	32	73.335.0635.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GS 6H M32 69 A0	32	73.345.0635.0	1
with threaded collar	BAS GUT GS 6H M32 69 A1	32	73.345.0635.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GT 6H M25 69 A0	25	73.342.0635.0	1
with threaded collar	BAS GUT GT 6H M25 69 A1	25	73.342.0635.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GT 6H M32 69 A0	32	73.346.0635.0	1
with threaded collar	BAS GUT GT 6H M32 69 A1	32	73.346.0635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
Size 6H see the product matrix			Page 24–25	


Dimensions

Bases

closed, 2 cable glands



closed, 1 cable gland




690 V Hoods, single locking lever Size 6

690 V Hoods Size 6



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
690 V Hoods, size 6				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GG 6 M20 69 A0	20	72.350.0635.0	1
with threaded collar	BAS GOT GG 6 M20 69 A1	20	72.350.0635.1	1
with intermediate support	BAS GOT GG 6 M20 69 A2	20	72.350.0635.2	1
with strain relief, IP54	BAS GOT GG 6 M20 69 A3	20	72.350.0635.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 6 M25 69 A0	25	72.353.0635.0	1
with threaded collar	BAS GOT GG 6 M25 69 A1	25	72.353.0635.1	1
with intermediate support	BAS GOT GG 6 M25 69 A2	25	72.353.0635.2	1
with strain relief, IP54	BAS GOT GG 6 M25 69 A3	25	72.353.0635.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 6 M20 69 A0	20	72.352.0635.0	1
with threaded collar	BAS GOT GI 6 M20 69 A1	20	72.352.0635.1	1
with intermediate support	BAS GOT GI 6 M20 69 A2	20	72.352.0635.2	1
with strain relief, IP54	BAS GOT GI 6 M20 69 A3	20	72.352.0635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 6 M25 69 A0	25	72.354.0635.0	1
with threaded collar	BAS GOT GI 6 M25 69 A1	25	72.354.0635.1	1
with intermediate support	BAS GOT GI 6 M25 69 A2	25	72.354.0635.2	1
with strain relief, IP54	BAS GOT GI 6 M25 69 A3	25	72.354.0635.3	1
Multipole connectors for cable-to-cable couplings M20				
with strain relief, IP54	BAS GOT GI 6 M20 69 A3	20	72.352.0635.3	1
with strain relief, IP54 Locking levers and gasket	BAS GOT GL 6 M20 69 A3	20	72.372.0635.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
Size 6 see the product matrix			Page 24–25	

Plastic cable glands may only be used with a shortened thread or together with an intermediate support.


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



690 V Bases, single locking lever Size 6

690 V Bases Size 6



open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 6	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 6 69 A		72.320.0628.0	1
with cover	BAS GUT GP 6 69 A		72.325.0628.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GL 6 M20 69 A0	20	72.330.0635.0	1
with threaded collar	BAS GUT GL 6 M20 69 A1	20	72.330.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GR 6 M20 69 A0	20	72.340.0635.0	1
with threaded collar	BAS GUT GR 6 M20 69 A1	20	72.340.0635.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GM 6 M20 69 A0	20	72.331.0635.0	1
with threaded collar	BAS GUT GM 6 M20 69 A1	20	72.331.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GS 6 M20 69 A0	20	72.341.0635.0	1
with threaded collar	BAS GUT GS 6 M20 69 A1	20	72.341.0635.1	1
1 cable gland, left, 1 x M25				
without cover				
with threaded collar	BAS GUT GM 6 M25 69 A1	25	72.335.0635.1	1
1 cable gland, right, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GN 6 M20 69 A0	20	72.332.0635.0	1
with threaded collar	BAS GUT GN 6 M20 69 A1	20	72.332.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GT 6 M20 69 A0	20	72.342.0635.0	1
with threaded collar	BAS GUT GT 6 M20 69 A1	20	72.342.0635.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GO 6 M20 69 A0	20	72.333.0635.0	1
with threaded collar,	BAS GUT GO 6 M20 69 A1	20	72.333.0635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GUT GU 6 M20 69 A0	20	72.343.0635.0	1
with threaded collar,	BAS GUT GU 6 M20 69 A1	20	72.343.0635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Hoods, single locking lever Size 10

500 V Hoods Size 10



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 10				
Lateral cable entry M20	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GG 10 M20 50 A0	20	71.350.1035.0	1
with threaded collar	BAS GOT GG 10 M20 50 A1	20	71.350.1035.1	1
with intermediate support	BAS GOT GG 10 M20 50 A2	20	71.350.1035.2	1
with strain relief, IP54	BAS GOT GG 10 M20 50 A3	20	71.350.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 10 M25 50 A0	25	71.353.1035.0	1
with threaded collar	BAS GOT GG 10 M25 50 A1	25	71.353.1035.1	1
with intermediate support	BAS GOT GG 10 M25 50 A2	25	71.353.1035.2	1
with strain relief, IP54	BAS GOT GG 10 M25 50 A3	25	71.353.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 10 M20 50 A0	20	71.352.1035.0	1
with threaded collar	BAS GOT GI 10 M20 50 A1	20	71.352.1035.1	1
with intermediate support	BAS GOT GI 10 M20 50 A2	20	71.352.1035.2	1
with strain relief, IP54	BAS GOT GI 10 M20 50 A3	20	71.352.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 10 M25 50 A0	25	71.354.1035.0	1
with threaded collar	BAS GOT GI 10 M25 50 A1	25	71.354.1035.1	1
with intermediate support	BAS GOT GI 10 M25 50 A2	25	71.354.1035.2	1
with strain relief, IP54	BAS GOT GI 10 M25 50 A3	25	71.354.1035.3	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 10 M20 50 A0	20	71.352.1035.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GL 10 M20 50 A0	20	71.372.1035.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 10 M20 50 A1	20	71.352.1035.1	1
with threaded collar	BAS GOT GL 10 M20 50 A1	20	71.372.1035.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GI 10 M20 50 A3	20	71.352.1035.3	1
with strain relief, IP54	BAS GOT GL 10 M20 50 A3	20	71.372.1035.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, single locking lever Size 10H, increased height design

500 V Hoods Size 10H, increased height design

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 10H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\Rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 10H M25 50 A0	25	76.350.1035.0	1
with threaded collar	BAS GOT GG 10H M25 50 A1	25	76.350.1035.1	1
Lateral cable entry M32				
with cable gland, IP54, $\Rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GG 10H M32 50 A0	32	76.353.1035.0	1
with threaded collar	BAS GOT GG 10H M32 50 A1	32	76.353.1035.1	1
with intermediate support	BAS GOT GG 10H M32 50 A2	32	76.353.1035.2	1
Top cable entry M25				
with cable gland, IP54, $\Rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 10H M25 50 A0	25	76.352.1035.0	1
with threaded collar	BAS GOT GI 10H M25 50 A1	25	76.352.1035.1	1
Top cable entry M32				
with cable gland, IP54, $\Rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 10H M32 50 A0	32	76.354.1035.0	1
with threaded collar	BAS GOT GI 10H M32 50 A1	32	76.354.1035.1	1
with intermediate support	BAS GOT GI 10H M32 50 A2	32	76.354.1035.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	



Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.



Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V Bases, single locking lever Size 10

500 V Bases, Size 10



open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 10	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 10 50 A		71.320.1028.0	1
with cover	BAS GUT GP 10 50 A		71.325.1028.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GL 10 M20 50 A0	20	71.330.1035.0	1
with threaded collar	BAS GUT GL 10 M20 50 A1	20	71.330.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GR 10 M20 50 A0	20	71.340.1035.0	1
with threaded collar	BAS GUT GR 10 M20 50 A1	20	71.340.1035.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GM 10 M20 50 A0	20	71.331.1035.0	1
with threaded collar	BAS GUT GM 10 M20 50 A1	20	71.331.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GS 10 M20 50 A0	20	71.341.1035.0	1
with threaded collar	BAS GUT GS 10 M20 50 A1	20	71.341.1035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GM 10 M25 50 A0	25	71.335.1035.0	1
with threaded collar	BAS GUT GM 10 M25 50 A1	25	71.335.1035.1	1
1 cable gland, right, 1 x M20				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GT 10 M20 50 A0	20	71.342.1035.0	1
with threaded collar	BAS GUT GT 10 M20 50 A1	20	71.342.1035.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GO 10 M20 50 A0	20	71.333.1035.0	1
with threaded collar	BAS GUT GO 10 M20 50 A1	20	71.333.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	BAS GUT GU 10 M20 50 A0	20	71.343.1035.0	1
with threaded collar	BAS GUT GU 10 M20 50 A1	20	71.343.1035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	

All Bases on this page are also available in M25 design.
The fifth digit of the part number always increases by 4 for M25 compared to the corresponding M20 designs.

Example:
71.341.1035.0 for M20 becomes 71.345.1035.0 for M25


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Bases, single locking lever Size 10H, increased height design

500 V Bases Size 10H, increased height design



closed M25 without cover with cover



closed M32 with threaded collar



Description	Type	M	Part No.	P.U.
500 V Bases, size 10H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GL 10H M25 50 A0	25	76.330.1035.0	1
with threaded collar	BAS GUT GL 10H M25 50 A1	25	76.330.1035.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GR 10H M25 50 A0	25	76.340.1035.0	1
with threaded collar	BAS GUT GR 10H M25 50 A1	25	76.340.1035.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GL 10H M32 50 A0	32	76.334.1035.0	1
with threaded collar	BAS GUT GL 10H M32 50 A1	32	76.334.1035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GR 10H M32 50 A0	32	76.344.1035.0	1
with threaded collar	BAS GUT GR 10H M32 50 A1	32	76.344.1035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GM 10H M25 50 A0	25	76.331.1035.0	1
with threaded collar	BAS GUT GM 10H M25 50 A1	25	76.331.1035.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GS 10H M25 50 A0	25	76.341.1035.0	1
with threaded collar	BAS GUT GS 10H M25 50 A1	25	76.341.1035.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GM 10H M32 50 A0	32	76.335.1035.0	1
with threaded collar	BAS GUT GM 10H M32 50 A1	32	76.335.1035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GR 10H M32 50 A0	32	76.345.1035.0	1
with threaded collar	BAS GUT GR 10H M32 50 A1	32	76.345.1035.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GT 10H M25 50 A0	25	76.342.1035.0	1
with threaded collar	BAS GUT GT 10H M25 50 A1	25	76.342.1035.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GT 10H M32 50 A0	32	76.346.1035.0	1
with threaded collar	BAS GUT GT 10H M32 50 A1	32	76.346.1035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Bases

closed, 2 cable glands



closed, 1 cable gland



500 V Hoods, double locking lever Size 10

500 V Hoods Size 10



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 10				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GA 10 M20 50 A0	20	70.350.1035.0	1
with threaded collar	BAS GOT GA 10 M20 50 A1	20	70.350.1035.1	1
with intermediate support	BAS GOT GA 10 M20 50 A2	20	70.350.1035.2	1
with strain relief, IP54	BAS GOT GA 10 M20 50 A3	20	70.350.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GA 10 M25 50 A0	25	70.353.1035.0	1
with threaded collar	BAS GOT GA 10 M25 50 A1	25	70.353.1035.1	1
with intermediate support	BAS GOT GA 10 M25 50 A2	25	70.353.1035.2	1
with strain relief, IP54	BAS GOT GA 10 M25 50 A3	25	70.353.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GC 10 M20 50 A0	20	70.352.1035.0	1
with threaded collar	BAS GOT GC 10 M20 50 A1	20	70.352.1035.1	1
with intermediate support	BAS GOT GC 10 M20 50 A2	20	70.352.1035.2	1
with strain relief, IP54	BAS GOT GC 10 M20 50 A3	20	70.352.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 10 M25 50 A0	25	70.354.1035.0	1
with threaded collar	BAS GOT GC 10 M25 50 A1	25	70.354.1035.1	1
with intermediate support	BAS GOT GC 10 M25 50 A2	25	70.354.1035.2	1
with strain relief, IP54	BAS GOT GC 10 M25 50 A3	25	70.354.1035.3	1
Technical data				
Material metal	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	-			
Gasket at Multipole connectors	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V Hoods, double locking lever with Locking levers, Size 10

500 V Hoods Size 10



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 10				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GD 10 M20 50 A0	20	70.355.1035.0	1
with threaded collar	BAS GOT GD 10 M20 50 A1	20	70.355.1035.1	1
with intermediate support	BAS GOT GD 10 M20 50 A2	20	70.355.1035.2	1
with strain relief, IP54	BAS GOT GD 10 M20 50 A3	20	70.355.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GD 10 M25 50 A0	25	70.358.1035.0	1
with threaded collar	BAS GOT GD 10 M25 50 A1	25	70.358.1035.1	1
with intermediate support	BAS GOT GD 10 M25 50 A2	25	70.358.1035.2	1
with strain relief, IP54	BAS GOT GD 10 M25 50 A3	25	70.358.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GF 10 M20 50 A0	20	70.357.1035.0	1
with threaded collar	BAS GOT GF 10 M20 50 A1	20	70.357.1035.1	1
with intermediate support	BAS GOT GF 10 M20 50 A2	20	70.357.1035.2	1
with strain relief, IP54	BAS GOT GF 10 M20 50 A3	20	70.357.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GF 10 M25 50 A0	25	70.359.1035.0	1
with threaded collar	BAS GOT GF 10 M25 50 A1	25	70.359.1035.1	1
with intermediate support	BAS GOT GF 10 M25 50 A2	25	70.359.1035.2	1
with strain relief, IP54	BAS GOT GF 10 M25 50 A3	25	70.359.1035.3	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GC 10 M20 50 A0	20	70.352.1035.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GK 10 M20 50 A0	20	70.372.1035.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GC 10 M20 50 A1	20	70.352.1035.1	1
with threaded collar	BAS GOT GK 10 M20 50 A1	20	70.372.1035.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GC 10 M20 50 A3	20	70.352.1035.3	1
with strain relief, IP54	BAS GOT GK 10 M20 50 A3	20	70.372.1035.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24-25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods with Locking levers



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, double locking lever Size 10H, increased height design

500 V Hoods Size 10H, increased height design

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 10H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GA 10H M25 50 A0	25	73.350.1035.0	1
with threaded collar	BAS GOT GA 10H M25 50 A1	25	73.350.1035.1	1
with intermediate support	BAS GOT GA 10H M25 50 A2	25	73.350.1035.2	1
with strain relief, IP54	BAS GOT GA 10H M25 50 A3	25	73.350.1035.3	1
Lateral cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GA 10H M32 50 A0	32	73.353.1035.0	1
with threaded collar	BAS GOT GA 10H M32 50 A1	32	73.353.1035.1	1
with intermediate support	BAS GOT GA 10H M32 50 A2	32	73.353.1035.2	1
with strain relief, IP54	BAS GOT GA 10H M32 50 A3	32	73.353.1035.3	1
Top cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GC 10H M25 50 A0	25	73.352.1035.0	1
with threaded collar	BAS GOT GC 10H M25 50 A1	25	73.352.1035.1	1
with intermediate support	BAS GOT GC 10H M25 50 A2	25	73.352.1035.2	1
with strain relief, IP54	BAS GOT GC 10H M25 50 A3	25	73.352.1035.3	1
Top cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GC 10H M32 50 A0	32	73.354.1035.0	1
with threaded collar	BAS GOT GC 10H M32 50 A1	32	73.354.1035.1	1
with intermediate support	BAS GOT GC 10H M32 50 A2	32	73.354.1035.2	1
with strain relief, IP54	BAS GOT GC 10H M32 50 A3	32	73.354.1035.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V Bases, double locking lever Size 10

500 V Bases, Size 10



open

without cover
with cover




closed

1 cable gland
without cover
with cover



closed

1 cable gland, bottom
without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 10				
Aluminum housing				
Open-bottom base				
without cover	BAS GUT GA 10 50 A		70.320.1028.0	1
with cover	BAS GUT GE 10 50 A		70.325.1028.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GB 10 M20 50 A0	20	70.330.1035.0	1
with threaded collar	BAS GUT GB 10 M20 50 A1	20	70.330.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GF 10 M20 50 A0	20	70.340.1035.0	1
with threaded collar	BAS GUT GF 10 M20 50 A1	20	70.340.1035.1	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 10 M25 50 A0	25	70.334.1035.0	1
with threaded collar	BAS GUT GB 10 M25 50 A1	25	70.334.1035.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 10 M25 50 A0	25	70.344.1035.0	1
with threaded collar	BAS GUT GF 10 M25 50 A1	25	70.344.1035.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GC 10 M20 50 A0	20	70.331.1035.0	1
with threaded collar	BAS GUT GC 10 M20 50 A1	20	70.331.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GG 10 M20 50 A0	20	70.341.1035.0	1
with threaded collar	BAS GUT GG 10 M20 50 A1	20	70.341.1035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 10 M25 50 A0	25	70.335.1035.0	1
with threaded collar	BAS GUT GC 10 M25 50 A1	25	70.335.1035.1	1
1 cable gland, right, 1 x M20				
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GH 10 M20 50 A0	20	70.342.1035.0	1
with threaded collar	BAS GUT GH 10 M20 50 A1	20	70.342.1035.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GD 10 M20 50 A0	20	70.333.1035.0	1
with threaded collar	BAS GUT GD 10 M20 50 A1	20	70.333.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GI 10 M20 50 A0	20	70.343.1035.0	1
with threaded collar	BAS GUT GI 10 M20 50 A1	20	70.343.1035.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 10 M25 50 A0	25	70.337.1035.0	1
with threaded collar	BAS GUT GD 10 M25 50 A1	25	70.337.1035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	
All Bases on this page are also available in M25 design. The fifth digit of the part number always increases by 4 for M25 compared to the corresponding M20 designs. Example: 70.341.1035.0 for M20 becomes 70.345.0635.0 for M25				


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Bases, double locking lever Size 10H, increased height design

500 V Bases Size 10H, increased height design

**closed M25
2 cable glands**
without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 10H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 10H M25 50 A0	25	73.330.1035.0	1
with threaded collar	BAS GUT GB 10H M25 50 A1	25	73.330.1035.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 10H M25 50 A0	25	73.340.1035.0	1
with threaded collar	BAS GUT GF 10H M25 50 A1	25	73.340.1035.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GB 10H M32 50 A0	32	73.334.1035.0	1
with threaded collar	BAS GUT GB 10H M32 50 A1	32	73.334.1035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GF 10H M32 50 A0	32	73.344.1035.0	1
with threaded collar	BAS GUT GF 10H M32 50 A1	32	73.344.1035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 10H M25 50 A0	25	73.331.1035.0	1
with threaded collar	BAS GUT GC 10H M25 50 A1	25	73.331.1035.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 10H M25 50 A0	25	73.341.1035.0	1
with threaded collar	BAS GUT GG 10H M25 50 A1	25	73.341.1035.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GC 10H M32 50 A0	32	73.335.1035.0	1
with threaded collar	BAS GUT GC 10H M32 50 A1	32	73.335.1035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GG 10H M32 50 A0	32	73.345.1035.0	1
with threaded collar	BAS GUT GG 10H M32 50 A1	32	73.345.1035.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 10H M25 50 A0	25	73.342.1035.0	1
with threaded collar	BAS GUT GH 10H M25 50 A1	25	73.342.1035.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GH 10H M32 50 A0	32	73.346.1035.0	1
with threaded collar	BAS GUT GH 10H M32 50 A1	32	73.346.1035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Bases

closed, 2 cable glands



closed, 1 cable gland



690 V Hoods, single locking lever Size 10

690 V Hoods Size 10



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
690 V Hoods, size 10				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GG 10 M20 69 A0	20	77.350.1035.0	1
with threaded collar	BAS GOT GG 10 M20 69 A1	20	77.350.1035.1	1
with intermediate support	BAS GOT GG 10 M20 69 A2	20	77.350.1035.2	1
with strain relief, IP54	BAS GOT GG 10 M20 69 A3	20	77.350.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 10 M25 69 A0	25	77.353.1035.0	1
with threaded collar	BAS GOT GG 10 M25 69 A1	25	77.353.1035.1	1
with intermediate support	BAS GOT GG 10 M25 69 A2	25	77.353.1035.2	1
with strain relief, IP54	BAS GOT GG 10 M25 69 A3	25	77.353.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 10 M20 69 A0	20	77.352.1035.0	1
with threaded collar	BAS GOT GI 10 M20 69 A1	20	77.352.1035.1	1
with intermediate support	BAS GOT GI 10 M20 69 A2	20	77.352.1035.2	1
with strain relief, IP54	BAS GOT GI 10 M20 69 A3	20	77.352.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 10 M25 69 A0	25	77.354.1035.0	1
with threaded collar	BAS GOT GI 10 M25 69 A1	25	77.354.1035.1	1
with intermediate support	BAS GOT GI 10 M25 69 A2	25	77.354.1035.2	1
with strain relief, IP54	BAS GOT GI 10 M25 69 A3	25	77.354.1035.3	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GI 10 M20 69 A0	20	77.352.1035.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GL 10 M20 69 A0	20	77.372.1035.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 10 M20 69 A1	20	77.352.1035.1	1
with threaded collar	BAS GOT GL 10 M20 69 A1	20	77.372.1035.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GI 10 M20 69 A3	20	77.352.1035.3	1
with strain relief, IP54	BAS GOT GL 10 M20 69 A3	20	77.372.1035.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



690 V Bases, single locking lever Size 10

690 V Bases, Size 10



open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 10	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 10 69 A		77.320.1028.0	1
with cover	BAS GUT GP 10 69 A		77.325.1028.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GL 10 M20 69 A0	20	77.330.1035.0	1
with threaded collar	BAS GUT GL 10 M20 69 A1	20	77.330.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GR 10 M20 69 A0	20	77.340.1035.0	1
with threaded collar	BAS GUT GR 10 M20 69 A1	20	77.340.1035.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GM 10 M20 69 A0	20	77.331.1035.0	1
with threaded collar	BAS GUT GM 10 M20 69 A1	20	77.331.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GS 10 M20 69 A0	20	77.341.1035.0	1
with threaded collar	BAS GUT GS 10 M20 69 A1	20	77.341.1035.1	1
1 cable gland, right, 1 x M20				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GT 10 M20 69 A0	20	77.342.1035.0	1
with threaded collar	BAS GUT GT 10 M20 69 A1	20	77.342.1035.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GO 10 M20 69 A0	20	77.333.1035.0	1
with threaded collar	BAS GUT GO 10 M20 69 A1	20	77.333.1035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	BAS GUT GU 10 M20 69 A0	20	77.343.1035.0	1
with threaded collar	BAS GUT GU 10 M20 69 A1	20	77.343.1035.1	1

Technical data

Material	Die cast aluminum alloy
Surface	silicon-free
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A
Gasket	NBR
Degree of protection	
with latched locking levers	IP54
with appropriate cable glands	IP65
Temperature range	-40 – +120 °C

Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Contact inserts				
See the product matrix			Page 24–25	

All Bases on this page are also available in M25 design.
The fifth digit of the part number always increases by 4 for M25 compared to the corresponding M20 designs.

Example:
77.331.1035.0 for M20 becomes 77.335.1035.0 for M25


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



690 V Hoods, double locking lever Size 10

690 V Hoods Size 10



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
690 V Hoods, size 10				
Lateral cable entry M20	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GA 10 M20 69 A0	20	72.350.1035.0	1
with threaded collar	BAS GOT GA 10 M20 69 A1	20	72.350.1035.1	1
with intermediate support	BAS GOT GA 10 M20 69 A2	20	72.350.1035.2	1
with strain relief, IP54	BAS GOT GA 10 M20 69 A3	20	72.350.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GA 10 M25 69 A0	25	72.353.1035.0	1
with threaded collar	BAS GOT GA 10 M25 69 A1	25	72.353.1035.1	1
with intermediate support	BAS GOT GA 10 M25 69 A2	25	72.353.1035.2	1
with strain relief, IP54	BAS GOT GA 10 M25 69 A3	25	72.353.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GC 10 M20 69 A0	20	72.352.1035.0	1
with threaded collar	BAS GOT GC 10 M20 69 A1	20	72.352.1035.1	1
with intermediate support	BAS GOT GC 10 M20 69 A2	20	72.352.1035.2	1
with strain relief, IP54	BAS GOT GC 10 M20 69 A3	20	72.352.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 10 M25 69 A0	25	72.354.1035.0	1
with threaded collar	BAS GOT GC 10 M25 69 A1	25	72.354.1035.1	1
with intermediate support	BAS GOT GC 10 M25 69 A2	25	72.354.1035.2	1
with strain relief, IP54	BAS GOT GC 10 M25 69 A3	25	72.354.1035.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	-			
Gasket at Multipole connectors	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods

Lateral cable entry



Top cable entry



690 V Hoods, double locking lever with Locking levers, Size 10

690 V Hoods Size 10



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
690 V Hoods, size 10				
Lateral cable entry M20	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GD 10 M20 69 A0	20	72.355.1035.0	1
with threaded collar	BAS GOT GD 10 M20 69 A1	20	72.355.1035.1	1
with intermediate support	BAS GOT GD 10 M20 69 A2	20	72.355.1035.2	1
with strain relief, IP54	BAS GOT GD 10 M20 69 A3	20	72.355.1035.3	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GD 10 M25 69 A0	25	72.358.1035.0	1
with threaded collar	BAS GOT GD 10 M25 69 A1	25	72.358.1035.1	1
with intermediate support	BAS GOT GD 10 M25 69 A2	25	72.358.1035.2	1
with strain relief, IP54	BAS GOT GD 10 M25 69 A3	25	72.358.1035.3	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GF 10 M20 69 A0	20	72.357.1035.0	1
with threaded collar	BAS GOT GF 10 M20 69 A1	20	72.357.1035.1	1
with intermediate support	BAS GOT GF 10 M20 69 A2	20	72.357.1035.2	1
with strain relief, IP54	BAS GOT GF 10 M20 69 A3	20	72.357.1035.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GF 10 M25 69 A0	25	72.359.1035.0	1
with threaded collar	BAS GOT GF 10 M25 69 A1	25	72.359.1035.1	1
with intermediate support	BAS GOT GF 10 M25 69 A2	25	72.359.1035.2	1
with strain relief, IP54	BAS GOT GF 10 M25 69 A3	25	72.359.1035.3	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GC 10 M20 69 A0	20	72.352.1035.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	BAS GOT GK 10 M20 69 A0	20	72.372.1035.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GC 10 M20 69 A1	20	72.352.1035.1	1
with threaded collar	BAS GOT GK 10 M20 69 A1	20	72.372.1035.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GC 10 M20 69 A3	20	72.352.1035.3	1
with strain relief, IP54	BAS GOT GK 10 M20 69 A3	20	72.372.1035.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24-25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods with Locking levers



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



690 V Bases, double locking lever Size 10

690 V Bases, Size 10



open

without cover
with cover



closed

1 cable gland


without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 10	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GA 10 69 A		72.320.1028.0	1
with cover	BAS GUT GE 10 69 A		72.325.1028.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GB 10 M20 69 A0	20	72.330.1035.0	1
with threaded collar	BAS GUT GB 10 M20 69 A1	20	72.330.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GF 10 M20 69 A0	20	72.340.1035.0	1
with threaded collar	BAS GUT GF 10 M20 69 A1	20	72.340.1035.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GC 10 M20 69 A0	20	72.331.1035.0	1
with threaded collar	BAS GUT GC 10 M20 69 A1	20	72.331.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GG 10 M20 69 A0	20	72.341.1035.0	1
with threaded collar	BAS GUT GG 10 M20 69 A1	20	72.341.1035.1	1
1 cable gland, left, 1 x M25				
without cover				
with threaded collar	BAS GUT GC 10 M25 69 A1	25	72.335.1035.1	1
1 cable gland, right, 1 x M20				
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GH 10 M20 69 A0	20	72.342.1035.0	1
with threaded collar	BAS GUT GH 10 M20 69 A1	20	72.342.1035.1	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GD 10 M20 69 A0	20	72.333.1035.0	1
with threaded collar	BAS GUT GD 10 M20 69 A1	20	72.333.1035.1	1
with cover				
with cable gland, IP54,  3 – 14.5 mm	BAS GUT GI 10 M20 69 A0	20	72.343.1035.0	1
with threaded collar	BAS GUT GI 10 M20 69 A1	20	72.343.1035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	

All Bases on this page are also available in M25 design.
The fifth digit of the part number always increases by 4 for M25 compared to the corresponding M20 designs.

Example:

72.331.1035.0 for M20 becomes 72.335.1035.0 for M25


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Hoods, single locking lever Size 16

500 V Hoods Size 16



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 16				
Aluminum housing				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 16 M25 50 A0	25	71.350.1635.0	1
with threaded collar	BAS GOT GG 16 M25 50 A1	25	71.350.1635.1	1
with intermediate support	BAS GOT GG 16 M25 50 A2	25	71.350.1635.2	1
with strain relief, IP54	BAS GOT GG 16 M25 50 A3	25	71.350.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GG 16 M32 50 A0	32	71.353.1635.0	1
with threaded collar	BAS GOT GG 16 M32 50 A1	32	71.353.1635.1	1
with intermediate support	BAS GOT GG 16 M32 50 A2	32	71.353.1635.2	1
with strain relief, IP54	BAS GOT GG 16 M32 50 A3	32	71.353.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 16 M25 50 A0	25	71.352.1635.0	1
with threaded collar	BAS GOT GI 16 M25 50 A1	25	71.352.1635.1	1
with intermediate support	BAS GOT GI 16 M25 50 A2	25	71.352.1635.2	1
with strain relief, IP54	BAS GOT GI 16 M25 50 A3	25	71.352.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 16 M32 50 A0	32	71.354.1635.0	1
with threaded collar	BAS GOT GI 16 M32 50 A1	32	71.354.1635.1	1
with intermediate support	BAS GOT GI 16 M32 50 A2	32	71.354.1635.2	1
with strain relief, IP54	BAS GOT GI 16 M32 50 A3	32	71.354.1635.3	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 16 M25 50 A0	25	71.352.1635.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GL 16 M25 50 A0	25	71.372.1635.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 16 M25 50 A1	25	71.352.1635.1	1
with threaded collar	BAS GOT GL 16 M25 50 A1	25	71.372.1635.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GI 16 M25 50 A3	25	71.352.1635.3	1
with strain relief, IP54	BAS GOT GL 16 M25 50 A3	25	71.372.1635.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, single locking lever Size 16H, increased height design

500 V Hoods Size 16H, increased height design

Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 16H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GG 40H M25 50 A0	25	76.350.4035.0	1
with threaded collar	BAS GOT GG 40H M25 50 A1	25	76.350.4035.1	1
with intermediate support	BAS GOT GG 40H M25 50 A2	25	76.350.4035.2	1
with strain relief, IP54	BAS GOT GG 40H M25 50 A3	25	76.350.4035.3	1
Lateral cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GG 40H M32 50 A0	32	76.353.4035.0	1
with threaded collar	BAS GOT GG 40H M32 50 A1	32	76.353.4035.1	1
with intermediate support	BAS GOT GG 40H M32 50 A2	32	76.353.4035.2	1
with strain relief, IP54	BAS GOT GG 40H M32 50 A3	32	76.353.4035.3	1
Lateral cable entry M40				
with cable gland, IP54,  19 – 27 mm	BAS GOT GG 40H M40 50 A0	40	76.360.4035.0	1
with threaded collar	BAS GOT GG 40H M40 50 A1	40	76.360.4035.1	1
Top cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GI 40H M25 50 A0	25	76.352.4035.0	1
with threaded collar	BAS GOT GI 40H M25 50 A1	25	76.352.4035.1	1
with intermediate support	BAS GOT GI 40H M25 50 A2	25	76.352.4035.2	1
with strain relief, IP54	BAS GOT GI 40H M25 50 A3	25	76.352.4035.3	1
Top cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GI 40H M32 50 A0	32	76.354.4035.0	1
with threaded collar	BAS GOT GI 40H M32 50 A1	32	76.354.4035.1	1
with intermediate support	BAS GOT GI 40H M32 50 A2	32	76.354.4035.2	1
with strain relief, IP54	BAS GOT GI 40H M32 50 A3	32	76.354.4035.3	1
Top cable entry M40				
with threaded collar	BAS GOT GI 40H M40 50 A1	40	76.362.4035.1	1
Multipole connectors for cable-to-cable couplings M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GI 40H M32 50 A0	32	76.354.4035.0	1
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GL 40H M32 50 A0	32	76.374.4035.0	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24-25	


Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Bases, single locking lever Size 16

500 V Bases, Size 16



open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 16	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 16 50 A		71.320.1628.0	1
with cover	BAS GUT GP 16 50 A		71.325.1628.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GL 16 M25 50 A0	25	71.330.1635.0	1
with threaded collar	BAS GUT GL 16 M25 50 A1	25	71.330.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GR 16 M25 50 A0	25	71.340.1635.0	1
with threaded collar	BAS GUT GR 16 M25 50 A1	25	71.340.1635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GM 16 M25 50 A0	25	71.331.1635.0	1
with threaded collar	BAS GUT GM 16 M25 50 A1	25	71.331.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GS 16 M25 50 A0	25	71.341.1635.0	1
with threaded collar	BAS GUT GS 16 M25 50 A1	25	71.341.1635.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GT 16 M25 50 A0	25	71.342.1635.0	1
with threaded collar	BAS GUT GT 16 M25 50 A1	25	71.342.1635.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GO 16 M25 50 A0	25	71.333.1635.0	1
with threaded collar	BAS GUT GO 16 M25 50 A1	25	71.333.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GU 16 M25 50 A0	25	71.343.1635.0	1
with threaded collar	BAS GUT GU 16 M25 50 A1	25	71.343.1635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Bases, single locking lever Size 16H, increased height design

500 V Bases Size 16H, increased height design

closed M25 2 cable glands without cover with cover



closed M32 2 cable glands without cover with cover



closed M25 1 cable gland, bottom without cover with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 16H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GL 40H M25 50 A0	25	76.330.4035.0	1
with threaded collar	BAS GUT GL 40H M25 50 A1	25	76.330.4035.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GR 40H M25 50 A0	25	76.340.4035.0	1
with threaded collar	BAS GUT GR 40H M25 50 A1	25	76.340.4035.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GL 40H M32 50 A0	32	76.334.4035.0	1
with threaded collar	BAS GUT GL 40H M32 50 A1	32	76.334.4035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GR 40H M32 50 A0	32	76.344.4035.0	1
with threaded collar	BAS GUT GR 40H M32 50 A1	32	76.344.4035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GM 40H M25 50 A0	25	76.331.4035.0	1
with threaded collar	BAS GUT GM 40H M25 50 A1	25	76.331.4035.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GS 40H M25 50 A0	25	76.341.4035.0	1
with threaded collar	BAS GUT GS 40H M25 50 A1	25	76.341.4035.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GM 40H M32 50 A0	32	76.335.4035.0	1
with threaded collar	BAS GUT GM 40H M32 50 A1	32	76.335.4035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GS 40H M32 50 A0	32	76.345.4035.0	1
with threaded collar	BAS GUT GS 40H M32 50 A1	32	76.345.4035.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GT 40H M25 50 A0	25	76.342.4035.0	1
with threaded collar	BAS GUT GT 40H M25 50 A1	25	76.342.4035.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GT 40H M32 50 A0	32	76.346.4035.0	1
with threaded collar	BAS GUT GT 40H M32 50 A1	32	76.346.4035.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GO 40H M25 50 A0	25	76.333.4035.0	1
with threaded collar	BAS GUT GO 40H M25 50 A1	25	76.333.4035.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GU 40H M25 50 A0	25	76.343.4035.0	1
with threaded collar	BAS GUT GU 40H M25 50 A1	25	76.343.4035.1	1
1 cable gland, bottom, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GO 40H M32 50 A0	32	76.337.4035.0	1
with threaded collar	BAS GUT GO 40H M32 50 A1	32	76.337.4035.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GU 40H M32 50 A0	32	76.347.4035.0	1
with threaded collar	BAS GUT GU 40H M32 50 A1	32	76.347.4035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


All Bases on this page are also available in M40 design.
Part numbers available on request.

Note: In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Bases


closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Hoods, double locking lever Size 16

500 V Hoods Size 16



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 16				
Lateral cable entry M25	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GA 16 M25 50 A0	25	70.350.1635.0	1
with threaded collar	BAS GOT GA 16 M25 50 A1	25	70.350.1635.1	1
with intermediate support	BAS GOT GA 16 M25 50 A2	25	70.350.1635.2	1
with strain relief, IP54	BAS GOT GA 16 M25 50 A3	25	70.350.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GA 16 M32 50 A0	32	70.353.1635.0	1
with threaded collar	BAS GOT GA 16 M32 50 A1	32	70.353.1635.1	1
with intermediate support	BAS GOT GA 16 M32 50 A2	32	70.353.1635.2	1
with strain relief, IP54	BAS GOT GA 16 M32 50 A3	32	70.353.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 16 M25 50 A0	25	70.352.1635.0	1
with threaded collar	BAS GOT GC 16 M25 50 A1	25	70.352.1635.1	1
with intermediate support	BAS GOT GC 16 M25 50 A2	25	70.352.1635.2	1
with strain relief, IP54	BAS GOT GC 16 M25 50 A3	25	70.352.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GC 16 M32 50 A0	32	70.354.1635.0	1
with threaded collar	BAS GOT GC 16 M32 50 A1	32	70.354.1635.1	1
with intermediate support	BAS GOT GC 16 M32 50 A2	32	70.354.1635.2	1
with strain relief, IP54	BAS GOT GC 16 M32 50 A3	32	70.354.1635.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	



Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.



Dimensions

Hoods

500 V Size 16 Lateral cable entry



500 V Size 16 Top cable entry



500 V Hoods, double locking lever with Locking levers, Size 16

500 V Hoods Size 16



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 16				
Lateral cable entry M25	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GD 16 M25 50 A0	25	70.355.1635.0	1
with threaded collar	BAS GOT GD 16 M25 50 A1	25	70.355.1635.1	1
with intermediate support	BAS GOT GD 16 M25 50 A2	25	70.355.1635.2	1
with strain relief, IP54	BAS GOT GD 16 M25 50 A3	25	70.355.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GD 16 M32 50 A0	32	70.358.1635.0	1
with threaded collar	BAS GOT GD 16 M32 50 A1	32	70.358.1635.1	1
with intermediate support	BAS GOT GD 16 M32 50 A2	32	70.358.1635.2	1
with strain relief, IP54	BAS GOT GD 16 M32 50 A3	32	70.358.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GF 16 M25 50 A0	25	70.357.1635.0	1
with threaded collar	BAS GOT GF 16 M25 50 A1	25	70.357.1635.1	1
with intermediate support	BAS GOT GF 16 M25 50 A2	25	70.357.1635.2	1
with strain relief, IP54	BAS GOT GF 16 M25 50 A3	25	70.357.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GF 16 M32 50 A0	32	70.359.1635.0	1
with threaded collar	BAS GOT GF 16 M32 50 A1	32	70.359.1635.1	1
with intermediate support	BAS GOT GF 16 M32 50 A2	32	70.359.1635.2	1
with strain relief, IP54	BAS GOT GF 16 M32 50 A3	32	70.359.1635.3	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 16 M25 50 A0	25	70.352.1635.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GK 16 M25 50 A0	25	70.372.1635.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GC 16 M25 50 A1	25	70.352.1635.1	1
with threaded collar	BAS GOT GK 16 M25 50 A1	25	70.372.1635.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GC 16 M25 50 A3	25	70.352.1635.3	1
with strain relief, IP54	BAS GOT GK 16 M25 50 A3	25	70.372.1635.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods with Locking levers


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, double locking lever Size 16H, increased height design

500 V Hoods Size 16H, increased height design

Lateral cable entry



Top cable entry





Description	Type	M	Part No.	P.U.
500 V Hoods, size 16H				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GA 40H M25 50 A0	25	73.350.4035.0	1
with threaded collar	BAS GOT GA 40H M25 50 A1	25	73.350.4035.1	1
with intermediate support	BAS GOT GA 40H M25 50 A2	25	73.350.4035.2	1
with strain relief, IP54	BAS GOT GA 40H M25 50 A3	25	73.350.4035.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GA 40H M32 50 A0	32	73.353.4035.0	1
with threaded collar	BAS GOT GA 40H M32 50 A1	32	73.353.4035.1	1
with intermediate support	BAS GOT GA 40H M32 50 A2	32	73.353.4035.2	1
with strain relief, IP54	BAS GOT GA 40H M32 50 A3	32	73.353.4035.3	1
Lateral cable entry M40				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 23 – 32 mm	BAS GOT GA 40H M40 50 A0	40	73.360.4035.0	1
with threaded collar	BAS GOT GA 40H M40 50 A1	40	73.360.4035.1	1
with intermediate support	BAS GOT GA 40H M40 50 A2	40	73.360.4035.2	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GC 40H M25 50 A0	25	73.352.4035.0	1
with threaded collar	BAS GOT GC 40H M25 50 A1	25	73.352.4035.1	1
with intermediate support	BAS GOT GC 40H M25 50 A2	25	73.352.4035.2	1
with strain relief, IP54	BAS GOT GC 40H M25 50 A3	25	73.352.4035.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GC 40H M32 50 A0	32	73.354.4035.0	1
with threaded collar	BAS GOT GC 40H M32 50 A1	32	73.354.4035.1	1
with intermediate support	BAS GOT GC 40H M32 50 A2	32	73.354.4035.2	1
with strain relief, IP54	BAS GOT GC 40H M32 50 A3	32	73.354.4035.3	1
Top cable entry M40				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 23 – 32 mm	BAS GOT GC 40H M40 50 A0	40	73.362.4035.0	1
with threaded collar	BAS GOT GC 40H M40 50 A1	40	73.362.4035.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	



Dimensions

Hoods

Lateral cable entry



Top cable entry



Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

500 V Hoods, double locking lever with Locking levers, Size 16H, increased height design

500 V Hoods Size 16H, increased height design

Lateral cable entry



Top cable entry





Description	Type	M	Part No.	P.U.
500 V Hoods, size 16H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	BAS GOT GD 40H M25 50 A0	25	73.355.4035.0	1
with threaded collar	BAS GOT GD 40H M25 50 A1	25	73.355.4035.1	1
with intermediate support	BAS GOT GD 40H M25 50 A2	25	73.355.4035.2	1
with strain relief, IP54	BAS GOT GD 40H M25 50 A3	25	73.355.4035.3	1
Lateral cable entry M32				
with cable gland, IP54, $\varnothing$ 15 – 26.5 mm	BAS GOT GD 40H M32 50 A0	32	73.358.4035.0	1
with threaded collar	BAS GOT GD 40H M32 50 A1	32	73.358.4035.1	1
with intermediate support	BAS GOT GD 40H M32 50 A2	32	73.358.4035.2	1
with strain relief, IP54	BAS GOT GD 40H M32 50 A3	32	73.358.4035.3	1
Top cable entry M25				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	BAS GOT GF 40H M25 50 A0	25	73.357.4035.0	1
with threaded collar	BAS GOT GF 40H M25 50 A1	25	73.357.4035.1	1
with intermediate support	BAS GOT GF 40H M25 50 A2	25	73.357.4035.2	1
with strain relief, IP54	BAS GOT GF 40H M25 50 A3	25	73.357.4035.3	1
Top cable entry M32				
with cable gland, IP54, $\varnothing$ 15 – 26.5 mm	BAS GOT GF 40H M32 50 A0	32	73.359.4035.0	1
with threaded collar	BAS GOT GF 40H M32 50 A1	32	73.359.4035.1	1
with intermediate support	BAS GOT GF 40H M32 50 A2	32	73.359.4035.2	1
with strain relief, IP54	BAS GOT GF 40H M32 50 A3	32	73.359.4035.3	1
Technical data				
Material metal/plastic	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	



Dimensions

Hoods

Lateral cable entry



Top cable entry



Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

500 V Bases, double locking lever Size 16

500 V Bases, Size 16



open

without cover
with cover



closed

1 cable gland, seitlich

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 16	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GA 16 50 A		70.320.1628.0	1
with cover	BAS GUT GE 16 50 A		70.325.1628.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 16 M25 50 A0	25	70.330.1635.0	1
with threaded collar	BAS GUT GB 16 M25 50 A1	25	70.330.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 16 M25 50 A0	25	70.340.1635.0	1
with threaded collar	BAS GUT GF 16 M25 50 A1	25	70.340.1635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 16 M25 50 A0	25	70.331.1635.0	1
with threaded collar	BAS GUT GC 16 M25 50 A1	25	70.331.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 16 M25 50 A0	25	70.341.1635.0	1
with threaded collar	BAS GUT GG 16 M25 50 A1	25	70.341.1635.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 16 M25 50 A0	25	70.342.1635.0	1
with threaded collar	BAS GUT GH 16 M25 50 A1	25	70.342.1635.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 16 M25 50 A0	25	70.333.1635.0	1
with threaded collar	BAS GUT GD 16 M25 50 A1	25	70.333.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GI 16 M25 50 A0	25	70.343.1635.0	1
with threaded collar	BAS GUT GI 16 M25 50 A1	25	70.343.1635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Bases, double locking lever Size 16H, increased height design

500 V Bases Size 16H, increased height design

closed M25 2 cable glands without cover with cover



closed M32 2 cable glands without cover with cover



closed M25 1 cable gland, bottom without cover with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 16H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GB 40H M25 50 A0	25	73.330.4035.0	1
with threaded collar	BAS GUT GB 40H M25 50 A1	25	73.330.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GF 40H M25 50 A0	25	73.340.4035.0	1
with threaded collar	BAS GUT GF 40H M25 50 A1	25	73.340.4035.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GB 40H M32 50 A0	32	73.334.4035.0	1
with threaded collar	BAS GUT GB 40H M32 50 A1	32	73.334.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GF 40H M32 50 A0	32	73.344.4035.0	1
with threaded collar	BAS GUT GF 40H M32 50 A1	32	73.344.4035.1	1
2 cable glands, 2 x M40				
without cover				
with threaded collar	BAS GUT GB 16H M40 50 A1	40	73.338.4035.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GC 40H M25 50 A0	25	73.331.4035.0	1
with threaded collar	BAS GUT GC 40H M25 50 A1	25	73.331.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GG 40H M25 50 A0	25	73.341.4035.0	1
with threaded collar	BAS GUT GG 40H M25 50 A1	25	73.341.4035.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GC 40H M32 50 A0	32	73.335.4035.0	1
with threaded collar	BAS GUT GC 40H M32 50 A1	32	73.335.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GG 40H M32 50 A0	32	73.345.4035.0	1
with threaded collar	BAS GUT GG 40H M32 50 A1	32	73.345.4035.1	1
1 cable gland, left, 1 x M40				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 19 – 27 mm	BAS GUT GC 16H M40 50 A0	40	73.339.4035.0	1
with threaded collar	BAS GUT GC 16H M40 50 A1	40	73.340.4035.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GH 40H M25 50 A0	25	73.342.4035.0	1
with threaded collar	BAS GUT GH 40H M25 50 A1	25	73.342.4035.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GH 40H M32 50 A0	32	73.346.4035.0	1
with threaded collar	BAS GUT GH 40H M32 50 A1	32	73.346.4035.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GD 40H M25 50 A0	25	73.333.4035.0	1
with threaded collar	BAS GUT GD 40H M25 50 A1	25	73.333.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GUT GI 40H M25 50 A0	25	73.343.4035.0	1
with threaded collar	BAS GUT GI 40H M25 50 A1	25	73.343.4035.1	1
1 cable gland, bottom, 1 x M32				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GD 40H M32 50 A0	32	73.337.4035.0	1
with threaded collar	BAS GUT GD 40H M32 50 A1	32	73.337.4035.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GUT GI 40H M32 50 A0	32	73.347.4035.0	1
with threaded collar	BAS GUT GI 40H M32 50 A1	32	73.347.4035.1	1

Technical data

Material	Die cast aluminum alloy
Surface	silicon-free
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A
Gasket	NBR
Degree of protection	
with latched locking levers	IP54
with appropriate cable glands	IP65
Temperature range	-40 – +120 °C

All Bases on this page are also available in M40 design.
Part numbers available on request.


Note: In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

Accessories, Dimensions


Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	10
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	10
Contact inserts				
See the product matrix			Page 24–25	

Bases


closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



690 V Hoods, single locking lever Size 16

690 V Hoods Size 16



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
690 V Hoods, size 16				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 16 M25 69 A0	25	77.350.1635.0	1
with threaded collar	BAS GOT GG 16 M25 69 A1	25	77.350.1635.1	1
with intermediate support	BAS GOT GG 16 M25 69 A2	25	77.350.1635.2	1
with strain relief, IP54	BAS GOT GG 16 M25 69 A3	25	77.350.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GG 16 M32 69 A0	32	77.353.1635.0	1
with threaded collar	BAS GOT GG 16 M32 69 A1	32	77.353.1635.1	1
with intermediate support	BAS GOT GG 16 M32 69 A2	32	77.353.1635.2	1
with strain relief, IP54	BAS GOT GG 16 M32 69 A3	32	77.353.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 16 M25 69 A0	25	77.352.1635.0	1
with threaded collar	BAS GOT GI 16 M25 69 A1	25	77.352.1635.1	1
with intermediate support	BAS GOT GI 16 M25 69 A2	25	77.352.1635.2	1
with strain relief, IP54	BAS GOT GI 16 M25 69 A3	25	77.352.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 16 M32 69 A0	32	77.354.1635.0	1
with threaded collar	BAS GOT GI 16 M32 69 A1	32	77.354.1635.1	1
with intermediate support	BAS GOT GI 16 M32 69 A2	32	77.354.1635.2	1
with strain relief, IP54	BAS GOT GI 16 M32 69 A3	32	77.354.1635.3	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 16 M25 69 A0	25	77.352.1635.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GL 16 M25 69 A0	25	77.372.1635.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 16 M25 69 A1	25	77.352.1635.1	1
with threaded collar	BAS GOT GL 16 M25 69 A1	25	77.372.1635.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GI 16 M25 69 A3	25	77.352.1635.3	1
with strain relief, IP54	BAS GOT GL 16 M25 69 A3	25	77.372.1635.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



690 V Bases, single locking lever Size 16

690 V Bases, Size 16



open

without cover
with cover



closed

1 cable gland, seitlich

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 16	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 16 69 A		77.320.1628.0	1
with cover	BAS GUT GP 16 69 A		77.325.1628.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GL 16 M25 69 A0	25	77.330.1635.0	1
with threaded collar	BAS GUT GL 16 M25 69 A1	25	77.330.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GR 16 M25 69 A0	25	77.340.1635.0	1
with threaded collar	BAS GUT GR 16 M25 69 A1	25	77.340.1635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GM 16 M25 69 A0	25	77.331.1635.0	1
with threaded collar	BAS GUT GM 16 M25 69 A1	25	77.331.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GS 16 M25 69 A0	25	77.341.1635.0	1
with threaded collar	BAS GUT GS 16 M25 69 A1	25	77.341.1635.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GT 16 M25 69 A0	25	77.342.1635.0	1
with threaded collar	BAS GUT GT 16 M25 69 A1	25	77.342.1635.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GO 16 M25 69 A0	25	77.333.1635.0	1
with threaded collar	BAS GUT GO 16 M25 69 A1	25	77.333.1635.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5–19 mm	BAS GUT GU 16 M25 69 A0	25	77.343.1635.0	1
with threaded collar	BAS GUT GU 16 M25 69 A1	25	77.343.1635.1	1

Technical data

Material	Die cast aluminum alloy
Surface	silicon-free
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A
Gasket	NBR
Degree of protection	
with latched locking levers	IP54
with appropriate cable glands	IP65
Temperature range	-40 – +120 °C

Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



690 V Hoods, double locking lever Size 16

690 V Hoods Size 16



Lateral cable entry




Top cable entry




Description	Type	M	Part No.	P.U.
690 V Hoods, size 16				
Aluminum housing				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GA 16 M25 69 A0	25	72.350.1635.0	1
with threaded collar	BAS GOT GA 16 M25 69 A1	25	72.350.1635.1	1
with intermediate support	BAS GOT GA 16 M25 69 A2	25	72.350.1635.2	1
with strain relief, IP54	BAS GOT GA 16 M25 69 A3	25	72.350.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GA 16 M32 69 A0	32	72.353.1635.0	1
with threaded collar	BAS GOT GA 16 M32 69 A1	32	72.353.1635.1	1
with intermediate support	BAS GOT GA 16 M32 69 A2	32	72.353.1635.2	1
with strain relief, IP54	BAS GOT GA 16 M32 69 A3	32	72.353.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 16 M25 69 A0	25	72.352.1635.0	1
with threaded collar	BAS GOT GC 16 M25 69 A1	25	72.352.1635.1	1
with intermediate support	BAS GOT GC 16 M25 69 A2	25	72.352.1635.2	1
with strain relief, IP54	BAS GOT GC 16 M25 69 A3	25	72.352.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GC 16 M32 69 A0	32	72.354.1635.0	1
with threaded collar	BAS GOT GC 16 M32 69 A1	32	72.354.1635.1	1
with intermediate support	BAS GOT GC 16 M32 69 A2	32	72.354.1635.2	1
with strain relief, IP54	BAS GOT GC 16 M32 69 A3	32	72.354.1635.3	1
Technical data				
Material metal/plastic	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	-			
Gasket at Multipole connectors	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	

Dimensions

Lateral cable entry



Top cable entry



Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.

690 V Hoods, double locking lever Size 16XL

690 V Hoods Size 16XL



Lateral cable entry with intermediate support



Description	Type	M	Part No.	P.U.
690 V Hoods, size 16XL	Aluminum housing			
Lateral cable entry M40				
with intermediate support	POW GOT GA 16 M40 69 A2	40	72.250.1635.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	-			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	

Dimensions

Lateral cable entry



690 V Hoods, double locking lever with Locking levers, Size 16

690 V Hoods Size 16



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
690 V Hoods, size 16				
Lateral cable entry M25	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GD 16 M25 69 A0	25	72.355.1635.0	1
with threaded collar	BAS GOT GD 16 M25 69 A1	25	72.355.1635.1	1
with intermediate support	BAS GOT GD 16 M25 69 A2	25	72.355.1635.2	1
with strain relief, IP54	BAS GOT GD 16 M25 69 A3	25	72.355.1635.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GD 16 M32 69 A0	32	72.358.1635.0	1
with threaded collar	BAS GOT GD 16 M32 69 A1	32	72.358.1635.1	1
with intermediate support	BAS GOT GD 16 M32 69 A2	32	72.358.1635.2	1
with strain relief, IP54	BAS GOT GD 16 M32 69 A3	32	72.358.1635.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GF 16 M25 69 A0	25	72.357.1635.0	1
with threaded collar	BAS GOT GF 16 M25 69 A1	25	72.357.1635.1	1
with intermediate support	BAS GOT GF 16 M25 69 A2	25	72.357.1635.2	1
with strain relief, IP54	BAS GOT GF 16 M25 69 A3	25	72.357.1635.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GF 16 M32 69 A0	32	72.359.1635.0	1
with threaded collar	BAS GOT GF 16 M32 69 A1	32	72.359.1635.1	1
with intermediate support	BAS GOT GF 16 M32 69 A2	32	72.359.1635.2	1
with strain relief, IP54	BAS GOT GF 16 M32 69 A3	32	72.359.1635.3	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 16 M25 69 A0	25	72.352.1635.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GK 16 M25 69 A0	25	72.372.1635.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GC 16 M25 69 A1	25	72.352.1635.1	1
with threaded collar	BAS GOT GK 16 M25 69 A1	25	72.372.1635.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GC 16 M25 69 A3	25	72.352.1635.3	1
with strain relief, IP54	BAS GOT GK 16 M25 69 A3	25	72.372.1635.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods with Locking levers


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



690 V Bases, double locking lever Size 16

690 V Bases, Size 16



open

without cover
with cover



closed

1 cable gland, lateral
cable entry

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 16	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GA 16 69 A		72.320.1628.0	1
with cover	BAS GUT GE 16 69 A		72.325.1628.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 16 M25 69 A0	25	72.330.1635.0	1
with threaded collar	BAS GUT GB 16 M25 69 A1	25	72.330.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 16 M25 69 A0	25	72.340.1635.0	1
with threaded collar	BAS GUT GF 16 M25 69 A1	25	72.340.1635.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 16 M25 69 A0	25	72.331.1635.0	1
with threaded collar	BAS GUT GC 16 M25 69 A1	25	72.331.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 16 M25 69 A0	25	72.341.1635.0	1
with threaded collar	BAS GUT GG 16 M25 69 A1	25	72.341.1635.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 16 M25 69 A0	25	72.342.1635.0	1
with threaded collar	BAS GUT GH 16 M25 69 A1	25	72.342.1635.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 16 M25 69 A0	25	72.333.1635.0	1
with threaded collar	BAS GUT GD 16 M25 69 A1	25	72.333.1635.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GI 16 M25 69 A0	25	72.343.1635.0	1
with threaded collar	BAS GUT GI 16 M25 69 A1	25	72.343.1635.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In the course of 2013, the design and order number of the housing will change. But the function of the housing will, of course, remain intact. Additionally, a new, flexible marking system will be available to you. In the transition phase, you can continue to order with the existing number. You can find more exact information and cross-reference lists in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



500 V Hoods, single locking lever Size 24

500 V Hoods Size 24



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 24				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 24 M25 50 A0	25	71.350.2435.0	1
with threaded collar	BAS GOT GG 24 M25 50 A1	25	71.350.2435.1	1
with intermediate support	BAS GOT GG 24 M25 50 A2	25	71.350.2435.2	1
with strain relief, IP54	BAS GOT GG 24 M25 50 A3	25	71.350.2435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GG 24 M32 50 A0	32	71.353.2435.0	1
with threaded collar	BAS GOT GG 24 M32 50 A1	32	71.353.2435.1	1
with intermediate support	BAS GOT GG 24 M32 50 A2	32	71.353.2435.2	1
with strain relief, IP54	BAS GOT GG 24 M32 50 A3	32	71.353.2435.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 24 M25 50 A0	25	71.352.2435.0	1
with threaded collar	BAS GOT GI 24 M25 50 A1	25	71.352.2435.1	1
with intermediate support	BAS GOT GI 24 M25 50 A2	25	71.352.2435.2	1
with strain relief, IP54	BAS GOT GI 24 M25 50 A3	25	71.352.2435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 24 M32 50 A0	32	71.354.2435.0	1
with threaded collar	BAS GOT GI 24 M32 50 A1	32	71.354.2435.1	1
with intermediate support	BAS GOT GI 24 M32 50 A2	32	71.354.2435.2	1
with strain relief, IP54	BAS GOT GI 24 M32 50 A3	32	71.354.2435.3	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 24 M25 50 A0	25	71.352.2435.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GL 24 M25 50 A0	25	71.372.2435.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GI 24 M25 50 A1	25	71.352.2435.1	1
with threaded collar	BAS GOT GL 24 M25 50 A1	25	71.372.2435.1	1
Locking levers and gasket				
Multipole connectors for cable-to-cable couplings M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 24 M32 50 A0	32	71.354.2435.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GL 24 M32 50 A0	32	71.374.2435.0	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket at Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, single locking lever Size 24H, increased height design

500 V Hoods Size 24H, increased height design

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 24H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GG 64H M25 50 A0	25	76.350.6435.0	1
with threaded collar	BAS GOT GG 64H M25 50 A1	25	76.350.6435.1	1
with intermediate support	BAS GOT GG 64H M25 50 A2	25	76.350.6435.2	1
with strain relief, IP54	BAS GOT GG 64H M25 50 A3	25	76.350.6435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GG 64H M32 50 A0	32	76.353.6435.0	1
with threaded collar	BAS GOT GG 64H M32 50 A1	32	76.353.6435.1	1
with intermediate support	BAS GOT GG 64H M32 50 A2	32	76.353.6435.2	1
with strain relief, IP54	BAS GOT GG 64H M32 50 A3	32	76.353.6435.3	1
Lateral cable entry M40				
with threaded collar	BAS GOT GG 64H M40 50 A1	40	76.360.6435.1	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GI 64H M25 50 A0	25	76.352.6435.0	1
with threaded collar	BAS GOT GI 64H M25 50 A1	25	76.352.6435.1	1
with intermediate support	BAS GOT GI 64H M25 50 A2	25	76.352.6435.2	1
with strain relief, IP54	BAS GOT GI 64H M25 50 A3	25	76.352.6435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GI 64H M32 50 A0	32	76.354.6435.0	1
with threaded collar	BAS GOT GI 64H M32 50 A1	32	76.354.6435.1	1
with intermediate support	BAS GOT GI 64H M32 50 A2	32	76.354.6435.2	1
with strain relief, IP54	BAS GOT GI 64H M32 50 A3	32	76.354.6435.3	1
Top cable entry M40				
with threaded collar	BAS GOT GI 64H M40 50 A1	40	76.362.6435.1	1
Technical data				
Material metal/plastic	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	



Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.



Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V Bases, single locking lever Size 24

500 V Bases, Size 24



open

without cover
with cover



closed

1 cable gland, lateral
cable entry

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 24	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 24 50 A		71.320.2428.0	1
with cover	BAS GUT GP 24 50 A		71.325.2428.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GL 24 M25 50 A0	25	71.330.2435.0	1
with threaded collar	BAS GUT GL 24 M25 50 A1	25	71.330.2435.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GR 24 M25 50 A0	25	71.340.2435.0	1
with threaded collar	BAS GUT GR 24 M25 50 A1	25	71.340.2435.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GM 24 M25 50 A0	25	71.331.2435.0	1
with threaded collar	BAS GUT GM 24 M25 50 A1	25	71.331.2435.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GS 24 M25 50 A0	25	71.341.2435.0	1
with threaded collar	BAS GUT GS 24 M25 50 A1	25	71.341.2435.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GT 24 M25 50 A0	25	71.342.2435.0	1
with threaded collar	BAS GUT GT 24 M25 50 A1	25	71.342.2435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GO 24 M25 50 A0	25	71.333.2435.0	1
with threaded collar	BAS GUT GO 24 M25 50 A1	25	71.333.2435.1	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5– 19 mm	BAS GUT GU 24 M25 50 A0	25	71.343.2435.0	1
with threaded collar	BAS GUT GU 24 M25 50 A1	25	71.343.2435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the housing will be equipped with an insulation strip.
With this modification, voltage ranges of up to 690 V can be covered.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



500 V Bases, single locking lever Size 24H, increased height design

500 V Bases Size 24H, increased height design

closed M25 2 cable glands without cover with cover



closed M32 2 cable glands without cover with cover



closed M25 1 cable gland, bottom without cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 24H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GL 64H M25 50 A0	25	76.330.6435.0	1
with threaded collar	BAS GUT GL 64H M25 50 A1	25	76.330.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GR 64H M25 50 A0	25	76.340.6435.0	1
with threaded collar	BAS GUT GR 64H M25 50 A1	25	76.340.6435.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GL 64H M32 50 A0	32	76.334.6435.0	1
with threaded collar	BAS GUT GL 64H M32 50 A1	32	76.334.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GR 64H M32 50 A0	32	76.344.6435.0	1
with threaded collar	BAS GUT GR 64H M32 50 A1	32	76.344.6435.1	1
2 cable glands, 2 x M40				
without cover				
with threaded collar	BAS GUT GL 64H M40 50 A1	40	76.338.6435.0	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GM 64H M25 50 A0	25	76.331.6435.0	1
with threaded collar	BAS GUT GM 64H M25 50 A1	25	76.331.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GS 64H M25 50 A0	25	76.341.6435.0	1
with threaded collar	BAS GUT GS 64H M25 50 A1	25	76.341.6435.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GM 64H M32 50 A0	32	76.335.6435.0	1
with threaded collar	BAS GUT GM 64H M32 50 A1	32	76.335.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GS 64H M32 50 A0	32	76.345.6435.0	1
with threaded collar	BAS GUT GS 64H M32 50 A1	32	76.345.6435.1	1
1 cable gland, left, 1 x M40				
without cover				
with threaded collar	BAS GUT GM 64H M40 50 A0	40	76.339.6435.0	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GT 64H M25 50 A0	25	76.342.6435.0	1
with threaded collar	BAS GUT GT 64H M25 50 A1	25	76.342.6435.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GT 64H M32 50 A0	32	76.346.6435.0	1
with threaded collar	BAS GUT GT 64H M32 50 A1	32	76.346.6435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GO 64H M25 50 A0	25	76.333.6435.0	1
with threaded collar	BAS GUT GO 64H M25 50 A1	25	76.333.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5– 19 mm	BAS GUT GU 64H M25 50 A0	25	76.343.6435.0	1
with threaded collar	BAS GUT GU 64H M25 50 A1	25	76.343.6435.1	1
1 cable gland, bottom, 1 x M32				
without cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GO 64H M32 50 A0	32	76.337.6435.0	1
with threaded collar	BAS GUT GO 64H M32 50 A1	32	76.337.6435.1	1
with cover				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GUT GU 64H M32 50 A0	32	76.347.6435.0	1
with threaded collar	BAS GUT GU 64H M32 50 A1	32	76.347.6435.1	1

Technical data

Material	Die cast aluminum alloy
Surface	silicon-free
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A
Gasket	NBR
Degree of protection	
with latched locking levers	IP54
with appropriate cable glands	IP65
Temperature range	-40 – +120 °C

All Bases with "cable gland bottom" on this page are also available in M40 design.
Part numbers available on request.


Note: In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

Accessories and Dimensions


Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	

Bases


closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



500 V Hoods, double locking lever Size 24

500 V Hoods Size 24



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
500 V Hoods, size 24				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GA 24 M25 50 A0	25	70.350.2435.0	1
with threaded collar	BAS GOT GA 24 M25 50 A1	25	70.350.2435.1	1
with intermediate support	BAS GOT GA 24 M25 50 A2	25	70.350.2435.2	1
with strain relief, IP54	BAS GOT GA 24 M25 50 A3	25	70.350.2435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GA 24 M32 50 A0	32	70.353.2435.0	1
with threaded collar	BAS GOT GA 24 M32 50 A1	32	70.353.2435.1	1
with intermediate support	BAS GOT GA 24 M32 50 A2	32	70.353.2435.2	1
with strain relief, IP54	BAS GOT GA 24 M32 50 A3	32	70.353.2435.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GC 24 M25 50 A0	25	70.352.2435.0	1
with threaded collar	BAS GOT GC 24 M25 50 A1	25	70.352.2435.1	1
with intermediate support	BAS GOT GC 24 M25 50 A2	25	70.352.2435.2	1
with strain relief, IP54	BAS GOT GC 24 M25 50 A3	25	70.352.2435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GC 24 M32 50 A0	32	70.354.2435.0	1
with threaded collar	BAS GOT GC 24 M32 50 A1	32	70.354.2435.1	1
with intermediate support	BAS GOT GC 24 M32 50 A2	32	70.354.2435.2	1
with strain relief, IP54	BAS GOT GC 24 M32 50 A3	32	70.354.2435.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods

500 V Size 24 Lateral cable entry



500 V Size 24 Top cable entry



500 V Hoods, double locking lever with Locking levers, Size 24

500 V Hoods Size 24



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



Description	Type	M	Part No.	P.U.
500 V Hoods, size 24	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GD 24 M25 50 A0	25	70.355.2435.0	1
with threaded collar	BAS GOT GD 24 M25 50 A1	25	70.355.2435.1	1
with intermediate support	BAS GOT GD 24 M25 50 A2	25	70.355.2435.2	1
with strain relief, IP54	BAS GOT GD 24 M25 50 A3	25	70.355.2435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GD 24 M32 50 A0	32	70.358.2435.0	1
with threaded collar	BAS GOT GD 24 M32 50 A1	32	70.358.2435.1	1
with intermediate support	BAS GOT GD 24 M32 50 A2	32	70.358.2435.2	1
with strain relief, IP54	BAS GOT GD 24 M32 50 A3	32	70.358.2435.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GF 24 M25 50 A0	25	70.357.2435.0	1
with threaded collar	BAS GOT GF 24 M25 50 A1	25	70.357.2435.1	1
with intermediate support	BAS GOT GF 24 M25 50 A2	25	70.357.2435.2	1
with strain relief, IP54	BAS GOT GF 24 M25 50 A3	25	70.357.2435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GF 24 M32 50 A0	32	70.359.2435.0	1
with threaded collar	BAS GOT GF 24 M32 50 A1	32	70.359.2435.1	1
with intermediate support	BAS GOT GF 24 M32 50 A2	32	70.359.2435.2	1
with strain relief, IP54	BAS GOT GF 24 M32 50 A3	32	70.359.2435.3	1
Multipole connectors for cable-to-cable couplings M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GC 24 M32 50 A0	32	70.354.2435.0	1
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GK 24 M32 50 A0	32	70.374.2435.0	1
Locking levers and gasket				
with threaded collar	BAS GOT GC 24 M32 50 A1	32	70.354.2435.1	1
with threaded collar	BAS GOT GK 24 M32 50 A1	32	70.374.2435.1	1
Locking levers and gasket				
with strain relief, IP54	BAS GOT GC 24 M32 50 A3	32	70.354.2435.3	1
with strain relief, IP54	BAS GOT GK 24 M32 50 A3	32	70.374.2435.3	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Hoods with Locking levers



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



500 V Hoods, double locking lever Size 24H, increased height design

500 V Hoods Size 24H, increased height design

Lateral cable entry



Top cable entry




Description	Type	M	Part No.	P.U.
500 V Hoods, size 24H	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GA 64H M25 50 A0	25	73.350.6435.0	1
with threaded collar	BAS GOT GA 64H M25 50 A1	25	73.350.6435.1	1
with intermediate support	BAS GOT GA 64H M25 50 A2	25	73.350.6435.2	1
with strain relief, IP54	BAS GOT GA 64H M25 50 A3	25	73.350.6435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GA 64H M32 50 A0	32	73.353.6435.0	1
with threaded collar	BAS GOT GA 64H M32 50 A1	32	73.353.6435.1	1
with intermediate support	BAS GOT GA 64H M32 50 A2	32	73.353.6435.2	1
with strain relief, IP54	BAS GOT GA 64H M32 50 A3	32	73.353.6435.3	1
Lateral cable entry M40				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 23 – 32 mm	BAS GOT GA 64H M40 50 A0	40	73.360.6435.0	1
with threaded collar	BAS GOT GA 64H M40 50 A1	40	73.360.6435.1	1
with intermediate support	BAS GOT GA 64H M40 50 A2	40	73.360.6435.2	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	BAS GOT GC 64H M25 50 A0	25	73.352.6435.0	1
with threaded collar	BAS GOT GC 64H M25 50 A1	25	73.352.6435.1	1
with intermediate support	BAS GOT GC 64H M25 50 A2	25	73.352.6435.2	1
with strain relief, IP54	BAS GOT GC 64H M25 50 A3	25	73.352.6435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 15 – 26.5 mm	BAS GOT GC 64H M32 50 A0	32	73.354.6435.0	1
with threaded collar	BAS GOT GC 64H M32 50 A1	32	73.354.6435.1	1
with intermediate support	BAS GOT GC 64H M32 50 A2	32	73.354.6435.2	1
with strain relief, IP54	BAS GOT GC 64H M32 50 A3	32	73.354.6435.3	1
Top cable entry M40				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 23 – 32 mm	BAS GOT GC 64H M40 50 A0	40	73.362.6435.0	1
with threaded collar	BAS GOT GC 64H M40 50 A1	40	73.362.6435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods

Lateral cable entry



Top cable entry



Note:

In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

500 V Hoods, double locking lever with Locking levers, Size 24H, increased height design

500 V Hoods Size 24H, increased height design

Lateral cable entry



Top cable entry




Description	Type	M	Part No.	P.U.
500 V Hoods, size 24H				
Lateral cable entry M25	Aluminum housing			
with cable gland, IP54, $\rightarrow \text{Ø}$ 7.5 – 19 mm	BAS GOT GD 64H M25 50 A0	25	73.355.6435.0	1
with threaded collar	BAS GOT GD 64H M25 50 A1	25	73.355.6435.1	1
with intermediate support	BAS GOT GD 64H M25 50 A2	25	73.355.6435.2	1
with strain relief, IP54	BAS GOT GD 64H M25 50 A3	25	73.355.6435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø}$ 15 – 26.5 mm	BAS GOT GD 64H M32 50 A0	32	73.358.6435.0	1
with threaded collar	BAS GOT GD 64H M32 50 A1	32	73.358.6435.1	1
with intermediate support	BAS GOT GD 64H M32 50 A2	32	73.358.6435.2	1
with strain relief, IP54	BAS GOT GD 64H M32 50 A3	32	73.358.6435.3	1
Lateral cable entry M40				
with threaded collar	BAS GOT GD 64H M40 50 A1	40	73.365.6435.1	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \text{Ø}$ 7.5 – 19 mm	BAS GOT GF 64H M25 50 A0	25	73.357.6435.0	1
with threaded collar	BAS GOT GF 64H M25 50 A1	25	73.357.6435.1	1
with intermediate support	BAS GOT GF 64H M25 50 A2	25	73.357.6435.2	1
with strain relief, IP54	BAS GOT GF 64H M25 50 A3	25	73.357.6435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \text{Ø}$ 15 – 26.5 mm	BAS GOT GF 64H M32 50 A0	32	73.359.6435.0	1
with threaded collar	BAS GOT GF 64H M32 50 A1	32	73.359.6435.1	1
with intermediate support	BAS GOT GF 64H M32 50 A2	32	73.359.6435.2	1
with strain relief, IP54	BAS GOT GF 64H M32 50 A3	32	73.359.6435.3	1
Top cable entry M40				
with threaded collar	BAS GOT GF 64H M40 50 A1	40	73.367.6435.0	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V Bases, double locking lever Size 24

500 V Bases, Size 24



open

without cover
with cover



closed

1 cable gland, lateral
cable entry

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 24				
Open-bottom base				
without cover	BAS GUT GA 24 50 A		70.320.2428.0	1
with cover	BAS GUT GE 24 50 A		70.325.2428.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 24 M25 50 A0	25	70.330.2435.0	1
with threaded collar	BAS GUT GB 24 M25 50 A1	25	70.330.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 24 M25 50 A0	25	70.340.2435.0	1
with threaded collar	BAS GUT GF 24 M25 50 A1	25	70.340.2435.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 24 M25 50 A0	25	70.331.2435.0	1
with threaded collar	BAS GUT GC 24 M25 50 A1	25	70.331.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 24 M25 50 A0	25	70.341.2435.0	1
with threaded collar	BAS GUT GG 24 M25 50 A1	25	70.341.2435.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 24 M25 50 A0	25	70.342.2435.0	1
with threaded collar	BAS GUT GH 24 M25 50 A1	25	70.342.2435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 24 M25 50 A0	25	70.333.2435.0	1
with threaded collar	BAS GUT GD 24 M25 50 A1	25	70.333.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GI 24 M25 50 A0	25	70.343.2435.0	1
with threaded collar	BAS GUT GI 24 M25 50 A1	25	70.343.2435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design of the revos housings will change. Through the use of an integrated insulation strip, voltage ranges of up to 690 V can then be covered. Additionally, a new, flexible marking system will be available to you.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



500 V Bases, double locking lever Size 24H, increased height design

500 V Bases Size 24H, increased height design


closed M25 2 cable glands without cover with cover



closed M32 2 cable glands without cover with cover



closed M25 1 cable gland, bottom without cover with cover



Description	Type	M	Part No.	P.U.
500 V Bases, size 24H	Aluminum housing			
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 64H M25 50 A0	25	73.330.6435.0	1
with threaded collar	BAS GUT GB 64H M25 50 A1	25	73.330.6435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 64H M25 50 A0	25	73.340.6435.0	1
with threaded collar	BAS GUT GF 64H M25 50 A1	25	73.340.6435.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GB 64H M32 50 A0	32	73.334.6435.0	1
with threaded collar	BAS GUT GB 64H M32 50 A1	32	73.334.6435.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GF 64H M32 50 A0	32	73.344.6435.0	1
with threaded collar	BAS GUT GF 64H M32 50 A1	32	73.344.6435.1	1
2 cable glands, 2 x M40				
without cover				
with threaded collar	BAS GUT GB 64H M40 50 A1	40	73.338.6435.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 64H M25 50 A0	25	73.331.6435.0	1
with threaded collar	BAS GUT GC 64H M25 50 A1	25	73.331.6435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 64H M25 50 A0	25	73.341.6435.0	1
with threaded collar	BAS GUT GG 64H M25 50 A1	25	73.341.6435.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GC 64H M32 50 A0	32	73.335.6435.0	1
with threaded collar	BAS GUT GC 64H M32 50 A1	32	73.335.6435.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GG 64H M32 50 A0	32	73.345.6435.0	1
with threaded collar	BAS GUT GG 64H M32 50 A1	32	73.345.6435.1	1
1 cable gland, left, 1 x M40				
without cover				
with threaded collar	BAS GUT GC 64H M40 50 A1	40	73.339.6435.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 64H M25 50 A0	25	73.342.6435.0	1
with threaded collar	BAS GUT GH 64H M25 50 A1	25	73.342.6435.1	1
1 cable gland, right, 1 x M32				
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GH 64H M32 50 A0	32	73.346.6435.0	1
with threaded collar	BAS GUT GH 64H M32 50 A1	32	73.346.6435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 64H M25 50 A0	25	73.333.6435.0	1
with threaded collar	BAS GUT GD 64H M25 50 A1	25	73.333.6435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GI 64H M25 50 A0	25	73.343.6435.0	1
with threaded collar	BAS GUT GI 64H M25 50 A1	25	73.343.6435.1	1
1 cable gland, bottom, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GD 64H M32 50 A0	32	73.337.6435.0	1
with threaded collar	BAS GUT GD 64H M32 50 A1	32	73.337.6435.1	1
with cover				
with cable gland, IP54,  15 – 26.5 mm	BAS GUT GI 64H M32 50 A0	32	73.347.6435.0	1
with threaded collar	BAS GUT GI 64H M32 50 A1	32	73.347.6435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			

All Bases with "cable gland bottom" on this page are also available in M40 design.
Part numbers available on request.


Note: In 2013 the housing will be equipped with an insulation strip. With this modification, voltage ranges of up to 690 V can be covered.

Accessories and Dimensions


Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	

Bases


closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



690 V Hoods, single locking lever

Size 24

690 V Hoods Size 24



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
690 V Hoods, size 24				
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GG 24 M25 69 A0	25	77.350.2435.0	1
with threaded collar	BAS GOT GG 24 M25 69 A1	25	77.350.2435.1	1
with intermediate support	BAS GOT GG 24 M25 69 A2	25	77.350.2435.2	1
with strain relief, IP54	BAS GOT GG 24 M25 69 A3	25	77.350.2435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GG 24 M32 69 A0	32	77.353.2435.0	1
with threaded collar	BAS GOT GG 24 M32 69 A1	32	77.353.2435.1	1
with intermediate support	BAS GOT GG 24 M32 69 A2	32	77.353.2435.2	1
with strain relief, IP54	BAS GOT GG 24 M32 69 A3	32	77.353.2435.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GI 24 M25 69 A0	25	77.352.2435.0	1
with threaded collar	BAS GOT GI 24 M25 69 A1	25	77.352.2435.1	1
with intermediate support	BAS GOT GI 24 M25 69 A2	25	77.352.2435.2	1
with strain relief, IP54	BAS GOT GI 24 M25 69 A3	25	77.352.2435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GI 24 M32 69 A0	32	77.354.2435.0	1
with threaded collar	BAS GOT GI 24 M32 69 A1	32	77.354.2435.1	1
with intermediate support	BAS GOT GI 24 M32 69 A2	32	77.354.2435.2	1
with strain relief, IP54	BAS GOT GI 24 M32 69 A3	32	77.354.2435.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods

Lateral cable entry



Top cable entry



690 V Bases, single locking lever with Locking levers, Size 24

690 V Bases, Size 24



open

without cover
with cover



closed

1 cable gland, lateral cable entry

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 24	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 24 69 A		77.320.2428.0	1
with cover	BAS GUT GP 24 69 A		77.325.2428.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GL 24 M25 69 A0	25	77.330.2435.0	1
with threaded collar	BAS GUT GL 24 M25 69 A1	25	77.330.2435.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GR 24 M25 69 A0	25	77.340.2435.0	1
with threaded collar	BAS GUT GR 24 M25 69 A1	25	77.340.2435.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GM 24 M25 69 A0	25	77.331.2435.0	1
with threaded collar	BAS GUT GM 24 M25 69 A1	25	77.331.2435.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GS 24 M25 69 A0	25	77.341.2435.0	1
with threaded collar	BAS GUT GS 24 M25 69 A1	25	77.341.2435.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GT 24 M25 69 A0	25	77.342.2435.0	1
with threaded collar	BAS GUT GT 24 M25 69 A1	25	77.342.2435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GO 24 M25 69 A0	25	77.333.2435.0	1
with threaded collar	BAS GUT GO 24 M25 69 A1	25	77.333.2435.1	1
with cover				
with cable gland, IP54,  7.5– 19 mm	BAS GUT GU 24 M25 69 A0	25	77.343.2435.0	1
with threaded collar	BAS GUT GU 24 M25 69 A1	25	77.343.2435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



690 V Hoods, double locking lever Size 24

690 V Hoods Size 24



Lateral cable entry




Top cable entry




Description	Type	M	Part No.	P.U.
690 V Hoods, size 24				
Lateral cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GA 24 M25 69 A0	25	72.350.2435.0	1
with threaded collar	BAS GOT GA 24 M25 69 A1	25	72.350.2435.1	1
with intermediate support	BAS GOT GA 24 M25 69 A2	25	72.350.2435.2	1
with strain relief, IP54	BAS GOT GA 24 M25 69 A3	25	72.350.2435.3	1
Lateral cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GA 24 M32 69 A0	32	72.353.2435.0	1
with threaded collar	BAS GOT GA 24 M32 69 A1	32	72.353.2435.1	1
with intermediate support	BAS GOT GA 24 M32 69 A2	32	72.353.2435.2	1
with strain relief, IP54	BAS GOT GA 24 M32 69 A3	32	72.353.2435.3	1
Top cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	BAS GOT GC 24 M25 69 A0	25	72.352.2435.0	1
with threaded collar	BAS GOT GC 24 M25 69 A1	25	72.352.2435.1	1
with intermediate support	BAS GOT GC 24 M25 69 A2	25	72.352.2435.2	1
with strain relief, IP54	BAS GOT GC 24 M25 69 A3	25	72.352.2435.3	1
Top cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	BAS GOT GC 24 M32 69 A0	32	72.354.2435.0	1
with threaded collar	BAS GOT GC 24 M32 69 A1	32	72.354.2435.1	1
with intermediate support	BAS GOT GC 24 M32 69 A2	32	72.354.2435.2	1
with strain relief, IP54	BAS GOT GC 24 M32 69 A3	32	72.354.2435.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	-			
Gasket at Multipole connectors	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	

Dimensions

Lateral cable entry



Top cable entry



Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.

690 V Hoods, double locking lever Size 24XL

690 V Hoods Size 24XL



Lateral cable entry



Description	Type	M	Part No.	P.U.
690 V Hoods, size 24XL	Aluminum housing			
Lateral cable entry M50				
with intermediate support	POW GOT GA 24 M50 69 A2	50	72.250.2435.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	-			
Gasket	-			
Degree of protection				
with latched locking levers	-			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Contact inserts				
See the product matrix			Page 24–25	

Dimensions

Lateral cable entry



690 V Hoods, double locking lever with Locking levers, Size 24

690 V Hoods Size 24



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
690 V Hoods, size 24	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GD 24 M25 69 A0	25	72.355.2435.0	1
with threaded collar	BAS GOT GD 24 M25 69 A1	25	72.355.2435.1	1
with intermediate support	BAS GOT GD 24 M25 69 A2	25	72.355.2435.2	1
with strain relief, IP54	BAS GOT GD 24 M25 69 A3	25	72.355.2435.3	1
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GD 24 M32 69 A0	32	72.358.2435.0	1
with threaded collar	BAS GOT GD 24 M32 69 A1	32	72.358.2435.1	1
with intermediate support	BAS GOT GD 24 M32 69 A2	32	72.358.2435.2	1
with strain relief, IP54	BAS GOT GD 24 M32 69 A3	32	72.358.2435.3	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	BAS GOT GF 24 M25 69 A0	25	72.357.2435.0	1
with threaded collar	BAS GOT GF 24 M25 69 A1	25	72.357.2435.1	1
with intermediate support	BAS GOT GF 24 M25 69 A2	25	72.357.2435.2	1
with strain relief, IP54	BAS GOT GF 24 M25 69 A3	25	72.357.2435.3	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 15 – 26.5 mm	BAS GOT GF 24 M32 69 A0	32	72.359.2435.0	1
with threaded collar	BAS GOT GF 24 M32 69 A1	32	72.359.2435.1	1
with intermediate support	BAS GOT GF 24 M32 69 A2	32	72.359.2435.2	1
with strain relief, IP54	BAS GOT GF 24 M32 69 A3	32	72.359.2435.3	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket for Multipole connectors	-			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Hoods with Locking levers

Lateral cable entry



Top cable entry



690 V Bases, double locking lever Size 24

690 V Bases, Size 24



open

without cover
with cover



closed

1 cable gland, lateral
cable entry

without cover
with cover



closed

1 cable gland, bottom

without cover
with cover



Description	Type	M	Part No.	P.U.
690 V Bases, size 24	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GA 24 69 A		72.320.2428.0	1
with cover	BAS GUT GE 24 69 A		72.325.2428.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GB 24 M25 69 A0	25	72.330.2435.0	1
with threaded collar	BAS GUT GB 24 M25 69 A1	25	72.330.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GF 24 M25 69 A0	25	72.340.2435.0	1
with threaded collar	BAS GUT GF 24 M25 69 A1	25	72.340.2435.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GC 24 M25 69 A0	25	72.331.2435.0	1
with threaded collar	BAS GUT GC 24 M25 69 A1	25	72.331.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GG 24 M25 69 A0	25	72.341.2435.0	1
with threaded collar	BAS GUT GG 24 M25 69 A1	25	72.341.2435.1	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GH 24 M25 69 A0	25	72.342.2435.0	1
with threaded collar	BAS GUT GH 24 M25 69 A1	25	72.342.2435.1	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GD 24 M25 69 A0	25	72.333.2435.0	1
with threaded collar	BAS GUT GD 24 M25 69 A1	25	72.333.2435.1	1
with cover				
with cable gland, IP54,  7.5 – 19 mm	BAS GUT GI 24 M25 69 A0	25	72.343.2435.0	1
with threaded collar	BAS GUT GI 24 M25 69 A1	25	72.343.2435.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	Handle: Polyamide, UL94-V0; stainless steel: V2A			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Note:

In 2013 the design and order numbers of the revos housings will change, but the function of the housings will remain intact. In addition, a new flexible marking system will be available to you. In the transition phase you can continue to order with the existing part number. You can find more detailed information and a cross-reference list in our e-Shop and on our homepage.


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



500 V / 690 V Hoods, double locking lever Size 32

500 V / 690 V Hoods, Size 32



Lateral cable entry



Top cable entry




Description	Type	M	Part No.	P.U.
500 V / 690 V Hoods, size 32				
Lateral cable entry M32	Aluminum housing			
with cable gland, IP54, $\rightarrow \varnothing \rightarrow$ 7.5 – 19 mm	BAS GOT GA 32 M32 50 A0	32	70.350.3235.0	1
with threaded collar	BAS GOT GA 32 M32 50 A1	32	70.350.3235.1	1
with intermediate support	BAS GOT GA 32 M32 50 A2	32	70.350.3235.2	1
with strain relief, IP54	BAS GOT GA 32 M32 50 A3	32	70.350.3235.3	1
Lateral cable entry M40				
with threaded collar	BAS GOT GA 32 M40 50 A1	40	70.353.3235.1	1
with intermediate support	BAS GOT GA 32 M40 50 A2	40	70.353.3235.2	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \rightarrow$ 7.5 – 19 mm	BAS GOT GC 32 M32 50 A0	32	70.352.3235.0	1
with threaded collar	BAS GOT GC 32 M32 50 A1	32	70.352.3235.1	1
with intermediate support	BAS GOT GC 32 M32 50 A2	32	70.352.3235.2	1
with strain relief, IP54	BAS GOT GC 32 M32 50 A3	32	70.352.3235.3	1
Top cable entry M40				
with threaded collar	BAS GOT GC 32 M40 50 A1	40	70.354.3235.1	1
with intermediate support	BAS GOT GC 32 M40 50 A2	40	70.354.3235.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods

Lateral cable entry



Top cable entry



500 V / 690 V Bases, double locking lever Size 32

500 V / 690 V Bases, Size 32



open





Description	Type	M	Part No.	P.U.
500 V / 690 V Base, size 32	Aluminum housing			
open				
without cover	BAS GUT GA 32 50 A		70.320.3228.0	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Contact inserts				
See the product matrix			Page 24–25	

Dimensions

Bases

open



500 V / 690 V Hoods, single locking lever Size 48

500 V / 690 V Hoods, Size 48



Lateral cable entry



Top cable entry




Description	Type	M	Part No.	P.U.
500 V / 690 V Hoods, size 48				
Lateral cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \rightarrow$ 7.5 – 19 mm	BAS GOT GG 48 M32 50 A0	32	70.350.4835.0	1
with threaded collar	BAS GOT GG 48 M32 50 A1	32	70.350.4835.1	1
with intermediate support	BAS GOT GG 48 M32 50 A2	32	70.350.4835.2	1
with strain relief, IP54	BAS GOT GG 48 M32 50 A3	32	70.350.4835.3	1
Lateral cable entry M40				
with threaded collar	BAS GOT GG 48 M40 50 A1	40	70.353.4835.1	1
with intermediate support	BAS GOT GG 48 M40 50 A2	40	70.353.4835.2	1
Top cable entry M32				
with cable gland, IP54, $\rightarrow \varnothing \rightarrow$ 7.5 – 19 mm	BAS GOT GI 48 M32 50 A0	32	70.352.4835.0	1
with threaded collar	BAS GOT GI 48 M32 50 A1	32	70.352.4835.1	1
with intermediate support	BAS GOT GI 48 M32 50 A2	32	70.352.4835.2	1
with strain relief, IP54	BAS GOT GI 48 M32 50 A3	32	70.352.4835.3	1
Top cable entry M40				
with threaded collar	BAS GOT GI 48 M40 50 A1	40	70.354.4835.1	1
with intermediate support	BAS GOT GI 48 M40 50 A2	40	70.354.4835.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods

Lateral cable entry



Top cable entry



500 / 690 V Bases, single locking lever Size 48

500 / 690 V Bases, Size 48



open
without cover
with cover



closed
1 cable gland
without cover
with cover





Description	Type	M	Part No.	P.U.
500 / 690 V Bases, size 48	Aluminum housing			
Open-bottom base				
without cover	BAS GUT GK 48 50 A		70.320.4828.0	1
with metal cover	BAS GUT GP 48 50 A		70.325.4828.0	1
Closed-bottom base				
1 cable glands left, 1 x M32				
without cover				
with cable gland, IP54,  15– 26.5 mm	BAS GUT GM48 M32 50 A0	32	70.331.4835.0	1
with threaded collar	BAS GUT GM48 M32 50 A1	32	70.331.4835.1	1
with strain relief IP54	BAS GUT GM48 M32 50 A3	32	70.331.4835.3	1
with metal cover				
with cable gland, IP54,  15– 26.5 mm	BAS GUT GS 48 M32 50 A0	32	70.341.4835.1	1
with strain relief IP54	BAS GUT GS 48 M32 50 A3	32	70.341.4835.3	1
1 cable gland, left, 1 x M40				
with metal cover				
with threaded collar	BAS GUT GR 48 M40 50 A1	40	70.344.4835.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Cable gland IP68, plastic material, gray	Connection range 16 – 28 mm	40	Z5.507.1953.0	1
Cable gland IP68, nickel-plated brass	Connection range 19 – 27 mm	40	Z5.507.1921.0	1
Contact inserts				
See the product matrix			Page 24–25	



Dimensions

Bases

open



closed, 1 cable gland



EMC Hoods, Size 6–24

EMC Hoods

Lateral cable entry



Size 6/6H



Size 24/24H




Description	Type	M	Part No.	P.U.
EMC Hoods				
Aluminum housing				
Lateral cable entry, size 6/6H				
with threaded collar M20	BAS GOE GG 6 M20 50 A1	20	70.350.0645.1	1
with threaded collar M25	BAS GOE GG 6 M25 50 A1	25	70.353.0645.1	1
with threaded collar M25, increased height design	BAS GOE GG 6H M25 50 A1	25	73.350.0645.1	1
with threaded collar M32, increased height design	BAS GOE GG 6H M32 50 A1	32	73.353.0645.1	1
Lateral cable entry, size 10/10H				
with threaded collar M20	BAS GOE GA 10 M20 50 A1	20	70.350.1045.1	1
with threaded collar M25	BAS GOE GA 10 M25 50 A1	25	70.353.1045.1	1
with threaded collar M25, increased height design	BAS GOE GA 10H M25 50 A1	25	73.350.1045.1	1
with threaded collar M32, increased height design	BAS GOE GA 10H M32 50 A1	32	73.353.1045.1	1
Lateral cable entry, size 16/16H				
with threaded collar M25	BAS GOE GG 16 M25 50 A1	25	70.350.1645.1	1
with threaded collar M32	BAS GOE GG 16 M32 50 A1	32	70.353.1645.1	1
with threaded collar M25, increased height design	BAS GOE GG 16H M25 50 A1	25	73.350.4045.1	1
with threaded collar M32, increased height design	BAS GOE GG 16H M32 50 A1	32	73.353.4045.1	1
with threaded collar M40, increased height design	BAS GOE GG 16H M40 50 A1	40	73.360.4045.1	1
Lateral cable entry, size 24/24H				
with threaded collar M25	BAS GOE GA 24 M25 50 A1	25	70.350.2445.1	1
with threaded collar M32	BAS GOE GA 24 M32 50 A1	32	70.353.2445.1	1
with threaded collar M25, increased height design	BAS GOE GA 24H M25 50 A1	25	73.350.6445.1	1
with threaded collar M32, increased height design	BAS GOE GA 24H M32 50 A1	32	73.353.6445.1	1
with threaded collar M40, increased height design	BAS GOE GA 24H M40 50 A1	40	73.360.6445.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	Special EMC plating, highly conductive			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	–			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland EMV IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.4821.0	1
Cable gland EMV IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.5021.0	1
Cable gland EMV IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.5221.0	1
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods Lateral cable entry

Size 6 and 10




Size 6H and 10H




Size	L1 [mm]
6	60.0
6H	60.0
10	73.0
10H	73.0

Size 16 and 24



Size 16H and 24H



Size	L2 [mm]
16	93.5
16H	93.5
24	120.0
24H	120.0


EMC Bases, Size 6–24

EMC Bases open

Size 6



Size 24




Description	Type	M	Part No.	P.U.
EMC Bases	Aluminum housing			
Open				
Size 6	BAS GUE GK 6 50 A		70.320.0638.0	1
Size 10	BAS GUE GA 10 50 A		70.320.1038.0	1
Size 16	BAS GUE GA 16 50 A		70.320.1638.0	1
Size 24	BAS GUE GA 24 50 A		70.320.2438.0	1
Technical data				
Material	Die cast aluminum alloy			
Surface	Special EMC plating, highly conductive			
Locking levers	Steel			
Gasket	–			
Degree of protection				
with latched locking levers	–			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Open-Bottom bases


Size 6




Size 10



Size 16



Size 24



250 V Hoods, single locking lever Size 10/15

250 V Hoods Size 10/15

Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings




Description	Type	M	Part No.	P.U.
250 V Hoods, size 10/15				
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	HD GOT GG 15 M20 50 A0	20	76.350.1535.0	1
with intermediate support	HD GOT GG 15 M20 50 A2	20	76.350.1535.2	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	HD GOT GG 15 M25 50 A0	25	76.353.1535.0	1
with threaded collar	HD GOT GG 15 M25 50 A1	25	76.353.1535.1	1
with intermediate support	HD GOT GG 15 M25 50 A2	25	76.353.1535.2	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	HD GOT GI 15 M20 50 A0	20	76.352.1535.0	1
with threaded collar	HD GOT GI 15 M20 50 A1	20	76.352.1535.1	1
with intermediate support	HD GOT GI 15 M20 50 A2	20	76.352.1535.2	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 7.5 – 19 mm	HD GOT GI 15 M25 50 A0	25	76.354.1535.0	1
with threaded collar	HD GOT GI 15 M25 50 A1	25	76.354.1535.1	1
with intermediate support	HD GOT GI 15 M25 50 A2	25	76.354.1535.2	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	HD GOT GI 15 M20 50 A0	20	76.352.1535.0	1
with cable gland, IP54, $\rightarrow \varnothing \leftarrow$ 3 – 14.5 mm	HD GOT GL 15 M20 50 A0	20	76.372.1535.0	1
Locking levers and gasket				
with threaded collar	HD GOT GI 15 M20 50 A1	20	76.352.1535.1	1
with threaded collar	HD GOT GL 15 M20 50 A1	20	76.372.1535.1	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	–			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



250 V Bases, single locking lever Size 10/15

250 V Bases, Size 10/15

open

without cover
with cover



closed

1 cable gland

without cover
with cover



closed

1 cable gland, lateral cable entry

without cover
with cover




Description	Type	M	Part No.	P.U.
250 V Bases, size 10/15				
Aluminum housing				
Open-bottom base				
without cover	HD GUT GK 15 50 A		76.320.1528.0	1
with metal cover	HD GUT MP 15 50 A		76.425.1528.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT GL 15 M20 50 A0	20	76.330.1535.0	1
with threaded collar	HD GUT GL 15 M20 50 A1	20	76.330.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT GR 15 M20 50 A0	20	76.440.1535.0	1
with threaded collar	HD GUT GR 15 M20 50 A1	20	76.440.1535.1	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT GL 15 M25 50 A0	25	76.334.1535.0	1
with threaded collar	HD GUT GL 15 M25 50 A1	25	76.334.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT GR 15 M25 50 A0	25	76.444.1535.0	1
with threaded collar	HD GUT GR 15 M25 50 A1	25	76.444.1535.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT GM15 M20 50 A0	20	76.331.1535.0	1
with threaded collar	HD GUT GM15 M20 50 A1	20	76.331.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT MS 15 M20 50 A0	20	76.441.1535.0	1
with threaded collar	HD GUT MS 15 M20 50 A1	20	76.441.1535.1	1
1 cable gland, right, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT GN 15 M20 50 A0	20	76.332.1535.0	1
with threaded collar	HD GUT GN 15 M20 50 A1	20	76.332.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 3 - 14.5 \text{ mm}$	HD GUT MN15 M20 50 A0	20	76.442.1535.0	1
with threaded collar	HD GUT MN15 M20 50 A1	20	76.442.1535.1	1
1 cable gland seitlich, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT GM15 M25 50 A0	25	76.335.1535.0	1
with threaded collar	HD GUT GM15 M25 50 A1	25	76.335.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT MS 15 M25 50 A0	25	76.445.1535.0	1
with threaded collar	HD GUT MS 15 M25 50 A1	25	76.445.1535.1	1
1 cable gland seitlich, right, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT GT 15 M25 50 A0	25	76.336.1535.0	1
with threaded collar	HD GUT GT 15 M25 50 A1	25	76.336.1535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow 7.5 - 19 \text{ mm}$	HD GUT MN15 M25 50 A0	25	76.446.1535.0	1
with threaded collar	HD GUT MN15 M25 50 A1	25	76.446.1535.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Bases


open




closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, lateral cable entry



250 V Hoods, single locking lever Size 16/25

250 V Hoods Size 16/25

Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings




Description	Type	M	Part No.	P.U.
250 V Hoods, size 16/25	Aluminum housing			
Lateral cable entry M20				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 3 – 14.5 mm	HD GOT GG 25 M20 50 A0	20	76.350.2535.0	1
with intermediate support	HD GOT GG 25 M20 50 A2	20	76.350.2535.2	1
Lateral cable entry M25				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 7.5 – 19 mm	HD GOT GG 25 M25 50 A0	25	76.353.2535.0	1
with intermediate support	HD GOT GG 25 M25 50 A2	25	76.353.2535.2	1
Top cable entry M20				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 3 – 14.5 mm	HD GOT GI 25 M20 50 A0	20	76.352.2535.0	1
with threaded collar	HD GOT GI 25 M20 50 A1	20	76.352.2535.1	1
with intermediate support	HD GOT GI 25 M20 50 A2	20	76.352.2535.2	1
Top cable entry M25				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 7.5 – 19 mm	HD GOT GI 25 M25 50 A0	25	76.354.2535.0	1
with threaded collar	HD GOT GI 25 M25 50 A1	25	76.354.2535.1	1
with intermediate support	HD GOT GI 25 M25 50 A2	25	76.354.2535.2	1
Multipole connectors for cable-to-cable couplings M20				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 3 – 14.5 mm	HD GOT GI 25 M20 50 A0	20	76.352.2535.0	1
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 3 – 14.5 mm	HD GOT GL 25 M20 50 A0	20	76.372.2535.0	1
Locking levers and gasket				
with threaded collar	HD GOT GI 25 M20 50 A1	20	76.352.2535.1	1
with threaded collar	HD GOT GL 25 M20 50 A1	20	76.372.2535.1	1
Locking levers and gasket				
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 7.5 – 19 mm	HD GOT GI 25 M25 50 A0	25	76.354.2535.0	1
with cable gland, IP54, $\rightarrow\varnothing\leftarrow$ 7.5 – 19 mm	HD GOT GL 25 M25 50 A0	25	76.374.2535.0	1
Locking levers and gasket				
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers at Multipole connectors	Stahl			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



250 V Bases, single locking lever Size 16/25

250 V Bases, Size 16/25

open

without cover
with cover



closed 1 cable gland

without cover
with cover




Description	Type	M	Part No.	P.U.
250 V Bases, size 16/25	Aluminum housing			
Open-bottom base				
without cover	HD GUT GK 25 50 A		76.320.2528.0	1
mit plasticdeckel	HD GUT GP 25 50 A		76.325.2528.0	1
with metal cover	HD GUT MP 25 50 A		76.425.2528.0	1
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	HD GUT GL 25 M20 50 A0	20	76.330.2535.0	1
with threaded collar	HD GUT GL 25 M20 50 A1	20	76.330.2535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	HD GUT MR 25 M20 50 A0	20	76.440.2535.0	1
with threaded collar	HD GUT MR 25 M20 50 A1	20	76.440.2535.1	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	HD GUT GL 25 M25 50 A0	25	76.334.2535.0	1
with threaded collar	HD GUT GL 25 M25 50 A1	25	76.334.2535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	HD GUT MR 25 M25 50 A0	25	76.444.2535.0	1
with threaded collar	HD GUT MR 25 M25 50 A1	25	76.444.2535.1	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	HD GUT GM 25 M20 50 A0	20	76.331.2535.0	1
with threaded collar	HD GUT GM 25 M20 50 A1	20	76.331.2535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	HD GUT MS 25 M20 50 A0	20	76.441.2535.0	1
with threaded collar	HD GUT MS 25 M20 50 A1	20	76.441.2535.1	1
1 cable gland, right, 1 x M20				
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	HD GUT MN 25 M20 50 A0	20	76.442.2535.0	1
with threaded collar	HD GUT MN 25 M20 50 A1	20	76.442.2535.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	HD GUT GM 25 M25 50 A0	25	76.335.2535.0	1
with threaded collar	HD GUT GM 25 M25 50 A1	25	76.335.2535.1	1
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	HD GUT MS 25 M25 50 A0	25	76.445.2535.0	1
with threaded collar	HD GUT MS 25 M25 50 A1	25	76.445.2535.1	1
1 cable gland, right, 1 x M25				
with metal cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	HD GUT MN 25 M25 50 A0	25	76.446.2535.0	1
with threaded collar	HD GUT MN 25 M25 50 A1	25	76.446.2535.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 6 – 12 mm	20	Z5.507.1353.0	10
Cable gland IP68, nickel-plated brass	Connection range 8 – 13 mm	20	Z5.507.1321.0	10
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Bases


open with cover




closed with cover, 2 cable glands



closed with cover, 1 cable gland



closed without cover, 1 cable gland



250 V Hoods, double locking lever Size 32/50

250 V Hoods Size 32/50

Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings




Description	Type	M	Part No.	P.U.
250 V Hoods, size 32/50	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	HD GOT GA 32 M25 69 A0	25	73.350.3235.0	1
with threaded collar	HD GOT GA 32 M25 69 A1	25	73.350.3235.1	1
with intermediate support	HD GOT GA 32 M25 69 A2	25	73.350.3235.2	1
Lateral cable entry M32				
with cable gland, IP54, $\varnothing$ 15 – 26.5 mm	HD GOT GA 32 M32 69 A0	32	73.353.3235.0	1
with threaded collar	HD GOT GA 32 M32 69 A1	32	73.353.3235.1	1
with intermediate support	HD GOT GA 32 M32 69 A2	32	73.353.3235.2	1
Top cable entry M25				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	HD GOT GC 32 M25 69 A0	25	73.352.3235.0	1
with threaded collar	HD GOT GC 32 M25 69 A1	25	73.352.3235.1	1
with intermediate support	HD GOT GC 32 M25 69 A2	25	73.352.3235.2	1
Top cable entry M32				
with cable gland, IP54, $\varnothing$ 15 – 26.5 mm	HD GOT GC 32 M32 69 A0	32	73.354.3235.0	1
with threaded collar	HD GOT GC 32 M32 69 A1	32	73.354.3235.1	1
with intermediate support	HD GOT GC 32 M32 69 A2	32	73.354.3235.2	1
Multipole connectors for cable-to-cable couplings M25				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	HD GOT GK 32 M25 69 A0	25	73.372.3235.0	1
with threaded collar	HD GOT GK 32 M25 69 A1	25	73.372.3235.1	1
with intermediate support	HD GOT GK 32 M25 69 A2	25	73.372.3235.2	1
Multipole connectors for cable-to-cable couplings M32				
with cable gland, IP54, $\varnothing$ 15 – 26.5 mm	HD GOT GK 32 M32 69 A0	32	73.374.3235.0	1
with threaded collar	HD GOT GK 32 M32 69 A1	32	73.374.3235.1	1
with intermediate support	HD GOT GK 32 M32 69 A2	32	73.374.3235.2	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods


Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings



250 V Hoods, double locking lever with Locking levers, Size 32/50

250 V Hoods Size 32/50

Lateral cable entry



Top cable entry




Description	Type	M	Part No.	P.U.
250 V Hoods, size 32/50	Aluminum housing			
Lateral cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	HD GOT GD 32 M25 69 A0	25	73.355.3235.0	1
with threaded collar	HD GOT GD 32 M25 69 A1	25	73.355.3235.1	1
with intermediate support	HD GOT GD 32 M25 69 A2	25	73.355.3235.2	1
Lateral cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	HD GOT GD 32 M32 69 A0	32	73.358.3235.0	1
with threaded collar	HD GOT GD 32 M32 69 A1	32	73.358.3235.1	1
with intermediate support	HD GOT GD 32 M32 69 A2	32	73.358.3235.2	1
Top cable entry M25				
with cable gland, IP54,  7.5 – 19 mm	HD GOT GF 32 M25 69 A0	25	73.357.3235.0	1
with threaded collar	HD GOT GF 32 M25 69 A1	25	73.357.3235.1	1
with intermediate support	HD GOT GF 32 M25 69 A2	25	73.357.3235.2	1
Top cable entry M32				
with cable gland, IP54,  15 – 26.5 mm	HD GOT GF 32 M32 69 A0	32	73.359.3235.0	1
with threaded collar	HD GOT GF 32 M32 69 A1	32	73.359.3235.1	1
with intermediate support	HD GOT GF 32 M32 69 A2	32	73.359.3235.2	1
Technical data				
Material metal/plastic	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Hoods with Locking levers

Lateral cable entry



Top cable entry



250 V Bases, double locking lever Size 32/50

250 V Bases, Size 32/50

open

without cover
with cover



closed

2 cable glands

without cover
with cover



closed

1 cable gland

without cover
with cover




Description	Type	M	Part No.	P.U.
250 V Bases, size 32/50	Aluminum housing			
Open-bottom base				
without cover	HD GUT GA 32 69 A		73.320.3228.0	1
with metal cover	HD GUT GE 32 69 A		73.325.3228.0	1
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	HD GUT GB 32 M25 69 A0	25	73.330.3235.0	1
with threaded collar	HD GUT GB 32 M25 69 A1	25	73.330.3235.1	1
with metal cover				
with cable gland, IP54,  7.5 – 19 mm	HD GUT GF 32 M25 69 A0	25	73.340.3235.0	1
with threaded collar	HD GUT GF 32 M25 69 A1	25	73.340.3235.1	1
2 cable glands, 2 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	HD GUT GB 32 M32 69 A0	32	73.334.3235.0	1
with threaded collar	HD GUT GB 32 M32 69 A1	32	73.334.3235.1	1
with metal cover				
with cable gland, IP54,  15 – 26.5 mm	HD GUT GF 32 M32 69 A0	32	73.344.3235.0	1
with threaded collar	HD GUT GF 32 M32 69 A1	32	73.344.3235.1	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54,  7.5 – 19 mm	HD GUT GC 32 M25 69 A0	25	73.331.3235.0	1
with threaded collar	HD GUT GC 32 M25 69 A1	25	73.331.3235.1	1
with metal cover				
with cable gland, IP54,  7.5 – 19 mm	HD GUT GH 32 M25 69 A0	25	73.342.3235.0	1
with threaded collar	HD GUT GH 32 M25 69 A1	25	73.342.3235.1	1
1 cable gland, left, 1 x M32				
without cover				
with cable gland, IP54,  15 – 26.5 mm	HD GUT GC 32 M32 69 A0	32	73.335.3235.0	1
with threaded collar	HD GUT GC 32 M32 69 A1	32	73.335.3235.1	1
with metal cover				
with cable gland, IP54,  15 – 26.5 mm	HD GUT GH 32 M32 69 A0	32	73.346.3235.0	1
with threaded collar	HD GUT GH 32 M32 69 A1	32	73.346.3235.1	1
Technical data				
Material	Die cast aluminum alloy			
Surface	silicon-free			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-40 – +120 °C			
Description	Type	M	Part No.	P.U.
Accessories				
Cable gland IP68, plastic material, gray	Connection range 7 – 16 mm	25	Z5.507.1553.0	10
Cable gland IP68, nickel-plated brass	Connection range 11 – 18 mm	25	Z5.507.1521.0	10
Cable gland IP68, plastic material, gray	Connection range 10 – 21 mm	32	Z5.507.1753.0	10
Cable gland IP68, nickel-plated brass	Connection range 15 – 21 mm	32	Z5.507.1721.0	10
Contact inserts				
See the product matrix			Page 24–25	


Dimensions

Bases, with and without Locking levers


open



closed, 2 cable glands



closed, 1 cable gland



90 V Hoods, single locking lever Size 6Ex

90 V Hoods Size 6Ex



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
90 V Hoods, size 6Ex	Housing, die cast zinc alloy			
Lateral cable entry M20				
with threaded collar	EX GOT GG 6 M20 09IA Z1	20	70.350.0636.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GG 6 M20 09IA Z3	20	70.350.0636.3	1
Lateral cable entry M25				
with threaded collar	EX GOT GG 6 M25 09IA Z1	25	70.353.0636.0	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GG 6 M25 09IA Z3	25	70.353.0636.3	1
Top cable entry M20				
with threaded collar	EX GOT GI 6 M20 09IA Z1	20	70.352.0636.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GI 6 M20 09IA Z3	20	70.352.0636.3	1
Top cable entry M25				
with threaded collar	EX GOT GI 6 M25 09IA Z1	25	70.354.0636.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GI 6 M25 09IA Z3	25	70.354.0636.3	1
Multipole connectors for cable-to-cable couplings with Locking levers and gasket				
Lateral cable entry M20				
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GT 6 M20 09IA Z4	20	99.731.3329.7	10
Lateral cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GT 6 M25 09IA Z4	25	99.732.3329.7	1
Top cable entry M20				
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GR 6 M20 09IA Z3	20	99.741.3329.7	10
Top cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GR 6 M25 09IA Z3	25	99.742.3329.7	10
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I


BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000


Dimensions

Hoods

Lateral cable entry




Top cable entry




Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Top cable entry



90 V Bases, single locking lever Size 6Ex

90 V Bases Size 6Ex



open
without cover
with cover



closed
**1 cable gland, lateral
cable entry**
without cover
with cover



closed
1 cable gland, bottom
with cover



Description	Type	M	Part No.	P.U.
90 V Bases, size 6Ex	Housing, die cast zinc alloy			
Open-bottom base				
without cover	EX GUT GK 6 09IA Z		70.320.0628.9	1
with cover	EX GUT GP 6 09IA Z		70.325.0628.9	1
cover with gasket	EX GUT GV 6 09IA Z		99.700.3329.7	10
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GL 6 M20 09IA Z0	20	70.330.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GR 6 M20 09IA Z0	20	70.340.0636.0	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GL 6 M25 09IA Z0	25	70.334.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GR 6 M25 09IA Z0	25	70.344.0636.0	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GM 6 M20 09IA Z0	20	70.331.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GS 6 M20 09IA Z0	20	70.341.0636.0	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GM 6 M25 09IA Z0	25	70.335.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GS 6 M25 09IA Z0	25	70.345.0636.0	1
1 cable gland, right, 1 x M20				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GT 6 M20 09IA Z0	20	70.342.0636.0	1
1 cable gland, right, 1 x M25				
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GT 6 M25 09IA Z0	25	70.346.0636.0	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GO 6 M20 09IA Z0	20	70.333.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GU 6 M20 09IA Z0	20	70.343.0636.0	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GO 6 M25 09IA Z0	25	70.337.0636.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GU 6 M25 09IA Z0	25	70.347.0636.0	1
Technical data				
Material metal/plastic	Die cast zinc alloy/Cover Polyamide			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I


BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000


Dimensions

Bases


open




closed, 2 cable glands, lateral cable entry



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



90 V Hoods, double locking lever Size 10Ex

90 V Hoods Size 10Ex



Lateral cable entry




Top cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
90 V Hoods, size 10Ex	Housing, die cast zinc alloy			
Lateral cable entry M20				
with threaded collar	EX GOT GA 10 M20 09IA Z1	20	70.350.1036.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GA 10 M20 09IA Z3	20	70.350.1036.3	1
Lateral cable entry M25				
with threaded collar	EX GOT GA 10 M25 09IA Z1	25	70.353.1036.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GA 10 M25 09IA Z3	25	70.353.1036.3	1
Top cable entry M20				
with threaded collar	EX GOT GC 10 M20 09IA Z1	20	70.352.1036.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GC 10 M20 09IA Z3	20	70.352.1036.3	1
Top cable entry M25				
with threaded collar	EX GOT GC 10 M25 09IA Z1	25	70.354.1036.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GC 10 M25 09IA Z3	25	70.354.1036.3	1
90 V Hoods, size 10Ex				
with Locking levers without gasket				
Lateral cable entry M20				
with threaded collar, with Locking levers	EX GOT GD 10 M20 09IA Z1	20	70.355.1036.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm, with Locking levers	EX GOT GD 10 M20 09IA Z3	20	70.355.1036.3	1
Lateral cable entry M25				
with threaded collar, with Locking levers	EX GOT GD 10 M25 09IA Z1	25	70.358.1036.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GD 10 M25 09IA Z3	25	70.358.1036.3	1
Top cable entry M20				
with threaded collar, with Locking levers	EX GOT GF 10 M20 09IA Z1	20	70.357.1036.1	1
with strain relief, IP54 → Ø ← 9 – 13.5 mm, with Locking levers	EX GOT GC 10 M20 09IA Z3	20	70.357.1036.3	1
Top cable entry M25				
with threaded collar, with Locking levers	EX GOT GF 10 M25 09IA Z1	25	70.359.1036.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GF 10 M25 09IA Z3	25	70.359.1036.3	1
Multipole connectors for cable-to-cable couplings with Locking levers and gasket				
Lateral cable entry M20				
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GS 10 M20 09IA Z4	20	99.733.3329.7	8
Lateral cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GS 10 M25 09IA Z4	25	99.734.3329.7	1
Top cable entry M20				
with strain relief, IP54 → Ø ← 9 – 13.5 mm	EX GOT GP 10 M20 09IA Z4	20	99.743.3329.7	8
Top cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GP 10 M25 09IA Z4	25	99.744.3329.7	8
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I

BVS 03 ATEX 184 X


EN 60079-0:2006 EN 60079-11:2007

EN 50303:2000


Dimensions

Hoods

Lateral cable entry




Top cable entry






Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Top cable entry



90 V Bases, double locking lever Size 10Ex

90 V Bases Size 10Ex



open

without cover
with cover



closed

1 cable gland, lateral
cable entry

without cover



closed

1 cable gland, bottom

without cover



Description	Type	M	Part No.	P.U.
90 V Bases, size 10Ex	Housing, die cast zinc alloy			
Open-bottom base				
without cover	EX GUT GA 10 09IA Z		70.320.1028.9	1
with cover, without Locking levers	EX GUT GE 10 09IA Z		70.325.1028.9	1
cover with gasket	EX GUT GX 10 09IA Z		99.706.3329.7	10
Closed-bottom base				
2 cable glands, 2 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GB 10 M20 09IA Z0	20	70.330.1036.0	1
with cover, without Locking levers				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GF 10 M20 09IA Z0	20	70.340.1036.0	1
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GB 10 M25 09IA Z0	25	70.334.1036.0	1
with cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GF 10 M25 09IA Z0	25	70.344.1036.0	1
1 cable gland, left, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GC 10 M20 09IA Z0	20	70.331.1036.0	1
with cover, without Locking levers				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GG 10 M20 09IA Z0	20	70.341.1036.0	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GC 10 M25 09IA Z0	25	70.335.1036.0	1
with cover, without Locking levers				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GG 10 M25 09IA Z0	25	70.345.1036.0	1
1 cable gland, bottom, 1 x M20				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GD 10 M20 09IA Z0	20	70.333.1036.0	1
with cover, without Locking levers				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 3 – 14.5 mm	EX GUT GI 10 M20 09IA Z0	20	70.343.1036.0	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GD 10 M25 09IA Z0	25	70.337.1036.0	1
with cover, without Locking levers				
with cable gland, IP54, $\rightarrow \text{Ø} \leftarrow$ 7.5 – 19 mm	EX GUT GI 10 M25 09IA Z0	25	70.347.1036.0	1
Technical data				
Material metal/plastic	Die cast zinc alloy/Cover Polyamide			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I





BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000



Dimensions

Bases



open





closed, 2 cable glands



closed, 1 cable gland, lateral cable entry



closed, 1 cable gland, bottom



90 V Hoods, double locking lever Size 16Ex

90 V Hoods Size 16Ex



Lateral cable entry




Top cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
90 V Hoods, size 16Ex	Housing, die cast zinc alloy			
Lateral cable entry M25				
with threaded collar	EX GOT GA 16 M25 09IA Z1	25	70.350.1636.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GA 16 M25 09IA Z3	25	70.350.1636.3	1
Lateral cable entry M32				
with threaded collar	EX GOT GA 16 M32 09IA Z1	32	70.353.1636.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GA 16 M32 09IA Z3	32	70.353.1636.3	1
Top cable entry M25				
with threaded collar	EX GOT GC 16 M25 09IA Z1	25	70.352.1636.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GC 16 M25 09IA Z3	25	70.352.1636.3	1
Top cable entry M32				
with threaded collar	EX GOT GC 16 M25 09IA Z1	32	70.354.1636.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GC 16 M25 09IA Z3	32	70.354.1636.3	1
90 V Hoods, size 16Ex				
with Locking levers without gasket				
Lateral cable entry M25				
with threaded collar, with Locking levers	EX GOT GD 16 M25 09IA Z1	25	70.355.1636.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GD 16 M25 09IA Z3	25	70.355.1636.3	1
Lateral cable entry M32				
with threaded collar, with Locking levers	EX GOT GD 16 M32 09IA Z1	32	70.358.1636.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm, with Locking levers	EX GOT GD 16 M32 09IA Z3	32	70.358.1636.3	1
Top cable entry M25				
with threaded collar, with Locking levers	EX GOT GF 16 M25 09IA Z1	25	70.357.1636.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GC 16 M25 09IA Z3	25	70.357.1636.3	1
Top cable entry M32				
with threaded collar, with Locking levers	EX GOT GF 16 M25 09IA Z1	32	70.359.1636.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm, with Locking levers	EX GOT GF 16 M25 09IA Z3	32	70.359.1636.3	1
Multipole connectors for cable-to-cable couplings with Locking levers and gasket				
Lateral cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GS 16 M25 09IA Z4	25	99.735.3329.7	1
Lateral cable entry M32				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GS 16 M32 09IA Z4	32	99.736.3329.7	1
Top cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GR 16 M25 09IA Z4	25	99.745.3329.7	1
Top cable entry M32				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GR 16 M32 09IA Z4	32	99.746.3329.7	1
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I

BVS 03 ATEX 184 X


EN 60079-0:2006 EN 60079-11:2007

EN 50303:2000


Dimensions

Hoods

Lateral cable entry




Top cable entry



Multipole connectors for cable-to-cable couplings

with Locking levers and gasket



Lateral cable entry



Multipole connectors for cable-to-cable couplings

with Locking levers and gasket

Top cable entry



90 V Bases, double locking lever Size 16Ex

90 V Bases Size 16Ex



open
without cover



Description	Type	M	Part No.	P.U.
90 V Bases, size 16Ex	Housing, die cast zinc alloy			
Open-bottom base				
without cover	EX GUT GA 16 09IA Z		70.320.1628.9	1
with cover, without Locking levers	EX GUT GE 16 09IA Z		70.325.1628.9	1
cover with gasket, without Locking levers	EX GUT GX 16 09IA Z		99.702.3329.7	10
Technical data				
Material metal/plastic	Die cast zinc alloy/Cover Polyamide			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section “facts & DATA” for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I





BVS 03 **ATEX** 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000

Dimensions

Bases

open



90 V Hoods, double locking lever Size 24Ex

90 V Hoods Size 24Ex



Lateral cable entry



Top cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
90 V Hoods, size 24Ex	Housing, die cast zinc alloy			
Lateral cable entry M25				
with threaded collar	EX GOT GA 24 M25 09IA Z1	25	70.350.2436.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GA 24 M25 09IA Z3	25	70.350.2436.3	1
Lateral cable entry M32				
with threaded collar	EX GOT GA 24 M32 09IA Z1	32	70.353.2436.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GA 24 M32 09IA Z3	32	70.353.2436.3	1
Top cable entry M25				
with threaded collar	EX GOT GC 24 M25 09IA Z1	25	70.352.2436.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GC 24 M25 09IA Z3	25	70.352.2436.3	1
Top cable entry M32				
with threaded collar	EX GOT GC 24 M25 09IA Z1	32	70.354.2436.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GC 24 M25 09IA Z3	32	70.354.2436.3	1
90 V Hoods, size 24Ex				
with Locking levers without gasket				
Lateral cable entry M25				
with threaded collar, with Locking levers	EX GOT GD 24 M25 09IA Z1	25	70.355.2436.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GD 24 M25 09IA Z3	25	70.355.2436.3	1
Lateral cable entry M32				
with threaded collar, with Locking levers	EX GOT GD 24 M32 09IA Z1	32	70.358.2436.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm, with Locking levers	EX GOT GD 24 M32 09IA Z3	32	70.358.2436.3	1
Top cable entry M25				
with threaded collar, with Locking levers	EX GOT GF 24 M25 09IA Z1	25	70.357.2436.1	1
with strain relief, IP54 → Ø ← 14 – 20 mm, with Locking levers	EX GOT GC 24 M25 09IA Z3	25	70.357.2436.3	1
Top cable entry M32				
with threaded collar, with Locking levers	EX GOT GF 24 M25 09IA Z1	32	70.359.2436.1	1
with strain relief, IP54 → Ø ← 21 – 28.5 mm, with Locking levers	EX GOT GF 24 M25 09IA Z3	32	70.359.2436.3	1
Multipole connectors for cable-to-cable couplings with Locking levers and gasket				
Lateral cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GS 24 M25 09IA Z4	25	99.737.3329.7	5
Lateral cable entry M32				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GS 24 M32 09IA Z4	32	99.738.3329.7	5
Top cable entry M25				
with strain relief, IP54 → Ø ← 14 – 20 mm	EX GOT GR 24 M25 09IA Z4	25	99.747.3329.7	4
Top cable entry M32				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	EX GOT GR 24 M32 09IA Z4	32	99.748.3329.7	4
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I


BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000


Dimensions

Hoods

Lateral cable entry




Top cable entry






Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Lateral cable entry



Multipole connectors for cable-to-cable couplings with Locking levers and gasket

Top cable entry



90 V Bases, double locking lever Size 24Ex


90 V Bases Size 24Ex



open without cover



closed 1 cable gland without cover



closed 1 cable gland, bottom without cover



Description	Type	M	Part No.	P.U.
90 V Bases, size 24Ex	Housing, die cast zinc alloy			
Open-bottom base				
without cover	EX GUT GA 24 09IA Z		70.320.2428.9	1
with cover, without Locking levers	EX GUT GE 24 09IA Z		70.325.2428.9	1
cover with gasket, without Locking levers	EX GUT GX 24 09IA Z		99.706.3329.7	10
Closed-bottom base				
2 cable glands, 2 x M25				
without cover				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GB 24 M25 09IA Z0	25	70.330.2436.0	1
with cover, without Locking levers				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GF 24 M25 09IA Z0	25	70.340.2436.0	1
1 cable gland, left, 1 x M25				
without cover				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GC 24 M25 09IA Z0	25	70.331.2436.0	1
with cover, without Locking levers				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GG 24 M25 09IA Z0	25	70.341.2436.0	1
1 cable gland, bottom, 1 x M25				
without cover				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GD 24 M25 09IA Z0	25	70.333.2436.0	1
with cover, without Locking levers				
with cable gland, IP54, $\varnothing$ 7.5 – 19 mm	EX GUT GI 24 M25 09IA Z0	25	70.343.2436.0	1
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	zinc-plated steel			
Gasket	NBR			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:





1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section “facts & DATA” for handling and assembly of the multipole connectors.
0344  I M1 Ex ia I
BVS 03 **ATEX** 184 X
EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000



Dimensions

Bases



open





closed, 2 cable glands



closed, 1 cable gland



closed, 1 cable gland, bottom



90 V Hoods, single locking lever, Size 48Ex

90 V Hoods Size 48Ex



Lateral cable entry



Top cable entry



Description	Type	M	Part No.	P.U.
90 V Hoods, size 48Ex	Housing, die cast zinc alloy			
Lateral cable entry M32				
with threaded collar	EX GOT GG 48 M32 09IA Z1	32	70.350.4836.1	1
with strain relief, IP54 → Ø 21 – 28.5 mm	EX GOT GG 48 M32 09IA Z3	32	70.350.4836.3	1
Lateral cable entry M40				
with threaded collar	EX GOT GG 48 M40 09IA Z1	40	70.353.4836.1	1
Top cable entry M32				
with threaded collar	EX GOT GI 48 M32 09IA Z1	32	70.352.4836.1	1
with strain relief, IP54 → Ø 21 – 28.5 mm	EX GOT GI 48 M32 09IA Z3	32	70.352.4836.3	1
Top cable entry M40				
with threaded collar	EX GOT GI 48 M40 09IA Z1	40	70.354.4836.1	1
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.

2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section “facts & DATA” for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I


BVS 03 **ATEX** 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000


Dimensions

Hoods

Lateral cable entry



Top cable entry



90 V Bases, single locking lever, Size 48Ex

90 V Bases Size 48Ex



open

without cover
with cover



closed

without cover
with cover



Description	Type	M	Part No.	P.U.
90 V Bases, size 48Ex	Housing, die cast zinc alloy			
Open-bottom base				
without cover	EX GUT GK48 09IA Z		70.320.2428.9	1
with metal cover	EX GUT GP48 09IA Z		70.325.2428.9	1
Closed-bottom base				
1 cable gland, left, 1 x M32				
without cover				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	BAS GUT GM 48 M32 09IA Z3	32	70.331.4836.3	1
with metal cover				
with strain relief, IP54 → Ø ← 21 – 28.5 mm	BAS GUT GS 48 M32 09IA Z3	32	70.341.4836.3	1
1 cable gland, left, 1 x M40				
with metal cover				
with cable gland, IP54, → Ø ← 27 – 37 mm	BAS GUT GR 48 M40 09IA Z3	40	70.344.4836.4	1
Technical data				
Material	Die cast zinc alloy			
Surface	silicon-free, light blue			
Locking levers	–			
Gasket	–			
Degree of protection				
with latched locking levers	IP54			
with appropriate cable glands	IP65			
Temperature range	-20 – +60 °C			
Contact inserts				
See the product matrix			Page 24–25	

Special conditions for safe use:

1. The heavy duty connectors must be attached to a device in such a way that a minimum protection rating of IP54 is maintained in accordance with EN 60529.
2. The plug connectors can be used in an ambient temperature ranges of -20 °C to +60 °C.

See section "facts & DATA" for handling and assembly of the multipole connectors.

0344  I M1 Ex ia I





BVS 03 ATEX 184 X

EN 60079-0:2006 EN 60079-11:2007 EN 50303:2000





Dimensions

Bases

open



closed



Multipole connector sets with 4 components screw connection 500 V / 16 A



Heavy duty connector kits, complete, consisting of:
male and female inserts, plugged together, loosely assembled into hoods and housings, and locked.



Screw connection



Screw connection

Housing	Number of poles	M	Part No.	P.U.	Female insert	Male insert	
Size 6	6-pole + ground	20	99.700.0000.6	1	●	●	
Size 10	10-pole + ground	20	99.701.0000.6	1	●	●	
Size 16	16-pole + ground	25	99.702.0000.6	1	●	●	
Size 24	24-pole + ground	25	99.703.0000.6	1	●	●	
Size 6	6-pole + ground	25	99.706.0000.6	1	●	●	
Size 10	10-pole + ground	25	99.707.0000.6	1	●	●	
Size 16	16-pole + ground	32	99.708.0000.6	1	●	●	
Size 24	24-pole + ground	32	99.709.0000.6	1	●	●	
Size 6	6-pole + ground	25	99.718.0000.6	1	●	●	
Size 10	10-pole + ground	25	99.719.0000.6	1	●	●	
Size 16	16-pole + ground	32	99.720.0000.6	1	●	●	
Size 24	24-pole + ground	32	99.721.0000.6	1	●	●	
Size 6	6-pole + ground	20	99.724.0000.6		●	●	
Size 10	10-pole + ground	20	99.725.0000.6	1	●	●	
Size 16	16-pole + ground	25	99.726.0000.6	1	●	●	
Size 24	24-pole + ground	25	99.727.0000.6	1	●	●	
For technical information see the individual components					70.300.xx40.0	70.310.xx.40.0	

● Part of the set belonging
to the order no.

xx = 06 for 6-pole
10 for 10-pole
16 for 16-pole
24 for 24-pole





With metric cable entry
on the side



With metric cable entry
on the top



Open



Closed,
with a metric cable entry

Hood	Hood	Bottom base	Bottom base
●		●	
●		●	
●		●	
●		●	
●		●	
●		●	
●		●	
●		●	
	●	●	
	●	●	
	●	●	
	●	●	
●			●
●			●
●			●
●			●
70.35x.xx35.0	70.352.xx35.0	70.320.xx28.0	70.331.xx35.0





***revos* accessories – all that you need**

We offer a wide range of accessories in our portfolio of heavy duty connectors, such as DIN rail mounting frames, knock-out cover plates, coding pins, cable glands, covers for our housings, labeling accessories, and the related tools.



Mounting frames for *revos* contact inserts



The mounting frames of the **revos** BASIC family are ideal for use in low-voltage switching systems. They are mounted directly to the 35x15 DIN rail according to DIN EN 50022 inside the control cabinet. Use of the DIN rail mounting frame on a 7.5 mm high DIN-rail 35 x 7.5 in accordance with DIN EN 50022 is only possible if the installation space behind it is free.

The system has the following advantages:

- Reduction of material and mounting costs
- Simple and trouble-free installation
- Wire harness assemblies possible
- Easy troubleshooting with hinged top that enables access to the back of the connector.
- Re-wiring is possible without disconnecting.

The robust contact inserts of the **revos** family in use worldwide are used for this purpose. The following contact inserts are available:

• **revos** BASIC
Size 6, 10, 16, 24

• **revos** POWER
Size 16, 24

• **revos** HD
40- and 64-pole

• **revos** FLEX
Size 6, 10, 16, 24

• **revos** BASIC EE
Size 6, 10, 16, 24

• **revos** DD
Size 6, 10, 16, 24

Mounting frames without contact inserts

Size 6





Description	Type	Part No.	P.U.
Mounting frame			
Size 6		Z5.574.0653.0	1
Size 10		Z5.574.1053.0	1
Size 16		Z5.574.1653.0	1
Size 24		Z5.574.2453.0	1
Size 2 x 6		Z5.574.1253.0	1
Technical data			
Installation	on TS 35x15 mounting rail		
Description	Type	Part No.	P.U.
Accessories			
Mounting frame with base plate and installation bolts for open-bottom bases Size 6/10/16		Z5.574.0053.0	1
Mounting frame with base plate and installation bolts for open-bottom bases Size 24		Z5.574.0153.0	1





Dimensions

Mounting frame

Size 6



Size 2 x 6



revos cover plates

Cover plates



Description	Type	Part No.	P.U.
Cover plates			
Size 6	Cover plate 6	07.416.6853.0	10
Size 10	Cover plate 10	07.416.6953.0	10
Size 16	Cover plate 16	07.416.7053.0	10
Size 24	Cover plate 24	07.416.7153.0	10
Technical data			
Material	Polyamide		
Color	RAL 7032		
Degree of protection	IP65		
Flammability	UL94-V0		

revos Cover plates are used to cover the cut-outs in partitions of control cabinets.



revos reducer plate

Reducer plate



Description	Type	Part No.	P.U.
Reducer plate			
GB 24/GB 6	Reduction plate 24 to 6	07.416.6353.0	10
GB 24/GB 10	Reduction plate 24 to 10	07.416.6453.0	10
GB 24/GB 16	Reduction plate 24 to 16	07.416.6553.0	10

Technical data

Material	Polyamide
Color	RAL 7032
Degree of protection	IP65
Flammability	UL94-V0

revos reducer plate adapt the cut-outs of size 24 to sizes 6, 10 or 16.



Coding of *revos* multipole connectors

Each family of contact inserts has its unique design. Mismatching of the different families' contact inserts is therefore impossible due to the design. However, if several connectors of the same size and family are mounted directly adjacent to one another, mismatching may occur during start-up of the machine or system.

Coding bolts of version A

Suitable for the following contact inserts / multipole adapters:

- **revos** BASIC
- **revos** POWER
- **revos** HD
- **revos** FLEX
- **revos** Ex

that are mounted to the housing at the **front**.

Suitable for:

- Screw termination inserts with part numbers:
70.2XX.XXXX.X
70.3XX.XXXX.X
70.4XX.XXXX.X
72.2XX.XXXX.X
72.3XX.XXXX.X
- Crimp termination inserts with part numbers:
70.7XX.XXXX.X
72.7XX.XXXX.X
73.7XX.XXXX.X
- Spring clamp termination inserts with part numbers:
70.5XX.XXXX.X
- Terminal block adapter inserts (mountable from the front) with part numbers:
70.7XX.XXXX.X
72.7XX.XXXX.X
73.7XX.XXXX.X

Coding options also exist for combinations of screw and crimp inserts and terminal block adapters.

In order to avoid mismatching we developed coding bolts, coding pins and female coding pieces that are to be assembled instead of the regular mounting screws of the contact inserts. Six different codings can be achieved when coding bolts are used.

Coding bolts of version B

Suitable for the following contact inserts / multipole adapters:

- **revos** BASIC
- **revos** POWER
- **revos** HD

that are mounted to the housing at the **rear**.

These are mainly multipole adapters that are mounted from the inside of the control cabinet.

Suitable for:


- Combination of screw, crimp, spring-type inserts and clamp adapters in connection with terminal block adapters (mountable from the back of the housing) with part numbers:
70.9XX.XXXX.X
72.9XX.XXXX.X
73.1XX.XXXX.X

Six coding options by means of locking pins

With the use of locking pins, there are a total of six combinations for 3, 6, 10, 16, 24-pin plug connectors

An additional six combinations are possible for the heavy duty connectors with two contact inserts (20, 26, 32 and 48-pin plug connectors).


One contact insert




- Coding bolt
- Mounting screws

ST Male connector
BU Female connector


Two contact inserts




Coding bolt  A B	Description	Part No.	P.U.
	Coding bolt		
	Version A	05.592.0621.0	100
	Version B	05.513.4212.0	100
	Technical data		
	Material	zinc-plated steel	
	Color	shiny metal	

Dimensions

Version A



Version B



Coding options for *revos* multipole connectors

72 coding options by means of coding pin,
coding key and coding socket

Part No. for Version A

Suitable for the following contact inserts/
multipole adapters:

revos BASIC, **revos** POWER, **revos** HD,

revos FLEX, **revos** Ex

that are mounted to the housing at the **front**.

Part No. for Version B

Suitable for the following contact inserts/
multipole adapters:

revos BASIC, **revos** POWER, **revos** HD







that are mounted to the housing at the **rear**.

The use of coding pins and female coding pieces
enables 16 different coding options.

With an additional coding bolt up to 72 coding
options are possible.

All mounting screws must be replaced by the coding
components.

With 15- or 25-pin plug connectors of the series
73.7 ... 16 coding options result, because the coding
pin cannot be used here.



Coding bolt, Coding pin
und Female coding piece




Description	Type	Part No.	P.U.
Version A			
Coding bolt		05.576.6912.0	50
Coding pin		05.576.6612.0	50
Female coding piece		05.576.6712.0	50
Version B			
Coding bolt		05.576.8512.0	50
Coding pin		05.576.8312.0	50
Female coding piece		05.576.8412.0	50


Technical data	
Material	zinc-plated steel
Color	shiny metal

Dimensions


Version A



Version B




Coding plan:




Example:



Coding between male
and female connector matching



Coding between the
coding bolts matching



Coding between the female connector
and the coding bolt not matching

Metric cable glands

Cable glands IP68, plastic



Description	Type			Part No.	P.U.
Cable glands plastic					
	Cable Ø [mm]	SW [mm]	l [mm]		
M20x1,5	6 – 12	24	9	Z5.507.1353.0	10
M25x1,5	7 – 16	28	11	Z5.507.1553.0	10
M32x1,5	10 – 21	36	11	Z5.507.1753.0	10
M40x1,5	16 – 28	46	11	Z5.507.1953.0	1
Technical data					
Material	Polyamide				
Color	RAL 7035				
Degree of protection	IP68				
Flammability	UL94-V0				

Cable glands IP68, metal



Description	Type			Part No.	P.U.
Cable glands metal					
	Cable Ø [mm]	SW [mm]	l [mm]		
M20x1,5	8 – 13	22	6	Z5.507.1321.0	10
M25x1,5	11 – 18	27	7	Z5.507.1521.0	10
M32x1,5	15 – 21	34	8	Z5.507.1721.0	10
M40x1,5	19 – 27	44	8	Z5.507.1921.0	1
Technical data					
Material	nickel-plated brass				
Color	-				
Degree of protection	IP68				
Flammability	-				


Cable glands EMC IP68, metal



Description	Type			Part No.	P.U.
Cable glands metal					
	Cable Ø [mm]	SW [mm]	l [mm]		
M20x1,5	8 – 13	22	6	Z5.507.4821.0	1
M25x1,5	11 – 18	30	7	Z5.507.5021.0	1
M32x1,5	15 – 21	34	8	Z5.507.5221.0	1
Technical data					
Material	nickel-plated brass				
Color	-				
Degree of protection	IP68				
Flammability	-				

Dimensions

Strain relief, IP54



Metric cable glands

Cable glands, IP54, with strain relief



Description	Type			Part No.	P.U.
Cable glands metal					
	Cable Ø [mm]	SW [mm]	l [mm]		
M20x1.5	8.5 – 14	24	6	Z5.507.5821.0	1
M25x1.5	12 – 20	34	7	Z5.507.6021.0	1
M32x1.5	18 – 28	42	8	Z5.507.6221.0	1
M40x1.5	24 – 34	52	8	on request	
Technical data					
Material	nickel-plated brass				
Color	-				
Degree of protection	IP54				
Flammability	-				

Bushing, IP54



Description	Type			Part No.	P.U.
Bushing metal					
	Cable Ø [mm]	SW [mm]	l [mm]		
M16x1.5	2 – 10.5	-	6	Z5.507.2121.0	1
M20x1.5	3 – 14.5	-	6	Z5.507.2221.0	1
M25x1.5	7.5 – 19	-	7	Z5.507.2321.0	1
M32x1.5	15 – 26.5	-	8	Z5.507.2421.0	1
Technical data					
Material	nickel-plated brass				
Color	-				
Degree of protection	IP54				
Flammability	-				


Strain relief, IP54




Description	Type			Part No.	P.U.
Cable glands metal					
	Cable Ø [mm]	SW [mm]	l [mm]		
M16x1.5	6 – 9	18	5	Z5.507.9521.0	10
M20x1.5	9 – 13.5	22	6	Z5.507.9621.0	10
M25x1.5	14 – 20	30	7	Z5.507.9721.0	10
M32x1.5	19 – 29	39	8	Z5.507.9821.0	10
Technical data					
Material	nickel-plated brass				
Color	-				
Degree of protection	IP54				
Flammability	-				

Dimensions


Cable glands, IP54, metal



Cable glands, IP54, with strain relief, metal



Strain relief, IP54, metal



Cable glands, Accessories

Reduction piece, nickel-plated brass



Description	Type	Part No.	P.U.
Reduction piece			
External thread [AG]	Internal thread [IG]	D [mm]	l [mm]
M20x1.5	M16x1.5	22	6
M25x1.5	M20x1.5	27	7
M32x1.5	M25x1.5	34	8
M40x1.5	M32x1.5	43	8
Technical data			
Material	nickel-plated brass		
Color	-		
Degree of protection	-		
Flammability	-		

Expansion piece, nickel-plated brass



Description	Type	Part No.	P.U.
Erweiterung			
External thread [AG]	Internal thread [IG]	D [mm]	l [mm]
M16x1.5	M20x1.5	22	5
M20x1.5	M25x1.5	27	6
M25x1.5	M32x1.5	34	7
M32x1.5	M40x1.5	43	8
Technical data			
Material	nickel-plated brass		
Color	-		
Degree of protection	-		
Flammability	-		

Adapter for PG-metric conversion



Description	Type	Part No.	P.U.
Adapter PG			
External thread [AG]	Internal thread [IG]	D [mm]	l [mm]
PG 13.5	M20x1.5	26	6.5
PG 16	M20x1.5	24	6.5
PG 21	M25x1.5	30	7
Technical data			
Material	nickel-plated brass		
Color	-		
Degree of protection	-		
Flammability	-		


Adapter for metric-PG conversion




Description	Type	Part No.	P.U.
Adapter metrisch			
External thread [AG]	Internal thread [IG]	D [mm]	l [mm]
M20x1.5	PG 13.5	22	6
M20x1.5	PG 16	24	6
M25x1.5	PG 21	30	7
M32x1.5	PG 29	39	8
Technical data			
Material	nickel-plated brass		
Color	-		
Degree of protection	-		
Flammability	-		

Dimensions

Reduction piece, nickel-plated brass




Expansion piece, nickel-plated brass



Adapter for PG-metric conversion



Adapter for metric-PG conversion



Cable glands, Accessories

Blind piece with gasket, brass




Description	Type			Part No.	P.U.
Blind piece brass					
Thread [AG]	D [mm]	l [mm]			
M20x1.5	22	6.5		Z5.507.4021.0	1
M25x1.5	28	7		Z5.507.4121.0	1
M32x1.5	35	8		Z5.507.4221.0	1
M40x1.5	44	8.5		on request	
Technical data					
Material	nickel-plated brass				
Color	Metalic				
Degree of protection	IP68				
Flammability	-				

Blind piece with gasket, plastic



Description	Type		Part No.	P.U.
Blind piece plastic				
Thread [AG]	D [mm]	l [mm]		
M20x1.5	24	6	Z5.507.4035.0	1
M25x1.5	30	7	Z5.507.4153.0	1
M32x1.5	38	8	Z5.507.4253.0	1
M40x1.5	48	9	Z5.507.4353.0	1
Technical data				
Material	Polyamide			
Color	gray, RAL 7035			
Degree of protection	IP68			
Flammability	UL94-V0			

Dimensions



Protective covers without locking levers for *revos* BASIC Housings

Protective covers without locking levers

Double locking lever

Size 10

without gasket with
tether cord and loop



Double locking lever

Size 16

without gasket with tether cord



Double locking lever

Size 10

with gasket




Description	Type	Part No.	P.U.
revos protective cover			
for single locking lever, without gasket			
Size 6	BAS AD DI 06	07.409.7056.0	10
Size 10	BAS AD DI 10	07.428.5553.0	10
Size 16	BAS AD DI 16	07.428.5653.0	10
Size 24	BAS AD DI 24	07.428.5753.0	10
with tether cord + loop			
Size 6	BAS AD DI 06 FSR	Z7.416.1556.0	10
for single locking lever, with gasket			
Size 6	BAS AD DB 06	Z7.427.8053.0	10
with tether cord + loop			
Size 6	BAS AD DJ 06 FSR	Z7.429.0453.0	10
for double locking lever, without gasket			
Size 10	BAS AD DA 10	07.409.7156.0	10
Size 16	BAS AD DA 16	07.409.7256.0	10
Size 24	BAS AD DA 24	07.409.7356.0	10
with tether cord			
Size 10	BAS AD DA 10 FS	Z7.409.8756.0	10
Size 16	BAS AD DA 16 FS	Z7.409.8856.0	10
Size 24	BAS AD DA 24 FS	Z7.409.8956.0	10
with tether cord + loop			
Size 10	BAS AD DA 10 FSR	Z7.409.1656.0	10
Size 16	BAS AD DA 16 FSR	Z7.409.1756.0	10
Size 24	BAS AD DA 24 FSR	Z7.409.1856.0	10
for double locking lever, with gasket			
Size 10	BAS AD DB 10	Z7.427.8153.0	10
Size 16	BAS AD DB 16	Z7.427.8253.0	10
Size 24	BAS AD DB 24	Z7.427.8353.0	10
with tether cord			
Size 10	BAS AD DB 10 FS	Z7.429.0153.0	10
Size 16	BAS AD DB 16 FS	Z7.429.0253.0	10
Size 24	BAS AD DB 24 FS	Z7.429.0353.0	10
with tether cord + loop			
Size 10	BAS AD DB 10 FSR	Z7.429.0553.0	10
Size 16	BAS AD DB 16 FSR	Z7.429.0653.0	10
Size 24	BAS AD DB 24 FSR	Z7.429.0753.0	10
Technical data			
Material/Gasket	Polyamide/NBR		
Color	silver gray, RAL 7001		
Degree of protection	IP65		
Flammability	UL94-V0		


Dimensions

Single locking lever without clamp

Size	L1 [mm]	L2 [mm]
6	62.5	75
10	75.5	90
16	96	110.5
24	122.5	137





tether cord




Double locking lever without clamp

Size	L3 [mm]
10	75.5
16	96
24	122.5



tether cord + loop



Protective covers with locking levers for *revos* BASIC Housings

Protective covers with locking levers

Double locking lever

Size 10


Plastic locking levers, with gasket



Double locking lever

Size 10

steel locking levers, with gasket



Double locking lever

Size 10

stainless steel locking levers, with gasket





Description	Type	Part No.	P.U.
revos protective cover for single locking lever, with gasket			
plastic locking levers			
Size 6	BAS AD DH 06 PA	Z7.428.1153.0	10
Size 10	BAS AD DH 10 PA	Z7.428.5553.0	10
Size 16	BAS AD DH 16 PA	Z7.428.5653.0	10
Size 24	BAS AD DH 24 PA	Z7.428.5753.0	10
steel locking levers			
Size 6	BAS AD DH 06 ST	Z7.428.1110.0	10
stainless steel locking levers			
Size 6	BAS AD DG 06 VA	Z7.428.1119.0	10
for single locking lever, without gasket			
plastic locking levers			
Size 6	BAS AD DG 06 PA	Z7.428.1553.0	10
steel locking levers			
Size 6	BAS AD DG 06 ST	Z7.428.1510.0	10
stainless steel locking levers			
Size 6	BAS AD DG 06 VA	Z7.428.1519.0	10
for double locking lever, with gasket			
plastic locking levers			
Size 10	BAS AD DD 10 PA	Z7.428.1253.0	10
Size 16	BAS AD DD 16 PA	Z7.428.1353.0	10
Size 24	BAS AD DD 24 PA	Z7.428.1453.0	10
steel locking levers			
Size 10	BAS AD DD 10 ST	Z7.428.1210.0	10
Size 16	BAS AD DD 16 ST	Z7.428.1310.0	10
Size 24	BAS AD DD 24 ST	Z7.428.1410.0	10
stainless steel locking levers			
Size 10	BAS AD DD 10 VA	Z7.428.1219.0	10
Size 16	BAS AD DD 16 VA	Z7.428.1319.0	10
Size 24	BAS AD DD 24 VA	Z7.428.1419.0	10
for double locking lever, without gasket			
plastic locking levers			
Size 10	BAS AD DC 10 PA	Z7.428.1653.0	10
Size 16	BAS AD DC 16 PA	Z7.428.1753.0	10
Size 24	BAS AD DC 24 PA	Z7.428.1853.0	10
steel locking levers			
Size 10	BAS AD DC 10 ST	Z7.428.1610.0	10
Size 16	BAS AD DC 16 ST	Z7.428.1710.0	10
Size 24	BAS AD DC 24 ST	Z7.428.1810.0	10
stainless steel locking levers			
Size 10	BAS AD DC 10 VA	Z7.428.1619.0	10
Size 16	BAS AD DC 16 VA	Z7.428.1719.0	10
Size 24	BAS AD DC 24 VA	Z7.428.1819.0	10
Technical data			
Material/Gasket	Polyamide/NBR		
Color	silver gray, RAL 7001		
Degree of protection	IP65		
Flammability	UL94-V0		

Dimensions



Single locking lever with clamp, plastic

Size	L1 [mm]	L2 [mm]
6	62.5	75
10	75.5	90
16	96	110.5
24	122.5	137



Double locking lever with clamp, plastic

Size	L3 [mm]	L4 [mm]
10	75.5	119
16	96	140
24	122.5	166



Protective cover for *revos* BASIC Housings Size 32

Protective covers without locking levers, without gasket




Protective covers with locking levers, with gasket




Description	Type	Part No.	P.U.
revos protective cover with tether cord + loop without locking levers, without gasket			
Size 32	BAS AD DA 32 FS ST	Z7.419.6228.0	10
with locking levers, with gasket			
Size 32	BAS AD DD 32 FS ST	Z7.419.6128.0	10
Technical data			
Material	Die cast aluminum		
Surface	Silicon-free		
Locking levers	Zinc-plated steel		
Gasket	NBR		
Degree of protection	IP65		

Dimensions

Protective covers without locking levers



Protective cover with locking levers




Protective cover for *revos* BASIC Housings Size 6–24

Protective cover latchable	Description	Type	Part No.	P.U.
	Protective cover rastbar			
	Size 6/6H	BAS AD DK 06	Z7.409.7056.0	10
	Size 10/10H	BAS AD DL 10	Z7.409.7156.0	10
	Size 16/16H	BAS AD DL 16	Z7.409.7256.0	10
	Size 24/24H	BAS AD DL 24	Z7.409.7356.0	10
	Technical data			
	Material	Polyamide		
	Color	RAL 7001		
	Degree of protection	-		
	Flammability	-		

Dimensions

Protective cover latchable




Protective cover for *revos* MINI Housings

Protective cover without gasket	Description	Type	Part No.	P.U.
	Protective cover for <i>revos</i> MINI Housings without gasket for male insert			
	plastic	MIN AD DA 7 P	07.417.6753.0	10
	Metal	MIN AD DA 7 Z	07.417.6729.0	10
	with gasket for female insert			
	plastic	MIN AD DB 7 P	07.417.6853.0	10
	Metal	MIN AD DB 7 Z	07.417.6829.0	10
	Technical data			
	Material	Die cast zinc alloy/Polyamide		
	Surface	Silicon-free		
	Locking levers	-		
	Gasket	NBR		
	Degree of protection	IP65		

Dimensions

Protective cover



Tools and Accessoires

Crimping tool kit



Description	Type	Part No.	P.U.
Crimping tool for <i>revos</i> contacts			
Crimping tool without crimping die and positioner		95.101.0800.0	1
Accessoires for crimping tool			
Crimping die			
Crimping die "A"		05.502.2000.0	1
Crimping die "B"		05.502.2100.0	1
Crimping die "C"		05.502.2200.0	1
Crimping die "D"		05.502.2300.0	1
Crimping die "E"		05.502.2400.0	1
Contact positioner			
Contact positioner 1		05.502.3100.0	1
Contact positioner 2		05.502.3200.0	1
Contact positioner 3		05.502.3300.0	1
Contact positioner 4		05.502.3800.0	1

For assignment of contacts to crimping tool see page 295.

Stripping tool



Description	Type	Part No.	P.U.
Tool			
Stripping tool	0.08 – 10mm ² / 28 – 7 AWG	95.350.0100.0	1


Screwdriver



Description	Type	Part No.	P.U.
Tool			
Screwdriver	Blade 0.6x3.5 form "B"	06.502.4000.0	5

For use with contact inserts and multipole adapters with spring clamp connection

Jumper bar for *revos* BASIC multipole adapters



Description	Type	Part No.	P.U.
Jumper bar for <i>revos</i> BASIC multipole adapters			
Insulated jumper bar			
Number of poles			
2-pole		Z7.256.0227.0	10
3-pole		Z7.256.0327.0	10
4-pole		Z7.256.0427.0	10
5-pole		Z7.256.0527.0	10
6-pole		Z7.256.0627.0	10
7-pole		Z7.256.0727.0	10
8-pole		Z7.256.0827.0	10
9-pole		Z7.256.0927.0	10
10-pole		Z7.256.1027.0	10
11-pole		Z7.256.1127.0	10
12-pole		Z7.256.1227.0	10
Technical data			
Material	Polyamide		
Rated voltage	500 V		
Rated current	16 A		

Jumper bar for *revos* HD multipole adapters



Description	Type	Part No.	P.U.
Jumper bar for <i>revos</i> HD multipole adapters			
Insulated jumper bar			
Number of poles			
2-pole		Z7.258.1225.0	10
3-pole		Z7.258.1325.0	10
4-pole		Z7.258.1425.0	10
5-pole		Z7.258.1525.0	10
6-pole		Z7.258.1625.0	10
7-pole		Z7.258.1725.0	10
8-pole		Z7.258.1825.0	10
9-pole		Z7.258.1925.0	10
10-pole		Z7.258.2025.0	10
Technical data			
Material	Polyamide		
Rated voltage	250 V		
Rated current	10 A		

Marking tag carriers

Marking tag carriers for multipole adapters



Description	Type	Part No.	P.U.
Marking tag carriers, complete			
40-pole		Z4.242.3753.0	10
64-pole		Z4.242.4053.0	10
Marking tags			
Single tag, max. 3-digits			
unmarked marking field 8.3x4.5 mm	9705 A	04.242.0850.0	500
marked marking field 8.3x4.5 mm	9705 A B	04.842.0850.0	500
Single tag, max. 8-digits			
unmarked marking field 14x4.5 mm	9705 AL	04.242.1553.0	500
marked marking field 14x4.5 mm	9705 AL B	04.842.1553.0	500
Marking strip with 12 tags, 6.7 mm spacing			
unmarked marking field 8.3x6.45 mm	9705A/6.7/12	04.242.6753.0	25
marked Please indicate the required	9705A/6.7/12 B	04.842.6753.0	25
marked 1 – 9	9705A/6.7/12 B 1- 9	99.000.0920.8	25
Marking strip with 12 tags, 6.7 mm spacing			
6-pole marked 1 – 6	9705A/6.7/2X 6 B 1- 6	99.002.0920.8	25
10-pole marked 1 – 10	9705A/6.7/12 B 1-10	99.003.0920.8	25
16-pole marked 1 – 16	9705A/6.7/2X12 B 1-16	99.004.0920.8	25
24-pole marked 1 – 24	9705A/6.7/2X12 B 1-24	99.005.0920.8	25

45° Marking tag carrier



Description	Type	Part No.	P.U.
Marking tag carriers			
2x4-digits, 45°	9705 A/4 W	04.242.2853.0	200
Marking tags			
Single tag, max. 3-digits			
unmarked marking field 8.3x4.5 mm	9705 A	04.242.0850.0	500
marked marking field 8.3x4.5 mm	9705 A B	04.842.0850.0	500
Single tag, max. 8-digits			
unmarked marking field 14x4.5 mm	9705 AL	04.242.1553.0	500
marked marking field 14x4.5 mm	9705 AL B	04.842.1553.0	500
Marking strip with 12 tags, 6.7 mm spacing			
unmarked marking field 8.3x6.45 mm	9705A/6.7/12	04.242.6753.0	25
marked Please indicate the required	9705A/6.7/12 B	04.842.6753.0	25
marked 1 – 9	9705A/6.7/12 B 1- 9	99.000.0920.8	25
Marking strip with 12 tags, 6.7 mm spacing			
6-pole marked 1 – 6	9705A/6.7/2X 6 B 1- 6	99.002.0920.8	25
10-pole marked 1 – 10	9705A/6.7/12 B 1-10	99.003.0920.8	25
16-pole marked 1 – 16	9705A/6.7/2X12 B 1-16	99.004.0920.8	25
24-pole marked 1 – 24	9705A/6.7/2X12 B 1-24	99.005.0920.8	25

90° Marking tag carrier



Description	Type	Part No.	P.U.
Marking tag carriers			
6-digits, 90°	9705 A/6.7/6-90GRAD	04.242.3053.0	200
complete for			
6-pole multipole adapters	9705 A/6.7/9-90GRAD 3	04.242.3353.0	50
10-pole multipole adapters	9705 A/6.7/6-90GRAD 5	04.242.3453.0	50
16-pole multipole adapters	9705 A/6.7/6-90GRAD 8	04.242.3553.0	25
24-pole multipole adapters	9705 A/6.7/6-90GRAD12	04.242.3653.0	25
Marking tags			
Single tag, max. 3-digits			
unmarked marking field 8.3x4.5 mm	9705 A	04.242.0850.0	500
marked marking field 8.3x4.5 mm	9705 A B	04.842.0850.0	500
Single tag, max. 8-digits			
unmarked marking field 14x4.5 mm	9705 AL	04.242.1553.0	500
marked marking field 14x4.5 mm	9705 AL B	04.842.1553.0	500
Marking strip with 12 tags, 6.7 mm spacing			
unmarked marking field 8.3x6.45 mm	9705A/6.7/12	04.242.6753.0	25
marked Please indicate the required	9705A/6.7/12 B	04.842.6753.0	25



Marking tags

Tear-off marking strip



Description	Contents	Type	Part No.	P.U.
Marking tags-Ast				
unmarked		9704 A	04.241.1150.0	25
marked with the same number				
	10x “1”	9704 A/1 B	04.841.1150.0	25
	10x “2”	9704 A/2 B	04.841.1250.0	25
	10x “3”	9704 A/3 B	04.841.1350.0	25
	10x “4”	9704 A/4 B	04.841.1450.0	25
	10x “5”	9704 A/5 B	04.841.1550.0	25
	10x “6”	9704 A/6 B	04.841.1650.0	25
	10x “7”	9704 A/7 B	04.841.1750.0	25
	10x “8”	9704 A/8 B	04.841.1850.0	25
	10x “9”	9704 A/9 B	04.841.1950.0	25
	10x “0”	9704 A/0 B	04.841.2050.0	25
marked with consecutive numbers	1 2 3 4 5 6 7 8 9 0	9704 A/1-0 B	04.841.2150.0	25
marked with the same uppercase letters				
	10x “A”	9704 A/AG B	04.841.2250.0	25
	10x “B”	9704 A/BG B	04.841.2350.0	25
	10x “C”	9704 A/CG B	04.841.2450.0	25
	10x “D”	9704 A/DG B	04.841.2550.0	25
	10x “E”	9704 A/EG B	04.841.2650.0	25
	10x “F”	9704 A/FG B	04.841.2750.0	25
	10x “G”	9704 A/GG B	04.841.2850.0	25
	10x “H”	9704 A/HG B	04.841.2950.0	25
	10x “I”	9704 A/IG B	04.841.3050.0	25
	10x “J”	9704 A/JG B	04.841.3150.0	25
	10x “K”	9704 A/KG B	04.841.3250.0	25
	10x “L”	9704 A/LG B	04.841.3350.0	25
	10x “M”	9704 A/MG B	04.841.3450.0	25
	10x “N”	9704 A/NG B	04.841.3550.0	25
	10x “O”	9704 A/OG B	04.841.3650.0	25
	10x “P”	9704 A/PG B	04.841.3750.0	25
	10x “Q”	9704 A/QG B	04.841.3850.0	25
	10x “R”	9704 A/RG B	04.841.3950.0	25
	10x “S”	9704 A/SG B	04.841.4050.0	25
	10x “T”	9704 A/TG B	04.841.4150.0	25
	10x “U”	9704 A/UG B	04.841.4250.0	25
	10x “V”	9704 A/VG B	04.841.4350.0	25
	10x “W”	9704 A/WG B	04.841.4450.0	25
	10x “X”	9704 A/XG B	04.841.4550.0	25
	10x “Y”	9704 A/YG B	04.841.4650.0	25
	10x “Z”	9704 A/ZG B	04.841.4750.0	25



Marking tags

Tear-off marking strip



Description	Contents	Type	Part No.	P.U.
marked with the same lowercase letters				
	10x “a”	9704 A/AK B	04.841.4850.0	25
	10x “b”	9704 A/BK B	04.841.4950.0	25
	10x “c”	9704 A/CK B	04.841.5050.0	25
	10x “d”	9704 A/DK B	04.841.5150.0	25
	10x “e”	9704 A/EK B	04.841.5250.0	25
	10x “f”	9704 A/FK B	04.841.5350.0	25
	10x “g”	9704 A/GK B	04.841.5450.0	25
	10x “h”	9704 A/HK B	04.841.5550.0	25
	10x “i”	9704 A/IK B	04.841.5650.0	25
	10x “j”	9704 A/JK B	04.841.5750.0	25
	10x “k”	9704 A/KK B	04.841.5850.0	25
	10x “l”	9704 A/LK B	04.841.5950.0	25
	10x “m”	9704 A/MK B	04.841.6050.0	25
	10x “n”	9704 A/NK B	04.841.6150.0	25
	10x “o”	9704 A/OK B	04.841.6250.0	25
	10x “P”	9704 A/PK B	04.841.6350.0	25
	10x “q”	9704 A/QK B	04.841.6450.0	25
	10x “r”	9704 A/RK B	04.841.6550.0	25
	10x “s”	9704 A/SK B	04.841.6650.0	25
	10x “t”	9704 A/TK B	04.841.6750.0	25
	10x “u”	9704 A/UK B	04.841.6850.0	25
	10x “v”	9704 A/VK B	04.841.6950.0	25
	10x “w”	9704 A/WK B	04.841.7050.0	25
	10x “x”	9704 A/XK B	04.841.7150.0	25
	10x “y”	9704 A/YK B	04.841.7250.0	25
	10x “z”	9704 A/ZK B	04.841.7350.0	25
marked with the same symbols				
	10x “+”	9704 A/+ B	04.841.7450.0	25
	10x “-”	9704 A/- B	04.841.7550.0	25
	10x “/”	9704 A// B	04.841.7650.0	25
	10x “.”	9704 A/. B	04.841.7750.0	25
Large packs				
Same numbers = 10 x 25 strips = 2500 tags	1 1 1 ... 0 0 0	111..BIS 000..	04.841.9050.0	1
Uppercase letters = 26 x 25 strips = 6500 tags	A A A ... Z Z Z	A BIS Z GB	04.841.9150.0	1
Lowercase letters = 26 x 25 strips = 6500 tags	a a a ... z z z	A BIS Z KB	04.841.9250.0	1






revos facts&DATA

On the following pages, you will find all important information on our **revos** products.

But our Wieland customer service team is also happy to help you, at telephone number +49 951 9324-991.

We look forward to hearing from you.



Conductor connections

Rated connection capacity and suitable conductor

Table 1: (EN 60 999-1: 2000): Relationship between rated connection capacity and diameter of the conductor

Rated connection capacity	Theoretical diameter of the largest conductor							Connectable conductor	
	Metric			AWG					
	Rigid		Flexible	Rigid		Flexible		Rigid	Flexible
	Solid	Multistrand			Solid	Multistrand	Multistrand	Must be set in the relevant product standard	
mm²	mm	mm	mm	Conductor size	mm	mm	mm		
0.2	0.51	0.53	0.61	24	0.54	0.61	0.64		
0.34	0.63	0.66	0.8	22	0.68	0.71	0.80		
0.5	0.9	1.1	1.1	20	0.85	0.97	1.02		
0.75	1.0	1.2	1.3	18	1.07	1.23	1.28		
1.0	1.2	1.4	1.5	-	-	-	-		
1.5	1.5	1.7	1.8	16	1.35	1.55	1.60		
2.5	1.9	2.2	2.3 a)	14	1.71	1.95	2.08		
4.0	2.4	2.7	2.9 a)	12	2.15	2.45	2.70		
6.0	2.9	3.3	3.9 a)	10	2.72	3.09	3.36		
10.0	3.7	4.2	5.1	8	3.34	3.89	4.32		
16.0	4.6	5.3	6.3	6	4.32	4.91	5.73		
25.0	-	6.6	7.8	4	5.45	6.18	7.26		
35	-	7.9	9.2	2	6.87	7.78	9.02		
					b)	b) / Class B	c) / Class I, K, M		

Note: The diameters of the largest rigid and flexible conductors are based on Table 1 in accordance with IEC 60 228A and IEC 30 344 and for AWG conductors on ASTM B 172-71 [4], ICEA Publication S-19-81 [5], ICEA Publication S-66-524 [6], and ICEA Publication S-66-516 [7]

^{a)} Dimensions only for flexible cables of class 5 in accordance with IEC 60 228A.

^{b)} Nominal diameter + 5%

^{c)} Largest diameter for each of the three classes I, K, M, + 5%

Theoretical diameter of the largest conductor and relationship between rated cross section and connectable conductors

Table 2: (EN 60 999-2: 2003): Relationship between rated cross section and diameter of the conductors

Rated cross section	Theoretical diameter of the largest conductor		Connectable conductor	
	Metric			
	Rigid	Flexible ^{a)}	Rigid	Flexible
	Multistrand		Must be set in the relevant product standard	
mm²	mm	mm		
50	9.1	11.0		
70	11.0	13.1		
95	12.9	15.1		
-	-	-		
120	14.5	17.0		
150	16.2	19.0		
185	18.0	21.0		
-	-	-		
240	20.6	24.0		
300	23.1	27.0		

Note: The diameters of the largest rigid and flexible conductors are based on Table 1 and Table 3 of IEC 60 228A.

^{a)} Dimensions only for flexible conductors of class 5 in accordance with IEC 60 228A.

Conductor connections

Standard cross sections of round copper conductors AWG/metric

Metric size ISO	Comparison between AWG/kcmil and metric sizes		
mm ²	AWG	kcmil	mm ²
0.1 *	28		0.081
0.14 *	26		0.128
0.2	24		0.205
-	22		0.324
0.5	20		0.519
0.75	18		0.82
1	-		-
1.5	16		1.3
2.5	14		2.1
4	12		3.3
6	10		5.3
10	8		8.4

Metric size ISO	Comparison between AWG/kcmil and metric sizes		
mm ²	AWG	kcmil	mm ²
16	6		13.3
25	4		21.2
.5	2		33.6
50	(1/0)	0	53.5
70	(2/0)	00	67.4
95	(3/0)	000	85
-	(4/0)	0000	107.2
120		250	127
150		300	152
185		350	177
240		500	253
300		600	304

* not standardized

Composition and dimensions of single, multi, fine and extra-fine-wire conductors made of copper

Extract from DIN VDE 0295 (06.92)

Nominal cross section	Solid		Multistrand		Fine strand	
	Maximum dimension diameter	Number of wires	Maximum dimension diameter	Number of wires	Maximum dimension diameter	Reference number of wires
mm ²		mm	-	mm		
0.5	0.9	1	-	-	1.1	16
0.75	1.0	1	-	-	1.3	24
1	1.2	1	-	-	1.5	32
1.5	1.5	1	-	-	1.8	30
2.5	1.9	1	-	-	2.3	50
4	2.4	1	-	-	2.9	56
6	2.9	1	-	-	3.9	84
10	3.7	1	4.2	7	5.1	80
16	4.6	1	5.3	7	6.3	126
25	-	-	6.6	7	7.8	196
35	-	-	7.9	7	9.2	276
50	-	-	9.1	19	11	396
70	-	-	11	19	13.1	360
95	-	-	12.9	19	15.1	475
120	-	-	14.5	37	17	608
150	-	-	16.2	37	19	756
185	-	-	18	37	21	925
240	-	-	20.6	61	24	1224

Current load capacity of cables or lines

Recommended values for current load capacity of cables or lines for fixed installation and open-air installation should be taken from DIN VDE 0298 Part4/08.2003

Current load capacity

Current load capacity of terminal blocks

(for terminal blocks) For copper conductors, the following tables apply:

Test current in accordance with DIN EN 60 947-7-1/VDE 0611 Part: 07.2003

Table 4: Value of the test current for heating, aging and voltage drop test for metric conductor sizes

Rated cross section mm ²	0.2	0.34	0.5	0.75	1	1.5	2.5	4	6	10	16
Test current A	4	5	6	9	13.5	17.5	24	32	41	57	76

Rated cross section mm ²	25	35	50	70	95	120	150	185	240	300
Test current A	101	125	150	192	232	269	309	353	415	520

The rated cross section of a terminal block is the manufacturer-specified value of the connectable conductor cross section to which specific thermal, mechanical and electrical requirements refer.

The rated connection capacity of a terminal block is a range and/or number of rated cross sections that the terminal block is intended for; it is specified individually for each terminal. The conductors can be rigid (solid or multistranded) or flexible. The specifications refer to unprepared conductor ends without ferrules and comprise the largest and smallest connectable conductor cross section. In general, two conductors of the same cross section and structure can be connected.

For terminal blocks with additional function, the rated current is established by the manufacturer according to the requirements of the additional function. Additional functions can be given by plug connections, disconnection points, fuses, relays or electronic components. The current load capacity of other terminals is established and evaluated based on the above determinations or in accordance with EN 60 999/VDE 0609 Part 1 or EN 60 998-1/VDE 0613 Part 1 or EN 60 335-1/DIN VDE 0700 Part 1, if applicable.

The current load capacity for plug connectors is determined and established based on DIN EN 61 984/VDE 0627: 09.2002 and

DIN EN 175 301-801: 09.2000, if applicable. The revos plug connectors must not be manipulated when under load.

Tightening torque

Tightening torque of screw connections

Extract from EN 60 947-1

Tightening torque for proving the mechanical tightness of screw connections

Table 4: Tightening torques for proving the mechanical tightness of screw connections/terminals

Thread diameter		Tightening torque (Nm)		
Metric standard values	Diameter range	I	II	III
1.6	1.6	0.05	0.1	0.1
2.0	1.6 to 2.0	0.1	0.2	0.2
2.5	2.0 to 2.8	0.2	0.4	0.4
3.0	2.8 to 3.0	0.25	0.5	0.5
-	3.0 to 3.2	0.3	0.6	0.6
3.5	3.2 to 3.6	0.4	0.8	0.8
4	3.6 to 4.1	0.7	1.2	1.2
4.5	4.1 to 4.7	0.8	1.8	1.8
5	4.7 to 5.3	0.8	2.0	2.0
6	5.3 to 6.0	1.2	2.5	3.0
8	6.0 to 8.0	2.5	3.5	6.0
10	8.0 to 10.0	-	4.0	10.0
12	10 to 12	-	-	14.0
14	12 to 15	-	-	19.0
16	15 to 20	-	-	25.0
20	20 to 24	-	-	36.0
24	24	-	-	50.0

Column I: Applies for screws without heads that do not protrude from the thread hole and for screws that can only be tightened with screwdrivers with an edge narrower than the screw's thread core diameter.

Column II: Applies for nuts and screws that are tightened with screwdrivers.

Column III: Applies for nuts and screws that can be tightened with tools other than screwdrivers.

Explanations of applications in hazardous areas

revos -multipole connectors are designed for special applications in hazardous areas. Their use in zone 0 for intrinsic circuits has been approved by the DEKRA EXAM test institute. The housings for the multipole connectors are manufactured from die cast zinc alloy.

Operating instructions for the connector series „revos Ex...”

A pluggable connection consists of a hood, a base as well as a female and male insert.

Installation of a pluggable connection must be prepared as follows:

- Closed bottom housings must be fixed with screws to a flat surface using the available bore holes.
- Open-bottom housings must be fixed with screws to a flat surface using the available bore holes.
Before fixing the housing to the surface, ensure that the seal fixed to the base at the time of delivery is mounted correctly.
- The female insert and male insert must be screwed into the hood (or alternatively screwed into the base) using the screws already attached to the frame of the male or female connector.
- The cables are connected to the male connectors and female connectors using the screw connection with a torque of 0.5 Nm.

The components are made ready for operation by plugging the hood and base together and latching them.

The relevant connectors must be mounted to device in a way that at least protection degree IP 54 according to EN 60529 is ensured.

The „revos Ex” connectors are designed for use in an ambient temperature range at installation site of –20°C bis +60°C.

Usage note:

The “revos Ex” plug connector series can be used with a rated voltage of 90 V and a permissible cable cross-section of 0.5 mm² to 2.5 mm² for the following application areas according to ATEX directive 94/9/EC and the EN 60079-0:2006, EN 60079-11:2007 and EN 50303:2000 standards:

 **I M1 Ex ia I**

Proof is provided by the marking of the Ex area on the individual components of the connector.

Permissible conductor cross section: 1.5 mm ² to	2.5 mm ²	to	16 A
	1.0 mm ²	to	10 A
	0.75 mm ²	to	6 A
	0.5 mm ²	to	3 A



EG-Baumusterprüfbescheinigung

- (1) - Richtlinie 94/9/EG -
(2) Geräte und Schutzsysteme zur bestimmungsgemäßen Verwendung in explosionsgefährdeten Bereichen

BVS 03 ATEX E 184 X

- (3) **Gerät:** Steckverbinderreihe revos Typ Ex**
(4) **Hersteller:** Wieland Electric GmbH
(5) **Anschrift:** D - 96052 Bamberg

- (7) Die Bauart dieses Gerätes sowie die verschiedenen zulässigen Ausführungen sind in der Anlage zu dieser Baumusterprüfbescheinigung festgelegt.
(8) Die Zertifizierungsstelle der Deutsche Montan Technologie GmbH, benannte Stelle Nr. 0158 gemäß Artikel 9 der Richtlinie 94/9/EG des Europäischen Parlaments und des Rates vom 23. März 1994, bescheinigt, dass das Gerät die grundlegenden Sicherheits- und Gesundheitsanforderungen für die Konzeption und den Bau von Geräten und Schutzsystemen zur bestimmungsgemäßen Verwendung in explosionsgefährdeten Bereichen gemäß Anhang II der Richtlinie erfüllt.
Die Ergebnisse der Prüfung sind in dem Prüfprotokoll BVS PP 03.1081 EG
(9) Die grundlegenden Sicherheits- und Gesundheitsanforderungen werden erfüllt.
EN 50014:1997+A1+A2 Allgemeine Bestimmungen
EN 50020:1994 Eigensicherheit
(10) Falls das Zeichen „X“ hinter der Bescheinigungsnummer steht, wird in besonderen Bedingungen für die sichere Anwendung des Gerätes hingewiesen.
(11) Diese EG-Baumusterprüfbescheinigung bezieht sich nur auf die in der Bescheinigung beschriebenen Geräte in Übereinstimmung mit der Richtlinie 94/9/EG. Für Herstellung und in Verkehr bringen des Gerätes sind weitere Anforderungen nicht durch diese Bescheinigung abgedeckt sind.
(12) Die Kennzeichnung des Gerätes muss die folgenden Angaben enthalten:

Ex I M2 EEx ia I

Deutsche Montan Technologie GmbH
Bochum, den 19. August 2003

Ulrich
Zertifizierungsstelle

Seite 1 von 2 zu BVS 03 X
Dieses Zertifikat darf nur unverändert weitergegeben werden.
Dienstadtstraße 9 44809 Bochum Telefon +Phone +Fax
(bis 31.05.2007) Deutsche Montan Technologie GmbH



2. Nachtrag

(Ergänzung gemäß Richtlinie 94/9/EG Anhang III Ziffer 6)
zur EG-Baumusterprüfbescheinigung
BVS 03 ATEX E 184 X

- Gerät:** Steckverbinderreihe revos Typ Ex**
Hersteller: Wieland Electric GmbH
Anschrift: 96052 Bamberg

Beschreibung

Der Grund für die Ausstellung dieses Nachtrages ist die Bestätigung der Übereinstimmung dieses Gerätes mit dem Normenstand der EN 60079-0:2006, EN 60079-11:2007 und EN 50303:2000, sowie die Änderung der Gerätekategorie auf M1.
Bei der Steckverbinderreihe revos Typ Ex** in 6-, 10-, 16-, 24-, und 48-poliger Ausführung handelt es sich um Rechteck-Steckverbinder in Schraubanschlussstechnik mit einem Bemessungsanschlussvermögen von 0,5 - 2,5mm², die ein Anschließen und Verbinden von ein- bzw. feindrähtigen Leitern ermöglicht. Die Gehäuseober- und -unterteile sind wahlweise sowohl mit Einhandverriegelung als auch mit Zweihandverriegelung ausgeführt und je nach Verwendung zum Geräteanbau, -einbau oder als freie Kabelverbindung einsetzbar.
Der Steckverbinder enthält nur Bauteile, die die Zündschutzart Eigensicherheit nicht beeinträchtigen. Aufgrund der Bauart sind die unterschiedlichen eigensicheren Stromkreise untereinander bis zu einer Summe der Scheitelwerte der Bemessungsspannungen von 90 V sicher getrennt.
Die grundlegenden Sicherheits- und Gesundheitsanforderungen der geänderten Ausführung werden erfüllt durch Übereinstimmung mit:

EN 60079-0:2006 Allgemeine Anforderungen
EN 60079-11:2007 Eigensicherheit
EN 50303:2000 M1 Betriebsmittel


Die Kennzeichnung des Gerätes muss die folgenden Angaben enthalten:

Ex I M1 Ex ia I


DEKRA EXAM GmbH
Dienstadtstraße 9 44809 Bochum Telefon +Phone +Fax
(bis 31.05.2007) EXAM BSG Prüf- und Zertifikatsstelle
Seite 1 von 2 zu BVS 03 ATEX E 184 X / M1
Dieses Zertifikat darf nur unverändert weitergegeben werden.
Telefon 0234/5996-150 E-mail 29-exam@dekra.com

revos BASIC single locking lever

Installation spacing and mounting dimensions




Minimum installation spacing for
revos BASIC open-bottom bases




Mounting diagram for revos BASIC
open-bottom bases of size 6 to 48

Size		6	10	16	24	48
Cut-out	L1	52	65	85.5	112	117
	L2	35	35	35	35	81
	L3	70	83	103	130	148
Installation spacing	L4	32	32	32	32	70
	d1	4.3	4.3	4.3	4.3	6.4
	M	M4	M4	M4	M4	M6



Minimum installation spacing for revos BASIC
closed-bottom bases of size 6 to 24

Size		6	10	16	24
Installation spacing	A1	50	50	45	45
	A2	51	51	46	46





Mounting diagram for revos BASIC
closed-bottom bases of size 6 to 48

Size		6	6H	10	10H	16	24	48
Installation spacing	L3	70	70	82	82	105	132	111
	L4	40	45	40	45	45	45	106
	d1	5.3	5.5	5.3	5.5	5.3	5.3	6.5
	M	M5	M5	M5	M5	M5	M5	M6

revos BASIC double locking lever


Installation spacing and mounting dimensions

Minimum installation spacing for **revos** BASIC open-bottom bases of size 10 to 24



Mounting diagram for **revos** BASIC open-bottom bases of size 10 to 32


Size		10	16	24	32
Cut-out	L1	65	85.5	112	86
	L2	35	35	35	71
Installation spacing	L3	83	103	130	110
	L4	32	32	32	65
Minimum Montageabstand	X1	121	139	166	
	d1	4.3	4.3	4.3	5.5
	M1	M4	M4	M4	M5



Mounting diagram for **revos** BASIC open-bottom bases of size 10 to 24

Size		10	10H	16	24
Befestigungsabstände	L3	82	82	105	132
	L4	40	45	45	45
	d1	5.5	5.5	5.5	5.5
	M1	M5	M5	M5	M5

EMC housings, cut-out and mounting dimensions




Mounting diagram for **revos** EMC open-bottom bases of size 6 to 24

Size		6	10	16	24
Cut-out	L1	52	65	85.5	112
	L2	35	35	35	35
Installation spacing	L3	70	83	103	130
	L4	32	32	32	32
	d1	4.3	4.3	4.3	4.3
	M1	M4	M4	M4	M4


revos HD

Housing line, cut-outs and mounting dimensions



Mounting diagram for **revos** HD open-bottom bases of size 10/15, 16/25 and 32/50

Size		10/15	16/25	32/50
Cut-out	L1	56	72	82
	L2	23	23	49
Installation spacing	L3	70	86	92
	L4	17.5	17.5	42
	d1	3.3	3.3	4.3
	M1	M3	M3	M4



Mounting diagram for **revos** HD closed-bottom bases of size 10/15, 16/25 and 32/50



Size		10/15	16/25	32/50
Installation spacing	L3	48	64	94
	L4	40	40	46
	d1	4.3	4.3	4.3
	M1	M4	M4	M4

Installation example for *revos*

Multipole hoods for cable-to-cable couplings

Size	Thread	Hood Pos. 1	Hood Pos. 2	Hood Pos. 3	Bottom-base Pos. 4	Bottom-base Pos. 5	Hood Pos. 6
6	M20	99.741.3329.7	70.352.0636.4	70.350.0636.4	99.700.3329.7	70.320.0628.9	99.731.3329.7
	M25	99.742.3329.7	70.354.0636.4	70.353.0636.4	—	—	99.732.3329.7
10	M20	99.743.3329.7	70.352.1036.4	70.350.1036.4	99.706.3329.7	70.320.1028.9	99.733.3329.7
	M25	99.744.3329.7	70.354.1036.4	70.353.1036.4	—	—	99.734.3329.7
16	M25	99.745.3329.7	70.352.1636.4	70.350.1636.4	99.702.3329.7	70.320.1628.9	99.735.3329.7
	M32	99.746.3329.7	70.354.1636.4	70.353.1636.4	—	—	99.736.3329.7
24	M25	99.747.3329.7	70.352.2436.4	70.350.2436.4	99.704.3329.7	70.320.2428.9	99.737.3329.7
	M32	99.748.3329.7	—	—	—	—	99.738.3329.7
48	M32	70.372.4836.4	70.375.4836.4	70.350.4828.4	—	70.320.4828.9	—
	M40	70.374.4836.4	70.376.4836.4	—	—	—	—

Handling instructions for the connectors are available in section on page 288.



Crimping tool

	Description	Type	Part No.	P.U.
	Tool			
	Crimping tool in the case		95.101.0800.0	
	Crimping die	"A"	05.502.2000.0	1
	Crimping die	"B"	05.502.2100.0	1
	Crimping die	"C"	05.502.2200.0	1
	Crimping die	"D"	05.502.2300.0	1
	Crimping die	"E"	05.502.2400.0	1
	Crimping die	"F"	05.502.2600.0	1
	Contact positioner	1	05.502.3100.0	1
	Contact positioner	2	05.502.3200.0	1
	Contact positioner	3	05.502.3300.0	1
	Contact positioner	4	05.502.3800.0	1



Crimping die
"A"



Crimping die
"B"



Crimping die
"C"



Crimping die
"D"



Crimping die
"E"



Crimping die
"F"



Contact
positioner
1



Contact
positioner
2



Contact
positioner
3



Contact
positioner
4



Assignment of contacts to appropriate crimping tool

Part No.									Suitable for														Extraction tool			
									revos BASIC	revos MOT	revos MINI Q5	revos MINI (7+8-pole)	revos MINI Q12	revos HD	revos FLEX (Modul 3-pole)	revos FLEX (Modul 4-pole)	revos FLEX (Modul 5-pole)	revos FLEX (Modul 5-pole)	revos FLEX High-voltage-module	revos FLEX (Modul 10-pole)	revos FLEX RJ45	revos DD		revos FLEX (Modul 20-pole)	revos BASIC switching contact	revos SLIDE
Female	Male	Contact diameter	mm²	AWG	Surface	Stripping length mm	Crimping die	Contact positioner																		
02.123.7001.0	05.543.7001.0	2.5	0.5	20	Au0,8	7	B	3	●	●	●														05.502.3500.0	
02.123.7001.7	05.543.7001.7	2.5	0.5	20	Au2	7	B	3	●	●	●														05.502.3500.0	
02.123.7002.0	05.543.7002.0	2.5	0.5	20	Ag	7	B	3	●	●	●														05.502.3500.0	
02.123.7021.0	05.543.7021.0	2.5	0.5	20	Sn	7	B	3	●	●	●														05.502.3500.0	
02.123.7101.0	05.543.7101.0	2.5	0.75-1.0	18	Au0,8	7	B	3	●	●	●														05.502.3500.0	
02.123.7101.7	05.543.7101.7	2.5	0.75-1.0	18	Au2	7	B	3	●	●	●														05.502.3500.0	
02.123.7102.0	05.543.7102.0	2.5	0.75-1.0	18	Ag	7	B	3	●	●	●														05.502.3500.0	
02.123.7121.0	05.543.7121.0	2.5	0.75-1.0	18	Sn	7	B	3	●	●	●														05.502.3500.0	
02.123.7201.0	05.543.7201.0	2.5	1.5	16	Au0,8	7	B	3	●	●	●														05.502.3500.0	
02.123.7201.7	05.543.7201.7	2.5	1.5	16	Au2	7	B	3	●	●	●														05.502.3500.0	
02.123.7202.0	05.543.7202.0	2.5	1.5	16	Ag	7	B	3	●	●	●														05.502.3500.0	
02.123.7221.0	05.543.7221.0	2.5	1.5	16	Sn	7	B	3	●	●	●														05.502.3500.0	
02.123.7301.0	05.543.7301.0	2.5	2.5	14	Au0,8	7	B	3	●	●	●														05.502.3500.0	
02.123.7301.7	05.543.7301.7	2.5	2.5	14	Au2	7	B	3	●	●	●														05.502.3500.0	
02.123.7302.0	05.543.7302.0	2.5	2.5	14	Ag	7	B	3	●	●	●														05.502.3500.0	
02.123.7321.0	05.543.7321.0	2.5	2.5	14	Sn	7	B	3	●	●	●														05.502.3500.0	
02.123.7401.0	05.543.7401.0	2.5	4	12	Au0,8	7	B	3	●	●	●														05.502.3500.0	
02.123.7401.7	05.543.7401.7	2.5	4	12	Au2	7	B	3	●	●	●														05.502.3500.0	
02.123.7402.0	05.543.7402.0	2.5	4	12	Ag	7	B	3	●	●	●														05.502.3500.0	
02.123.7421.0	05.543.7421.0	2.5	4	12	Sn	7	B	3	●	●	●														05.502.3500.0	
02.124.0900.0	05.544.0900.0	1.58	0.2-0.56	24-20	Sn	4	E	2			●		●												05.502.0000.0	
02.124.0929.0	05.544.0929.0	1.58	0.2-0.56	24-20	Sn	4	E	2			●		●												05.502.0000.0	
02.124.1000.0	05.544.1000.0	1.58	0.75-1.50	18-16	Sn	4	E	2			●		●												05.502.0000.0	
02.124.1029.0	05.544.1029.0	1.58	0.75-1.50	18-16	Sn	4	E	2			●		●												05.502.0000.0	
02.124.1400.0	05.544.1400.0	1.58	0.5-1.50	20-16	Au	4	E	2			●		●												05.502.0000.0	
02.124.1429.0	05.544.1429.0	1.58	0.5-1.50	20-16	Au	4	E	2			●		●												05.502.0000.0	
02.125.2929.8	05.544.1829.8	3.6	1.5	16	Ag	10	B	none						●											05.502.0910.0	
02.125.3029.8	05.544.1929.8	3.6	2.5	14	Ag	10	B	none						●											05.502.0910.0	
02.125.3129.8	05.544.3129.8	3.6	4	12	Ag	10	D	1						●											05.502.0910.0	
02.125.3229.8	05.544.3229.8	3.6	6	10	Ag	10	D	1						●											05.502.0910.0	
02.125.3329.8	05.544.3329.8	3.6	10	8	Ag	10	D	1						●											05.502.0910.0	
02.125.3429.8	05.544.3429.8	2.5	0.5-1.5	20-16	Ag	4	C	2							●	●									05.502.0610.0	
02.125.3529.8	05.544.3529.8	2.5	1.5-2.5	16-14	Ag	4	C	2							●	●									05.502.0610.0	
02.125.3629.7	05.544.3629.7	2.5	0.5	20	Au	8	B	1								●	●								05.502.0810.0	
02.125.3629.8	05.544.3629.8	2.5	0.5	20	Ag	8	B	1								●	●								05.502.0810.0	
02.125.3729.7	05.544.3729.7	2.5	0.75-1.0	18	Au	8	B	1									●	●							05.502.0810.0	
02.125.3729.8	05.544.3729.8	2.5	0.75-1.0	18	Ag	8	B	1									●	●							05.502.0810.0	
02.125.3829.8	05.544.3829.8	2.5	1.5	16	Ag	8	B	1									●	●							05.502.0810.0	
02.125.3929.7	05.544.3929.7	2.5	2.5	14	Au	8	B	1									●	●							05.502.0810.0	
02.125.3929.8	05.544.3929.8	2.5	2.5	14	Ag	8	B	1									●	●							05.502.0810.0	
02.125.4029.8	05.544.4029.8	2.5	4	12	Ag	8	B	1									●	●							05.502.0810.0	
02.125.4129.7	05.544.4129.7	1.6	0.14-0.37	26-22	Au	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4129.8	05.544.4129.8	1.6	0.14-0.37	26-22	Ag	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4229.7	05.544.4229.7	1.6	0.5	20	Au	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4229.8	05.544.4229.8	1.6	0.5	20	Ag	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4329.7	05.544.4329.7	1.6	0.75-1.0	18	Au	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4329.8	05.544.4329.8	1.6	0.75-1.0	18	Ag	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4429.7	05.544.4429.7	1.6	1.5	16	Au	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4429.8	05.544.4429.8	1.6	1.5	16	Ag	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4529.7	05.544.4529.7	1.6	2.5	14	Au	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4529.8	05.544.4529.8	1.6	2.5	14	Ag	8	B	1				●							●	●	●				05.502.0710.0	
02.125.4629.7	05.544.4629.7	1.0	0.09-0.25	28-24	Au	3	A	4														●			05.502.0410.0	
02.125.4729.7	05.544.4729.7	1.0	0.25-0.5	24-20	Au	3	A	4														●			05.502.0410.0	
	05.543.9021.0	2.5	0.5	20	Sn	7	B	3															●		05.502.3500.0	
	05.543.9121.0	2.5	0.75-1.0	18	Sn	7	B	3															●		05.502.3500.0	
	05.543.9221.0	2.5	1.5	16	Sn	7	B	3															●		05.502.3500.0	
	05.543.9321.0	2.5	2.5	14	Sn	7	B	3															●		05.502.3500.0	
	05.543.9421.0	2.5	4	12	Sn	7	B	3															●		05.502.3500.0	
02.125.1121.0	05.544.5621.0	1.65	1.5	16	Ag	3	B	3																●	05.502.3500.0	
Z7.280.4227.0		1.6			Ag	6	F					●													05.502.0710.0	

Selection criteria and characteristics of the different contact platings tin, silver and gold

Contact platings

The core of an electric plug connection is the contact pair, consisting of the socket and plug contacts. Contacts are produced almost exclusively from copper alloys, and Wieland Electric GmbH uses contact platings made of tin, silver and gold, depending on the product specification:

Tin is corrosion-resistant; silver offers favorable conditions at high current and with cyclical switching processes; gold offers protection against aggressive environmental conditions.

- **revos** – 16 A plug connector in screw and crimp design are available in all three surface platings, tin, silver and gold.
- **revos** – 16 A plug connectors with spring clamp contacts are available with silver-plating
- **revos** – 16 A multipole adapters are normally available tin-plated.
- **revos** – hybrid plug connectors are normally supplied in a tin version for $I \leq 16$ A in and in a silver-plated version for $I > 16$ A.



Tin-plated



Silver-plated



Gold-plated

Wieland Hotline · Advice

We are there for you

Phone +49 951 9324 991

Fax +49 951 9326 991

AT.TS@wieland-electric.com

Inserts with tin-plated contacts:

Offers excellent resistance to the corrosive gases SO_2 and H_2S . Tin-plated contacts are especially well suited for transmitting low voltages and current in the millivolt and μA range, but also for typical signal voltages, such

as 24 V and lower ampere, or network voltage and corresponding current.

Inserts connectors with silver-plated contacts:

Silver-plated contacts extend the operating life of the plug connector when there is strong current, in particular with cyclical motor start-up current that is markedly above the nominal current of the plug connectors. For example, in use on plastic injection molding machines that switch current on and off within seconds. Silver-plated contacts have proven themselves when the maximum current load capacity limit of 16 A was almost surpassed. Here, too, longer life cycles can be achieved.

In the range of high contact temperatures ($> 100\text{ }^\circ\text{C}$), silver-plated contacts are preferable to tin-plated contacts.

Aging of silver contacts due to the influence of industrial atmospheres.

During the lifetime of the silver contacts, a silver sulfide layer can form due to the increased affinity of silver for sulfur, which is present in industrial atmospheres in small amounts. Through the chemical reaction of the silver with the gaseous sulfur in the surrounding air, brown to black layers arise, which result in coloring of the surface.

The chemical reaction of the silver surfaces on the plug systems of Wieland Electric GmbH can be delayed by passivating the silver-plated surfaces at the factory with an additional layer. This passivation protects the silver temporarily from a reaction with the gaseous sulfur in the surrounding air. Every currently known passivation layer will protect the silver surface for a limited time only, and a silver sulfide layer, including a black-brown coloration, will form.

This soft layer is extremely thin and is broken through when the contacts are mated. As a result, low transmission resistance is assured, even for colored contacts. This has been proven in numerous examinations in our laboratory.

Inserts connectors with gold-plated contacts:

In areas where high signal precision is required and the signals are transmitted through extremely small current and low voltage, signal distortions can occur with silver contacts with a silver sulfide layer. To simplify, the following values can be used: For current $< 5\text{ mA}$ and voltages up to 5 V, tin-plated or gold-plated contacts

are recommended.

But for extreme applications, only gold-plated contacts should be used.

Conclusion:

Fundamentally, tin-plated contacts are very good or better suited than silver-plated contacts for all types of signal current. For stronger current, when used with high ambient temperatures or a cyclical electric current, longer service lives can be expected with silver-plated contacts. Gold-plated contacts should be used in the range of very low voltage and current.

Wieland has decades of experience in the area of plug-gable connection technology. We offer the best-possible contact with the optimal plating for every application.

Definition of the IP degrees of protection

For applications in industrial environments, degrees of protections and standards were defined that specify the environmental impact regarding contact, protection against foreign bodies and humidity to which a system can be exposed without being damaged. The degrees of protection are defined in the IP standard of DIN EN 60 529: degrees of protection achieved through housings (IP code).

The IP code consists of a two-digit number that indicates the relevant protection degree. The first digit specifies the protection degree for the protection against contact and foreign bodies while the second digit specifies the protection against water and humidity.

Practical notes:

For “normal” industrial systems where multipole connectors are used in closed factory halls, protection according to IP54 is normally offered = protected against dust + protected against splashing water. This protection is normally completely sufficient. For systems in outdoor applications (vehicles, snow guns, etc.) we recommend protection according to IP65 = dustproof + protected against jets of water. A protection according to IP67 or IP68 is required for only a few outdoor applications unless a continuous immersion of the components cannot be avoided.

The following tables are to describe the protection degrees in detail:

Table 1: Protection against contact and foreign bodies

1st	Protection against accidental contact	Protection against foreign bodies
0	No protection	No protection
1	Protection against contact with large parts of the body, for example the back of the hand	Protection against foreign bodies with a diameter of 50 mm and larger.
2	Protection against contact with the finger of 12.5 mm and larger.	Protection against foreign bodies with a diameter of 12.5 mm and larger.
3	Protection against contact with tools and wires larger than 2.5 mm	Protection against foreign bodies with a diameter of 2.5 mm and larger.
4	Protection against contact with tools and wires larger than 1 mm	Protection against foreign bodies with a diameter of 1 mm and larger.
5	Complete protection against accidental contact	Protection against dust: Penetration of dust is not fully prevented, but dust must not penetrate to such an extent that the equipment's functionality or safety is restricted in any way
6	Complete protection against accidental contact	Dustproof: No penetration of dust possible with a negative pressure of 20 mbar.

Definition of the IP degrees of protection

Table 2: Water protection

2nd	Protection against ingress of water
0	No protection
1	Protection against dripping water: Dripping water falling vertically must not have a damaging effect
2	Protection against dripping water up to a tilt of 15°: Dripping water falling vertically must not have a damaging effect, if the equipment is tilted by up to 15°.
3	Protection against spraying water: Water that is sprayed in an angle of up to 60° must not have any damaging effect
4	Protection against splashing water: Water spraying from all directions towards the equipment must not have any damaging effect
5	Protection from jets of water: Jets of water directed towards the equipment from all directions must not have any damaging effect
6	Protection from powerful jets of water: Powerful jets of water that are directed towards the housing from all directions must not have any damaging effect.
7	Protection from temporary immersion in water: Water must not ingress in a quantity that has a damaging effect, if the housing is temporarily immersed in water under standardized pressure and time conditions
8	Protection from continuous immersion in water: Water must not ingress in a quantity that has a damaging effect, if the housing is continuously immersed in water under conditions agreed upon between the manufacturer and the user. The conditions must however be more severe than for key figure 7.
9 K	Protected against ingress of water from all directions, even with highly increased pressure against the housing. (High-pressure/steam jet cleaner, 80–100 bar)

Definition of the IP degrees of protection

Degrees of protection against water, designated by the second index number

The second index number defines the level of protection provided by the housing against damaging influences on the equipment resulting from the intrusion of water.

Table 3 gives short descriptions and definitions for the degrees of protection defined by the second index number.

Degrees of protection listed in this table may only be determined using the second index number and not through reference to the brief description or definition.

Up to the second index number 6, the description means that the requirements for all lower index numbers are also fulfilled.

A housing designated with just the second index number 7 or 8 is considered unsuitable for exposure to jet-spray water (designated with the second index number 5 or 6) and does not need to meet the requirements of index numbers 5 or 6, unless equipped with a double designation according to the following table:

Table 3: Degrees of protection

The housing meets the test for			
jet-spray water, second index number	Temporary/permanent submersion second index number	Description and label	Area of application
5	7	IPX5 / IPX7	Multipurpose
6	7	IPX6 / IPX7	Multipurpose
5	8	IPX5 / IPX8	Multipurpose
6	8	IPX6 / IPX8	Multipurpose
	7	IPX7	Restricted
	8	IPX8	Restricted

Housings for **"multipurpose"** use, as specified in the last column, must meet the requirements, both when exposed to jet-spray water or when temporarily or permanently submerged.

Housings for **"restricted"** use, as specified in the last column, are considered suitable only for temporary or permanent submersion and unsuitable for exposure to jet-spray water.




Derating behavior of *revos* industrial multipole connectors

Like any other connector, the **revos** industrial multipole connector also faces a reduction in the values for the current carrying capability when the ambient temperature rises.

This behavior is called derating behavior. Basic information on the derating behavior of connectors is provided in standard DIN EN 60 512 sec. 3.

Each contact insert is characterized by its rated current, among other things. The rated current is the current that a connector can carry in an ambient temperature of 40°C, simultaneously continued (not intermittent) over all contacts without exceeding the permissible upper temperature limit.

The derating curve shows the maximum current I at the given ambient temperature without the connector exceeding the upper temperature limit.



Curve of current carrying capability derived from the basic curve Source DIN EN 60 512-5-2-2002

Information on how to change over from PG to metric threads

Basic legal conditions

The European standard EN 50 262 "Metric Cable Glands for Electrical Installation" was ratified on April 01, 1989 by CENELEC (European Committee for Electrotechnical Standardization) and put into force.

Basic legal conditions

The big difference in the new EN standard is it has the character of a safety standard.

As a building standard it only defines the metric thread and its lead.

PG threads
are available on
request!

Detailed table of contents

				Page
Introduction				6–25
revos	revos MINI		3 to 12-pole, 50–400 V, 10 A	28–31
Contact inserts see from page 26	revos BASIC	500 V 16 A	6 to 48-pole, 500 V, 16 A, screw connection	32–33
			6 to 48-pole, 500 V, 16 A, spring clamp connection	34–35
			6 to 24-pole, 500 V, 16 A, double spring clamp connection	36–37
			6 to 48-pole, 500 V, 16 A, crimp connection	38–39
	revos BASIC EE		10 to 46-pole, 500 V, 16 A, crimp connection	40–41
Multipole adapters	revos BASIC		6 to 24-pole, 500 V, 16 A, multipole adapters, screw connection	42–43
			6 to 24-pole, 500 V, 16 A, set of 2 components, single locking lever	44–45
			10 to 24-pole, 500 V, 16 A, set of 2 components, double locking lever	46–47
			6 to 24-pole, 500 V, 16 A, multipole adapters, spring clamp connection	48–49
Contact inserts	revos BASIC	400/690 V 16 A	3 to 32-pole, 400/690 V, 16 A, screw connection	50–51
		690 V 16 A	6 to 48-pole, 690 V, 16 A, screw connection	52–53
			6 to 48-pole, 690 V, 16 A, crimp connection	54–55
		830 V 16 A	3 to 20-pole, 830 V, 16 A, spring clamp connection	56–57
	revos DD	250 V 10 A	24 to 108-pole, 250 V, 10 A, crimp connection	58–59
	revos HD	250 V 10 A	10 to 32-pole, 250 V, 10 A, screw connection	60–61
			15 to 80-pole, 250 V, 10 A, crimp connection	62–65
			40 and 64-pole, 250 V multipole adapters, screw connection	66–67
	revos POWER	400 V – 690 V 35 A	6-pole + ground, 400–690 V, 35 A, screw connection	68–69
		400/690 V 82 A	4-pole + ground, 400/690 V, 82 A, screw connection	70
		690 V 4x35 A, 6x16 A	4/6-pole + ground, 690 V, screw connection	71
		400/690 V 40 A + 230/400 V 16 A	6-/6-pole + ground, screw connection	72
		400/690 V 100 A + 400/690 V 40 A + 230/400 V 16 A	3-/3-/6-pole + ground, screw connection	73
		690 V 82 A + 400 V 16A	4-/2-pole + ground, 690/400 V, screw connection	74
Multipole adapters		400 V and 690 V 35A	6-pole + ground, 400 V/6-pole + ground, 690 V, screw connection	76
		500 V	4-/6-pole + ground, 500 V, screw connection	77
Connector and Multipole adapter with trigger action frame	revos BASIC	500 V	6 to 24-pole, 500 V, 16 A, trigger action frame, screw connection	80
			6 to 24-pole, 500 V, 16 A, trigger action frame, multipole adapters, screw connection	82–83
			6 to 24-pole, 500 V, 10 A, trigger action frame, crimp connection	84–85
		690 V	6 to 24-pole, 690 V, 16 A, trigger action frame, screw connection	86–87
			6 to 24-pole, 690 V, 16 A, trigger action frame, multipole adapters, screw connection	88–89
			6 to 24-pole, 690 V, 10 A, trigger action frame, crimp connection	90–91
	revos HD	250 V 10 A	40- und 64-pole, 250 V, 10 A, trigger action frame, crimp connection	92–93
			40- und 64-pole, 250 V, 10 A, trigger action frame, multipole adapters, screw connection	94–95
	revos IT		Data cable feed-through	96
			9 to 2x50-pole D-Sub connectors	97
Contact inserts	revos ☞	90 V 16 A	6 to 48-pole, 3–16 A, screw connection	98–99
Modular pluggable connector system	revos FLEX	100 V to 5,5 kV	3 to 20-pole modular inserts, 250 V to 1000 V, crimp connection/modular blind piece	100–105
			Pneumatic-, high-voltage-module	106–107
			high-current module	108
			spring clamp-, USB-, Profibus-, RJ45 module, module frame	109–112
Connector	revos MOT	690 V 16 A	10-pole, 690 V, 16 A plastic connector with contact inserts	114–115
revos housings see from page 116	revos MINI		Hoods and Bases, metal and plastic	118–119
	revos BASIC	Size 6/6H	Hoods 500 V, single locking lever	120–121
			Hoods 500 V + 690 V, single locking lever, 6H	122–123
			Bases 500 V, single locking lever	124–125
			Bases 500 V + 690 V, single locking lever, 6H	126–127
			Hoods 690 V, single locking lever	128–129
			Bases 690 V, single locking lever	130–131
		Size 10/10H	Hoods 500 V, single locking lever 10, 10H	132–135
			Bases 500 V, single locking lever 10, 10H	136–139
			Hoods 500 V, double locking lever 10, 10H	140–145
			Bases 500 V, double locking lever 10, 10H	146–149
			Hoods 690 V, single locking lever	150–151
			Bases 690 V, single locking lever	152–153
			Hoods 690 V, double locking lever	154–157
			Bases 690 V, double locking lever	158–159

				Page		
	revos BASIC	Size 16/16H	Hoods 500 V, single locking lever 16, 16 H	160–163		
			Bases 500 V, single locking lever 16, 16 H	164–167		
			Hoods 500 V, double locking lever 16, 16 H	168–173		
			Bases 500 V, double locking lever 16, 16 H	174–177		
			Hoods 690 V, single locking lever	178–179		
			Bases 690 V, single locking lever	180–181		
			Hoods 690 V, double locking lever 16, 16XL	182–183		
			Hoods 690 V, double locking lever, with Locking levers	184–185		
			Bases 690 V, double locking lever	186–187		
		Size 24/24H	Hoods 500 V, single locking lever	188–191		
			Bases 500 V, single locking lever	192–195		
			Hoods 500 V, double locking lever	196–201		
			Bases 500 V, double locking lever	202–205		
			Hoods 690 V, single locking lever	206–207		
			Bases 690 V, single locking lever	208–209		
			Hoods 690 V, double locking lever 24, 24XL	210–211		
			Hoods 690 V, double locking lever, with Locking levers	212–213		
			Bases 690 V, double locking lever	214–215		
		Size 32	Hoods/Bases 500/690 V, double locking lever	216–217		
		Size 48	Hoods/Bases 500/690 V, single locking lever	218–221		
		Size 6 to 24	EMC hoods 500 V, double locking lever	222		
			EMC bases 500 V, double locking lever	223		
		revos HD	Size 10/15	Hoods 250 V, Size 10/15, single locking lever	224–225	
				Bases 250 V, Size 10/15, single locking lever	226–227	
			Size 16/25	Hoods 250 V, Size 16/25, single locking lever	228–229	
				Bases 250 V, Size 16/25, single locking lever	230–231	
			Size 32/50	Hoods 250 V, Size 32/50, double locking lever	232–235	
				Bases 250 V, Size 32/50, double locking lever	236–237	
	revos 	Size 6Ex	Hoods 90 V, single locking lever	238–239		
			Bases 90 V, single locking lever	240–241		
		Size 10Ex	Hoods 90 V, double locking lever	242–243		
			Bases 90 V, double locking lever	244–245		
		Size 16Ex	Hoods 90 V, double locking lever	246–247		
			Bases 90 V, double locking lever	248–249		
		Size 24Ex	Hoods 90 V, double locking lever	250–251		
			Bases 90 V, double locking lever	252–253		
		Size 48Ex	Hoods 90 V, single locking lever	254–255		
			Bases 90 V, single locking lever	256–257		
		sets /4 components	revos BASIC	Size 6 to 24 / 500 V	Complete multipole connector sets (housing + contact inserts)	258–259
		revos Accessoires see from page 260	revos	mounting frame	Mounting frame size 6 to 24 for DIN rail mount	262–263
revos	cover and reducer plates		Cover and reducer plates for control cabinet installation	264–265		
revos	coding accessories		Coding bolts, coding pins and female coding pieces	266–269		
revos	cable glands		Metal and plastic glands IP68	270		
			Metal glands IP54	271		
			Reduction pieces, expansion pieces and PG/metric adapter	272		
			Blind piece	273		
revos BASIC	protective cover		Size 6 to 32 Protective cover with or without locking levers, IP65	274–276		
			Size 6 to 24, protective cover, latchable	277		
revos MINI	protective cover		Protective cover with and without gasket, IP65	277		
revos	tools	Crimping tool, insulation stripping tool, Screwdriver and Jumper bar	278			
revos	marking accessories	Marking accessories and marking tag carriers	279–281			
facts&DATA see from page 282			Conductor connections	284–285		
			Current load capacity, tightening torque	286–287		
			Explanations of applications in hazardous areas	288–289		
			Installation spacing and mounting dimensions	290–292		
			revos  mounting dimension	293		
			Crimping tool, Assignment of contacts to appropriate crimping tool	294–295		
			Selection criteria for the contact surfaces tin, silver and gold	296–297		
			Definition of the IP degrees of protection	298–300		
			Derating behavior of revos industrial multipole connectors	301		
			Information on how to change over from PG to metric threads	301		

Spanning various industries and products.



0601.1 "gesis^{TOP} Luminaires connector concepts"



0602.1 "gesis^{LINECT} Universal Connector System for Recessed Luminaires"



0640.1 "gesis^{MINI} the pluggable electrical installation with a compact design"



0500.1 "selos / fasis DIN Rail Terminal Blocks, Catalog"



0800.1 "interface Solutions for the Control Cabinet"



0860.1 "safety System Solutions for Automation Technology"



0400.1 "Electro-technical solutions for wind energy systems"



0401.1 "Electro-technical solutions for the control cabinet"



0402.1 "Components for heating, ventilation, and air conditioning"



0910.1 "Corporate Sustainability Environmental Statement Bamberg and Gerach locations"



0009.0 "Wieland apprenticeship Auf der Erfolgsstraße."



0902.1 "The system partner in automation technology and in building automation technology"



0600.1 "gesis^{CON} GST 18
Electrical installation of
buildings via plug & play



0700.1 "gesis^{ELECTRONIC}
Decentralized building
automation with plug & play"

Building and installation techn.

Automation technology

Further documents and
brochures can be downloaded
quickly and easily via the
Download Center on
our homepage.



0406.1 "Solutions for heavy duty
construction equipment
and vehicles"



0710.1 "gesis^{SOLAR}
Electrical Installation Technology
for Photovoltaics"

Industries

Wieland connects.



Wieland 100 years in Bamberg.

Wieland is one of the most important employers in Bamberg and the surrounding area. The book portrays the life of the company's founder Friedrich H. ("Fritz") Wieland and the following generations, closely intertwined with the company's history. Available in bookshops.

Wieland Hotline · Advice

Additional information



General information and news:
www.wieland-electric.com

Visit our e-catalog at
<https://eshop.wieland-electric.com>

SALES SERVICE

We are there for you

Phone +49 951 9324-990

- To contact our sales department regarding availability, delivery schedules, and pricing

TECHNICAL SUPPORT

Our Technical Service is, of course, happy to help you if you have questions regarding industrial heavy duty connectors.

Phone +49 951 9324-991

Fax +49 951 9326-991
AT.TS@wieland-electric.com

revos CONFIGURATOR



The software tool simplifies the selection of the components for heavy-duty plug connectors.

Wieland subsidiaries

... and the addresses of our representatives worldwide are available at:

www.wieland-electric.com



USA
Wieland Electric Inc.
North American Headquarters
2889 Brighton Road
Oakville, Ontario L6H 6C9
Phone +1 905 8298414
Fax +1 905 8298413
www.wielandinc.com



CANADA
Wieland Electric Inc.
North American Headquarters
2889 Brighton Road
Oakville, Ontario L6H 6C9
Phone +1 905 8298414
Fax +1 905 8298413
www.wieland-electric.ca



GREAT BRITAIN
Wieland Electric Ltd.
Riverside Business Centre,
Walnut Tree Close
GB-Guildford /Surrey GU1 4UG
Phone +44 1483 531213
Fax +44 1483 505029
sales@wieland.co.uk



FRANCE
Wieland Electric SARL.
Le Céramê Hall 6
47, avenue des Genottes
CS 48313
95803 Cergy-Pontoise Cedex
Phone +33 1 30320707
Fax +33 1 30320714
infos@wieland-electric.fr



SPAIN
Wieland Electric S.L.
C/ Maria Auxiliadora 2 bajos
E-08017 Barcelona
Phone +34 93 2523820
Fax +34 93 2523825
ventas@wieland-electric.com



ITALY
Wieland Electric S.r.l.
Via Edison, 209
I-20019 Settimo Milanese
Phone +39 02 48916357
Fax +39 02 48 920685
info@wieland-electric.it



POLAND
Wieland Electric Sp. Zo.o.
Św. Antoniego 8
62-080 Swadzim
Phone +48 61 2225400
Fax +48 61 8407166
office@wieland-electric.pl



CHINA
Wieland Electric Trading
Unit 2703
International Soho City
889 Renmin Rd.,
Huang Pu District
PRC- Shanghai 200010
Phone +86 21 63555833
Fax +86 21 63550090
info-shanghai@wieland-electric.cn



DENMARK
Wieland Electric A/S
Vallørækken 26
DK-4600 Køge
Phone +45 70 266635
Fax +45 70 266637
sales@wieland-electric.dk



BELGIUM
ATEM – Wieland Electric NV
Bedrijvenpark De Veert 4
B-2830 Willebroek
Phone +32 3 8661800
Fax +32 3 8661828
info.belgium@wieland-electric.com



◀ Informational material for
ordering and for downloading
from our websites

Subject to technical modifications!
gesis®, **podis**®, **samos**® are registered trademarks of
Wieland Electric GmbH



wieland

Headquarters:

Wieland Electric GmbH
Brennerstraße 10 – 14
96052 Bamberg, Germany

Sales and Marketing Center:

Wieland Electric GmbH
Benzstraße 9
96052 Bamberg, Germany

Phone +49 951 9324-0

Fax +49 951 9324-198

www.wieland-electric.com

info@wieland-electric.com

Technical Support:

Phone +49 951 9324-991

Fax +49 951 9326-991

AT.TS@wieland-electric.com

Industrial technology

Solutions for the control cabinet

- DIN rail terminal blocks
 - Screw, tension spring or push-in connection technology
 - Wire cross sections up to 240 mm²
 - Numerous special functions
 - Software solutions interfacing to CAE systems
- Safety
 - Safe signal acquisition
 - Safety switching devices
 - Modular safety modules
 - Compact safety controllers
 - Application consulting and training
- Network engineering and fieldbus systems
 - Remote maintenance via VPN industrial router and VPN service portal
 - Industrial Ethernet switches
 - PLC and I/O systems, standard and increased environmental conditions
- Interface
 - Power supply units
 - Overvoltage protection
 - Coupling relays, semiconductor switches
 - Timer relays, measuring and monitoring relays
 - Analog coupling and converter modules
 - Passive interfaces

Solutions for field applications

- Decentralized installation and automation technology
 - Electrical installation for wind tower
 - Fieldbus interfaces and motor starters
- Connectors for industrial applications
 - Rectangular and round connectors
 - Aluminum or plastic housings
 - Degree of protection up to IP 68
 - Current-carrying capacity up to 100 A
 - Connectors for hazardous areas
 - Modular, application-specific technology

PC board terminals and connectors

- Screw or spring clamp connection technology
- Spacings: 3.5 mm to 10.16 mm
- Reflow or wave soldering process

Building and installation technology

- Building installation systems
 - Main power supply connectors IP 20/IP 65 ... IP 68
 - Bus connectors
 - Low-voltage connectors
 - Power distribution system with flat cables
 - Distribution systems
 - Bus systems in KNX, LON and radio technology
 - DIN rail terminal blocks for electrical installations
 - Overvoltage protection

0530.1 C 03/13

**contacts
are
green.**