

# Miniature One-touch Fittings

## One-touch Mini

# Series KJ

Applicable Tubing:  $\varnothing 3.2$ ,  $\varnothing 4$ ,  $\varnothing 6$   
 Connection Thread: M3, M5, R 1/8



### Guide 1

### Guide 2

### Chuck

Suitable for use with nylon, soft nylon and urethane.  
 Large retaining force.  
 Has large retaining force.

### Seal

Can be used for a wide range of pressures from a low vacuum up to a pressure of 1.0 MPa

The use of a special profile ensures sealing and reduces resistance when the tube is inserted.

### Gasket

### Release button (Light gray)

#### Light force for removal

When the fitting is removed from the tubing, the chuck and collet are released, thus preventing them from biting into the tube to an unnecessary degree. Unique shape allows easy tube release.

### Tube

### Body (White)

### O-ring

### Stud

Effective when piping in a confined space.

- The body and the threaded portion can rotate (for positioning to some extent).
- Stud is electroless nickel plated.
- Standard with preapplied thread seal 1/8

PAT.PEND

Optimum piping in less space with 20% reduction of the outside diameter

Thread seal is standard.

Copper-free specifications (With electroless nickel plated.)

Possible to use in vacuum to -100 kPa



### Applicable Tubing

|                 |                                                       |
|-----------------|-------------------------------------------------------|
| Tubing material | Nylon, Soft nylon, Polyurethane                       |
| Tubing O.D.     | $\varnothing 3.2$ , $\varnothing 4$ , $\varnothing 6$ |

### Specifications


















|                               |                                                |                                                                                    |
|-------------------------------|------------------------------------------------|------------------------------------------------------------------------------------|
| Fluid                         | Air/Water <sup>Note)</sup>                     |                                                                                    |
| Maximum operating pressure    | 1.0 MPa                                        |                                                                                    |
| Operating vacuum pressure     | -100 kPa                                       |                                                                                    |
| Proof pressure                | 3.0 MPa                                        |                                                                                    |
| Ambient and fluid temperature | -5 to 60°C, Water: 0 to 40°C (No freezing)     |                                                                                    |
| Thread                        | Mounting section                               | JIS B 0203 (Taper thread for piping)<br>JIS B 0209, Class 2 (Metric coarse thread) |
|                               | Nut section                                    | JIS B 0211 Class 2 (Metric fine thread)                                            |
| Thread seal (Standard)        | With thread seal                               |                                                                                    |
| Copper-free (Standard)        | Brass parts are all electroless nickel plated. |                                                                                    |



Note) Applicable for general industrial water. Please consult with SMC if using for other kinds of fluid. Also, the surge pressure must be under the maximum operating pressure.

### Principal Parts Material

|                         |                                   |
|-------------------------|-----------------------------------|
| Body                    | Stainless steel 303, C3604BD, PBT |
| Stud                    | C3604BD (Thread portion)          |
| Chuck, Guide 2          | Stainless steel 304               |
| Release button, Guide 1 | POM                               |
| Seal, O-ring            | NBR                               |
| Gasket                  | Stainless steel 304, NBR          |

| Model                                                     |                                                                                                                                                                                |                                                                                                                                                                                    |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Hex. socket head male connector</b><br><b>KJS</b> P. 4 | <br><br>     | <b>Bulkhead union</b><br><b>KJE</b> P. 9                                                                                                                                           |
|                                                           |                                                                                                                                                                                | <br><br>         |
|                                                           |                                                                                                                                                                                | <b>Extended male elbow</b><br><b>KJW</b> P. 6                                                                                                                                      |
|                                                           |                                                                                                                                                                                | <br><br>     |
| <b>Male connector</b><br><b>KJH</b> P. 4                  | <br><br>     | <b>Plug-in elbow</b><br><b>KJL</b> P. 5                                                                                                                                            |
|                                                           |                                                                                                                                                                                | <br><br>         |
| <b>Female connector</b><br><b>KJF</b> P. 4                | <br><br>     | <b>Reducer elbow</b><br><b>KJL</b> P. 6                                                                                                                                            |
|                                                           |                                                                                                                                                                                | <br><br>         |
| <b>Straight union</b><br><b>KJH</b> P. 4                  | <br><br>   | <b>Male branch tee</b><br><b>KJT</b> P. 6                                                                                                                                          |
|                                                           |                                                                                                                                                                                | <br><br>       |
| <b>Different diameter straight</b><br><b>KJH</b> P. 5     | <br><br> | <b>Union tee</b><br><b>KJT</b> P. 7                                                                                                                                                |
|                                                           |                                                                                                                                                                                | <br><br>     |
| <b>Male elbow</b><br><b>KJL</b> P. 5                      | <br><br> | <b>Different diameter tee</b><br><b>KJT</b> P. 7                                                                                                                                   |
|                                                           |                                                                                                                                                                                | <br><br>     |
| <b>Union elbow</b><br><b>KJL</b> P. 5                     | <br><br> | <b>Male run tee</b><br><b>KJY</b> P. 7                                                                                                                                             |
|                                                           |                                                                                                                                                                                | <br><br>     |
|                                                           |                                                                                                                                                                                | <b>Branch "Y"</b><br><b>KJU</b> P. 9                                                                                                                                               |
|                                                           |                                                                                                                                                                                | <br><br> |
|                                                           |                                                                                                                                                                                | <b>Plug-in reducer</b><br><b>KJR</b> P. 9                                                                                                                                          |
|                                                           |                                                                                                                                                                                | <br><br> |
| <b>Gasket/Seal for M5 thread</b>                          |                                                                                                                                                                                |                                                                                                                                                                                    |
| <b>Part no.: M-5G2</b>                                    |                                                                                                                                                                                |                                                                                                                                                                                    |
| <b>Material: Stainless steel 304, NBR</b>                 |                                                                                                                                                                                |                                                                                                                                                                                    |

**Gasket/Seal for M5 thread**  
**Part no.: M-5G2**  
**Material: Stainless steel 304, NBR**

## ⚠ Precautions

Be sure to read before handling.  
 Refer to pages 15-18-3 to 15-18-4 for Safety Instructions and Common Precautions on the products mentioned in this catalog, and refer to pages 15-1-10 to 15-1-11 for Precautions on every series.

### Interchangeability of Series KJ and KQ

#### ⚠ Caution

- Do not use the plug-in KQ Series with the KJ Series, it will not hold.
- For combinations other than the plug-in KQs, they are interchangeable.

### Installation and Removal of One-touch Mini Fittings

#### ⚠ Caution

##### Installing of tube

- Cut the tube perpendicularly, using caution not to damage its surface. (Use tube cutter TK-1, 2 or 3. Do not cut the tube with cutting pliers, nippers, scissors, etc.)
- Grasp the tube, then slowly push it until it comes to a stop.
- Then, pull it back gently to make sure that it does not come out.

##### Removing of tube

(Use one hand for removal.)

- Hold the release button with the thumb and forefinger.
- Grasp the tube with the remaining three fingers and palm.
- Then, pull out the tube with three fingers and palm while pushing in the release button with the thumb and the forefinger.
- To reuse the released tube, cut off the damaged portion of the tube.

# Series KJ

## Male Connector: KJH

<M3, M5>



<R 1/8>




| Applicable tubing O.D. (mm) | Connection thread T | Model     | H (width across flats) | L    | A     | M    | Effective area (mm <sup>2</sup> ) |          | Weight (g) |
|-----------------------------|---------------------|-----------|------------------------|------|-------|------|-----------------------------------|----------|------------|
|                             |                     |           |                        |      |       |      | Nylon                             | Urethane |            |
| 3.2                         | M3 x 0.5            | KJH23-M3  | 7                      | 16.3 | 13.7  | 12.7 | 0.9                               | 0.9      | 1.6        |
|                             | M5 x 0.8            | KJH23-M5  |                        | 16.7 | 13.6  |      |                                   |          | 2          |
|                             | R 1/8               | KJH23-01S | 10                     | 13.8 | 9.8*  |      | 3                                 | 2.5      | 4.7        |
| 4                           | M3 x 0.5            | KJH04-M3  | 8                      | 16.3 | 13.7  | 12.7 | 0.9                               | 0.9      | 1.9        |
|                             | M5 x 0.8            | KJH04-M5  |                        | 17   | 13.9  |      | 4                                 | 4        | 2.4        |
|                             | R 1/8               | KJH04-01S | 10                     | 14.8 | 10.8* |      |                                   |          | 4.6        |
| 6                           | M5 x 0.8            | KJH06-M5  | 10                     | 17.8 | 14.7  | 13.5 | 4                                 | 4        | 3.3        |
|                             | R 1/8               | KJH06-01S |                        | 19.4 | 15.4* |      | 10                                | 10       | 5.2        |




\* Reference dimensions after R thread installation.

<M3, M5>



<R 1/8>



## Hexagon Socket Head Male Connector: KJS

<M3, M5>



<R 1/8>




| Applicable tubing O.D. (mm) | Connection thread T | Model     | H (width across flats) | Note) øD | L    | A     | M    | Effective area (mm <sup>2</sup> ) |          | Weight (g) |
|-----------------------------|---------------------|-----------|------------------------|----------|------|-------|------|-----------------------------------|----------|------------|
|                             |                     |           |                        |          |      |       |      | Nylon                             | Urethane |            |
| 3.2                         | M3 x 0.5            | KJS23-M3  | 1.5                    | 7        | 16.3 | 13.7  | 12.7 | 1.4                               | 1.4      | 1.3        |
|                             | M5 x 0.8            | KJS23-M5  | 2                      |          | 19.7 | 16.6  |      | 2.5                               | 2.5      | 2.8        |
| 4                           | M3 x 0.5            | KJS04-M3  | 1.5                    | 8        | 16.3 | 13.7  | 12.7 | 1.4                               | 1.4      | 1.6        |
|                             | M5 x 0.8            | KJS04-M5  | 2.5                    |          | 18.7 | 15.6  |      | 4                                 | 4        | 2.7        |
|                             | R 1/8               | KJS04-01S | 3                      | 9.8      | 19.7 | 15.7* |      |                                   |          | 5.4        |
| 6                           | M5 x 0.8            | KJS06-M5  | 2.5                    | 10       | 19.5 | 16.4  | 13.5 | 4                                 | 4        | 3.3        |
|                             | R 1/8               | KJS06-01S | 4                      |          | 20   | 16*   |      | 10                                | 10       | 5.2        |






\* Reference dimensions after R thread installation.  
Note) øD: Max. diameter

<M3, M5>



<R 1/8>




## Female Connector: KJF



| Applicable tubing O.D. (mm) | Connection thread T | Model    | H (width across flats) | Note) øD | L1   | L2  | M    | Effective area (mm <sup>2</sup> ) |          | Weight (g) |
|-----------------------------|---------------------|----------|------------------------|----------|------|-----|------|-----------------------------------|----------|------------|
|                             |                     |          |                        |          |      |     |      | Nylon                             | Urethane |            |
| 3.2                         | M3 x 0.5            | KJF23-M3 | 7                      | 7        | 16.5 | 6.8 | 12.7 | 3                                 | 2.5      | 2.6        |
|                             | M5 x 0.8            | KJF23-M5 |                        |          | 18.8 | 7.9 |      |                                   |          | 2.8        |
| 4                           | M3 x 0.5            | KJF04-M3 | 8                      | 8        | 16.1 | 6.4 | 12.7 | 4                                 | 4        | 3.2        |
|                             | M5 x 0.8            | KJF04-M5 |                        |          | 18.7 | 7.8 |      |                                   |          | 3.8        |
| 6                           | M5 x 0.8            | KJF06-M5 | 10                     | 10       | 18   | 7.5 | 13.5 | 10                                | 10       | 5.3        |



Note) øD: Max. diameter



## Straight Union: KJH



| Applicable tubing O.D. (mm) | Model    | Note) øD | L    | M    | Effective area (mm <sup>2</sup> ) |          | Weight (g) |
|-----------------------------|----------|----------|------|------|-----------------------------------|----------|------------|
|                             |          |          |      |      | Nylon                             | Urethane |            |
| 3.2                         | KJH23-00 | 8.4      | 26.3 | 12.7 | 3                                 | 2.5      | 1.4        |
| 4                           | KJH04-00 | 9.3      | 26.3 | 12.7 | 4                                 | 4        | 1.7        |
| 6                           | KJH06-00 | 11.6     | 28   | 13.5 | 10                                | 10       | 2.5        |



Note) øD: Max. diameter

