

REV. 1


DCO 16539

| | |
|-----------------|----------------|
| COIL: @ 25°C | |
| RESISTANCE | 700 OHMS ± 10% |
| NOMINAL VOLTAGE | 26.5 VDC |
| MUST OPERATE | 13.5 VDC |
| MUST RELEASE | 1.5 VDC |

| | |
|--------------|-----------------------------|
| ENVIRONMENT: | |
| VIBRATION | 10 CPS TO 2000 CPS @ 20 g's |
| SHOCK | 100 g's 6 MS. DURATION |
| TEMPERATURE | -65 °C TO +125 °C |

NOTES: OPERATE 4 MS MAX
 RELEASE 2 MS MAX : BOUNCE 3 MS MAX
 DRY CIRCUIT MISS TEST PERFORMED ON
 EACH RELAY

CUSTOMER DATA SHEET



CONTACT RATING: 2A 30 VDC
 RESISTIVE .75A 30 VDC INDUCTIVE
 100,000 OPERATIONS

DR. RB 9/22/92 | CK. TLG 10-11-00

CII Technologies™
 advanced control electronic solutions

CUST. HI-G
 CUST. NO. 2K-2A-126D REV. "HFW" RELAY

HFW1201S296