



REV.	DATE	DESCRIPTION
A	09/30/03	ADD STRIPPING DIMENSIONS



CRIMP NOTES:
 1. CRIMPED FERRULE
 HEX CRIMP SIZE .213"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex MINI-UHF CRIMP PLUG (FOR RG-55/U, 223/U, 142/U, 400/U CABLE)							
8						DRAWN	G.R.S.		09/30/03						
7															
6															
5	COVER	BRASS	NICKEL	1											
4	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	SHEET	1 OF 1								
3	CONTACT PIN	BRASS	GOLD	1											
2	INSULATOR	DELTRIN	NATURAL	1											
1	BODY	DIE CAST	NICKEL	1											
	DESCRIPTION	MATERIAL	FINISH	QTY		DO NOT SCALE DRAWING	CAD FILE	C:/182/182324.DWG	DWG. NO.	182324.DWG	REV.	A	SIZE	A	SCALE