



P	LTR	DESCRIPTION	DATE	DWN	APVD
	M3	REVISED PER ECO-12-007718	08MAY12	KH	DR
	M4	REVISED PER ECO-17-007400	24NOV2017	RS	DR



- 1 STAMP AMP 16-14* APPROX AS SHOWN.

2 WIRE INSULATION : $\phi 2.667-3.810[\phi .105-.150]$

3 BODY MATERIAL THK: $0.787 \pm 0.051[.031 \pm .002]$

4 APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE.

5 MEETS M7928/4-106, CLASS 1 & 2
MEETS M7928/13-106, CLASS 1 & 2

6 MATERIAL:
BODY & SLEEVE: COPPER PER ASTM B152
INSULATION: PVF2

7 FINISH:
BODY & SLEEVE: TIN/LEAD (93-7) PLATE PER
ASTM B545 (3% MIN LEAD CONTENT)
INSULATION: COLOR-NATURAL.

1000	LOOSE PIECE	 53415-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°C [302°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		 TE Connectivity								
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES] 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	NAME									
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED			TERMINAL, RING TONGUE, PVF2 , P.I.D.G. WIRE SIZE: 16-14 AWG									
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL  6	FINISH  7	DWN JR RUTH 250CT07	CHK T MICHIELUTTI 250CT07	APVD T MICHIELUTTI 250CT07	PRODUCT SPEC —	APPLICATION SPEC 114-2157	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-53415	RESTRICTED TO —
CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 1		REV M4					