


HM6116LFP-2, HM6116LFP-3, HM6116LFP-4


2048-word × 8-bit High Speed Static CMOS RAM

FEATURES


- High Density Small-sized Package
- Projection Area Reduced to One-Thirds of Conventional DIP
- Thickness Reduced to a Half of Conventional DIP
- Single 5V Supply
- High Speed: Fast Access Time 120ns/150ns/200ns (max.)
- Low Power Standby and Standby: 10μW (typ.)
- Low Power Operation; Operation: 160mW (typ.)
- Completely Static RAM: No Clock nor Timing Strobe Required
- Directly TTL Compatible: All Input and Output
- Equal Access and Cycle Time
- Capability of Battery Back up Operation



FUNCTIONAL BLOCK DIAGRAM



PIN ARRANGEMENT



ABSOLUTE MAXIMUM RATINGS

Item	Symbol	Rating	Unit
Voltage on Any Pin Relative to GND	V_T	-0.5* to +7.0	V
Operating Temperature	T_{op}	0 to +70	°C
Storage Temperature	T_{stg}	-55 to +125	°C
Temperature Under Bias	T_{bias}	-10 to +85	°C
Power Dissipation	P_T	1.0	W

* Pulse width 50ns : -3.5V

■ TRUTH TABLE

$\overline{CS}$	$\overline{OE}$	$\overline{WE}$	Mode	V_{CC} Current	I/O Pin	Ref. Cycle
H	X	X	Not Selected	I_{SB}, I_{SB1}	High Z	
L	L	H	Read	I_{CC}	Dout	Read Cycle (1)~(3)
L	H	L	Write	I_{CC}	Din	Write Cycle (1)
L	L	L	Write	I_{CC}	Din	Write Cycle (2)

■ RECOMMENDED DC OPERATING CONDITIONS ($T_a=0$ to $+70^\circ\text{C}$)

Item	Symbol	min	typ	max	Unit
Supply Voltage	V_{CC}	4.5	5.0	5.5	V
	GND	0	0	0	V
Input Voltage	V_{IH}	2.2	3.5	6.0	V
	V_{IL}	-3.0*	—	0.8	V

* Pulse Width : 50ns, DC : V_{IL} min = -0.3V.■ DC AND OPERATING CHARACTERISTICS ($V_{CC}=5V\pm 10\%$, GND=0V, $T_a=0$ to $+70^\circ\text{C}$)

Item	Symbol	Test Conditions	HM6116LFP-2			HM6116LFP-3/-4			Unit
			min	typ*	max	min	typ*	max	
Input Leakage Current	$ I_{LI} $	$V_{CC}=5.5V$, $V_{in}=GND$ to V_{CC}	—	—	2	—	—	2	μA
Output Leakage Current	$ I_{LO} $	$\overline{CS}=V_{IH}$ or $\overline{OE}=V_{IH}$, $V_{Lo}=GND$ to V_{CC}	—	—	2	—	—	2	μA
Operating Power Supply Current	I_{CC}	$\overline{CS}=V_{IL}$, $I_{Lo}=0mA$	—	35	70	—	30	60	mA
	I_{CC1}^{**}	$V_{IH}=3.5V$, $V_{IL}=0.6V$, $I_{Lo}=0mA$	—	30	—	—	25	—	mA
Average Operating Current	I_{CCt}	Min cycle, duty=100%	—	35	70	—	30	60	mA
Standby Power Supply Current	I_{SB}	$\overline{CS}=V_{IH}$	—	4	12	—	4	12	mA
	I_{SB1}	$\overline{CS}\geq V_{CC}-0.2V$, $V_{in}\geq V_{CC}-0.2V$ or $V_{in}\leq 0.2V$	—	2	50	—	2	50	μA
Output Voltage	V_{OL}	$I_{OL}=4mA$	—	—	0.4	—	—	—	V
		$I_{OL}=2.1mA$	—	—	—	—	—	0.4	V
	V_{OH}	$I_{OH}=-1.0mA$	2.4	—	—	2.4	—	—	V

* : $V_{CC}=5V$, $T_a=25^\circ\text{C}$

** : Reference Only

■ AC CHARACTERISTICS ($V_{CC}=5V\pm 10\%$, $T_a=0$ to $+70^\circ\text{C}$)

● AC TEST CONDITIONS

Input Pulse Levels: 0.8 to 2.4V

Input Rise and Fall Times: 10 ns

Input and Output Timing Reference Levels: 1.5V

Output Load: 1TTL Gate and $C_L = 100pF$ (including scope and jig)

● READ CYCLE

Item	Symbol	HM6116LFP-2		HM6116LFP-3		HM6116LFP-4		Unit
		min	max	min	max	min	max	
Read Cycle Time	t_{RC}	120	—	150	—	200	—	ns
Address Access Time	t_{AA}	—	120	—	150	—	200	ns
Chip Select Access Time	t_{ACS}	—	120	—	150	—	200	ns
Chip Selection to Output in Low Z	t_{CLZ}	10	—	15	—	15	—	ns
Output Enable to Output Valid	t_{OE}	—	80	—	100	—	120	ns
Output Enable to Output in Low Z	t_{OLZ}	10	—	15	—	15	—	ns
Chip deselection to Output in High Z	t_{CHZ}	0	40	0	50	0	60	ns
Chip Disable to Output in High Z	t_{ONZ}	0	40	0	50	0	60	ns
Output Hold from Address Change	t_{OH}	10	—	15	—	15	—	ns

●WRITE CYCLE

Item	Symbol	HM6116LFP-2		HM6116LFP-3		HM6116LFP-4		Unit
		min	max	min	max	min	max	
Write Cycle Time	t_{WC}	120	—	150	—	200	—	ns
Chip Selection to End of Write	t_{CW}	70	—	90	—	120	—	ns
Address Valid to End of Write	t_{AW}	105	—	120	—	140	—	ns
Address Set Up Time	t_{AS}	20	—	20	—	20	—	ns
Write Pulse Width	t_{WP}	70	—	90	—	120	—	ns
Write Recovery Time	t_{WR}	5	—	10	—	10	—	ns
Output Disable to Output in High Z	t_{OHZ}	0	40	0	50	0	60	ns
Write to Output in High Z	t_{WHZ}	0	50	0	60	0	60	ns
Data to Write Time Overlap	t_{DW}	35	—	40	—	60	—	ns
Data Hold from Write Time	t_{DH}	5	—	10	—	10	—	ns
Output Active from End of Write	t_{OW}	5	—	10	—	10	—	ns


■CAPACITANCE ($f=1\text{MHz}$, $T_a=25^\circ\text{C}$)

Item	Symbol	Test Conditions	typ	max	Unit
Input Capacitance	C_{in}	$V_{in}=0\text{V}$	3	5	pF
Input/Output Capacitance	$C_{i/o}$	$V_{i/o}=0\text{V}$	5	7	pF


Note) This parameter is sampled and not 100% tested.

■TIMING WAVEFORM


●READ CYCLE (1) ⁽¹⁾



●READ CYCLE (2) ^{(1) (2) (4)}




●READ CYCLE (3) ^{(1) (3) (4)}




- NOTES: 1. $\overline{WE}$ is High for Read Cycle
 2. Device is continuously selected, $\overline{CS} = V_{IL}$
 3. Address Valid prior to or coincident with $\overline{CS}$ transition Low.
 4. $\overline{OE} = V_{IL}$.

●WRITE CYCLE (1)



●WRITE CYCLE (2) (5)



- NOTES: 1. A write occurs during the overlap (t_{WP}) of a low $\overline{CS}$ and a low $\overline{WE}$.
2. t_{WR} is measured from the earlier of $\overline{CS}$ or $\overline{WE}$ going high to the end of write cycle.
3. During this period, I/O pins are in the output state so that the input signals of opposite phase to the outputs must not be applied.
4. If the $\overline{CS}$ low transition occurs simultaneously with the $\overline{WE}$ low transitions or after the $\overline{WE}$ transition, output remain in a high impedance

- state.
5. $\overline{OE}$ is continuously low. ($\overline{OE} = V_{IL}$)
6. D_{out} is the same phase of write data of this write cycle.
7. D_{out} is the read data of next address.
8. If $\overline{CS}$ is Low during this period, I/O pins are in the output state. Then the data input signals of opposite phase to the outputs must not be applied to them.

■LOW V_{CC} DATA RETENTION CHARACTERISTICS ($T_a = 0$ to $+70^\circ\text{C}$)

Item	Symbol	Test Conditions	min	typ	max	Unit
V_{CC} for Data Retention	V_{DR}	$\overline{CS} \geq V_{CC} - 0.2\text{V}$ $V_{IN} \geq V_{CC} - 0.2\text{V}$ or $V_{IN} \leq 0.2\text{V}$	2.0	—	—	V
Data Retention Current	I_{CCDR}^*	$V_{CC} = 3.0\text{V}$, $\overline{CS} \geq 2.8\text{V}$ $V_{IN} \geq 2.8\text{V}$ or $V_{IN} \leq 0.2\text{V}$	—	—	30	μA
Chip Deselect to Data Retention Time	t_{CDR}	See Retention Waveform	0	—	—	ns
Operation Recovery Time	t_R		$**t_{RC}$	—	—	ns

* V_{IL} min = -0.3V , $10\mu\text{A}$ max (at $T_a = 0$ to $+40^\circ\text{C}$)

** t_{RC} - Read Cycle Time.

●Low V_{CC} DATA RETENTION WAVEFORM