


SERIES**1025R, 1026R****1025****1026**MILITARY
QPL
APPROVEDTraditional
First QualityRoHS
Compliant**Molded Unshielded RF Coils**

Actual Size

**Military Specifications (1025 Series Only)**

MS75083 (LT4K); MS75084 (LT10K); MS75085 (LT10K)

Physical Parameters

	Inches	Millimeters
Length	0.250 ± 0.010	6.35 ± 0.25
Diameter	0.095 ± 0.010	2.41 ± 0.25
Lead Size		
AWG #24 TCW	0.020 ± 0.0015	0.508 ± 0.038
Lead Length	1.5 ± 0.12	38.1 ± 3.05

Current Rating at 90°C Ambient

LT4K 35°C Rise

LT10K 15°C Rise

Operating Temperature Range

LT4K -55°C to +125°C

LT10K -55°C to +105°C

Maximum Power Dissipation at 90°C

Phenolic: LT4K 0.21 W

Iron: LT10K 0.09 W

Ferrite: LT10K 0.073 W

Weight Max. (Grams) 0.3

• For in-between values see Series 1782 (page 41)

Note (1026 Series only) Self Resonant Frequency (SRF) values are calculated and for reference only.**Marking** DELEVAN; inductance with units and tolerance; date code (YYWWL). Note: An R before the date code indicates a RoHS component.

Example: 1025R-16K

<i>Front:</i>	<i>Reverse:</i>
DELEVAN	2.2uH±10%
2.2uH±10%	R 0850B

Optional Tolerances: J = 5% H = 3% G = 2% F = 1%

*Complete part # must include series # PLUS the dash #

For surface finish information,
refer to www.delevanfinishes.com

DASH NUMBER*	MIL DASH #	INDUCTANCE (μH)	TOLERANCE	Q MINIMUM	SRF MINIMUM (MHz)	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)
MS75083- SERIES 1025 PHENOLIC CORE (LT4K)							
-94K	1	0.10	±10%	40	25.0	680.0	0.08
-96K	2	0.12	±10%	40	25.0	640.0	0.09
-00K	3	0.15	±10%	38	25.0	600.0	0.10
-02K	4	0.18	±10%	35	25.0	550.0	0.12
-04K	5	0.22	±10%	33	25.0	510.0	0.14
-06K	6	0.27	±10%	33	25.0	430.0	0.16
-08K	7	0.33	±10%	30	25.0	410.0	0.22
-10K	8	0.39	±10%	30	25.0	365.0	0.30
-12K	9	0.47	±10%	30	25.0	330.0	0.35
-14K	10	0.56	±10%	30	25.0	300.0	0.50
-16K	11	0.68	±10%	28	25.0	275.0	0.60
-18K	12	0.82	±10%	28	25.0	250.0	0.85
-20K	13	1.0	±10%	25	25.0	230.0	1.00
MS75084- SERIES 1025 IRON CORE (LT10K)							
-22K	1	1.2	±10%	25	7.9	150.0	0.18
-24K	2	1.5	±10%	28	7.9	140.0	0.22
-26K	3	1.8	±10%	30	7.9	125.0	0.30
-28K	4	2.2	±10%	30	7.9	115.0	0.40
-30K	5	2.7	±10%	37	7.9	100.0	0.55
-32K	6	3.3	±10%	45	7.9	90.0	0.85
-34K	7	3.9	±10%	45	7.9	80.0	1.00
-36K	8	4.7	±10%	45	7.9	75.0	1.20
-38K	9	5.6	±10%	50	7.9	65.0	1.80
-40K	10	6.8	±10%	50	7.9	60.0	2.00
-42K	11	8.2	±10%	55	7.9	55.0	2.70
-44K	12	10.0	±10%	55	7.9	50.0	3.30
-46K	13	12.0	±10%	45	2.5	40.0	2.70
-48K	14	15.0	±10%	45	2.5	35.0	2.80
-50K	15	18.0	±10%	50	2.5	30.0	3.10
-52K	16	22.0	±10%	50	2.5	25.0	3.30
-54K	17	27.0	±10%	50	2.5	20.0	3.50
MS75085- SERIES 1025 FERRITE CORE (LT10K)							
-56K	1	33.0	±10%	45	2.5	24.0	3.40
-58K	2	39.0	±10%	45	2.5	22.0	3.60
-60K	3	47.0	±10%	45	2.5	20.0	4.50
-62K	4	56.0	±10%	45	2.5	18.0	5.70
-64K	5	68.0	±10%	50	2.5	15.0	6.70
-66K	6	82.0	±10%	50	2.5	14.0	7.30
-68K	7	100.0	±10%	50	2.5	13.0	8.00
-70K	8	120.0	±10%	30	0.79	12.0	13.00
-72K	9	150.0	±10%	30	0.79	11.0	15.00
-74K	10	180.0	±10%	30	0.79	10.0	17.00
-76K	11	220.0	±10%	30	0.79	9.0	21.00
-78K	12	270.0	±10%	30	0.79	8.0	25.00
-80K	13	330.0	±10%	30	0.79	7.0	28.00
-82K	14	390.0	±10%	30	0.79	6.5	35.00
-84K	15	470.0	±10%	30	0.79	6.0	42.00
-86K	16	560.0	±10%	30	0.79	5.0	46.00
-88K	17	680.0	±10%	30	0.79	4.2	60.00
-90K	18	820.0	±10%	30	0.79	3.8	65.00
-92K	19	1000.0	±10%	30	0.79	3.4	72.00
SERIES 1026 PHENOLIC CORE (LT4K)							
-00M		0.022	±20%	50	50.0	900.0	0.010
-02K		0.027	±10%	40	25.0	875.0	0.030
-04K		0.033	±10%	40	25.0	850.0	0.035
-06K		0.039	±10%	40	25.0	825.0	0.040
-08K		0.047	±10%	40	25.0	800.0	0.045
-10K		0.056	±10%	40	25.0	775.0	0.050
-12K		0.068	±10%	40	25.0	750.0	0.060
-14K		0.082	±10%	40	25.0	725.0	0.070

Packaging Tape & reel: 12" reel, 3500 pieces max.; 14" reel, 6000 pieces max.**Made in the U.S.A.**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[1025-56K](#) [1025-58K](#) [1025-60K](#) [1025-62K](#) [1025-64K](#) [1025-66K](#) [1025-68K](#) [1025-70K](#) [1025-72K](#) [1025-74K](#) [1025-76K](#) [1025-78K](#) [1025-80K](#) [1025-82K](#) [1025-84K](#) [1025-86K](#) [1025-88K](#) [1025-90K](#) [1025-92K](#) [1025-32K](#) [1025-34K](#) [1025-36K](#) [1025-38K](#) [1025-40K](#) [1025-42K](#) [1025-44K](#) [1025-46K](#) [1025-48K](#) [1025-50K](#) [1025-52K](#) [1025-54K](#) [1025-04K](#) [1025-08K](#) [1025-10K](#) [1025-12K](#) [1025-14K](#) [1025-16K](#) [1025-18K](#) [1025-20K](#) [1025-22K](#) [1025-24K](#) [1025-26K](#) [1025-28K](#) [1025-30K](#) [1025-94K](#) [1025-96K](#) [1025R-30K](#) [1025R-38K](#) [1025R-34K](#) [1025R-32K](#) [1025R-36K](#) [1025R-66K](#) [1025R-62K](#) [1025R-60K](#) [1025R-68K](#) [1025R-64K](#) [1025R-82K](#) [1025R-86K](#) [1025R-84K](#) [1025R-88K](#) [1025R-80K](#) [1025R-04K](#) [1025R-08K](#) [1025R-42K](#) [1025R-46K](#) [1025R-44K](#) [1025R-40K](#) [1025R-48K](#) [1025R-54K](#) [1025R-58K](#) [1025R-50K](#) [1025R-56K](#) [1025R-52K](#) [1025R-78K](#) [1025R-70K](#) [1025R-74K](#) [1025R-72K](#) [1025R-76K](#) [1025R-90K](#) [1025R-94K](#) [1025R-96K](#) [1025R-92K](#) [1025R-16K](#) [1025R-10K](#) [1025R-12K](#) [1025R-18K](#) [1025R-14K](#) [1025R-26K](#) [1025R-22K](#) [1025R-28K](#) [1025R-20K](#) [1025R-24K](#) [1025-52J](#) [1025R-44KTR](#) [1025R-48KTR](#) [1025R-52KTR](#) [1025R-00KTR](#) [1025R-60KTR](#) [1025R-68KTR](#) [1025R-24KTR](#)