


NICKEL METAL HYDRIDE BATTERIES: INDIVIDUAL DATA SHEET

HHR300CH Cylindrical C size (HR 26/50) for backup use

Dimensions (with Tube) (mm)



Specifications

	mm	inch
Diameter	25.8+0/-1.0	1.02+0/-0.04
Height	50.0+0/-1.5	1.97+0/-0.06
Approximate Weight	Grams	Ounces
	80	2.82

Nominal Voltage		1.2V	
Discharge Capacity ¹	Average ²	3300 mAh	
	Rated (Min.)	3100 mAh	
Approx. Internal impedance at 1000Hz at charged state.		5mΩ	
Charge	Standard	300mA (0.1lt) x 16hrs.	
	Rapid ³	1500mA (1lt) x 2.4 hrs. ⁴	
	Low Rate	155mA x 32 hrs. 100mA x 48 hrs.	
Ambient Temperature	Charge	°C	°F
		0°C to 45°C	32°F to 113°F
		10°C to 40°C	32°F to 104°F
	Discharge	-10°C to 45°C	14°F to 149°F
		-10°C to 65°C	14°F to 113°F
	Storage	< 1 year	-20°C to 35°C -4°F to 95°F
		< 3 months	-20°C to 35°C -4°F to 95°F
		< 1 month	-20°C to 55°C -4°F to 131°F

¹ After charging at 0.1lt for 16 hours, discharging at 0.2lt.

² For reference only.

³ Need specially designed control system

Control System:

dT/dt cut-off; 1 to 2°C/min

-ΔV cut-off; -ΔV per cell = 5 to 10 mV

T-control; T=65°C


Rapid charger timer; 2.4h (at 1.25a)

Trickle timer; within 2h



⁴ With control system

Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge / discharge specs, warning label contents and unit design.

Typical Charge Characteristics



Typical Discharge Characteristics



Note: ¹[It] was previously expressed as [C]. [It] is an IEC standard expression for the amount of charge or discharge current and is expressed as: $It(A) = Cn (Ah)/1h$.

• [It] is the reference test current in amperes

• [Cn] is the rated capacity of the cell or battery in Ampere-hours. n = the time base [hours] for which the rated capacity is declared

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panasonic:](#)

[HHR-300CHA03](#)