


MATERIAL:-
 CAST ALUMINUM. * THIS SLEEVE MADE FROM ALUMINUM SHEET METAL.

REFERENCE:
 SD21894 - YOU-R

VIEW AFTER INSTALLATION



INSTALLATION NOTES:-

1. SMEAR PENETROX "A" OR EQUIVALENT ON THE CONTACT GROOVES AND ON THE CONDUCTOR STRANDS. SCRATCH BRUSHING AFTER APPLYING THE COMPOUND IS RECOMMENDED. PENETROX "A" MAY BE PURCHASED FROM THE BURNDY ENGINEERING CO. PENETROX "A" IS NOT INCLUDED IN CATALOG NO.
2. CLOSING AND PARTIAL ROUNDING OF THE LEGS OF THE "U" SHAPE BY STRIKING WITH A Mallet, HAMMER OR LINEMAN'S PLIERS IS REQUIRED TO FACILITATE INSERTION OF THE REPAIR SLEEVE IN THE Y34A HYPERPRESS.
3. INDENTS TO START AT ONE END OF THE SLEEVE AND WORK TOWARDS THE OTHER, 2 CRIMPS MADE SIMULTANEOUSLY

* FOR REPAIR SLEEVES DESIGNED FOR INSTALLATION WITH THE SAME DIES USED TO INSTALL NYSPLICES ON THESE CONDUCTORS, REFER TO DRAWING SD21894 WHICH LISTS THE YOU-R TYPE.

CONDUCTOR	CATALOG NO.	LETTERING	DIE INDEX NO.	INSTALLATION DATA	HYDRESS	DIE SET	CRIMPS	LENGTH FT/100	REF. ENG.		
ACSR (AAC) 7-1	YOUAR	6.25	#4 ACSR 6-1 7-1 #4 AAC, T USE DIE INDEX # 237	237	W-237	12	A-237	U-237	6	2.0	PC23812
#4 (232) 7-1											
#2 (3/16) 6-1	YOU2R	8.25	*2 ACSR 6-1 7-1 USE DIE INDEX # 239	239	W-239	16	A-239	U-239	8	3.0	PC-23352
#2 (3/16) 7-1				693	W-693			U-693			
#1 (3/16) 6-1	YOU1R	8.75	*1 ACSR 6-1 8-1 USE DIE INDEX # 241	693	W-693	20		U-693			
80MCM (3/16) 8-1				241	W-241		A-241	U-241	10	3.5	PC 24472
16 (3/16) 6-1	YOU25R	8.75	1/16 ACSR 6-1 USE DIE INDEX BG 243	BG	FIXED	30	A-	U-54	30	3.5	PC 23353
26 (1/4) 6-1	YOU26R	10.06	2/16 ACSR 6-1 USE DIE INDEX 245 247	243	W-243	20	A-243	U-243	10		
3/0 (5/16) 6-1	YOU27R	10.06	3/16 ACSR 6-1 USE DIE INDEX # 247	245	W-245	24	A-245	U-245	12	4.5	PC 23238
101.8 MCM 12-7	YOU251RG1	10.06	101.8 MCM ACSR 12-7 USE DIE INDEX # 247	247	W-247	24	A-247	U-247	12	5.0	PC 23058
134.6 MCM 12-7	YOU261RG1	11.82	134.6 MCM ACSR 12-7 USE DIE INDEX # 249	247	W-247	24	A-247	U-247	12	5.0	PC23238
410 (5/16) 6-1	YOU28R	11.82	410 6-1, 159 MCM 12-7 ACSR USE DIE INDEX # 249	249	W-249	28	A-249	U-249	14	6.5	PC24361
159 MCM 12-7											
190.8 MCM 12-7	YOU30R	11.56	190.8 12-7, 266.8 6-7, 267 8 18-7 ACSR USE DIE INDEX # 251	249	W-249	28	A-249	U-249	14	6.5	PC23239
266.8 MCM 6-7											
266.8 MCM 18-1											
266.8 MCM 26-7											
336.4 MCM 18-1	YOU321R	11.56	336.4 MCM 18-1 ACSR - 350 MCM 19STR ALUM- USE DIE INDEX 547	251	---	-	A-251	U-251	20	7.5	PC23447
				547	---	-	A-547	U-547		7.5	PC29608
				655	---	-	---	U-655	20		

13	7-30-71	YOUAR, ADDED #4 (232) TSTR AAC. (EC1919)	RGP	J.P.S.
12	10-26-64	REV. REF. PRINT (EC30537)	M.A.M.	W.H.
11	3-4-64	REV. REF. PRINT (EC17812)	M.A.M.	W.H.
10	10-11-54	18-1 STR. OF 266.8 MCM ADDED TO YOU30R (EC10407)	MSR	W.H.
9	2-3-54	350 MCM ADDED TO YOU321R LETTERING (EC9533)	MSR	R.G.
8	12-1-53	YOU321R ADDED (D.O.12687)	R.T.R.	W.H.
7	7-6-53	120.8 MCM ADDED TO YOU27R (EC9899)	P.D.	C.L.
6	7-15-52	PENETROX NOTES ADDED (EC17355)	F.H.	C.L.
5	3-28-51	REV. REF. PRINT (EC3038, 5439)	C.L.	C.L.
4	2-9-51	REV. REF. PRINT (EC3038, 5439)	C.L.	C.L.
3	12-5-50	REV. REF. PRINT (EC3038, 5439)	C.L.	C.L.
2	11-10-50	REV. REF. PRINT (EC3038, 5439)	C.L.	C.L.
1	10-27-50	REV. REF. PRINT (EC3038, 5439)	C.L.	C.L.

REPAIR SLEEVE (A.C.S.R.)

YOU-R (TABLE)

BURNDY
 ENGINEERING CO. INC.
 SD22443

13