

10

11

12

13

14

15

0.6
REC
P/

1. -A- : CARD EDGE POSITION
2. -B- : CENTER OF PWB THICKNESS
3. EJECTOR MECHANISM HEIGHT
4. STAND OFF HEIGHT
5. CARD EJECT TRAVEL : MIN. 7mm
6. DIM "X"

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,6

7. GENERAL TOLERANCE : ±0.3
8. SEE FIG. OF REF. DWG(TA-1115)
FOR PIN ASSIGNMENT.

DO NOT SCALE PRINT


DF-004A REV C

THIS INFORMATION IS CONFIDENTIAL
NO FURTHER DISCLOSURE IS MADE
WITHOUT WRITTEN AUTHORIZATION FROM

MATERIAL	FINISH	QTY.
RETARDANT RESIN (UL94V-0)	NONE	2
PHOSPHOR BRONZE	UNDER : 0.5µm MIN. Ni CONTACT AREA : 0.1µm MIN. Au OVER : 0.5µm MIN. Pd-Ni	136
PHOSPHOR BRONZE	SOLDER TAIL : 2.5µm MIN. Sn-Pb UNDER : 1.27µm MIN. Ni (SHIELD1,2) SELECTIVE : 0.1µm MIN. Au (SHIELD1)	2+2
FR4	UNDER : 0.5µm MIN. Ni ALL OVER : 0.1µm MIN. Au	1
STAINLESS STEEL	SELECTIVE UNDER : 0.5µm MIN. Ni SELECTIVE OVER : 0.1µm MIN. Au	2
RETARDANT RESIN (UL94V-0)	NONE	4
RETARDANT RESIN (UL94V-0)	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	5
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	2
STAINLESS STEEL	NONE	1
STAINLESS STEEL	NONE	2
RETARDANT RESIN (UL94V-0)	NONE	1



www.fciconnect.com

[illegible]

PDM: Rev:E STATUS: **Released** Printed: May 31, 2004

17.1

72.8±1

10

7

4.8

0.85

10.3

13.73(FULL)

1. -A- : CARD EDGE POSITION
2. -B- : CENTER OF PWB THICKNESS
3. EJECTOR MECHANISM HEIGHT
4. STAND OFF HEIGHT
5. CARD EJECT TRAVEL : MIN. 7mm
6. DIM "X"

4.25±0.1	3.5±0.1	5.0±0.1
OTHERS	36,67	1,17,34,35,51,6


7. GENERAL TOLERANCE : ±0.3

8. SEE FIG. OF REF. DWG(TA-1115)
FOR PIN ASSIGNMENT.

DO NOT SCALE PRINT

THIS INFORMATION IS CONFIDENTIAL
NO FURTHER DISCLOSURE IS MADE
WITHOUT WRITTEN AUTHORIZATION FROM
THE COMPANY

DF-004A REV C



MATERIAL			FINISH	QTY
WE RETARDANT RESIN (UL94V-0)			NONE	2
PHOSPHOR BRONZE	UNDER : 0.5mm MIN. Ni CONTACT AREA : 0.1mm MIN. Au OVER 0.5mm MIN. Pd-Ni SOLDER TAIL : 2.5mm MIN. Sn-Pb			13
PHOSPHOR BRONZE	UNDER : 1.27mm MIN. Ni (SHIELD1,2) SELECTIVE : 0.1mm MIN. Au (SHIELD1)			2+
FR4	UNDER : 0.5mm MIN. Ni ALL OVER : 0.1mm MIN. Au			1
STAINLESS STEEL	SELECTIVE UNDER : 0.5mm MIN. Ni SELECTIVE OVER : 0.1mm MIN. Au			2
WE RETARDANT RESIN (UL94V-0)	NONE			4
WE RETARDANT RESIN (UL94V-0)	NONE			4
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			5
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			2
STAINLESS STEEL	NONE			2
WE RETARDANT RESIN (UL94V-0)	NONE			1



FCI



www.fciconnect.com

TITLE Card Bus II EJECTOR ASSY
(ABOVE BOARD, FOLDABLE EJECT STYLE)


SCALE	SIZE	DWG. NO.	REV	SHEET
---	B	73835	E	2 of

PRODUCT NO.
73835-05RRx

REVISIONS				
REV	DESCRIPTION	ECN	BY	DATE
D	GUARDIAN SITE TRANSFER	T03-0300	WL	07/17/03



RECOMMENDED RECEPTACLE PAD LAYOUT



STAND OFF	l	
0.5 mm	P.W.B. THK 1.2mm	P.W.B. THK 1.6mm
	3mm	

RECOMMENDED M2 SCREW LENGTH

NOTE

1. GENERAL TOLERANCE : ± 0.3
2. RECOMMENDED TIGHTING TORQUE : 0.196 N.m [2.0 kgf.cm]
MAX. : 0.245 N.m [2.5 kgf.cm]

DO NOT SCALE PRINT THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN BERG PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM BERG ELECTRONICS JAPAN K.K.



SHEET INDEX	ISSUE																	A FCI www.fciconnect.com
	SH NO.																	
TOLERANCES UNLESS OTHERWISE SPECIFIED		MAT		DR <i>H. Yamagaki</i>		DATE 6/16/98		CUSTOMER COPY		TITLE D/D Card Bus EJECTOR (ABOVE BOARD STYLE)								
LINEAR	±0.3	—H—		ENGR <i>H. Yamagaki</i>		2/10/01												
		FINISH		CHK				THIRD ANGLE PROJ										
ANGLES	±2°	—H—		APPD				UNIT MM INCH		SCALE 1/1	SIZE B	DWG. NO. 73835	REV D	SHEET 3 of				




www.fciconnect.com

PRODUCT NO.
73835-05LLx

REVISIONS				
REV	DESCRIPTION	ECN	BY	DATE
D	GUARDIAN SITE TRANSFER	T03-0300	WL	07/17/03



RECOMMENDED RECEPTACLE PAD LAYOUT



STAND OFF	l	
0.5 mm	P.W.B. THK 1.2mm	P.W.B. THK 1.6mm
	3mm	

RECOMMENDED M2 SCREW LENGTH

- NOTE
1. GENERAL TOLERANCE : ±0.3
 2. RECOMMENDED TIGHTING TORQUE : 0.196 N.m [2.0 kgf.cm]
MAX. : 0.245 N.m [2.5 kgf.cm]

KEEP OUT ZONE

2. RECOMMENDED TIGHTING TORQUE : 0.196 N.m [2.0 kgf.cm] MAX. : 0.245 N.m [2.5 kgf.cm]																
SHEET INDEX		ISSUE														A FCI www.fciconnect.com
		SH NO.														
TOLERANCES UNLESS OTHERWISE SPECIFIED			MAT		DR		DATE		CUSTOMER COPY		TITLE D/D Card Bus EJECTOR (ABOVE BOARD STYLE)					
±0.3			—H—		H. Yamagaki		6/16/98		ENG							
LINEAR			FINISH		H. Yamagaki		2/10/01		CHK		THIRD ANGLE PROJ 					
			—H—		APPD											
ANGLES		±2°									UNIT		MM INCH		SCALE	
DO NOT SCALE PRINT		THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN BERG PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM BERG ELECTRONICS JAPAN K.K.														
DF-004A REV C																
		1/1														
		B														
		DWG. NO.														
		73835														
		REV														
		D														
		SHEET														
		4 of 4														