

## HV440DB1 Demo Board

by James Lei, Applications Engineering Section Head

### Introduction

The Supertex HV440 is a power-efficient, switch-mode ring generator IC requiring minimal external components.


The HV440DB1 demo board contains all the circuitry necessary to drive a 5 REN (North American) ringer load. Simply connect power supplies, ringer load, and enable input as shown below.

For a more detailed description on using the HV440, please refer to Application Note AN-H37.

### Specifications


Ringing Frequency	20Hz $\pm 2$ Hz
Ringing Amplitude	62V <sub>RMS</sub> $\pm 5\%$
Ringer THD	<10%
Output Offset	-48V <sub>DC</sub> $\pm 4$ V (using a 5V $\pm 5\%$ supply)
Max Ringer Load	5 REN (North American)

### Board Layout and Connections



## Supply Sequencing

The +5V supply must always be powered up before the  $V_{NN1}$  and  $V_{PP1}$  supplies. In addition, the Enable input should be ON only after the supplies have stabilized, and should be OFF before the supplies are powered-down. The following sequencing is recommended.



## 20 REN Capability

A demo board capable of driving 20 RENs (HV440DB2) is also available from Supertex. However, the supplied board (HV440DB1) may be modified to provide 20 RENs, as outlined below. Refer to the board layout and connection diagram at the beginning of this note for component locations.

1. Remove R20
2. Solder a Supertex TP2522N8 in the Q1 location and a Supertex TN2524N8 in the Q2 location
3. Change L1 to 1.0mH (510mA rating)\*
4. Change C9 to 470nF (200VDC rating)
5. Change C5 to 330pF
6. Change R18 and R19 to 1.2Ω (1/8W rating)
7. Ensure that the  $V_{NN1}$  and  $V_{PP1}$  supplies are capable of 150mA and have at least 200μF of output capacitance

\* Not all inductors behave similarly, especially at higher frequencies. The recommended inductor is a J. W. Miller 6K-102K.

## Other Ringing Frequencies

By simply changing two resistors, the supplied circuit may be modified to provide ringing frequencies other than 20Hz. The following table lists the resistors to change for some standard ringing frequencies. Please refer to the board layout and connection diagram at the beginning of this note for component locations.

Ringing Frequency <sup>1</sup>	R4, R5	Accuracy <sup>2</sup>
16.7Hz	243kΩ	0.6%
20Hz	205kΩ	-0.5%
25Hz	162kΩ	0.8%
30Hz	137kΩ	-0.7%
33.3Hz	121kΩ	1.3%
40Hz	102kΩ	0.0%
42Hz	97.6kΩ	-0.4%
50Hz	80.6kΩ	1.3%
54Hz	75.0kΩ	0.8%
60Hz	68.1kΩ	-0.1%
66.7Hz	60.4kΩ	1.3%


1 Values for other frequencies may be determined from  $f_{ring} = (2\pi RC)^{-1}$  where  $R=R4=R5$  and  $C=C3=C4$ .

2 Not including component tolerances.

## Output Ripple Reduction

As supplied, the HV440DB1 has less than 1V<sub>RMS</sub> of output ripple. To obtain even lower ripple, C9 may be increased. However, do not exceed 2μF, as distortion of the ringing signal may result. The capacitor should be rated for 200VDC, non-polarized.

# HV440DB1 Schematic



**HV440DB1****5 REN Ring Generator Demo Board BOM**

Desig	Description	Value	Tol	Rating
R1	Thick film chip resistor	10.0K	1%	1/8W
R2	Thick film chip resistor	1.82K	1%	1/8W
R3	Thick film chip resistor	4.87K	1%	1/8W
R4	Thick film chip resistor	205K	1%	1/8W
R5	Thick film chip resistor	205K	1%	1/8W
R6	Thick film chip resistor	1.00K	1%	1/8W
R7	Thick film chip resistor	576	1%	1/8W
R8	Thick film chip resistor	1.50K	1%	1/8W
R9	Thick film chip resistor	10.0K	1%	1/8W
R10	Thick film chip resistor	5.11K	1%	1/8W
R11	Thick film chip resistor	3.32K	1%	1/8W
R12	Thick film chip resistor	1.00K	1%	1/8W
R13	Thick film chip resistor	10.0K	1%	1/8W
R14	Thick film chip resistor	11.0K	1%	1/8W
R15	Thick film chip resistor	1.00M	1%	1/8W
R16	Thick film chip resistor	10K	5%	1/8W
R17	Thick film chip resistor	1K	5%	1/8W
R18	Thick film chip resistor	3.9	5%	1/8W
R19	Thick film chip resistor	3.9	5%	1/8W
R20	Jumper	0	—	—
C1	X7R ceramic chip capacitor	10nF	10%	50V
C2	X7R ceramic chip capacitor	10nF	10%	50V
C3	Surface mount film capacitor	39nF	2%	50V
C4	Surface mount film capacitor	39nF	2%	50V
C5	NPO ceramic chip capacitor	680pF	5%	50V
C6	X7R ceramic chip capacitor	10nF	10%	50V
C7	X7R ceramic chip capacitor	0.1µF	10%	50V
C8	X7R ceramic chip capacitor	0.1µF	10%	50V
C9	Metallized polyester film capacitor	0.22µF	10%	250V
C10	Tantalum electrolytic chip capacitor	2.2µF	20%	10V
C11	Aluminum electrolytic capacitor	4.7µF	20%	100V
C12	Aluminum electrolytic capacitor	4.7µF	20%	250V
C13	X7R ceramic chip capacitor	680pF	10%	50V
L1	Inductor	10mH	15%	120mA
D1-D2	Diode array, fast recovery	BAV99	—	70V
D3	Diode, fast recovery	BAS21	—	250V
D4	Diode, fast recovery	BAS21	—	250V
U1	Quad operational amplifier IC	LM2902M	—	—
U2	Dual high speed comparator IC	LM2903M	—	—
U3	High Voltage Ring Generator IC	HV440WG	—	—

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Supertex:](#)

[HV440DB1](#)