





REV.	ECN NO.	DATE
1.0	RELEASED	05/25/01
2.0	REVISED P/N	03/04/04
3.0	UPDATE TOL.	12/16/04



P.C.B LAYOUT



SPECIFICATIONS

CURRENT RATING : 3 AMPS

INSULATOR RESISTANCE : 5000 MEGOHMS MIN.

CONTACT RESISTANCE : 20 MILLIOHMS MAX.

DIELECTRIC WITHSTANDING : AC 500V

MAX PROCESSING TEMP : 230°C FOR 30 ~ 60 SECONDS
(260°C FOR 10 SECONDS)

OPERATING TEMPERATURE : -40°C ~ +125°C

CONTACT MATERIAL : PHOSPHOR BRONZE.

INSULATOR MATERIAL : NYLON, UL 94V-0

*CONTACT PLATING: P=OVERALL GOLD FLASH; T=OVERALL TIN

ORDERING INFORMATION:

1. Replace "*" with plating code
2. Replace "xx" with number of positions (Pins)

SCALE	3:1	DRAW	JFW	Sullins Electronics San Marcos, CA Tel: 760 744-0125 www.SullinsElectronics.com	
UNIT	MM	CHECK	AJT		
TOLERANCE		AP"E		NAME: FEMALE HEADER, 2.54mm SPACING 7.1mm PROFILE, SMT	
.0=±0.35 .00=±0.2 ANG=±5°		PROJECTION		(PART NO)	PP_Cxx1KFXC
				(DRAW NO)	7012