





| REV. | DATE     | DESCRIPTION           |
|------|----------|-----------------------|
| NC   | 05/06/99 | INITIAL RELEASE       |
| A    | 11/06/06 | UPDATE DRAWING FORMAT |



RECOMMENDED CABLE  
STRIPPING DIM'S.



|   |               |              |         |     |                                                                                                                                        |                   |        |                                                                          |  |        |          |
|---|---------------|--------------|---------|-----|----------------------------------------------------------------------------------------------------------------------------------------|-------------------|--------|--------------------------------------------------------------------------|--|--------|----------|
| 8 |               |              |         |     | UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [ ] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.             | APPROVALS         | DATE   | Amphenol Connex                                                          |  |        |          |
| 7 |               |              |         |     |                                                                                                                                        | DRAWN             | G.R.S. |                                                                          |  |        |          |
| 6 | FERRULE       | COPPER       | GOLD    | 1   | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:<br>0.5 – 8mm ± 0.20mm<br>8 – 30mm ± 0.40mm<br>30 – 120mm ± 0.50mm           | CHECKED           |        | PART DESCRIPTION<br><br>MMCX CRIMP PLUG<br>(FOR RG-178B/U, 196A/U CABLE) |  |        |          |
| 5 | RETAINER RING | PHOS. BRONZE | GOLD    | 1   |                                                                                                                                        | ISSUED            |        |                                                                          |  |        |          |
| 4 | BARREL        | BRASS        | GOLD    | 1   | UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:<br>.020 – .315 = ± 0.007"<br>.315 – 1.180 = ± 0.015"<br>1.180 – 4.724 = ± 0.020" | SHEET             | 1 OF 1 | PART NO.<br><br>262100                                                   |  |        |          |
| 3 | CONTACT PIN   | BRASS        | GOLD    | 1   |                                                                                                                                        |                   |        |                                                                          |  |        |          |
| 2 | INSULATOR     | TEFLON       | NATURAL | 1   | DO NOT SCALE DRAWING                                                                                                                   | CAD FILE          |        | DWG. NO. 262100.DWG                                                      |  |        |          |
| 1 | BODY          | BRASS        | GOLD    | 1   |                                                                                                                                        | C:/262/262100.DWG |        |                                                                          |  |        |          |
|   | DESCRIPTION   | MATERIAL     | FINISH  | QTY |                                                                                                                                        | REV. A            |        |                                                                          |  | SIZE A | SCALE NA |