





REV	ECN	APP'D
-	4000	JT 4/3/00



NOTES:

1. MATERIALS:

BODY: POLYETHERIMIDE PER MIL-P-46184.

GROMMET: SILICONE BLEND ELASTOMER.

DIODE: JANTX1N5618.

INTERNAL PIN CONTACT:

COPPER ALLOY, HARD GOLD PLATE PER MIL-G-45204.

2. PERFORMANCE SPECIFICATION PER MIL-T-81714.

(SUBJECT TO LIMITATIONS OF THE
ELECTRONIC COMPONENTS)

TEMPERATURE: -65°C TO 200°C.

INSULATION RESISTANCE: 5000 MEGOHMS MIN AT 25°C.

DIELECTRIC WITHSTANDING VOLTAGE:

1500 VRMS AT SEA LEVEL,

AND 200 VRMS AT 100,000 FT. ALTITUDE.

CURRENT RATING: 7.5A FOR SIZE 20 CONTACTS.

VIBRATION AND SHOCK: PER MIL-T-81714 PARA 3.5.8 & 9.

3. MODULE ACCEPTS SOCKET CONTACTS (10) M39029/22-192.

4. MODULE TO BE MOUNTED ON M81714/67 RAIL SYSTEM.

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±1.0°	PROJECTION 	SPECIFICATION DRAWING ENGR J.TON 01-JUNE-00		TITLE SJE SERIES ELECTRONIC MODULE JANTX1N5618 DIODE	
ORIGINAL 	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		CHKD  4/3/00 APPD  4/3/00	SIZE A	DWG NO. SJE020010	REV -
		CODE: 58982		SCALE: NONE		SHEET 1 OF 1