





REV.	DATE	ECR NO.	DESCRIPTION
A	05/29/03	—	UPDATE DRAWING FORMAT.
B	01/04/09	—	ADD HEX CRIMP NOTES.



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .213" [5.41].
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	GRS	01/04/09						
7						CHECKED								
6						ISSUED				PART DESCRIPTION TNC R/A CRIMP PLUG (FOR RG–55/U, 142A/U, 223/U, 400/U)				
5	NUT	BRASS	NICKEL	1		SHEET		1 OF 1						
4	FERRULE	COPPER	NICKEL	1						PART NO. 122430				
3	CONTACT PIN	BRASS	GOLD	1										
2	INSULATOR	PTFE	NATURAL	1						DWG. NO. 122430.DWG				
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/122/122430.DWG		REV. B		SIZE A	SCALE NA		