




- NOTES
- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 2 - POLE , CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING **MARKED** ON SIDE OF SWITCH
 - 3  FURNISHED UNASSEMBLED
 - 4 - FOR TERMINAL COVER, SEE MICRO SWITCH CATALOG LISTING 5PA7
 - 5  **APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS**
 - 6  FAA-PMA MUST BE MARKED ON SWITCH
 - 7  FOR MANUFACTURING DETAIL SEE THE CORRESPONDING ASSEMBLY DRAWING FOR EACH LISTING FOR FAA-PMA
 - 8 WEIGHT .07 LBS APPROX

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± 0.040 ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± 0.0005 ANGLES ± 3	DRAWN	JAF	29JUN94	Honeywell				
	CHECK	-	-					
	THIRD ANGLE PROJECTION 	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - TOGGLE			
		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	DRAWING NAME 1TL11_SERIES_CHART 1	REV 21
RASTER			SCALE	1 : 1	SHEET	1 OF 1		