







	13	12	11	10	9	8	7	6	5	4	3	2	1
	STRIP MATERIAL NUMBER	LOOSE PIECE MATERIAL NUMBER	AWG SIZE	FINISH		DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"	DIM. "F"		
J	194170011	194170047	16-14	PREPLATED TIN 75 μ MIN. THICK OVER NICKEL FLASH		.230/5.84	.182/4.62	.141/3.58	.155/3.94	.591/15.00	1.000/25.40		
	194170024	194170048	22-18			.181/4.60	.143/3.63	.108/2.74	.112/2.84	.591/15.00	1.000/25.40		
	194170025	194170049	16-14	SELECT HARD GOLD 30 μ MIN. THICK WITH SELECT TIN 100 μ MIN. THICK OVER NICKEL 50 μ MIN. THICK OVERALL		.230/5.84	.182/4.62	.141/3.58	.155/3.94	.591/15.00	1.000/25.40		
	194170026	194170050	22-18			.181/4.60	.143/3.63	.108/2.74	.112/2.84	.591/15.00	1.000/25.40		
	194170027	194170051	16-14	PREPLATED TIN 75 μ MIN. THICK OVER NICKEL FLASH		.230/5.84	.182/4.62	.141/3.58	.155/3.94	.621/15.77	1.030/26.16		
	194170028	194170052	22-18			.181/4.60	.143/3.63	.108/2.74	.112/2.84	.621/15.77	1.030/26.16		
I	194170029	194170053	16-14	SELECT HARD GOLD 30 μ MIN. THICK WITH SELECT TIN 100 μ MIN. THICK OVER NICKEL 50 μ MIN. THICK OVERALL		.230/5.84	.182/4.62	.141/3.58	.155/3.94	.621/15.77	1.030/26.16		
	194170030	194170054	22-18			.181/4.60	.143/3.63	.108/2.74	.112/2.84	.621/15.77	1.030/26.16		



NOTES:

1. MATERIAL: COPPER ALLOY .012/0.30 THK.
2. FINISH: SEE CHART
3. TERMINAL FOR USE WITH 19419-**** PLUG HOUSING ASSEMBLY.
4. STRIP TERMINALS ARE REELED AS SHOWN ABOVE ON 24" REELS, 4000 PARTS PER REEL.
5. LOOSE TERMINALS ARE BULK PACKAGED IN QUANTITIES OF 400.
6. APPLICATION TOOLING AND CRIMP SPECIFICATIONS: 63865-6000 (14-16 AWG), 63865-6100 (18-22 AWG), 63811-3900 (HAND TOOL).

UPDATED VIEWS EC NO: WNA2012-0151 DRW:WLEUNG 2011/09/13 CHKD: APPR:DTITUS 2012/01/19 REV:	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 						
				mm	INCH	DRAWN BY JPAWLICK	DATE 05/05/03	TITLE MALE PIN TERMINAL, 22-18 & 16-14 AWG, .059/1.50 X .031/0.79							
			4 PLACES	± ---	± ---	CHECKED BY JPAWLICK	DATE 05/05/02								
			3 PLACES	± ---	± .010	APPROVED BY RDEROSS					MOLEX INCORPORATED				
			2 PLACES	± 0.25	± .02										
			1 PLACE	± 0.5	± ---	DATE 05/05/03									
			ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.			SHEET NO.				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART			SD-19417-001			1 OF 1						
SIZE			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												