

9

8

7

6

5

4

3

2

1



E

D

C


B

A





注記 NOTES

- 製品詳細寸法については図面5047541000を参照下さい。
REFER TO THE 5047541000 ABOUT DIMENSIONS IN DETAIL.
- 梱包数量：5000個/リール
NUMBER OF CONNECTORS：5000 PCS/REEL
- リードテープ長さ
LEAD TAPE LENGTH



- 材料 MATERIAL
キャリアテープ(CARRIER TAPE)：ポリスチレン(POLYSTYRENE)
トップテープ(TOP TAPE)：PET, PE, PEF
リール(REEL)：ポリスチレン(PS)リサイクル材含む
POLYSTYRENE(PS)RECYCLE MATERIAL CONTAINED
- ELV及びRoHS適合品
ELV AND RoHS COMPLIANCT



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
REVISED	EC NO: 106328 DRWN: YCHEN128 CHK'D: YKOBAYASHI02 APPR: TKUSUHARA01	2016/07/05 2016/07/07 2016/07/07	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex®							
					MM	10:1								
			ANGULAR TOL ± 1.0 °		DRWN BY		DATE		0.3 FPC CONN. B/F LA75 SERIES TAPING PKG					
					AYOSHII01		2016/03/18							
			4 PLACES ± 0.03		CHK'D BY		DATE							
			3 PLACES ± 0.03		YKOBAYASHI02		2016/03/31							
			2 PLACES ± 0.05		APPR BY		DATE		PRODUCT CUSTOMER DRAWING					
	1 PLACE ± 0.1		TKUSUHARA01		2016/03/31									
	0 PLACES ± 0.2		DRAWING SIZE	THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER					
	B	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			504754	SEE CHART				
DOCUMENT NUMBER									DOC TYPE	DOC PART	SHEET NUMBER			
								5047540000	PSD	000	1 OF 2			

9

8

7

6


5


4

3

2

1





推奨基板レイアウト
RECOMMENDED P.C. BOARD
PATTERN LAYOUT

推奨メタルマスク厚さ : 0.1mm
RECOMMENDED METAL MASK THICKNESS : 0.1mm


推奨開口率 : 80%
APERTURE RATE : 80%

注記
NOTE


1. 必ず基板に実装してからアクチュエ-タを操作して下さい。
PLEASE OPERATE THE ACTUATOR AFTER MOUNTING ON THE SUBSTRATE.

2. FPCについて
ABOUT FPC
補強フィルム材質はポリイミドを推奨します。ベースフィルムは25μmを推奨します。
接着剤は熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は導通不良の原因になりますので、染み出しが無い様、お願い致します。
RECOMMENDED STIFFENER MATERIAL: POLYIMIDE
RECOMMENDED BASE FILM THICKNESS: 25 MICROMETER
RECOMMENDED ADHESIVE: THERMOSETTING ADHESIVE
NOTE: PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

打抜き方向は導体側から補強板側を推奨致します。
RECOMMENDED PUNCHER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFENER FILM SIDE.



FPC構成推奨仕様
STRUCTURE OF FPC



適合金メッキFPC推奨寸法
仕上がり厚さ : 0.2±0.03
APPLICABLE FPC WITH GOLD PLATING
RECOMMENDED DIMENSION
THICKNESS :0.2±0.03

