

TS-120-G-A-1

TD-108-G-AA

(2,54 mm) .100"

TS, TD, HTS SERIES

# PRECISION MACHINED TERMINAL STRIPS

## SPECIFICATIONS

For complete specifications see  
www.samtec.com?TS,  
www.samtec.com?TD or  
www.samtec.com?HTS

### Insulator Material:

Black G.F. Polyester (TS, TD)  
Black Liquid Crystal Polymer (HTS)

### Terminal Material:

Brass, except Style G is  
Phosphor Bronze

### Plating:

Au over 50µ" (1,27 µm) Ni or  
Sn over 100µ" (2,54 µm) Cu  
or 50µ" (1,27 µm) Ni

### Operating Temp Range:

-55°C to +125°C with Gold  
-55°C to +105°C with Tin

### RoHS Compliant:

Yes

### Lead-Free Solderable:

Wave only

## RECOGNITIONS

For complete scope  
of recognitions see  
www.samtec.com/quality



**Mates with:**  
SS, SD, HSS, SL,  
SDL, ESS, ESD

**Note:** Some lengths,  
styles and options are  
non-standard, non-returnable.

**TYPE  
STRIP**


**1**

**NO. PINS  
PER ROW**


**PLATING  
OPTION**

**LEAD  
STYLE**


**TS**  
= Single  
Row Terminal  
Strip



**HTS**  
= Single Row  
High Temp  
Terminal Strip



**TD**  
= Double Row  
Terminal Strip



**-G**  
= 20µ" (0,51 µm) Gold  
Except -J & -L are  
10µ" (0,25 µm) Gold


**-T**

= Tin

**01 thru 32**  
= TS Series


**01 thru 36**  
= HTS & TD Series

**-AA**



Component No. = T-1R5-


**-A, -A-1, -A-2**



-A Component No. = T-1R0-  
-A-X Component No. = T-1R7

| LEAD STYLE | X (DIA)     | Y (±.015)   |
|------------|-------------|-------------|
| -A         | (0,46) .018 | (3,96) .156 |
| -A-1       | (0,64) .025 | (5,33) .210 |
| -A-2       | (0,89) .035 | (5,33) .210 |


**-C, -C-1, -C-2**



-C Component No. = T-1R2-  
-C-X Component No. = T-1R9-


| LEAD STYLE | X (DIA)     | Y (±.015)   |
|------------|-------------|-------------|
| -C         | (0,46) .018 | (3,96) .156 |
| -C-1       | (0,64) .025 | (5,33) .210 |
| -C-2       | (0,89) .035 | (5,33) .210 |

**-G-1**




Component No. = T-1R5-

**-J**



Component No. = S-1P1-

**-L-1, -L-2, -L-3**



Component No. = S-1W1

| LEAD STYLE | Y (DIA)      | Z (±.015)    |
|------------|--------------|--------------|
| -L-1       | (12,95) .510 | (17,86) .703 |
| -L-2       | (9,14) .360  | (14,05) .553 |
| -L-3       | (6,60) .260  | (11,51) .453 |

Due to technical progress, all designs, specifications and components are subject to change without notice.

**WWW.SAMTEC.COM**

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329  
SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0  
SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292  
SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385  
SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685