

# REG96PUN1RHU

temperature control relay REG - 96 x 48 mm -  
100..240 V AC - 1 relay NO



## Main

Range of product	Zelio Control
Product or component type	Modular measurement and control relays
Relay type	Temperature control relays
Product specific application	HVAC Heating or cooling Industrial machines Packaging
Relay name	REG
Outer dimension	1/8 DIN 96 x 48 mm
Analogue input type	Current 0...20 mA Current 4...20 mA Temperature probe Pt 100 Thermocouple thermocouple J, K, R, B, S, T, E, N, PLII Voltage 0...5 V Voltage 1...5 V Voltage 0...10 V Voltage 2...10 V Voltage 0...0.1 V
[Us] rated supply voltage	100...240 V AC
Output type	1 relay NO at 220 V AC / 3 A
Alarm output	3 SPDT
Communication port protocol	Modbus

## Complementary

Supply voltage limits	85...264 V
Measurement accuracy	0.3 % full scale
Sampling duration	200 ms
Power consumption in VA	12 VA at 100...240 V AC
Method of access	Slave
Transmission frame	RTU
Physical interface	RS485 non isolated
Exchange mode	Half duplex
Transmission rate	9600, 19200 kbit/s
Function available	PID Auto tuning Fuzzy logic Hysteresis on-off Manual operation Ramp 16 steps Soft start
Marking	CE
Operating position	Any position
Local signalling	1 LED red for process output 1 active (C1) 1 LED red for process output 2 active (C2) 1 LED for alarm output 1 active (D01) 1 LED for alarm output 2 active (D02) 1 LED for alarm output 3 active (D03) 1 LED green for setpoint value indicator (SV) 1 LED red for process value indicator (PV) 4 digits 7 segments red for process value 4 digits 7 segments green for setpoint value

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mounting support	Panel
------------------	-------

## Environment

Standards	CSA C22-2 No 24-93 EN 61010-1 EN 61326-1
Product certifications	GOST CURus (873)
Ambient air temperature for storage	-20...60 °C
Ambient air temperature for operation	-10...50 °C
Relative humidity	90 % without condensation
Operating altitude	2000 m
Storage altitude	3000 m
Vibration resistance	1 gn at 10...70 Hz conforming to IEC 60068-2-6
Shock resistance	5 gn conforming to IEC 60068-2-27
IP degree of protection	IP20 (rear) IP66 (front face) conforming to IEC 60529
NEMA degree of protection	NEMA 4X (front face)