



1750Y



NOTE: ALL LEADS 18.0" OUT MIN., STRIPPED .5"

DIMENSIONS:

A	2.500" ±0.063
B	3.328" ±0.125
C	3.060" ±0.063
D	1.875" ±0.063
E	2.376" ±0.063
G	0.185" X 0.370" ±0.015



ELECTRICAL DATA:

Turns ratio:	27.87 : 1
Inductance	@240V, 60Hz => 21.22H (Open circuit)
DCR	@ 20C, WHT - RED = 289.0 Ω ±20% @ 20C, BLK - GRN = 0.480 Ω ±20%
FREQ. RESP	@ 15W (305V), 70Hz - 15kHz, WHT - RED ±1db (1kHz Ref.)
Pri. Impedance	6200 Ω CT (305V)
Sec. Impedance	8 Ω (10.95V)
Power	15 WATTS



**HAMMOND
ELECTRONICS**

52 RANKIN PLACE,
 WATERLOO, ONTARIO, N2L 3Z5.
 PHONE (519) 886-6181
 FAX # (519) 886-9540

TITLE

OUTPUT TRANSFORMER

			DR BY IOAN POP
0	05/11/09	PRELIMINARY.	I.P. DATE 05/11/09
NO	DATE	REVISION	DIM IN(X)MM()

1750Y