


# eNOVA-945GSE

5.25" SBC with AUPS sub-system, Intel® Atom™ Processor N270 1.6 GHz, Wide range 9-28VDC input, Dual PCIe Mini card



## Features

1. Intel® Atom™ N270 Processor 1.6 GHz for ultra low voltage fan-less support
2. Equipped with AUPS sub-system acts as a simple UPS system
3. Support Dual PCIe mini card for expansions
4. Wide range 9-28V DC input
5. Support LVDS, TV-out, VGA display output
6. CF socket for storage expansion
7. TPM support

## Specifications

- ◆ CPU  
Intel® Atom™ Processor N270 1.6GHz with 533 MHz FSB 512K L2 Cache
- ◆ System Chipset  
Intel® 945GSE / Intel® ICH7M
- ◆ BIOS  
AMI BIOS
- ◆ Memory  
One 200-pin 400/533 DDR2 SDRAM SO-DIMM supported (system max. 2GB)
- ◆ Ethernet  
Dual Realtek PCIe 8111CP GbE Controller
- ◆ Graphic  
On Intel® Graphics Media Accelerator 950 (Intel® GMA 950)
- ◆ I/O Interface  
3 x RS-232 1 x RS-232/422/485  
6 x USB2.0 1 x LPT  
2 x SATA with 5V DC output  
1 x IDE 1 x 6pin header for KB/MS
- ◆ Expansions  
1 x PC/104+ (ISA+PCI bus)  
2 x PCIe mini card
- ◆ DC connector  
2pcs 1 x 2pin 5V power connector (Major for 2.5" HDD used)
- ◆ Digital I/O  
8-bit digital I/O (4-bit input, 4-bit output)
- ◆ Infrared Interface  
1 x 5-pin pin header
- ◆ Super IO  
ITE8718F
- ◆ Display Output  
Analog CRT Support for CRT Hot plug Support HDTV by component interface 18-bit dual-channel LVDS Support up to UXGA (1600x 1200)
- ◆ Audio  
AC'97 ALC655 codec
- ◆ SSD  
CF Type II
- ◆ TPM  
1 x 20pin pin header
- ◆ Watchdog Timer  
Software programmable supports 1~255 sec. system reset
- ◆ Power Supply  
Maximum input voltage range 9V~28V Recommend operating input voltage range 12V~24V  
1x internal 2 x 2-pin power connector
- ◆ Power Consumption  
1.19A@12V (Intel® Atom™ N270 processor with 1 GB DDR2)
- ◆ Temperature  
Operation: 0°C ~ 40°C with AUPS sub-system  
Operation: 0°C ~ 60°C without AUPS sub-system
- ◆ Humidity: Operation: 5% ~ 95%, non-condensing
- ◆ Dimensions: 203mm x 146mm
- ◆ Weight: GW:1000g, NW:400g



DDR2 533 CF Type II

## Packing List


|                                                          |         |
|----------------------------------------------------------|---------|
| 1 x eNOVA-945GSE single board computer                   |         |
| 1 x VGA cable (P/N: 32000-033804-RS)                     |         |
| 1 x KB/MS Y cable (P/N: 32000-023800-RS)                 |         |
| 1 x Audio cable (P/N: 32000-072100-RS)                   |         |
| 4 x RS-232 cable (P/N: 32200-000049-RS)                  |         |
| 2 x SATA 5V power output Cable Kit (P/N:32000-114000-RS) |         |
| 1 x USB cable (P/N:32000-070301-RS)                      |         |
| 1 x Mini jumper pack                                     |         |
| 1 x Utility CD                                           | 1 x QIG |

## Ordering Information

| Part No.              | Description                                                                                          |
|-----------------------|------------------------------------------------------------------------------------------------------|
| eNOVA-945GSE-N270-R10 | 5.25" SBC with AUPS sub-system, Intel® Atom™ N270 1.6 GHz, Wide range 9-28V DC input, Dual PCIe Mini |
| HDTV/CABLESET-01      | HDTV cable set with s-video, composite and component interfaces                                      |
| 32100-088600-RS       | SATA power cable                                                                                     |
| 32200-015100-RS       | LPT cable                                                                                            |
| 32100-192900-RS       | One 4-pin (2x2) to one 4-pin(1x4) DC power cable with terminal block                                 |
| 32200-000009-RS       | IDE flat cable 44p/44p                                                                               |
| 32200-833600-RS       | RS-422/485 cable                                                                                     |
| WMPCIE-V01-R10        | 802.11b+g PCIe mini card wireless LAN module with Atheros                                            |
| WMUSB-V01-R10         | 802.11b+g USB embedded module with VIA                                                               |
| TPM-WI01-R10          | 20-pin WINBOND TPM module, S/W management Tool                                                       |
| BATKIT-2S2P3800-R10   | 2S2P 7.4V 3800 mAh AUPS battery kit                                                                  |
| BAT-LI-2S2P3800       | 2S2P 7.4V 3800 mAh SMART battery                                                                     |
| BATKIT-4S2P3800-R10   | 4S2P 14.8V 3800 mAh AUPS battery kit                                                                 |
| BAT-LI-4S2P3800       | 4S2P 14.8V 3800 mAh SMART battery kit                                                                |

# NOVA-945GSE

5.25" SBC, Intel® Atom™ Processor N270 1.6 GHz, LVDS/ VGA/ HDTV, Dual PCIe Mini, Dual PCIe GbE, USB2.0, SATA, RoHS




## Features

1. Intel® Atom™ Processor N270 1.6 GHz for ultra low voltage fan-less support DDR2 400/533 SO-DIMM Memory support up to 2GB
2. Support Dual PCIe mini Card, PCI slot for expansion
3. Support LVDS, TV-out, VGA Display output
4. CF Socket for Storage Expansion
5. TPM support

## Specifications

- ◆ CPU  
Intel® Atom™ Processor N270 1.6GHz with 533 MHz FSB
- ◆ System Chipset  
Intel® 945GSE+ICH7M
- ◆ BIOS  
AMI Flash BIOS
- ◆ Memory  
One 200-pin 400/533 DDR2 SDRAM SO-DIMM supported (system max. 2GB)
- ◆ Ethernet  
Dual Realtek PCIe RTL8111CP GbE LAN
- ◆ Graphic  
Intel® Generation 3.5 integrated GFX Core (133 MHz)
- ◆ I/O Interface  
3 x RS-232 1 x RS-232/422/485  
6 x USB2.0 2 x SATA with 5V output  
1 x LPT 1 x IDE  
1 x 6-pin header for KB/MS
- ◆ Expansion  
1 x PC/104+ (ISA+PCI bus)  
2 x PCIe mini card  
1 x PCI
- ◆ Digital I/O  
8-bit digital I/O (4-bit input, 4-bit output)
- ◆ Infrared Interface  
1 x Infrared Interface by pin header
- ◆ Super IO  
ITE8718F
- ◆ Display Output  
Analog CRT Support for CRT Hot plug Support HDTV by component interface 18-bit dual-channel LVDS Support up to UXGA (1600 x 1200)
- ◆ Audio  
AC'97 ALC655 codec
- ◆ SSD  
CF Type II
- ◆ Watchdog Timer  
software programmable 1-255 sec. by super I/O
- ◆ TPM  
1 x 20-pin pinheader
- ◆ Power Supply  
AT/ATX Power
- ◆ Power Consumption  
5V@2.89A, 12V@0.04A (Intel® Atom™ N270 with 1GB DDR2)
- ◆ Temperature  
Operation: 0°C ~ 60°C (32 ~ 140° F)
- ◆ Humidity  
Operation: 5% ~ 95%, non-condensing
- ◆ Dimensions: 203 mm x 146 mm
- ◆ Weight: GW:1000g, NW:400g



SO-DIMM CF Type II

## Packing List

|                                          |         |
|------------------------------------------|---------|
| 1 x NOVA-945GSE single board computer    |         |
| 1 x VGA cable (P/N: 32000-033804-RS)     |         |
| 1 x KB/MS Y cable (P/N: 32000-023800-RS) |         |
| 1 x Audio cable (P/N: 32000-072100-RS)   |         |
| 2 x SATA cable (P/N: 32000-062800-RS)    |         |
| 4 x RS-232 cable (P/N: 32200-000049-RS)  |         |
| 1 x USB cable (P/N: 32000-070301-RS)     |         |
| 1 x Mini jumper pack                     |         |
| 1 x Utility CD                           | 1 x QIG |

## Ordering Information

| Part No.             | Description                                                                                                       |
|----------------------|-------------------------------------------------------------------------------------------------------------------|
| NOVA-945GSE-N270-R10 | 5.25" SBC, Intel® Atom™ Processor N270 1.6GHz, LVDS/ VGA/ HDTV, Dual PCIe Mini, Dual PCIe GbE, USB2.0, SATA, RoHS |
| HDTV/CABLESET-01     | HDTV cable set with S-Video, composite and component interfaces                                                   |
| 32200-000009-RS      | 44-pin 2.5" IDE cable                                                                                             |
| 32100-088600-RS      | SATA Power cable                                                                                                  |
| 32200-015100-RS      | LPT cable                                                                                                         |
| WMPCIE-V01-R10       | 802.11b+g PCIe mini card wireless LAN module with atheros                                                         |
| WMUSB-V01-R10        | 802.11b+g USB embedded module with VIA                                                                            |
| TPM-WI01-R10         | 20-pin WINBOND TPM module, S/W management tool                                                                    |
| 32200-833600-RS      | RS-422/485 cable                                                                                                  |