

# LCD Module Technical Specification

First Edition  
Dec 12, 2005  
Final Revision  
\*\*\*\*\*

Type No.

**T-52017D121J-FW-A-ABN**



Approved by (Quality Assurance Division)



Checked by (ACI Engineering Division)



Prepared by (ACI Engineering Division)

| No. | Item                                    | Page |
|-----|-----------------------------------------|------|
| --  | CONTENTS                                | 1    |
| 1   | APPLICATION                             | 2    |
| 2   | OVERVIEW                                | 3    |
| 3   | ABSOLUTE MAXIMUM RATINGS                | 4    |
| 4   | ELECTRICAL CHARACTERISTICS              | 4    |
| 5   | INTERFACE PIN CONNECTION                | 7    |
| 6   | INTERFACE TIMING                        | 9    |
| 7   | BLOCK DIAGRAM                           | 14   |
| 8   | MECHANICAL SPECIFICATION                | 15   |
| 9   | OPTICAL CHARACTERISTICS                 | 17   |
| 10  | RELIABILITY TEST CONDITION              | 19   |
| 11  | INSPECTION STANDARDS                    | 20   |
| 12  | HANDLING PRECAUTIONS FOR TFT-LCD MODULE | 21   |
| --  | PACKGING SPECIFICATION                  | 24   |
| --  | PRODUCTS NUMBER LABELING FORMS          | 28   |
| --  | LAMP UNIT FOR 12.1" SVGA                | 33   |

# 1. APPLICATION

This specification applies to color TFT-LCD module, T-52017D121J-FW-A-ABN.

These specification papers are the proprietary product of OPTREX and include materials protected under copyright of OPTREX. No part of this document may be reproduced in any form or by any means without the express written permission of OPTREX.

OPTREX does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a product specified in this document. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of OPTREX or of others.

OPTREX classifies the usage of the TFT-LCD module as follows. Please confirm the usage before using the product.

## (1) Standard Usage

Computers, office equipment, factory automation equipment, test and measurement equipment, communications, transportation equipment(automobiles, ships, trains, etc.), provided, however, that operation is not influenced by TFT-LCD directly.

## (2) Special Usage

Medical equipment, safety equipment, transportation equipment, provided, however, that TFT-LCD is necessary to its operation.

## (3) Specific Usage

Cockpit Equipment, military systems, aerospace equipment, nuclear reactor control systems, life support systems and any other equipment. OPTREX should make a contract that stipulate apportionment of responsibilities between OPTREX and our customer.

The product specified in this document is designed for “Standard Usage” unless otherwise specified in this document. If customers intend to use the product for applications other than those specified for “Standard Usage”, they should contact OPTREX sales representative in advance.

OPTREX has been making continuous effort to improve the reliability of its products. Customers should implement sufficient reliability design of their application equipments such as redundant system design, fail-safe functions, anti-failure features.

OPTREX assumes no responsibility for any damage resulting from the use of the product that does not comply with the instructions and the precautions specified in this document.

Please contact and consult a OPTREX sales representative for any questions regarding this product.

## 2. OVERVIEW

T-52017D121J-FW-A-ABN is 12.1" color TFT-LCD (Thin Film Transistor Liquid Crystal Display) module composed of LCD panel, driver ICs, control circuit, and backlight unit.

By applying 6 bit or 8 bit digital data,  $800 \times 600$ , 262 K-color or 16.7 M-color images are displayed on the 12.1" diagonal screen. Input power voltage is 3.3V for LCD driving.

The type of data and control signals are digital and transmitted via LVDS interface per Typ. 40MHz clock cycle.

Inverter for backlight is not included in this module. General specifications are summarized in the following table:

| ITEM                                  | SPECIFICATION                                        |
|---------------------------------------|------------------------------------------------------|
| Display Area (mm)                     | 246.0(H) $\times$ 184.5(V)<br>(12.106-inch diagonal) |
| Number of Dots                        | $800 \times 3$ (H) $\times$ 600 (V)                  |
| Pixel Pitch (mm)                      | 0.3075 (H) $\times$ 0.3075 (V)                       |
| Color Pixel Arrangement               | RGB vertical stripe                                  |
| Display Mode                          | Normally whiteTN                                     |
| Number of Color                       | 262 K(6 bit/color), 16.7 M(8 bit/color)              |
| Brightness (cd/m <sup>2</sup> )       | 1000                                                 |
| Wide Viewing Angle Technology         | Optical Compensation Film                            |
| Viewing Angle (CR $\geq$ 10)          | -60~60° (H) -75~45° (V)                              |
| Surface Treatment                     | Antireflection and hard-coating 2H                   |
| Electrical Interface                  | LVDS(6 bit/8 bit)                                    |
| Optimum Viewing Angle(Contrast ratio) | 6 o'clock                                            |
| Module Size (mm)                      | 280.0 (W) $\times$ 219.0 (H) $\times$ 17.8 (D)       |
| Module Mass (g)                       | 1150                                                 |
| Backlight Unit                        | CCFL, 4-tubes, edge-light, replaceable               |

Characteristic value without any note is typical value.

### 3. ABSOLUTE MAXIMUM RATINGS

| ITEM                                                  | SYMBOL                   | MIN. | MAX     | UNIT              |
|-------------------------------------------------------|--------------------------|------|---------|-------------------|
| Power Supply Voltage for LCD                          | VCC                      | 0    | 4.0     | V                 |
| Logic Input Voltage                                   | VI                       | -0.3 | VCC+0.3 | V                 |
| Lamp Voltage                                          | VL                       | 0    | 2000    | V <sub>rms</sub>  |
| Lamp Current                                          | IL                       | 0    | 18      | mA <sub>rms</sub> |
| Lamp Frequency                                        | FL                       | --   | 80      | kHz               |
| Operation Temperature(Panel) <small>Note 1,2)</small> | T <sub>op(Panel)</sub>   | -20  | 70      | °C                |
| Operation Temperature(Ambient) <small>Note 2)</small> | T <sub>op(Ambient)</sub> | -20  | 70      | °C                |
| Storage Temperature <small>Note 2)</small>            | T <sub>stg</sub>         | -20  | 80      | °C                |

[Note]

1) Measured at the center of active area and at the center of panel back surface

2) Top, Tstg ≤ 40°C : 90%RH max. without condensation

Top, Tstg > 40°C : Absolute humidity shall be less than the value of 90%RH at 40°C without condensation.

### 4. ELECTRICAL CHARACTERISTICS


(1) TFT-LCD

Ambient temperature: Ta = 25°C

| ITEM                            | SYMBOL | MIN. | TYP. | MAX. | UNIT  | Remarks         |
|---------------------------------|--------|------|------|------|-------|-----------------|
| Power Supply Voltages for LCD   | VCC    | 3.0  | 3.3  | 3.6  | V     | *1)             |
| Power Supply Currents for LCD   | ICC    | --   | 300  | 450  | mA    | VCC = 3.3 V *2) |
| Permissive Input Ripple Voltage | VRP    | --   | --   | 100  | mVp-p | VCC = 3.3V      |

\*1) Power and signals sequence:

$t_1 \leq 10 \text{ ms}$                        $200 \text{ ms} \leq t_4$   
 $0 < t_2 \leq 50 \text{ ms}$                  $200 \text{ ms} \leq t_5$   
 $0 < t_3 \leq 50 \text{ ms}$                  $0 \leq t_6$




VCC-dip conditions:

1) When  $2.6\text{ V} \leq VCC < 3.0\text{ V}$ ,  $t_d \leq 10\text{ ms}$

2) When  $VCC < 2.6\text{ V}$

VCC-dip conditions should also follow the power and signals sequence.



\*2) Typical current condition:

64-gray-bar pattern

600 line mode

$VCC = +3.3\text{ V}$ ,  $f_H = 37.9\text{ kHz}$ ,  $f_V = 60.0\text{ Hz}$ ,  $f_{CLK} = 40\text{ MHz}$

(2) Backlight


$T_a = 25^\circ\text{C}$

| ITEM                  | SYMBOL | MIN.   | TYP. | MAX. | UNIT  | Remarks                                        |
|-----------------------|--------|--------|------|------|-------|------------------------------------------------|
| Lamp Voltage          | VL     | --     | 540  | --   | Vrms  | IL = 12.0 mArms                                |
| Lamp Current          | IL     | 6.0    | 12.0 | 14.0 | mArms | * 2), *6)                                      |
| Lamp Frequency        | FL     | 30     | --   | 60   | kHz   | * 3)                                           |
| Starting Lamp Voltage | VS     | 1000   | --   | --   | Vrms  | $T_a = 25^\circ\text{C}$                       |
|                       |        | 1200   | --   | --   |       | $T_a = 0^\circ\text{C}$                        |
|                       |        | 1290   | --   | --   |       | $T_a = -20^\circ\text{C}$                      |
| Lamp Life Time        | LT     | 50,000 | --   | --   | h     | * 4), *5) IL = 12.0mArms, Continuous operation |

[Note]

\*1) Please use synchronous inverter.

\*2) Lamp Current measurement method (The current meter is inserted in low voltage line.)



\*3) Lamp frequency of inverter may produce interference with horizontal synchronous frequency, and this may cause horizontal beat on the display. Therefore, please adjust lamp frequency, and keep inverter as far from module as possible or use electronic shielding between inverter and module to avoid the interference.


\*4) Lamp life time is defined as the time either when the brightness becomes 50% of the initial value, or when the starting lamp voltage does not meet the value specified in this table.

\*5) The life time of the backlight depends on the ambient temperature. The life time will decrease under low/high temperature.

\*6) Please use the inverter which has symmetrical current wave form as follows,

The degree of unbalance: less than 10%

The ratio of wave height: less than  $\sqrt{2} \pm 10\%$



$I_{PH}$ : High side peak

$I_{PL}$ : Low side peak

The degree of unbalance =  $|I_{PH} - I_{PL}| / I_{rms} \times 100(\%)$   
The ratio of wave height =  $I_{PH}(\text{or } I_{PL}) / I_{rms}$

CURRENT WAVE FORM

## 5. INTERFACE PIN CONNECTION

### (1) CN 1(Interface Signal)


Used connector: FI-SEB20P-HFE

Corresponding connector: FI-S20S[for discrete Wire], FI-SE20M[for SMT]

| Pin No. | Symbol  | Function(ISP 6 bit compatibility mode)                    |                            | Function(ISP 8 bit compatibility mode) |
|---------|---------|-----------------------------------------------------------|----------------------------|----------------------------------------|
|         |         | 6 bit input                                               | 8 bit input                |                                        |
| 1       | VCC     | +3.3 V Power supply                                       |                            | ←                                      |
| 2       | VCC     | +3.3 V Power supply                                       |                            | ←                                      |
| 3       | GND     | GND                                                       |                            | ←                                      |
| 4       | GND     | GND                                                       |                            | ←                                      |
| 5       | Link 0- | R0, R1, R2, R3, R4, R5, G0                                | R2, R3, R4, R5, R6, R7, G2 | R0, R1, R2, R3, R4, R5, G0             |
| 6       | Link 0+ | R0, R1, R2, R3, R4, R5, G0                                | R2, R3, R4, R5, R6, R7, G2 | R0, R1, R2, R3, R4, R5, G0             |
| 7       | GND     | GND                                                       |                            | ←                                      |
| 8       | Link 1- | G1, G2, G3, G4, G5, B0, B1                                | G3, G4, G5, G6, G7, B2, B3 | G1, G2, G3, G4, G5, B0, B1             |
| 9       | Link 1+ | G1, G2, G3, G4, G5, B0, B1                                | G3, G4, G5, G6, G7, B2, B3 | G1, G2, G3, G4, G5, B0, B1             |
| 10      | GND     | GND                                                       |                            | ←                                      |
| 11      | Link 2- | B2, B3, B4, B5, DENA                                      | B4, B5, B6, B7, DENA       | B2, B3, B4, B5, DENA                   |
| 12      | Link 2+ | B2, B3, B4, B5, DENA                                      | B4, B5, B6, B7, DENA       | B2, B3, B4, B5, DENA                   |
| 13      | GND     | GND                                                       |                            | ←                                      |
| 14      | CLKIN-  | Clock -                                                   |                            | ←                                      |
| 15      | CLKIN+  | Clock +                                                   |                            | ←                                      |
| 16      | GND     | GND                                                       |                            | ←                                      |
| 17      | Link3-  | See: *2)                                                  | R0, R1, G0, G1, B0, B1     | R6, R7, G6, G7, B6, B7                 |
| 18      | Link3+  | See: *2)                                                  | R0, R1, G0, G1, B0, B1     | R6, R7, G6, G7, B6, B7                 |
| 19      | MODE    | Low=ISP 6 bit compatibility mode                          |                            | High=ISP 8 bit compatibility mode      |
| 20      | SC      | Scan direction control. ( Low : Normal , High : Reverse ) |                            | ←                                      |

\*1) The shielding case is connected with GND.

\*2) Recommended wiring of Pin 17,18 (6 bit input)



### (2) CN 2,3(Backlight)

Backlight-side connector: BHR-04VS-1 (JST)


Inverter-side connector: SM04(4.0)B-BHS-1(JST)

| Pin No. | Symbol | Function           |
|---------|--------|--------------------|
| 1, 2    | CTH    | VLH (High voltage) |
| 4       | CTL    | VL (Low voltage)   |


[Note]VLH - VL = VL

### (3) ISP data mapping


#### a. ISP 6 bit compatibility mode(6 bit input)



#### b. ISP 6 bit compatibility mode(8 bit input)



#### c. ISP 8 bit compatibility mode





## 6. INTERFACE TIMING

LVDS transmitter input signal

### (1) Timing Specifications


| ITEM |            |               | SYMBOL           | MIN  | TYP  | MAX  | UNIT             |
|------|------------|---------------|------------------|------|------|------|------------------|
| DCLK | Frequency  |               | f <sub>CLK</sub> | 35   | 40   | 42   | MHz              |
|      | Period     |               | t <sub>CLK</sub> | 23.8 | 25   | 28.6 | ns               |
| DENA | Horizontal | Active Time   | t <sub>HA</sub>  | 800  | 800  | 800  | t <sub>CLK</sub> |
|      |            | Blanking Time | t <sub>HB</sub>  | 20   | 256  | --   | t <sub>CLK</sub> |
|      |            | Frequency     | f <sub>H</sub>   | 35.2 | 37.9 | 39.2 | kHz              |
|      |            | Period        | t <sub>H</sub>   | 25.5 | 26.4 | 28.4 | μs               |
|      | Vertical   | Active Time   | t <sub>VA</sub>  | 600  | 600  | 600  | t <sub>H</sub>   |
|      |            | Blanking Time | t <sub>VB</sub>  | 3    | 28   | --   | t <sub>H</sub>   |
|      |            | Frequency     | f <sub>V</sub>   | 55   | 60   | 64.2 | Hz               |
|      |            | Period        | t <sub>V</sub>   | 15.6 | 16.7 | 18.2 | ms               |

[Note]


- 1) DENA (Data Enable) should always be positive polarity as shown in the timing specification.
- 2) DCLK should appear during all invalid period.
- 3) LVDS timing follows the timing specifications of LVDS receiver IC: THC63LVDF84B(Thine).

## (2) Timing Chart

### a. Horizontal Timing Chart



### b. Vertical Timing Chart



### (3) Color Data Assignment

#### a. 6 bit input

| COLOR          |           | INPUT DATA |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|----------------|-----------|------------|----|----|----|----|-----|--------|----|----|----|----|-----|--------|----|----|----|----|-----|
|                |           | R DATA     |    |    |    |    |     | G DATA |    |    |    |    |     | B DATA |    |    |    |    |     |
|                |           | R5         | R4 | R3 | R2 | R1 | R0  | G5     | G4 | G3 | G2 | G1 | G0  | B5     | B4 | B3 | B2 | B1 | B0  |
|                |           | MSB        |    |    |    |    | LSB | MSB    |    |    |    |    | LSB | MSB    |    |    |    |    | LSB |
| BASIC<br>COLOR | BLACK     | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | RED(63)   | 1          | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | GREEN(63) | 0          | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | BLUE(63)  | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   |
|                | CYAN      | 0          | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1   |
|                | MAGENTA   | 1          | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   |
|                | YELLOW    | 1          | 1  | 1  | 1  | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | WHITE     | 1          | 1  | 1  | 1  | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1   |
| RED            | RED(1)    | 0          | 0  | 0  | 0  | 0  | 1   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | RED(2)    | 0          | 0  | 0  | 0  | 1  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                | RED(62)   | 1          | 1  | 1  | 1  | 1  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | RED(63)   | 1          | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
| GREEN          | GREEN(1)  | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 1   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | GREEN(2)  | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 1  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                | GREEN(62) | 0          | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 0   | 0      | 0  | 0  | 0  | 0  | 0   |
|                | GREEN(63) | 0          | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0   |
| BLUE           | BLUE(1)   | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 1   |
|                | BLUE(2)   | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 1  | 0   |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                |           |            |    |    |    |    |     |        |    |    |    |    |     |        |    |    |    |    |     |
|                | BLUE(62)  | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 0   |
|                | BLUE(63)  | 0          | 0  | 0  | 0  | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1   |

[Note]

1) Definition of gray scale

Color (n) --- n indicates gray scale level.

Higher n means brighter level.

2) Data

1:High, 0: Low

b. 8 bit input

| COLOR          |            | INPUT DATA |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|----------------|------------|------------|----|----|----|----|-----|----|-----|--------|----|----|----|----|----|-----|----|--------|----|----|----|----|----|----|-----|---|
|                |            | R DATA     |    |    |    |    |     |    |     | G DATA |    |    |    |    |    |     |    | B DATA |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            | R7         | R6 | R5 | R4 | R3 | R2  | R1 | R0  | G7     | G6 | G5 | G4 | G3 | G2 | G1  | G0 | B7     | B6 | B5 | B4 | B3 | B2 | B1 | B0  |   |
| MSB            |            |            |    |    |    |    | LSB |    | MSB |        |    |    |    |    |    | LSB |    | MSB    |    |    |    |    |    |    | LSB |   |
| BASIC<br>COLOR | BLACK      | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | RED(255)   | 1          | 1  | 1  | 1  | 1  | 1   | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | GREEN(255) | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1  | 1   | 1  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | BLUE(255)  | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 1      | 1  | 1  | 1  | 1  | 1  | 1  | 1   | 1 |
|                | CYAN       | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1  | 1   | 1  | 1      | 1  | 1  | 1  | 1  | 1  | 1  | 1   | 1 |
|                | MAGENTA    | 1          | 1  | 1  | 1  | 1  | 1   | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 1      | 1  | 1  | 1  | 1  | 1  | 1  | 1   | 1 |
|                | YELLOW     | 1          | 1  | 1  | 1  | 1  | 1   | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1  | 1   | 1  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | WHITE      | 1          | 1  | 1  | 1  | 1  | 1   | 1  | 1   | 1      | 1  | 1  | 1  | 1  | 1  | 1   | 1  | 1      | 1  | 1  | 1  | 1  | 1  | 1  | 1   | 1 |
| RED            | RED(1)     | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 1   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | RED(2)     | 0          | 0  | 0  | 0  | 0  | 0   | 1  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                | RED(255)   | 1          | 1  | 1  | 1  | 1  | 1   | 1  | 1   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
| GREEN          | GREEN(1)   | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 1  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                | GREEN(2)   | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 1   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                | GREEN(255) | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 1      | 1  | 1  | 1  | 1  | 1  | 1   | 1  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 0   | 0 |
| BLUE           | BLUE(1)    | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 0  | 1   |   |
|                | BLUE(2)    | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 0      | 0  | 0  | 0  | 0  | 0  | 1  | 0   |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                |            |            |    |    |    |    |     |    |     |        |    |    |    |    |    |     |    |        |    |    |    |    |    |    |     |   |
|                | BLUE(255)  | 0          | 0  | 0  | 0  | 0  | 0   | 0  | 0   | 0      | 0  | 0  | 0  | 0  | 0  | 0   | 0  | 1      | 1  | 1  | 1  | 1  | 1  | 1  | 1   | 1 |

[Note]

1) Definition of gray scale

Color (n) --- n indicates gray scale level.


Higher n means brighter level.

2) Data


1:High, 0: Low

(4) Display Position and Scan Direction

D(X,Y) shows the data number of input signal for LCD panel signal processing PCB.



## 7. BLOCK DIAGRAM




(1) Front Side



(Unit: mm)

## (2) Rear Side



CN1 : FI-SEB20P-HFE (JAE)  
CN2, CN3: BHR-04VS-1 (JST)

UNDEFINED TOLERANCES TO BE  $\pm 0.5\text{mm}$ .  
EXCEPT FOR THICKNESS OF PET FILM.

(Unit:mm)

### [Note]

We recommend you referring to the detailed drawing for your design.  
Please contact our company sales representative when you need the detailed drawing.



## 9. OPTICAL CHARACTERISTICS

Ta=25°C, VCC=3.3V, Input Signals: Typ. Values shown in Section 6

| ITEM                 |            | SYMBOL          | CONDITION                            | MIN    | TYP    | MAX   | UNIT              | Remarks   |
|----------------------|------------|-----------------|--------------------------------------|--------|--------|-------|-------------------|-----------|
| Contrast Ratio       |            | CR              | $\theta_V=0^\circ, \theta_H=0^\circ$ | 500    | 700    | --    | --                | *1)*2)*5) |
| Luminance            |            | L <sub>w</sub>  | $\theta_V=0^\circ, \theta_H=0^\circ$ | 800    | 1000   | --    | cd/m <sup>2</sup> | *1)*5)    |
| Luminance Uniformity |            | $\Delta L_w$    | $\theta_V=0^\circ, \theta_H=0^\circ$ | --     | --     | 30    | %                 | *1)*3)*5) |
| Response Time        |            | t <sub>r</sub>  | $\theta_V=0^\circ, \theta_H=0^\circ$ | --     | 6      | --    | ms                | *1)*4)*5) |
|                      |            | t <sub>f</sub>  | $\theta_V=0^\circ, \theta_H=0^\circ$ | --     | 19     | --    | ms                | *1)*4)*5) |
| Viewing Angle        | Horizontal | $\theta_H$      | CR ≥ 10                              | -45~45 | -60~60 | --    | °                 | *1)*5)    |
|                      | Vertical   | $\theta_V$      |                                      | -40~30 | -75~45 | --    | °                 | *1)*5)    |
|                      | Horizontal | $\theta_H$      | CR ≥ 5                               | -65~65 | -80~80 | --    | °                 | *1)*5)    |
|                      | Vertical   | $\theta_V$      |                                      | -50~40 | -80~55 | --    | °                 | *1)*5)    |
| Image sticking       |            | t <sub>is</sub> | 2 h                                  | --     | --     | 2     | s                 | *6)       |
| Color Coordinates    | Red        | R <sub>x</sub>  | $\theta_V=0^\circ, \theta_H=0^\circ$ | 0.549  | 0.579  | 0.609 | --                | *1)*5)    |
|                      |            | R <sub>y</sub>  |                                      | 0.296  | 0.326  | 0.356 |                   |           |
|                      | Green      | G <sub>x</sub>  |                                      | 0.304  | 0.334  | 0.364 |                   |           |
|                      |            | G <sub>y</sub>  |                                      | 0.497  | 0.527  | 0.557 |                   |           |
|                      | Blue       | B <sub>x</sub>  |                                      | 0.134  | 0.164  | 0.194 |                   |           |
|                      |            | B <sub>y</sub>  |                                      | 0.125  | 0.155  | 0.185 |                   |           |
|                      | White      | W <sub>x</sub>  |                                      | 0.283  | 0.313  | 0.343 |                   |           |
|                      |            | W <sub>y</sub>  |                                      | 0.299  | 0.329  | 0.359 |                   |           |


[Note]

These items are measured using CS1000(MINOLTA) for color coordinates, EZContrast(ELDIM) for viewing angle and CS1000 or BM-5A(TOPCON) for others under the dark room condition (no ambient light) after more than 30 minutes from turning on the lamp unless noted.

Condition: IL = 12.0 mArms, FL=55kHz

\*1) Measurement Point

Contrast Ratio, Luminance, Response Time, Viewing Angle, Color Coordinates: DisplayCenter  
Luminance Uniformity: point 1~5 shown in a figure below




\*2) Definition of Contrast Ratio

CR=Luminance with all white pixels / Luminance with all black pixels


\*3) Definition of Luminance Uniformity

$$\Delta L_w = [L_w(\text{MAX})/L_w(\text{MIN}) - 1] \times 100$$

\*4) Definition of Response Time




\*5) Definition of Viewing Angle( $\theta_v$ ,  $\theta_H$ )



\*6) Image sticking:

Continuously display the test pattern shown in the figure below for two-hours. Then display a completely white screen. The previous image shall not persist more than two seconds at 25°C.



TEST PATTERN FOR IMAGE STICKING TEST

## 10. RELIABILITY TEST CONDITION

### (1) Temperature and Humidity

| TEST ITEM                                   | CONDITIONS                                     |
|---------------------------------------------|------------------------------------------------|
| HIGH TEMPERATURE<br>HIGH HUMIDITY OPERATION | 40°C, 90%RH, 240 h<br>(No condensation)        |
| HIGH TEMPERATURE OPERATION                  | 70°C, 240 h                                    |
| LOW TEMPERATURE OPERATION                   | -20°C, 240 h                                   |
| HIGH TEMPERATURE STORAGE                    | 80°C, 240 h                                    |
| LOW TEMPERATURE STORAGE                     | -20°C, 240 h                                   |
| THERMAL SHOCK                               | BETWEEN -20°C (1h) and 80°C(1h),<br>100 CYCLES |

### (2) Shock & Vibration

| ITEM                         | CONDITIONS                                                                                                                                                                                                                                                               |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SHOCK<br>(NON-OPERATION)     | Shock level: 1470m/s <sup>2</sup> (150G)<br>Waveform: half sinusoidal wave, 2ms<br>Number of shocks: one shock input in each direction of three mutually perpendicular axes for a total of six shock inputs                                                              |
| VIBRATION<br>(NON-OPERATION) | Vibration level: 9.8m/s <sup>2</sup> (1.0G)<br>Waveform: sinusoidal<br>Frequency range: 5 to 500Hz<br>Frequency sweep rate: 0.5 octave /min<br>Duration: one sweep from 5 to 500 Hz in each of three mutually perpendicular axis(each x,y,z axis: 1 hour, total 3 hours) |

### (3) Judgment standard

The judgment of the above tests should be made as follow:

Pass: Normal display image, no damage of the display function. (ex. no line defect)

Partial transformation of the module parts should be ignored.

Fail: No display image, damage of the display function. (ex. line defect)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera:](#)

[T-52017D121J-FW-A-ABN](#)