

1

2

3

4

A

B

C

D

A

B

C

D

1.00 TYP

N x 2.00
SEE NOTE 3

POS.3

POS.1

2.00

4.00

C

D

POS.4

POS.2

PLATING
ZONE

(POST LENGTH)
SEE NOTE 8

1.00 OR 1.50 (SEE NOTE 9)

STACK HEIGHT ± 0.25
SEE NOTE 7

1.50

1.50

OAL
(OVER ALL LENGTH)
(SEE PIN STYLE)

3.00 ± 0.25

2.00 TYP

0.51 REF

(N-1) x 2.00

SEE NOTE 3

$\oplus 0.20(M) B C$

2.00

X

$\varnothing 0.80 \pm 0.10$ TYP

$\oplus 0.20(M) X Y$

2.00

Y

(N-1) x 2.00

(RECOMMENDED HOLE PATTERN)

$\square 0.51 \pm 0.02$ TYP REF

$\oplus 0.20(M) B D$

B

2.00 TYP

spec ref	-	dr	wwcadmin	2010/10/31	projection	MM	size	A3	scale	10:1
tolerance std	ISO 406 ISO 1101	eng	Guo-Min Sun	2014/10/29	chr	-	ecn no	ELX-N-19241-1	rel level	Released
surface	ISO 1302	appr	Feagle Pan	2014/10/29	product family	MINITEK	rel level	Released	rev	K
linear	0.X ± 0.5 0.XX ± 0.25 0.XXX ± 0.150	www.fci.com	cat. no.	-	Product - Customer Drw	sheet 1 of 2				
angular	0° $\pm 3^\circ$									



2.0MM UNSHROUDED HEADER
BOARD TO BOARD THRU-HOLE

PRODUCT NUMBER DESCRIPTION :
59132 - X XX - XX - XXX XLF

PLATING
S = 0.38µm GOLD ON CONTACT AREA
0.38µm GOLD ON TAIL
G = 0.76µm GOLD ON CONTACT AREA
0.76µm GOLD ON TAIL
F = 0.20µm GOLD ON CONTACT AREA
0.20µm GOLD ON TAIL
T = 0.76µm GOLD ON CONTACT AREA
2.54µm 100% MATTE TIN ON TAIL
H = GOLD FLASH ON CONTACT AREA
2.54µm 100% MATTE TIN ON TAIL


LEAD FREE (SEE NOTE 11)
RETENTION (SEE NOTES 6 & 10)
R: RETENTIVE LEG
STACKER HEIGHT (SEE NOTE 7)
PACKAGING: - = BAGS
(SEE NOTE 5) U = TUBES
POSITIONS PER ROW = "N"
(02 TO 25)
OMIT FROM PRODUCT NUMBER FOR
LEAD FREE WITH RETENTIVE LEG PRODUCT

- NOTES:
- 1. MATERIAL HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL 94V-0, COLOR BLACK
 - 2. MATERIAL TERMINAL: COPPER ALLOY
 - ③ TO DETERMINE DIMENSIONS:
N=NUMBER OF POSITIONS PER ROW
EX.: 10 POS., N x 2.00 = 20.00 TOTAL POSITIONS
 - 4. 0.9kg MIN. PIN RETENTION IN EITHER DIRECTION.
 - 5. PACKAGING;
(A) STANDARD PACKAGING: IN POLY BAGS.
(B) SPECIAL PACKAGING: IN TUBE.
FOR ALL SPECIAL PACKAGING,FCI MUST BE
CONTACTED FOR AVAILABILITY IN SIZE REQUESTED.

PIN STYLE	OAL
22	08.2
24	09.6
26	10.2
28	11.8
30	13.5
32	14.1
34	15.6
36	17.1
38	19.1
40	21.1
42	18.0

- ⑨. DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.
- ⑩. OMIT FROM PRODUCT NUMBER IF FEATURE IS NOT APPLICABLE.
- ⑪. P/N:59132-XXXLF IS SAME AS P/N:59132-XXX. THE SUFFIX 'LF' IS ADDED FOR EASY LEAD FREE IDENTIFICATION.
- 12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- 13. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.
- 14. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 15. A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

- ⑥. RETENTION LEG:
2.3kg MAX INSERTION FORCE AND 1 kg MIN RETENTION FORCE PER RETENTIVE PIN USING 1.57 THICK CIRCUIT BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER. RETENTION IS TWO PINS PER PART ADJACENT TO ONE ANOTHER.
- ⑦. STACK HEIGHT IS DETERMINED BY CUSTOMER APPLICATION REQUIREMENTS. SPECIFIED IN mm.
EXAMPLE: 3.7mm STACK HEIGHT=59132-XXX-XX-037X.
- ⑧. POST LENGTH IS DETERMINED BY: (OAL)-(3.00)-(STACK HGT.)
=POST LENGTH.MINIMUM MATING LENGTH TO BE 2.0mm.

dr	wcadmin	2010/10/31	projection 	MM 	size	A3	scale	5:1	
eng	Guo-Min Sun	2014/10/29			ecn no	ELX-N-19241-1			
chr	-	-			product family	MINITEK			
appr	Feagle Pan	2014/10/29			rel level	Released			
			2.0MM UNSHROUDED HEADER		dwg no	59132		rev	K
www.fci.com			BOARD TO BOARD THRU-HOLE						
cat. no.			-		Product - Customer Drw			sheet 2 of 2	

FCI
Copyright FCI.