


Product number C12500_MIRA-M

| | | | |
|-----------------|---------------|-------------|------------|
| Family | Mira | FWHM | 28 degrees |
| Type | Lens | Efficiency | 83 % |
| LED | MT-G | cd/lm | 2.200 |
| Color | Clear | Gerber File | Available |
| Diameter | 32.4 mm | | |
| Height | 14.7 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | - | | |
| Fastening | - | | |
| Status | On production | | |


Product number CA12503_MIRA-M

| | | | |
|-----------------|---------------|-------------|-------------------|
| Family | Mira | FWHM | 28 degrees |
| Type | Assembly | Efficiency | 83 % |
| LED | MT-G | cd/lm | (simulated) 0.000 |
| Color | White | Gerber File | Available |
| Diameter | 35 mm | | |
| Height | 15.8 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | On production | | |


Product number C12501_MIRA-W

| | | | |
|-----------------|---------------|-------------|------------|
| Family | Mira | FWHM | 38 degrees |
| Type | Lens | Efficiency | 80 % |
| LED | MT-G | cd/lm | 1.400 |
| Color | Clear | Gerber File | Available |
| Diameter | 32.4 mm | | |
| Height | 14.7 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | - | | |
| Fastening | - | | |
| Status | On production | | |


Product number CA12504_MIRA-W

| | | | |
|-----------------|---------------|-------------|-------------------|
| Family | Mira | FWHM | 44 degrees |
| Type | Assembly | Efficiency | 82 % |
| LED | MT-G | cd/lm | (simulated) 0.000 |
| Color | White | Gerber File | Available |
| Diameter | 35 mm | | |
| Height | 15.8 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | On production | | |

Product number C12502_MIRA-WW

| | | | |
|-----------------|---------------|-------------|------------|
| Family | Mira | FWHM | 58 degrees |
| Type | Lens | Efficiency | 81 % |
| LED | MT-G | cd/lm | 0.900 |
| Color | Clear | Gerber File | Available |
| Diameter | 32.4 mm | | |
| Height | 14.7 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | - | | |
| Fastening | Glue | | |
| Status | On production | | |

Product number CA12505_MIRA-WW

| | | | |
|-----------------|---------------|-------------|-------------------|
| Family | Mira | FWHM | 66 degrees |
| Type | Assembly | Efficiency | 81 % |
| LED | MT-G | cd/lm | (simulated) 0.000 |
| Color | White | Gerber File | Available |
| Diameter | 35 mm | | |
| Height | 15.8 mm | | |
| Style | Round | | |
| Optic Material | PC | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | On production | | |



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for MT-G series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PC with high UV and temperature resistance (120 degrees of Celcius / 248 degrees of Fahrenheit). Allows use of high current and temperature conditions.

Please find more information about used materials from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PC%20Makrolon%202400_2407_2456_2458-UL.pdf

- Optic holder molded by high quality PC material (120 dergees of Celcius / 248 degrees of Fahrenheit).
- Fastening to heat sink with a PU foam adhesive tape of automotive grade. Please find fastening details by clicking link: http://www.ledil.com/datasheets/DataSheet_TAPE.pdf


NOTE 1: We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the tape.

NOTE 2: Assembly to the surface must be made straight, so the tape bonds constant and balanced with fastening surface. Slanted assembly might cause unbalanced bond to the surface. All surfaces where tape is applied must be clean, dry and free from grease and dirt.


If cleaning of PCB surfaces is needed, please follow strictly the cleaning instructions of your LED manufacturer - this is important as cleaning shall under no circumstances damage LEDs or other electronics components on the PCB.

Further note that optical components shall not be cleaned with any chemicals - only micro fiber cloth may be used to remove fingerprints or other traces from handling.


Relative intensity of C12501_MIRA-W



Relative intensity of C12502_MIRA-WW (MT-G)



Relative intensity of CA12505_MIRA-WW (MT-G)




D


C

B


A




Isometric view



Bottom view



Front view



Top view

Dimension D:

- C12500_MIRA-M 29,7mm
- C12501_MIRA-W 28,4mm
- C12502_MIRA-WW 28,4mm

Material: PC

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

DRAWING TITLE


Datasheet MIRA lens

| | | | | | | |
|--------------------|--------------------|-----------|--|--|---------------------|----------|
| DRAWN BY mav | DATE 02.04.2012 | SIZE A4 | | | DRAWING NUMBER - | REV 1 |
| CHECKED BY sn | DATE 02.04.2012 | SCALE 1:1 | | | WEIGHT(g) | |
| DESIGNED BY mav | DATE 29.11.2011 | SHEET 1/1 | | | | |


D

A


Luminaire: Ledil Oy C12500-Mira-M (Cree MT-G 714lm @ 250mA) Efficiency=83%
Lamps: 1 x Cree MT-G 714lm @ 250mA




Luminaire: Ledil Oy C12501-Mira-W (Cree MT-G 714lm @ 250mA) Efficiency=80%
Lamps: 1 x Cree MT-G 714lm @ 250mA




Luminaire: Ledil Oy C12502-Mira-WW (Cree MT-G 714lm @ 250mA) Efficiency=81%
Lamps: 1 x Cree MT-G 714lm @ 250mA



Luminaire: Ledil Oy C12500-Mira-M (Cree MT-G 714lm @ 250mA) Efficiency=83%
Lamps: 1 x Cree MT-G 714lm @ 250mA



Luminaire: Ledil Oy C12501-Mira-W (Cree MT-G 714lm @ 250mA) Efficiency=80%
Lamps: 1 x Cree MT-G 714lm @ 250mA



Luminaire: Ledil Oy C12502-Mira-WW (Cree MT-G 714lm @ 250mA) Efficiency=81%
Lamps: 1 x Cree MT-G 714lm @ 250mA

