


THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED
TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS
MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT
WRITTEN AUTHORIZATION FROM AMP INCORPORATED,
HARRISBURG, PA.

WGC NO. 603225

UNIT OF MEASURE	A	B	C	D	E	L		MAX. BUNDLE DIA.	MIN. TENSILE STRENGTH
INCHES	.393	.501	.299	.325	.063	8.93		2.0	120 lbs.
MM	9.98	12.72	7.59	8.26	1.60	226.		50.8	54.43 kg.



NOTES:

1. MOISTURIZED 1 TO 2.5% WATER.
2. PACKAGED IN HEAT SEALED 3 MIL POLYBAG WITH LABEL PER DWG 404707.

3 OBSOLETE

4 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

APC ENGINEERING

JUL 13 1990

ISSUED BY CCIS

CUSTOMER
DRAWING
UNPUBLISHED

	3-603225-9	NATURAL 500 TY2HL	
	3-603225-0 	BLACK 500 TY2HLB	
	4-603225-9 	NATURAL 50 TY2HD	
	4-603225-0	BLACK 50 TY2HDB	

DWG SIZE	PART No.	DESCRIPTION	ITEM NO
-------------	----------	-------------	------------

REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REVISION)

QTY. REQ'D. PER ASSY.

PARTS LIST

		MATERIAL NYLON 6/6		HEAT TREAT		FINISH	
		DIMENSIONS ARE IN INCHES		DRAWN BY: AD-TEK/VL		DATE: 6/25/90	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHECK BY: BJM 6/90		APPROVED BY:	
		2 PL DEC ±		AMP AMP INCORPORATED Harrisburg, Pa..		RELEASE: J. Hamed 6/90	
		3 PL DEC ± .039					
		4 PL DEC ±					
		ANGLES ±		NAME: HEAVY DUTY CABLE TIE 8-7/8 INCH			
		SURF TEXTURE: ✓					
AEG 28NOV 09		REMOVE BURRS, BREAK SHARP EDGES, .015 R. MAX.					
211-6/90				SCALE:		DRAWING No.: 603225	
APD DATE		A		SHEET : 1 OF 1		REV.: B1	