



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'HSTTVA50-Y'

Your search criteria matched only one product, shown below

HSTTVA50-Y



Dual Wall Polyolefin DAMP-SHRINK™ Heat Shrink Tubing in 6" Pieces

- For damp locations
- Flexible tubing with an adhesive inner wall which seals and protects components from moisture and corrosion
- For use when a flexible adhesive lined tubing is needed
- Material Type: Polyolefin Cross -Linked with adhesive
- Shrink ratio: 2:1
- Temperature range: -67°F to 230°F (-55°C to 110°C)
- Flammability: Outer wall flame retardant
- Voltage rating: 600 V
- Mil Spec: AMSDTL-23053/4 Class 2

	Part Number	HSTTVA50-Y
	RoHS Compliancy Status	Compliant
	Part Description	Dual Wall Adhesive Lined Thin Wall Heat Shrink (UL224 VWV)
	Material	Polyolefin Cross-linked with adhesive
	Color	Black
	Military Specification	AMS-DTL-23053/4 Class 2
	Length (In.)	6.00
	Length (mm)	152.4
	Flammability Rating	Outer Wall Flame Retardant
	Max. Recovered I.D. (In.)	.250
	Max. Recovered I.D. (mm)	6.4
	Min. Expanded I.D. (In.)	.500
	Min. Expanded I.D. (mm)	12.7
	Nominal Diameter (In.)	.500
	Nominal Diameter (mm)	12.7
	Nominal Recovered Wall Thickness (In.)	.032
	Nominal Recovered Wall Thickness (mm)	0.8
	Pieces per Package	4
	Pricing Description	Heat Shrink Thin, Adhesive, .50"(12.7mm) Dia
	Shrink Ratio	2:1
	Temperature Range	-67°F to 230°F
	Min. Order UOM	PK
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.