




Part Number & Date Code Printing

PART NUMBER						Plating: 0.76» AU
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	G±0.25	
09	30.81	24.99	16.96	16.79	5.90	D09P23B6GL4A**
15	39.14	33.32	25.18	25.12	5.90	D15P23B6GL4A**
25	53.03	47.04	39.12	38.84	5.70	D25P23B6GL4A**
37	69.32	63.50	55.68	55.30	5.70	D37P23B6GL4A**

REQUIREMENTS

Technical characteristics:

Shell: steel tin/Zinc Cr3 plated

Insulators: self-extinguishing black polyster, ULclass94V0

Contacts size 20: brass, gold on mating end, bright tin on termination end over nickel on entire contact

Cycles : 500 for protection 6

Harpoons: phosphor bronze, tin plated

Metal plate for electrical continuity: brass, tin/Zinc Cr3 plated

Nuts: brass, tin/Zinc Cr3 plated torque: 0.7N/m

Electrical characteristics:

max. current rating: 5A

Test voltage: 1000V

Rated voltage: 300V

Contact resistance: ≤15mΩ

Shell resistance: ≤5mΩ


Insulation resistance: ≥5000MΩ

Climatic characteristics:


Operating temperature range: -55°C +125°C

Dimensions:

in accordance with MIL-C-24308




SECTION HH




LF FOR LEAD FREE

SPECIAL CODE 4A-SPECIAL CLINCH NUT




PC card drilling dimensions(after plating)

(thickness 1.60±0.20mm)



FOR ROHS DETAILS REFER DWG.NO: C01-8646-0000

mat'l. code SEE.NOTES				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family DELTA-D										
ltr	ecn no	dr	date	tolerances unless		otherwise specified				title										
B	05-0124	JS	2005/07/27	angles	linear	0.X± 0.1				MALE DELTA D RIGHT NGLED WITH NUT,										
C	06-0074	SK	2006/06/08			0.XX± 0.1				HARPOON & METAL PLATE .SP4A										
D	ELXI-I-15060	AB	2013/06/25			X±1°				0.XXX± 0.1		scale 1:1		dwg no						
-	-	-	-	dr	JOHN.SLEEBA		2005/06/14				sheet 1 of 1								size	5
-	-	-	-	enr	ALIAS.BABU		2013/06/25				C01-8646-0736								A3	
-	-	-	-	chr	MITHUN.PAUL		2013/06/25													
-	-	-	-	appd	BIJU.K.PAUL		2013/06/25				type								CUSTOMER Drawing	
sheet index		revision	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
		sheet	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	