



SIGN	DATE	DESCRIPTION	APPROVER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



N=Number of contacts



Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/450VAC
- Current rating: 10A/10A
- Wire range: 0.75-1.5mm²
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval:

RoHS Compliant

PART NUMBER:

OSTHAXX2150

No. of Poles

02: 2 Poles

03: 3 Poles

... ..

12: 12 Poles

COLOR


0: Black

2: Red

5: Green (Standard)

8: Grey

C: Multiple Colors



P.C.B. LAYOUT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE							
OSTHA-7.62mm Horizontal (180° wire inlet) series, 2p-12p							
PART NO.				DWG NO.			
OSTHAXX2150				OSTHAXX2150.DWG			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		
Shi Jun 2006.11.01		Marvin 2006.11.01	Steady 2006.10.11	Steady 2006.10.11			
					Tolerance		
					X. ±0.50		
					X.X ±0.30		
					X.XX ±0.10		
					X° ±1°		