



Flush mounting panel

Part no. M22-E1

Article no. 216541

Only in conjunction with a corresponding enclosure and when properly mounted.

No legend plates possible when arranged in column.

Program

Range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Accessories			Surface mounting enclosure
Basic function accessories			Flush mounting plates
Single unit/Complete unit			Single unit
			No legend plates possible with vertical arrangements Degree of protection only in conjunction with a suitable enclosure and correct mounting. Aluminium light anodized, including M22-XE...
Protection type			IP65
Number of locations		Qty.	1
Colour			
			
RAL Value			RAL 7035
Connection to SmartWire-DT			no

Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified
Degree of Protection	UL/CSA Type 3R, 4X, 12, 13



Technical data according to ETIM 4.0

Width		mm	72
Height		mm	72
Material			aluminum
Number of locations			1
Openings diameter		mm	22
Color			-

CAD-Data

Product standards CAD data: <http://eaton-moeller.partcommunity.com>

Dimensions



① Insulation plate

Front fixing (style: flush mounting)

Additional product information (links)

AWA1160-1746 (IL04716003Z) RMQ-Titan System	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/17460805.pdf
Engineering	
Key to part numbers	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RMQ-TITAN_de.pdf
Engineering	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/PRO_RMQTitan_D_de.pdf
Ordering example for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf
Order form for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf