



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16						
			J1	REVISED PER ECO-06-018713	30AUG2006	MC	JH


- 1 . PARTS PACKAGED UNASSEMBLED
- △ THREE SAFTEY WIRE HOLES $\phi 0.61$ [.024] MINIMUM, EQUALLY SPACED AROUND CIRCUMFERENCE
- △ BELDEN 9292 (WITH 95% BRAID COVERAGE)
4. SEE I.S. 2028-1




VIEW W
RECOMMENDED STRIP LENGTH
SCALE 2:1




VIEW X
RECOMMENDED STRIP LENGTH
SCALE 2:1



VIEW Y
RECOMMENDED STRIP LENGTH
SCALE 2:1



VIEW Z
RECOMMENDED STRIP LENGTH
SCALE 2:1



OBSOLETE	BRAND REX T-13485	2-225662-2 AMP	220015-1	47.22 [1.859]	W	2-331987-0	2-51695-9	225081-3	2-225662-2
	ITT,NAB-61S-BAA	2-225662-0 AMP	220015-1	47.22 [1.859]	W	1-331987-5	2-51695-9	225081-3	2-225662-0
OBSOLETE	△ RG-226/U MODIFIED	1-225662-8 AMP	220015-1	47.22 [1.859]	W	1-331987-5	2-51695-6	225081-3	1-225662-8
	RG-141/U & 141A/U	1-225662-4 AMP	220045-2	42.85 [1.687]	Z	225801-2	225778-2	225776-2	1-225662-7
SUPERSEDED BY 225392-1	RG-55A/U & 223/U	1-225662-3 AMP	220045-2	42.85 [1.687]	X	225560-8	225343-4	225412-6	1-225662-4
	RG-58A/U & 58C/U	1-225662-2 AMP	220045-2	42.85 [1.687]	X	225560-7	225343-2	225412-3	1-225662-3
OBSOLETE	RG-393/U	1-225662-1 AMP	220015-1	47.22 [1.859]	X	225560-8	225343-2	225412-6	1-225662-2
	RG-11A/U & 144/U	225662-4 AMP	220015-1	47.22 [1.859]	Y	225490-5	2-51695-3	225081-3	1-225662-1
OBSOLETE	RG-213/U	225662-2 AMP	220015-1	47.22 [1.859]	W	1-331987-5	2-51695-2	225081-3	225662-4
	RG-9/U,9A/U,9B/U & 214/U	225662-1 AMP	220015-1	47.22 [1.859]	W	1-331987-5	2-51695-1	225081-3	225662-2
CABLE SIZE		STAMPING	CRIMP TOOL	A	VIEW	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC ± -
1 PLC ± -
2 PLC ± 0.41 [016]
3 PLC ± -
4 PLC ± -
ANGLES ± -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

MATERIAL

DWN
B. SCOTT
CHK
M. SNEED
APVD

05-31-91
06-20-91

NAME

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

PRODUCT SPEC
108-12019
APPLICATION SPEC

SIZE
A1

WEIGHT
1.3 OZ MAX

CUSTOMER DRAWING

RESTRICTED TO

SCALE 4:1
SHEET 1 OF 1
REV J1