





REV.	DATE	ECR NO.	DESCRIPTION
A	12/05/99	—	UPDATE DRAWING
B	01/21/07	—	UPDATE DRAWING FORMAT
C	04/07/08	XXXXXX	REVISE BODY, FERRULE PLATING TO NEXCOTE



RECOMMENDED CABLE
STRIPPING DIMS.



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.						04/07/08	
7						CHECKED								
6					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm	ISSUED		PART DESCRIPTION N CRIMP JACK (FOR RG-8X, LMR240, B7808A CABLE)						
5						SHEET	1 OF 1							
4	FERRULE	BRASS	NEXCOTE	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”			PART NO. 172148						
3	CONTACT PIN	BER. COPPER	GOLD	1										
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 1721248.DWG						
1	BODY	BRASS	NEXCOTE	1										
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING		CAD FILE	C:/172/172148.DWG	REV. C	SIZE A	SCALE NA