

										1
LOC	DIST	P	F	REVISIONS						
G	14			ZONE	LTR	DESCRIPTION			DATE	APPD
					C	REV & REDRAWN PER 0720-0061-93			4-19-93	1AP DAP

METRIC


DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
12-10 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

- 1

STAMP AMP 12-10* APPROX AS SHOWN
- 2

MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS



								323754	
								PART NO	
AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 343°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL COPPER PER ASTM B-152 ANNEALED FINISH NICKEL PLATE 0.00762[.000300] MIN THK PER QQ-N-290	DR 4-19-93 TA BRINKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3608				
				CHK 4-19-93 DA PATTERSON					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE		APPD 4-19-93 DE MILLER	NAME SPLICE, PARALLEL, HEAT RESISTANT, STRATO-THERM™				
		WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS SOLID OR STRANDED		APPD 4-19-93 JL MECKLEY					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111			PRODUCT SPEC -					
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO C=323754		
				WEIGHT -	SCALE 10:1		SHEET 1 OF 1		