




COIL: @ +25 °C
 RESISTANCE 40 OHMS ± 10%
 NOMINAL VOLTAGE 6.0 VDC
 MUST OPERATE 3.6 VDC
 MUST RELEASE .35 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE OF -12 VDC WITH BIFILAR COIL

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 11/1/91 CK. (V1) 2.0

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/22-023L

TYPE "HMB" RELAY

HMB1201F01L