


3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43045

Dual Row, Vertical, SMT With Solderable Fitting Nail



Features and Benefits

- Solder tabs provide retention to PCB
- Fully polarized to mating receptacle
- Tape and reel packaging eliminates handling and provides for higher PCB board placement speeds compared to tray packing or hand assembly

Reference Information

Product Specification: PS-43045
Packaging: Tape and reel
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R72040445
Mates With: 43025
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold


Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43045-0218	43045-0219	43045-0220	Yes
4	43045-0418	43045-0419	43045-0420	
6	43045-0618	43045-0619	43045-0620	
8	43045-0818	43045-0819	43045-0820	
10	43045-1018	43045-1019	43045-1020	
12	43045-1218	43045-1219	43045-1220	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
14	43045-1418	43045-1419	43045-1420	Yes
16	43045-1618	43045-1619	43045-1620	
18	43045-1818	43045-1819	43045-1820	
20	43045-2018	43045-2019	43045-2020	
22	43045-2218	43045-2219	43045-2220	
24	43045-2418	43045-2419	43045-2420	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43045

Dual Row Right Angle



Features and Benefits

- Snap-in peg locks header to PCB for optimum retention
- Fully polarized to mating receptacle
- Surface Mount Compatible

Reference Information

Product Specification: PS-43045
Packaging: Tray
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R72040445
Mates With: 43025
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Mechanical

Insertion Force to PCB: 7.5kgf max. (16.5 lb)

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43045-0200	43045-0201	43045-0202	Yes
4	43045-0400	43045-0401	43045-0402	
6	43045-0600	43045-0601	43045-0602	
8	43045-0800	43045-0801	43045-0802	
10	43045-1000	43045-1001	43045-1002	
12	43045-1200	43045-1201	43045-1202	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
14	43045-1400	43045-1401	43045-1402	Yes
16	43045-1600	43045-1601	43045-1602	
18	43045-1800	43045-1801	43045-1802	
20	43045-2000	43045-2001	43045-2002	
22	43045-2200	43045-2201	43045-2202	
24	43045-2400	43045-2401	43045-2402	