

Features

- LOW POWER CONSUMPTION.
- SOLID STATE BLUE LIGHT SOURCE.
- SUITABLE FOR FULL COLOR LED DISPLAYS AND INDICATORS DIAGNOSTIC/ANALYTICAL EQUIPMENT.


L7104NBx BLUE

L7104PBx BLUE

Package Dimensions

Description

The Blue source color devices are made with InGaN on SiC Light Emitting Diode.



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.
3. Lead spacing is measured where the lead emerge package.
4. Specifications are subjected to change without notice.

Selection Guide

Part No.	Dice	Case-Color	Iv (mcd) @ 20 mA		Viewing Angle
			Min.	Typ.	
L7104NBD	Blue (InGaN)	BLUE DIFFUSED	20	100	30°
L7104NBT	Blue (InGaN)	BLUE TRANSPARENT	90	150	20°
L7104NBC	Blue (InGaN)	WATER CLEAR	90	150	20°
L7104PBD	Blue (InGaN)	BLUE DIFFUSED	100	200	30°
L7104PBT	Blue (InGaN)	BLUE TRANSPARENT	120	300	20°
L7104PBC	Blue (InGaN)	WATER CLEAR	400	550	20°

Note:

1. $\theta_{1/2}$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at T_A=25°C


Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
λ_{peak}	Peak Wavelength	Blue (NB) Blue (PB)	445 468		nm	I _F =20mA
$\Delta\lambda_{1/2}$	Spectral Line Halfwidth	Blue (NB) Blue (PB)	20 26		nm	I _F =20mA
C	Capacitance	Blue (NB) Blue (PB)	110 110		pF	V _F =0V;f=1MHz
V _F	Forward Voltage	Blue (NB) Blue (PB)	3.7 3.5	4.0 4.0	V	I _F =20mA
I _R	Reverse Current	All		10	uA	V _R = 5V

Absolute Maximum Ratings at T_A=25°C


Parameter	Blue (NB)	Blue (PB)	Units
Power dissipation	120	102	mW
DC Forward Current	30	30	mA
Peak Forward Current [1]	100	100	mA
Reverse Voltage	5	5	V
Operation Temperature	-20°C To +80°C		
Storage Temperature	-30°C To +85°C		
Lead Soldering Temperature [2]	260°C For 5 Seconds		

Notes:


- 1/10 Duty Cycle, 0.1ms Pulse Width.
2. 4mm below package base.




Blue L7104NBD,L7104NBC,L7104NBT




FORWARD CURRENT Vs. FORWARD VOLTAGE




FORWARD CURRENT DERATING CURVE




RELATIVE INTENSITY Vs. FORWARD CURRENT




Blue L7104PBD,L7104PBC,L7104PBT



FORWARD CURRENT Vs. FORWARD VOLTAGE



FORWARD CURRENT DERATING CURVE



RELATIVE INTENSITY Vs. FORWARD CURRENT

