



The high-performance, compact MXP120™ Sealed Connection System is designed to perform in harsh environments and can replace common 1.50mm systems in space-constrained safety-restraint, body electronics and powertrain applications

Features and Benefits

Versatile sealed connection system using space-saving 1.20mm terminals on 4.00mm pitch	Meets power requirements up to 13.0A Suitable for sealed safety-restraint, body electronics and powertrain applications
Single wire seal (SWS) connection system with robust perimeter seal	IP68 rated. IPX9K under evaluation Withstands high-pressure spray environments
Reduced package size when compared to existing 1.50mm connection systems	Offers significant space-savings for confined design parameters
Accommodates wire gauges up to 1.00mm²	Limits connector pitch to 4.00mm with SWS
Compatible with AK and USCAR interfaces; designed using worldwide AK cavity definition	Confirms global acceptance and marketability
Female receptacles feature medium or long shrouds for 1-by-4 circuit and above (short shrouds for below 4-circuit)	Ensures all circuit sizes and keying options are scoop proof
Female receptacles with Independent Secondary Locking (ISL) Male blade connectors with Primary Lock Reinforcement (PLR)	Ensures efficient terminal positioning and detection of partial installation of terminals
Female receptacles feature integral locking-latch with bridge protection and audible click	Secure mating performance Avoids damage to the latch during packaging and transit

MXP120™ Sealed Connector System

- 34900 Single-Row Receptacles
- 34899 Single-Row Blade Connectors

Black Housings:
Body Electronics & Powertrain Applications



1-by-2 Circuit



1-by-3 Circuit



1-by-4 Circuit



1-by-6 Circuit

Yellow Housings:
Safety Applications



1-by-2 Circuit



1-by-3 Circuit



1-by-4 Circuit



1-by-6 Circuit

Applications

Sealed applications in automotive and commercial vehicles:

Black Outer Housings:

Body electronics connections in wet areas T3-V1-S2 with tin terminals;
T3-V2-S2 with silver terminals:

- Exterior lighting
- Turn signals (indicators)
- Door-lock mechanisms

Powertrain (T4-V4-S3 - 155°C high-vibration for severe applications,
high-pressure jets)

- Fuel injection
- Emission controls
- Ignition coil

Yellow Outer Housings:

Safety systems T3-V2-S2 125°C on-engine vibration:

- Supplemental Inflatable Restraints (SIR)
- Safety Restraint Systems (SRS)
- Seat-belt pretensioners
- Airbags - steering wheel / side / curtain

MXP120™ Sealed Connector System



In-vehicle Safety Systems



Body Electronics in Wet Areas and
Powertrain Applications

Specifications

REFERENCE INFORMATION

Packaging:

Housings – 4-cell bulk pack

Use With:

Receptacle terminals – 1.2 LL SWS
from Tyco and Kostal

Blade terminals – 1.2 CB SWS
from Tyco

Cavity Plugs – Tyco

Designed In: Millimeters

RoHS: Yes

Halogen Free: Yes

ELECTRICAL

Voltage (max.): 500V DC

Current (max.): 13.0A

Contact Resistance:

8 milliohms max.

Dielectric Withstanding Voltage:

1000V AC min for 60sec.

Insulation Resistance:

100 Megohms min.

PHYSICAL

Housing: PA SPS resin

Operating Temperature:

-40 to +125°C

Flammability:

Per ISO3795 or GMW3191

Burn rate: 100mm/ Mn max.

Material self-extinguishing

For full Product Specification
please refer to: PS-34900-0001

Ordering Information

Gender	Circuit Size	Series No.	Outer Shroud Size	Housing Colour	Cavity Insert Color	Coding	Clip Slot†
Female	1x2 1x3 1x4 1x6	<u>34900</u>	Short Medium Long	Yellow Black	Black Light Grey Dark Grey Stone Grey	A B C D E F G	-
Male		<u>34899</u>			-		7mm (USCAR) 11mm (MX150)

† Custom clip-slots available, volume dependant - contact Molex