


STAMP: KINGS 125-57-9



NOTES:

1. FOR USE WITH TIMES AA-5B87 CABLE.
2. FOR CABLING INSTRUCTIONS SEE 3-440-2
3. FOR CABLE TRIMMING USE KTJ-150 & KTD-138.
4. FOR CRIMPING USE DIE SIZE KTH-1077.
5. ITEM ⑤ TO BE SUPPLIED UNASSEMBLED.
6. INTERFACE PER MIL-STD-348 PER FIG. 313-1.

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES FRACTIONS & 2 PLACE DECIMALS $\pm .010$
- 3 PLACE DECIMALS $\pm .004$ ANGLES $\pm 0^{\circ}30'$
- 1 R CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.

2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.
6. ALL PLATING IN ACCORDANCE WITH KER 10004.

125-57-9
(SHEET 1 OF 2)

S-D

REVISIONS

ISSUE	CHANGES
0	ER 31052 KH 4 AUG 89
1	CN 31446 A KH 9 MAR 90

S-D

SCALE 4:1

APPROX SURFACE AREA

WAS: E-15910

USED ON

REF

TNC PLUG

DRAWN KH	DATE 4 AUG 89
APPR CT	DATE 24 AUG 89
APPR JT	DATE 24 AUG 89

KINGS
ELECTRONICS CO. INC.
WALLINGFORD, CT 06492

125-57-9

(SHEET 1 OF 2) S-D

ITEM	REQ'D	DESCRIPTION	PART NO.	125-57-9 (SHEET 2 OF 2)							
1	1	W/P K-GRIP SLEEVE	2-1335-1M27	REVISIONS <table border="1"> <thead> <tr> <th>ISSUE</th> <th>CHANGES</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>ER 31052 KH 4 AUG 89</td> </tr> <tr> <td>1</td> <td>CN 31446 A KH 8 MAR 90</td> </tr> </tbody> </table>		ISSUE	CHANGES	0	ER 31052 KH 4 AUG 89	1	CN 31446 A KH 8 MAR 90
ISSUE	CHANGES										
0	ER 31052 KH 4 AUG 89										
1	CN 31446 A KH 8 MAR 90										
2	1	K-GRIP									
3	1	INSULATOR		S=D							
4	1	BODY ASS'Y									
5	1	TNC CAPTIVE CRIMP CONTACT M	1-5990-1MA9								
6	1	COUPLING NUT									
7	1	C-RING									
8	1	GASKET									
USED ON: REF: FINISH SPEC. KER 10004				PARTS LIST							
DRAWN PS DATE 4AUG89 DESIGN KH DATE 4AUG89 APPR. <i>CT</i> DATE 24AUG89				 KINGS ELECTRONICS CO. INC. TUCKAHOE, NEW YORK 10780							
MAY 2007 THIS DRAWING BECAME THE PROPERTY OF				125-57-9 (SHEET 2 OF 2)							