



SPECIFICATIONS

Rating:	50mA @ 50 VDC
Electrical Life:	100,000 cycles typical
Contact Resistance:	50mΩ initial @ 2-4 VDC 100mA for both silver and gold plated contacts
Insulation Resistance:	100MΩ min.
Dielectric Strength:	1,000 Vrms at sea level
Operating Force:	130 ± 50 gf, 160 ± 50 gf, 300 ± 50 gf
Packaging:	Through-hole in tubes

MATERIALS

Housing:	Liquid Crystal Polymer (LCP)
Actuator:	Liquid Crystal Polymer (LCP)
Cover:	Tin plated steel or stainless steel
Seal:	Silicon rubber
Contacts:	Silver plated phosphor bronze, gold over nickel phosphor bronze
Terminals:	Silver plated copper alloy, gold over nickel copper alloy

HOW TO ORDER



Series	Model No.	Actuator Length	Operating Force	Contact Material	Termination
GS					
GS	None = Standard E = Earth Ground R = Right Angle	4.70 5.20 6.34* 6.84* 6.90 8.54* 10.00 11.54*	F130 F160 F300	Q = Silver R = Gold	P = PC PIN G = Gull Wing

*Actuator length for right angle version only.


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.



GS



P.C. MOUNTING





Schematic




GSE

EARTH GROUND



P.C. MOUNTING




Schematic


PROCESS SEALED TACT SWITCHES





GSR



P.C. MOUNTING




Schematic




GS


SMT



P.C. MOUNTING



Schematic



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.