


Ring Lug Terminal Blocks ST5, ST5-16mm², ST6 and ST25



Weidmuller's comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications. Bolt-type screw terminals with threads from M3.5 to M5 can be used depending on the conductor cross-section.

- Touch-safe (Premium line)
- Self-locking nut
- Combi-foot for use with TS 35 and TS 32
- CSA / UL approved
- Standard screw or test sleeve
- High Voltage Capacity

Weidmuller, Canada

10 Spy Court
Markham, Ontario L3R 5H6
Telephone: (800) 268-4080
Facsimile: (877) 300-5635
Email: info1@weidmuller.ca
Website: www.weidmuller.ca

Weidmuller, Mexico


Blvd. Hermanos Serdán 698
Col. San Rafael Oriente
Puebla, Puebla, Mexico
C.P. 72029
Telephone: 01 222 2686267
Facsimile: 01 222 2686219
Email: clientes@weidmuller.com.mx
Website: www.weidmuller.com.mx

Weidmuller, United States


821 Southlake Blvd.
Richmond, Virginia 23236
Telephone: (800) 849-9343
Facsimile: (804) 379-2593
Email: info@weidmuller.com
Website: www.weidmuller.com

Ring Lug Terminal Blocks

Premium Line ("New" Touch-Safe)




ST5 N / EN
Feed through



Self-locking Nut

10.2 / 0.402

ST5PN / EN
Feed through



Self-locking Nut

13.2 / 0.519



Width (mm / Inch)


Insulating material (UL94)

Rated data	IEC/DIN-VDE		IEC/DIN-VDE	
Voltage	800 V	600 V	800 V	600 V
Current	35 A	35 A	46 A	46 A
Cross-section	4 mm²	22 - 10 AWG	6 mm²	22 - 8 AWG
Impulse voltage	8 KV		8 KV	
Pollution severity	3		3	
Torque range	1.0 Nm		1.2 Nm	
Torque range - connections	0.5 - 0.8 Nm		0.5 - 0.8 Nm	
(See Lug Dimensions Chart P7) Thread	M3.5		M4	
Ordering Data	Part No.		Part No.	
(Beige)	C905234600 (screw)		C905221600 (screw)	
(Beige)	C905381600 (sleeve)		C905382600 (sleeve)	
Disconnect* (Beige)				
Disconnect* (Beige)				

Accessories

End plate	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
 (Beige) AP PA	1.5/059	C905235600	1.5/059	C905222600
Adapter sleeve - Pin	Part No.		Part No.	
 STB 21.6 (Beige)	1071000000		1071000000	
Pin PS4	0299600000		0299600000	
Partition plate	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
 (BG) TW PA				
(BG) TW HP				
(BG) TW PA				
TW HP - TS 32				
Cross-connection	Part No.		Part No.	
Kit				
VH				
Q2	C905236600		C905223600	
Q3	C905237600		C905224600	
Q4	C905238600		C905225600	
Q5				
Q7				
Q10	C905239600		C905226600	
Q50				
QL2				
QL3				
QL4				
QL5				
QL7				
QL10				
QL50				
Sleeve VH 13.5				
Kit (1 Screw + 1 Washer)				
Connection for short-circuit	Part No.		Part No.	
 ZQV 10/2				
End brackets	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
 EW35 - TS 35	8.5/334	0383560000	8.5/334	0383560000
WEW35/2 - TS 35	8.0/315		8.0/315	
EWK1 - TS 32	8.5/334	0206160000	8.5/334	0206160000
EWK2 - TS 32	15.0/59		15.0/59	
WEW35 - TS 35	12.2/48		12.2/48	
Rails	Part No.		Part No.	
TS 35 steel	0383400000		0383400000	
TS 35 steel slotted	0514500000		0514500000	
TS 32 steel	0122800000		0122800000	

*Quick connection, incorporated test-point, circuit disconnecting

ST6 / EN
Feed through

Self-locking Nut

11.2 / 0.441


PA (V0)

IEC/DIN-VDE	
800 V	600 V
41 A	40 A
6 mm ²	26 - 10 AWG
8 kV	
3	
1.5 - 1.8 Nm	
0.5 - 0.8 Nm	
M4	

Part No.

C904908601 (screw)

C904908600 (sleeve)

ST6 T / EN
Test disconnect

Self-locking Nut

11.2 / 0.441


PA (V0)

IEC/DIN-VDE	
800 V	600 V
41 A	40 A
6 mm ²	26 - 10 AWG
8 kV	
3	
1.5 - 1.8 Nm	
0.5 - 0.8 Nm	
M4	

Part No.

C904909601 (screw)

C904909600 (sleeve)

ST25 / EN
Feed through

Self-locking Nut

18.2 / 0.716

PA (V0)

IEC/DIN-VDE	
1000 V	1000 V
101 A	100 A
25 mm ²	20 - 3 AWG
8 kV	
3	
2.5 (M5) / 3.2 (M6)	
1.2 - 1.9 Nm	
M5 & M6	

Part No.

C905265600 (M5) (screw)

C905379600 (M5) (sleeve)

Part No.

C905264600 (M6) (screw)

C905380600 (M6) (sleeve)

Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
1.0/.039	C904910600	1.0/.039	C905222600	1.5/.059	C905266600

Part No.		Part No.		Part No.	
0299600000		0299600000		0299600000	
Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.

Part No.	Part No.	Part No.
C905064600	C905064600	C012361000
C905065600	C905065600	C012371000
C905066600	C905066600	C012381000

C905067600	C905067600	C033861000
------------	------------	------------

C904925600	C904925600	
C904926600	C904926600	
C904927600	C904927600	

C904929600	C904929600	
------------	------------	--

C904288000	C904288000	
------------	------------	--

C904940600	C904940600	
------------	------------	--

Part No.	Part No.	Part No.
1739680000	1739680000	


Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
8.5/.334		8.5/.334		8.5/.334	
8.0/.315	1061200000	8.0/.315	1061200000	8.0/.315	
8.5/.334		8.5/.334		8.5/.334	
15.0/.59	0199360000	15.0/.59	0199360000	15.0/.59	0199360000
12.2/.48		12.2/.48		12.2/.48	1059000000

Part No.	Part No.	Part No.
0383400000	0383400000	0383400000
0514500000	0514500000	0514500000
0122800000	0122800000	0122800000

Accessories


Lug Dimensions Chart (Terminals DIN 46237)

Terminal Type	Ø	A (Max) mm/Inch
ST5 N / EN	M3.5	8.0/.315
ST5PN / EN	M4	10.0/.394
ST6 / EN	M4	8.0/.315
ST6 T / EN	M4	8.0/.315
ST25 V1 / EN	M5	15.0/.590
ST25 V1 / EN	M6	15.0/.590
ST25 V2 / EN	M5	15.0/.590
ST25 V2 / EN	M6	15.0/.590
ST5 16mm ²	M5	12.0/.473
ST5 / EN	M3.5	8.0/.315
ST5P / EN	M4	10.0/.394
ST5P1 V1 / EN	M4	10.0/.394
ST5P1 V2 / EN	M4	10.0/.394
ST5P1 V4 / EN	M4	10.0/.394
ST5P1 V5 / EN	M5	12.0/.473



Dekafix Preprinted Markers for Terminals

Length x Pitch	Vertical Print	Horizontal Print
	5 x 5mm	5 x 5mm
Model	DEK 5/5	DEK 5/5
1-50	0473560001	0473460001
51-100	0473560051	0473460051
101-150	0473560101	0473460101
151-200	0473560151	0473460151
201-250	0473560201	0473460201
251-300	0473560251	0473460251
301-350	0473560301	0473460301
351-400	0473560351	0473460351
401-450	0473560401	0473460401
451-500	0473560451	0473460451




Additional number sequences, letters and symbols are available.

Dekafix Multi-Card Markers (Blank & Custom Print)

Model	Type	Part Number
DEK 5/5 MC	Blank	1609801044
DEK 5/5 MC	Custom Print	1854500000

Support and Hoods


Terminal Block	ADP	HP
ST5 ST5P ST5P1 / ST5 N / ST5 PN	ADP - 0485300000 (1m)	HP2 - 0485660000
ST5 - 16mm ²	ADP - 0447700000 (1m)	---
ST25	ADP - 04854000000 (1m)	HP3 - 0485760000
ST6 ST6T	ADP3 - 0485400000 (1m)	HP4 - 0485860000





Screwdrivers

For Screw, Sleeve or Self-locking versions only.

Terminal Type	Description	a (mm/Inch)	b (mm/Inch)	c (mm/Inch)	Part Number
ST5 N / EN	SD 1.0x5.5x150	1.0/.039	5.5/.216	150/5.91	9008350000
ST5PN / EN	SD 1.0x5.5x150	1.0/.039	5.5/.216	150/5.91	9008350000
ST6 / EN	SD 1.0x5.5x150	1.0/.039	5.5/.216	150/5.91	9008350000
ST6 T / EN (Terminal)	SD 1.0x5.5x150	1.0/.039	5.5/.216	150/5.91	9008350000
ST6 T / EN (Disconnect)	SD 0.5x3.0x8.0	0.5/.019	3.0/.118	8.0/.314	9008320000
ST25 V1 / EN	SD 1.2x6.5x150	1.2/.047	6.5/.255	150/5.91	9009010000
ST25 V2 / EN	SD 1.2x6.5x150	1.2/.047	6.5/.255	150/5.91	9009010000
ST5 / EN	SDK PH1			80/3.14	9008480000
ST5P / EN	SDK PH1			80/3.14	9008480000
ST5P1 V2 / EN	SDK PH1			80/3.14	9008480000
ST5P1 V4 / EN	SDK PH1			80/3.14	9008480000
ST5P1 V5 / EN	SDK PH2			100/3.93	9008490000



ST5 / EN
Feed throughST5P / EN
Feed through

Width (mm / Inch)	9.7 / 0.382		9.7 / 0.382	
Insulating material (UL94)	PA (V2)		PA (V2)	
Rated data	IEC/DIN-VDE	UL	IEC/DIN-VDE	UL
Voltage	800 V	600 V	800 V	600 V
Current	35 A	35 A	35 A	45 A
Cross-section	4 mm ²	20 - 10 AWG	4 mm ²	22 - 10 AWG
Impulse voltage	6 kV		6 kV	
Pollution severity	3		3	
Torque range	0.8 - 1.6 Nm		0.8 - 1.6 Nm	
Torque range - connections	M3.5		M3.5	
(See Lug Dimensions Chart P7) Thread	M3.5		M3.5	
Ordering Data	Part No.		Part No.	
(Beige)	C9000676		C9001456	
(Beige)				
Disconnect (Beige)				
Disconnect (Beige)				

Accessories


End plate	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
(Beige) AP PA	1.5/.059	C9000686	1.5/.059	C9000686
Adapter sleeve - Pin	Part No.		Part No.	
STB 21.6 (Beige) Pin PS4				
Partition plate	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
(BG) TW PA	1.5/.059	C904318600	1.5/.059	C904318600
(BG) TW HP	0.5/.019	0474700000	0.5/.019	0474700000
(BG) TW PA				
TW HP - TS 32				
Cross-connection	Part No.		Part No.	
Kit				
VH				
Q2				
Q3				
QL2				
QL3				
QL4				
Q4				
Q2				
Q3				
Q4				
Q5				
Q7				
Q10				
Q50				
QL2	C9001370		C9001370	
QL3	C9001380		C9001380	
QL4	C9001390		C9001390	
QL5				
QL7				
QL10	C9000750		C9000750	
QL50				
Sleeve VH 13.5				
Kit (1 Screw + 1 Washer)				
Connection for short-circuit	Part No.		Part No.	
ZQV 10/2				
End brackets	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
EW35 - TS 35	8.5/.334	0383560000	8.5/.334	0383560000
WEW35/2 - TS 35	8.0/.315		8.0/.315	
EWK1 - TS 32	8.5/.334	0206160000	8.5/.334	0206160000
EWK2 - TS 32	15.0/.59		15.0/.59	
WEW35 - TS 35	12.2/.48		12.2/.48	
Rails	Part No.		Part No.	
TS 35 steel	0383400000		0383400000	
TS 35 steel slotted	0514500000		0514500000	
TS 32 steel	0122800000		0122800000	

Standard Line

Ring Lug Terminal Blocks

ST5P1 V2 / EN

Feed through




Screw

13.2 / 0.519

PA (V2)

ST5P1 V1 / EN

Feed through




Nut

13.2 / 0.519

PA (V2)

ST5P1 V4 and 5 / EN

Feed through




Self-locking Nut

13.2 / 0.519

PA (V2)

ST5S-16mm²

Feed through




Nut

16.5 / 0.642

PA (V0)

STL5-16mm²

Test disconnect



Nut

16.5 / 0.642

PA (V0)

IEC/DIN-VDE		IEC/DIN-VDE		IEC/DIN-VDE		IEC/DIN-VDE		IEC/DIN-VDE	
500 V	300 V	500 V	300 V	500 V	300 V	800 V	600 V	800 V	600 V
46 A	46 A	46 A	46 A	46 A	46 A	76 A	65 A	76 A	65 A
6 mm ²	24 - 6 AWG	6 mm ²	24 - 6 AWG	6 mm ²	24 - 6 AWG	16 mm ²	AWG 12...10	16 mm ²	AWG 12...10
6 kV		6 kV		6 kV		8 kV		8 kV	
3		3		3		3		3	
1.2 - 1.9 Nm		1.2 - 2.4 Nm		1.2 - 2.4 Nm		2.0 - 4.0 Nm		2.0 - 4.0 Nm	
0.8 - 1.6 Nm		0.8 - 1.6 Nm		0.8 - 1.6 Nm		0.8 - 1.6 Nm		0.8 - 1.6 Nm	
M4		M4		M4 & M5		M5		M5	
Part No.		Part No.		Part No.		Part No.		Part No.	
C904916600		C904904600		C904922600 (M4)		0448360000			
				C904915600 (M5)					
								0448460000	

Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
1.5/.059	C9001506	1.5/.059	C9001506	1.5/.059	C9001506	1.5/.059	0447260000	1.5/.059	0447260000

Part No.	Part No.	Part No.	Part No.	Part No.
----------	----------	----------	----------	----------

Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
1.5/.059	C904319600	1.5/.059	C904319600	1.5/.059	C904319600	1.5/.059	0477660000	1.5/.059	0477660000
0.5/.019	0474700000	0.5/.019	0474700000	0.5/.019	0474700000				

Part No.	Part No.	Part No.	Part No.	Part No.
----------	----------	----------	----------	----------

C904913600	C904913600	C904913600	3834300000	3834300000
C904914600	C904914600	C904914600		
C904917600	C904917600	C904917600		

C904918600	C904918600	C904918600		
-------------------	-------------------	-------------------	--	--

C904919600	C904919600	C904919600		
-------------------	-------------------	-------------------	--	--

Part No.	Part No.	Part No.	Part No.	Part No.
----------	----------	----------	----------	----------

Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.	Width (mm/Inch)	Part No.
8.5/.334	0383560000	8.5/.334	0383560000	8.5/.334	0383560000	8.5/.334	0383560000	8.5/.334	0383560000
8.0/.315		8.0/.315		8.0/.315	1061200000	8.0/.315	1061200000	8.0/.315	1061200000
8.5/.334	0206160000	8.5/.334	0206160000	8.5/.334	0206160000	8.5/.334	0206160000	8.5/.334	0206160000
15.0/.59		15.0/.59		15.0/.59		15.0/.59		15.0/.59	
12.2/.48		12.2/.48		12.2/.48		12.2/.48		12.2/.48	

Part No.	Part No.	Part No.	Part No.	Part No.
0383400000	0383400000	0383400000	0383400000	0383400000
0514500000	0514500000	0514500000	0514500000	0514500000
0122800000	0122800000	0122800000	0122800000	0122800000