




LOC	DIST	REVISIONS				
G	86	P	LTR	DESCRIPTION	DATE	APVD
		B		REV PER 063A-0561-01	09OCT02	JR MS



- 1 COPPER PER ASTM B-75 ANNEALED
- 2 NICKEL PLATE 0.00254[.000100] MIN THK PER QQ-N-290



696123-1

AMP

PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		RECOMMENDED OPERATING TEMPERATURE: -
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 96.3-117.0mm² [190,000-231,000] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	14OCT99	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK M SPICER	14OCT99			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.51 [.020] 3 PLC ±- 4 PLC ±- ANGLES ±5°	APVD M SPICER	14OCT99	NAME TERMINAL, BENT 90, AMPPOWER, WIRE SIZE: 4/0 AWG		
		PRODUCT SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C-696123
MATERIAL -	FINISH -	APPLICATION SPEC 114-2150		WEIGHT .106 lbs	SCALE 2:1	SHEET 1 OF 1
- 1		- 2		CUSTOMER DRAWING		
				REV B		