

Features

2 Pole Changeover (DPDT)
30 A Power relay

66.22 PCB connections & mount
66.82 Faston 250 connections
 - Flange mount

- Reinforced insulation between coil and contacts according to EN 60335-1; 8 mm creepage and clearance distances
- AC coils & DC coils
- Cadmium Free option available
- ATEX compliant (EX nC) option available



For outline drawing see page 7

FOR UL RATINGS SEE:
"General technical information" page V

66.22



- 30 A rated contacts
- PCB mount - bifurcated terminals





Copper side view

66.82



- 30 A rated contacts
- Flange mount
- Faston 250 connections



Contact specification		66.22	66.82
Contact configuration		2 CO (DPDT)	2 CO (DPDT)
Rated current/Maximum peak current	A	30/50 (NO) - 10/20 (NC)	30/50 (NO) - 10/20 (NC)
Rated voltage/Maximum switching voltage V AC		250/440	250/440
Rated load AC1	VA	7,500 (NO) - 2,500 (NC)	7,500 (NO) - 2,500 (NC)
Rated load AC15 (230 V AC)	VA	1,200 (NO)	1,200 (NO)
Single phase motor rating (230 V AC)	kW	1.5 (NO)	1.5 (NO)
Breaking capacity DC1: 30/110/220 V	A	25/0.7/0.3 (NO)	25/0.7/0.3 (NO)
Minimum switching load	mW (V/mA)	1,000 (10/10)	1,000 (10/10)
Standard contact material		AgCdO	AgCdO
Coil specification		66.22	66.82
Nominal voltage (U _N)	V AC (50/60 Hz)	6 - 12 - 24 - 110/115 - 120/125 - 230 - 240	
	V DC	6 - 12 - 24 - 110 - 125	
Rated power AC/DC	VA (50 Hz)/W	3.6/1.7	3.6/1.7
Operating range	AC	(0.8...1.1)U _N	(0.8...1.1)U _N
	DC	(0.8...1.1)U _N	(0.8...1.1)U _N
Holding voltage	AC/DC	0.8 U _N /0.5 U _N	0.8 U _N /0.5 U _N
Must drop-out voltage	AC/DC	0.2 U _N /0.1 U _N	0.2 U _N /0.1 U _N
Technical data		66.22	66.82
Mechanical life AC/DC	cycles	10 · 10 ⁶	10 · 10 ⁶
Electrical life at rated load AC1	cycles	100 · 10 ³	100 · 10 ³
Operate/release time	ms	8/15	8/15
Insulation between coil and contacts (1.2/50 μs)	kV	6 (8 mm)	6 (8 mm)
Dielectric strength between open contacts	V AC	1,500	1,500
Ambient temperature range	°C	-40...+70	-40...+70
Environmental protection		RT II	RT II
Approvals (according to type)		RINA	

Features

2 Pole NO (DPST-NO)
30 A Power relay

66.22-x300 PCB mount
66.82-x300 Faston 250 connections
- Flange mount

- Reinforced insulation between coil and contacts according to EN 60335-1; 8 mm creepage and clearance distances
- AC coils & DC coils
- Cadmium Free option available
- ATEX compliant (EX nC) option available

66.22-x30x





- 30 A rated contacts
- PCB mount - bifurcated terminals



66.82-x30x



- 30 A rated contacts
- Flange mount
- Faston 250 connections



Copper side view



For outline drawing see page 7

FOR UL RATINGS SEE:
"General technical information" page V

Contact specification

Contact configuration		2 NO (DPST-NO)	2 NO (DPST-NO)
Rated current/Maximum peak current	A	30/50	30/50
Rated voltage/Maximum switching voltage V AC		250/440	250/440
Rated load AC1	VA	7,500	7,500
Rated load AC15 (230 V AC)	VA	1,200	1,200
Single phase motor rating (230 V AC)	kW	1.5	1.5
Breaking capacity DC1: 30/110/220 V	A	25/0.7/0.3	25/0.7/0.3
Minimum switching load	mW (V/mA)	1,000 (10/10)	1,000 (10/10)
Standard contact material		AgCdO	AgCdO

Coil specification

Nominal voltage (U _N)	V AC (50/60 Hz)	6 - 12 - 24 - 110/115 - 120/125 - 230 - 240	
	V DC	6 - 12 - 24 - 110 - 125	
Rated power AC/DC	VA (50 Hz)/W	3.6/1.7	3.6/1.7
Operating range	AC	(0.8...1.1)U _N	(0.8...1.1)U _N
	DC	(0.8...1.1)U _N	(0.8...1.1)U _N
Holding voltage	AC/DC	0.8 U _N /0.5 U _N	0.8 U _N /0.5 U _N
Must drop-out voltage	AC/DC	0.2 U _N /0.1 U _N	0.2 U _N /0.1 U _N

Technical data

Mechanical life AC/DC	cycles	10 · 10 ⁶	10 · 10 ⁶
Electrical life at rated load AC1	cycles	100 · 10 ³	100 · 10 ³
Operate/release time	ms	8/10	8/10
Insulation between coil and contacts (1.2/50 μs)	kV	6 (8 mm)	6 (8 mm)
Dielectric strength between open contacts	V AC	1,500	1,500
Ambient temperature range	°C	-40...+70	-40...+70
Environmental protection		RT II	RT II

Approvals (according to type)



Features

2 Pole NO (DPST-NO), ≥ 1.5 mm contact gap
30 A Power relay

- 66.22-x600** PCB mount
- 66.22-x600S** PCB mount - 5 mm gap between PCB and relay base
- 66.82-x600** Faston 250 connections - Flange mount

- ≥ 1.5 mm contact gap (according to VDE 0126-1-1 for solar inverter applications)
- Reinforced insulation between coil and contacts according to EN 60335-1; 8 mm creepage and clearance distances
- Wash tight version (RT III) available
- DC coils
- Cadmium Free option available
- ATEX compliant (EX nC) option available


For outline drawing see page 7

FOR UL RATINGS SEE:
"General technical information" page V

NEW 66.22-x60x



- PCB mount - bifurcated terminals




Copper side view

NEW 66.22-x60xS



- PCB mount - bifurcated terminals
- 5 mm gap between PCB and relay base





Copper side view

NEW 66.82-x60x



- Flange mount
- Faston 250 connections



Contact specification		66.22-x60x		66.22-x60xS		66.82-x60x	
Contact configuration		2 NO (DPST-NO)		2 NO (DPST-NO)		2 NO (DPST-NO)	
Rated current/Maximum peak current	A	30/50		30/50		30/50	
Rated voltage/Maximum switching voltage	V AC	250/440		250/440		250/440	
Rated load AC1	VA	7,500		7,500		7,500	
Rated load AC15 (230 V AC)	VA	1,200		1,200		1,200	
Single phase motor rating (230 V AC)	kW	1.5		1.5		1.5	
Breaking capacity DC1: 30/110/220 V	A	25/1.2/0.5		25/1.2/0.5		25/1.2/0.5	
Minimum switching load	mW (V/mA)	1,000 (10/10)		1,000 (10/10)		1,000 (10/10)	
Standard contact material		AgCdO		AgCdO		AgCdO	
Coil specification		66.22-x60x		66.22-x60xS		66.82-x60x	
Nominal voltage (U_N)	V AC (50/60 Hz)	—		—		—	
	V DC	6 - 12 - 24 - 110 - 125		6 - 12 - 24 - 110 - 125		6 - 12 - 24 - 110 - 125	
Rated power AC/DC	VA (50 Hz)/W	—/1.7		—/1.7		—/1.7	
Operating range	AC	—		—		—	
	DC	$(0.8 \dots 1.1) U_N$		$(0.7 \dots 1.1) U_N$		$(0.8 \dots 1.1) U_N$	
Holding voltage	AC/DC	—/0.5 U_N		—/0.5 U_N		—/0.5 U_N	
Must drop-out voltage	AC/DC	—/0.1 U_N		—/0.1 U_N		—/0.1 U_N	
Technical data		66.22-x60x		66.22-x60xS		66.82-x60x	
Mechanical life	cycles	$10 \cdot 10^6$		$10 \cdot 10^6$		$10 \cdot 10^6$	
Electrical life at rated load AC1	cycles	$100 \cdot 10^3$		$100 \cdot 10^3$		$100 \cdot 10^3$	
Operate/release time	ms	15/4		15/4		15/4	
Insulation between coil and contacts (1.2/50 μ s)	kV	6 (8 mm)		6 (8 mm)		6 (8 mm)	
Dielectric strength between open contacts	V AC	2,500		2,500		2,500	
Ambient temperature range	°C	-40...+70		-40...+70		-40...+70	
Environmental protection		RT II		RT II		RT II	
Approvals (according to type)							

66 Series - Power relays 30 A

Ordering information

Example: 66 series relay, Faston 250 (6.3x0.8 mm) with top flange mount, 2 CO (DPDT) 30 A contacts, 24 V DC coil.

A

Series **66** . **8** **2** . **9** . **0 2 4** . **0** **0** **0** **0** **S**

Type
2 = PCB
8 = Faston 250 (6.3x0.8 mm) with top flange mount

No. of poles
2 = 2 pole 30 A (versions 0, 1)
2 = 2 pole 25 A (version 3)

Coil version
8 = AC (50/60 Hz)
9 = DC

Coil voltage
See coil specifications

A: Contact material
0 = Standard AgCdO
1 = AgNi

B: Contact circuit
0 = CO (nPDT)
3 = NO (nPST)
6 = NO (nPST), ≥ 1.5 mm contact gap

C: Options
0 = None

D: Special versions
0 = Standard
1 = Wash tight (RT III)
3 = ATEX compliant (Ex nC)

S = PCB version with 5 mm gap between PCB and relay base (only 66.22)

Selecting features and options: only combinations in the same row are possible.

Preferred selections for best availability are shown in **bold**.

Type	Coil version	A	B	C	D
66.22	AC-DC	0 - 1	0 - 3	0	0 - 1
	DC	0 - 1	6	0	0 - 1
66.22....S	DC	0 - 1	6	0	0 - 1 - 3
66.82	AC-DC	0 - 1	0 - 3	0	0 - 1 - 3
	DC	0 - 1	6	0	0 - 1 - 3


Technical data

Insulation according to EN 61810-1		
Nominal voltage of supply system	V AC	230/400
Rated insulation voltage	V AC	400
Pollution degree		3
Insulation between coil and contact set		
Type of insulation		Reinforced (8 mm)
Overvoltage category		III
Rated impulse voltage	kV (1.2/50 μ s)	6
Dielectric strength	V AC	4,000
Insulation between adjacent contacts		
Type of insulation		Basic
Overvoltage category		III
Rated impulse voltage	kV (1.2/50 μ s)	4
Dielectric strength	V AC	2,500
Insulation between open contacts		
Type of disconnection	2 CO	2 NO, ≥ 1.5 mm (x60x version)
Overvoltage category	Micro-disconnection	Full-disconnection *
Rated impulse voltage	—	II
Rated impulse voltage	kV (1.2/50 μ s)	2.5
Dielectric strength	V AC/kV (1.2/50 μ s)	1,500/2
		2,500/3
Conducted disturbance immunity		
Burst (5...50)ns, 5 kHz, on A1 - A2	EN 61000-4-4	level 4 (4 kV)
Surge (1.2/50 μ s) on A1 - A2 (differential mode)	EN 61000-4-5	level 4 (4 kV)
Other data		
Bounce time: NO/NC	ms	7/10
Vibration resistance (10...150)Hz: NO/NC	g	20/19
Shock resistance	g	20
Power lost to the environment	without contact current	W
	with rated current	W
		2.3
		5
Recommended distance between relays mounted on PCB	mm	≥ 10


* Only in applications where over voltage category II is permitted. In applications of over voltage category III: Micro-disconnection.

Contact specification


F 66 - Electrical life (AC) v contact current
250 V (normally open contact)




F 66 - Electrical life (AC) v contact current
440 V (normally open contact)



H 66 - Maximum DC breaking capacity



H 66 - Maximum DC breaking capacity, x60x versions
(>1.5mm contact gap)



- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of $\geq 100 \cdot 10^3$ can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
Note: the release time for the load will be increased.

Coil specifications


DC coil data

Nominal voltage U_N	Coil code	Operating range		Resistance	Rated coil consumption
V		U_{min} V	U_{max} V	R Ω	I at U_N mA
6	9.006	4.8	6.6	21	283
12	9.012	9.6	13.2	85	141
24	9.024	19.2	26.4	340	70.5
110	9.110	88	121	7,000	15.7
125	9.125	100	138	9,200	13.6


AC coil data

Nominal voltage U_N	Coil code	Operating range		Resistance	Rated coil consumption I at U_N (50Hz)
V		U_{min} V	U_{max} V	R Ω	mA
6	8.006	4.8	6.6	3	600
12	8.012	9.6	13.2	11	300
24	8.024	19.2	26.4	50	150
110/115	8.110	88	126	930	32.6
120/125	8.120	96	137	1,050	30
230	8.230	184	253	4,000	15.7
240	8.240	192	264	5,500	15

R 66 - DC coil operating range v ambient temperature



R 66 - AC coil operating range v ambient temperature



- 1 - Max. permitted coil voltage.
- 2 - Min. pick-up voltage with coil at ambient temperature.
- 3 - Min. pick-up voltage with coil at ambient temperature (66.22-x60xS).

- 1 - Max. permitted coil voltage.
- 2 - Min. pick-up voltage with coil at ambient temperature.

Features compliant variant ATEX, II 3G Ex nC IIC Gc

MARKING



Specific marking of explosion protection

II

Component for surface plant (different from mines)

3

Category 3: normal level of protection

GAS

G

Explosive atmosphere due to presence of combustible gas vapour or mist

Ex nC

Sealed device (type of protection for category 3G)

IIC

Gas group

Gc

Equipment Protection Level

 $-40^{\circ}\text{C} \leq T_a \leq +70^{\circ}\text{C}$

Ambient temperature

EUT 14 ATEX 0150 U

EUT: laboratory which issues the CE type certificate

14: year of issue of certificate

0150: number of CE type certificate

U: ATEX component



Electrical characteristics

Characteristics of terminals

Rated current/Maximum peak current	A	25/50 (NO) – 10/20 (NC)
Rated voltage/Maximum switching voltage	V AC	250/400
Rated load AC1	VA	6,250 (NO) – 2,500 (NC)
Rated load AC15	VA	1,200 (NO)
Capacity for single phase motor (230 V AC)	kW	1.5 (NO)
Breaking capacity DC1: 30/110/220 V	A	25/0.7/0.3 (NO)

Characteristics of coil

Rated voltage (U_N)	V AC (50/60 Hz)	6 - 12 - 24 - 110/115 - 120/125 - 230 - 240
	V DC	6 - 12 - 24 - 110 - 125
Rated Power AC/DC	VA (50 Hz)/W	3.6 / 1.7
Operating range	AC/DC	$(0.8 \dots 1.1)U_N$

General characteristics

Ambient temperature	$^{\circ}\text{C}$	$-40 \dots +70$
---------------------	--------------------	-----------------

Special condition for safe use


The component must be placed inside an enclosure that meets the general requirements for enclosures as per clause 6.3 of EN 60079-15. The connections must be made in compliance with the requirements of clause 7.2.4 or 7.2.5 of EN 60079-15.

Wiring

The cross-section of conductors connected to the terminals, must be at least 4 mm² for the Type 66.82.


Layout pcb

The minimum cross-section of the tracks of the printed circuit board must be 0.58 mm², while the width must be at least 4 mm for Types "66.22" and "66.22....S".




Outline drawings


Type 66.22




Type 66.22-0300




Type 66.22-0600




Type 66.22-0600S




Type 66.82



Type 66.82-0300



Type 66.82-0600



Accessories




066.07

Top 35 mm rail (EN 60715) mount for types 66.82.xxxx.0x00


066.07



066.07 with relay



066.07



066.07 with relay

